

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032914

Luminaire Tested: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032914
REPORT IS A COMBINATION OF REPORTS P1000140 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9926.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032914

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032914

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47	47	47
1	97	93	89	86	89	86	83	80	72	70	67	59	58	56	47	46	45	40	40	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34	34	34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	29	29	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25	25	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22	22	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19	19	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17	17	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15	15	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14	14	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16390	16390	16390
5°	16391	15903	15905
10°	16252	15401	15218
15°	16029	14776	14408
20°	15735	14064	13484
25°	15370	13295	12581
30°	15013	12511	11568
35°	14620	11716	10578
40°	14151	10860	9561
45°	13713	10012	8554
50°	13213	9085	7530
55°	12675	8135	6475
60°	12077	7126	5432
65°	11499	5969	4428
70°	10677	4752	3384
75°	9625	3457	2367
80°	8037	2121	1701
85°	6047	1222	935

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13713 cd/sqm

TEST NUMBER: P1032914

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	1.9
10°-20°	527.0	5.3
20°-30°	760.8	7.7
30°-40°	862.2	8.7
40°-50°	832.5	8.4
50°-60°	692.1	7.0
60°-70°	477.7	4.8
70°-80°	241.4	2.4
80°-90°	65.3	0.7
90°-100°	124.0	1.2
100°-110°	371.4	3.7
110°-120°	630.9	6.4
120°-130°	832.1	8.4
130°-140°	934.5	9.4
140°-150°	918.5	9.3
150°-160°	772.5	7.8
160°-170°	514.0	5.2
170°-180°	180.0	1.8
0°-30°	1476.7	14.9
0°-40°	2339.0	23.6
0°-60°	3863.6	38.9
0°-90°	4648.1	46.8
90°-120°	1126.3	11.3
90°-150°	3811.4	38.4
90°-180°	5278.0	53.2
0°-180°	9926.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2007	2001	1982	1998	1994	190
15°	1911	1898	1859	1856	1845	539
25°	1728	1700	1637	1611	1596	796
35°	1494	1445	1368	1316	1288	934
45°	1219	1162	1070	994	966	940
55°	923	862	762	682	652	826
65°	628	562	463	397	379	620
75°	334	277	205	169	160	352
85°	83	52	48	45	45	91
90°	4	21	32	41	44	11
95°	88	102	112	116	116	96
105°	343	344	350	354	359	363
115°	641	641	638	637	636	633
125°	934	934	933	930	927	833
135°	1205	1214	1214	1211	1206	932
145°	1464	1470	1471	1470	1465	916
155°	1677	1677	1676	1682	1676	772
165°	1826	1821	1818	1827	1821	515
175°	1899	1892	1890	1901	1890	180
180°	1902	1902	1902	1902	1902	

TEST NUMBER: P1032914

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2009.9	2009.9	2009.9	2009.9	2009.9
2.5°	2016.0	2009.9	1992.9	2009.9	2008.3
5°	2006.8	2000.6	1982.2	1997.6	1994.5
7.5°	1992.9	1986.8	1963.7	1974.5	1969.8
10°	1971.4	1963.7	1936.0	1942.1	1936.0
12.5°	1943.7	1934.5	1900.6	1903.7	1894.4
15°	1911.4	1897.5	1859.0	1856.0	1845.2
17.5°	1874.4	1854.4	1809.8	1802.1	1786.7
20°	1829.8	1809.8	1757.5	1745.2	1725.2
22.5°	1780.6	1757.5	1700.5	1680.5	1665.1
25°	1728.2	1700.5	1637.4	1611.3	1595.9
27.5°	1674.4	1640.5	1574.3	1543.6	1522.0
30°	1617.4	1579.0	1506.6	1468.2	1443.5
32.5°	1557.4	1512.8	1437.4	1391.2	1368.1
35°	1494.3	1445.1	1368.1	1315.8	1288.1
37.5°	1428.1	1377.4	1292.7	1235.8	1208.1
40°	1357.3	1306.6	1218.8	1154.2	1126.5
42.5°	1289.6	1235.8	1143.4	1077.3	1048.0
45°	1218.8	1161.9	1069.6	994.2	966.5
47.5°	1146.5	1088.0	992.6	914.1	883.4
50°	1072.6	1012.6	914.1	837.2	807.9
52.5°	997.2	938.8	837.2	758.7	727.9
55°	923.4	861.8	761.8	681.8	652.5
57.5°	851.0	786.4	687.9	606.3	584.8
60°	772.6	711.0	612.5	532.5	507.9
62.5°	701.8	637.1	535.6	463.2	444.8
65°	627.9	561.7	463.2	397.0	378.6
67.5°	550.9	487.8	395.5	337.0	315.5
70°	478.6	414.0	326.3	275.5	260.1
72.5°	401.7	344.7	263.2	221.6	207.8
75°	334.0	277.0	204.7	169.3	160.1
77.5°	263.2	213.9	152.4	127.7	124.7
80°	195.4	150.8	104.6	100.0	98.5
82.5°	137.0	97.0	75.4	72.3	70.8
85°	83.1	52.3	47.7	44.6	44.6
87.5°	35.4	23.1	21.5	20.0	21.5
90°	4.4	20.6	32.4	41.2	44.1
92.5°	38.3	57.4	64.7	69.1	70.6
95°	88.3	101.5	111.8	116.2	116.2
97.5°	141.2	153.0	164.8	170.7	170.7
100°	206.0	211.8	225.1	228.0	228.0
102.5°	273.6	275.1	286.9	291.3	292.8
105°	342.8	344.3	350.1	354.5	359.0
107.5°	414.9	416.3	417.8	423.7	422.2
110°	488.4	491.4	489.9	487.0	491.4



TEST NUMBER: P1032914

CATALOG NUMBER: S124RDIW-B1195D1560UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	564.9	564.9	562.0	562.0	562.0
115°	641.4	641.4	638.5	637.0	635.5
117.5°	713.5	713.5	712.0	707.6	703.2
120°	785.6	791.5	787.1	779.7	782.7
122.5°	860.6	862.1	860.6	856.2	848.9
125°	934.2	934.2	932.7	929.8	926.8
127.5°	1000.4	1004.8	1001.9	998.9	997.4
130°	1071.0	1075.4	1075.4	1072.5	1066.6
132.5°	1143.1	1146.0	1144.6	1141.6	1140.1
135°	1204.9	1213.7	1213.7	1210.8	1206.4
137.5°	1274.0	1278.4	1281.4	1277.0	1278.4
140°	1343.2	1346.1	1346.1	1344.6	1343.2
142.5°	1406.4	1409.4	1407.9	1407.9	1407.9
145°	1463.8	1469.7	1471.2	1469.7	1465.3
147.5°	1522.7	1530.0	1528.5	1527.1	1525.6
150°	1575.6	1581.5	1581.5	1581.5	1580.0
152.5°	1625.6	1628.6	1630.0	1634.5	1630.0
155°	1677.1	1677.1	1675.7	1681.5	1675.7
157.5°	1721.3	1718.3	1718.3	1722.7	1718.3
160°	1759.5	1758.0	1756.6	1761.0	1753.6
162.5°	1794.8	1790.4	1788.9	1797.8	1790.4
165°	1825.7	1821.3	1818.4	1827.2	1821.3
167.5°	1850.7	1844.8	1844.8	1853.7	1844.8
170°	1871.3	1864.0	1865.4	1874.3	1864.0
172.5°	1886.0	1880.1	1880.1	1890.4	1880.1
175°	1899.3	1891.9	1890.4	1900.7	1890.4
177.5°	1905.2	1897.8	1897.8	1908.1	1896.3
180°	1902.2	1902.2	1902.2	1902.2	1902.2

(END OF REPORT)