

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1032926

Luminaire Tested: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1032926
REPORT IS A COMBINATION OF REPORTS P1000187 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6726.0 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1032926

CATALOG NUMBER: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1032926

CATALOG NUMBER: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76
1	103	99	95	91	98	94	90	87	84	82	79	76	74	72	68	67	65
2	94	87	81	75	89	82	77	72	74	70	66	67	64	61	60	58	55
3	86	77	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48
4	79	68	60	54	75	65	58	52	59	53	48	53	49	45	48	44	41
5	73	61	53	47	69	58	51	45	53	47	42	48	43	39	44	40	36
6	67	55	47	41	64	53	45	40	48	42	37	44	39	35	40	35	32
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29
8	58	46	38	32	55	44	36	31	40	34	29	37	31	28	34	29	26
9	54	42	34	29	51	40	33	28	37	31	27	34	29	25	31	27	23
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	25	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17042	17042	17042
5°	17044	16536	16538
10°	16899	16014	15824
15°	16667	15365	14981
20°	16362	14624	14021
25°	15983	13825	13083
30°	15611	13009	12029
35°	15202	12183	11000
40°	14716	11293	9942
45°	14259	10411	8895
50°	13741	9447	7830
55°	13180	8459	6733
60°	12557	7410	5648
65°	11957	6207	4604
70°	11104	4941	3518
75°	10008	3594	2460
80°	8357	2207	1769
85°	6287	1271	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14259 cd/sqm

TEST NUMBER: P1032926

CATALOG NUMBER: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	2.9
10°-20°	547.9	8.1
20°-30°	791.1	11.8
30°-40°	896.6	13.3
40°-50°	865.7	12.9
50°-60°	719.7	10.7
60°-70°	496.8	7.4
70°-80°	251.0	3.7
80°-90°	65.0	1.0
90°-100°	20.3	0.3
100°-110°	133.9	2.0
110°-120°	255.7	3.8
120°-130°	324.6	4.8
130°-140°	347.3	5.2
140°-150°	324.8	4.8
150°-160°	261.9	3.9
160°-170°	168.9	2.5
170°-180°	58.2	0.9
0°-30°	1535.6	22.8
0°-40°	2432.1	36.2
0°-60°	4017.5	59.7
0°-90°	4830.2	71.8
90°-120°	410.0	6.1
90°-150°	1406.7	20.9
90°-180°	1896.0	28.2
0°-180°	6726.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2087	2080	2061	2077	2074	198
15°	1988	1973	1933	1930	1919	560
25°	1797	1768	1703	1676	1660	828
35°	1554	1503	1423	1368	1339	971
45°	1267	1208	1112	1034	1005	977
55°	960	896	792	709	678	859
65°	653	584	482	413	394	645
75°	347	288	213	176	166	366
85°	86	54	50	46	46	95
90°	1	6	10	13	14	6
95°	25	10	10	13	13	31
105°	138	141	143	147	131	144
115°	258	259	258	259	259	253
125°	362	364	363	364	365	323
135°	449	449	450	451	452	346
145°	518	519	519	520	520	324
155°	568	568	567	569	567	262
165°	599	597	597	600	596	169
175°	613	610	610	614	609	58
180°	613	613	613	613	613	

TEST NUMBER: P1032926

CATALOG NUMBER: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2089.9	2089.9	2089.9	2089.9	2089.9
2.5°	2096.3	2089.9	2072.3	2089.9	2088.3
5°	2086.7	2080.3	2061.1	2077.1	2073.9
7.5°	2072.3	2065.9	2041.9	2053.1	2048.3
10°	2049.9	2041.9	2013.1	2019.5	2013.1
12.5°	2021.1	2011.5	1976.3	1979.5	1969.9
15°	1987.5	1973.1	1933.1	1929.9	1918.7
17.5°	1949.1	1928.3	1881.9	1873.9	1857.9
20°	1902.7	1881.9	1827.5	1814.7	1793.9
22.5°	1851.5	1827.5	1768.3	1747.5	1731.5
25°	1797.1	1768.3	1702.7	1675.5	1659.5
27.5°	1741.1	1705.9	1637.1	1605.1	1582.6
30°	1681.9	1641.9	1566.6	1526.6	1501.0
32.5°	1619.5	1573.0	1494.6	1446.6	1422.6
35°	1553.8	1502.6	1422.6	1368.2	1339.4
37.5°	1485.0	1432.2	1344.2	1285.0	1256.2
40°	1411.4	1358.6	1267.4	1200.2	1171.4
42.5°	1341.0	1285.0	1189.0	1120.2	1089.8
45°	1267.4	1208.2	1112.2	1033.8	1005.0
47.5°	1192.2	1131.4	1032.2	950.5	918.5
50°	1115.4	1053.0	950.5	870.5	840.1
52.5°	1037.0	976.2	870.5	788.9	756.9
55°	960.2	896.1	792.1	708.9	678.5
57.5°	884.9	817.7	715.3	630.5	608.1
60°	803.3	739.3	636.9	553.7	528.1
62.5°	729.7	662.5	556.9	481.7	462.5
65°	652.9	584.1	481.7	412.9	393.7
67.5°	572.9	507.3	411.3	350.5	328.1
70°	497.7	430.5	339.3	286.4	270.4
72.5°	417.7	358.5	273.6	230.4	216.0
75°	347.3	288.0	212.8	176.0	166.4
77.5°	273.6	222.4	158.4	132.8	129.6
80°	203.2	156.8	108.8	104.0	102.4
82.5°	142.4	100.8	78.4	75.2	73.6
85°	86.4	54.4	49.6	46.4	46.4
87.5°	36.8	24.0	22.4	20.8	22.4
90°	1.4	6.4	10.1	12.8	13.7
92.5°	6.9	6.0	9.6	12.4	12.4
95°	25.2	9.6	10.1	12.8	13.3
97.5°	48.1	58.2	10.1	12.4	12.8
100°	75.1	83.4	20.2	12.4	12.8
102.5°	105.4	110.9	116.4	13.3	13.3
105°	137.9	140.7	143.0	147.1	130.6
107.5°	167.7	169.1	172.3	174.6	176.4
110°	198.0	199.3	202.1	203.0	204.4

TEST NUMBER: P1032926

CATALOG NUMBER: S124RDIW-B1195D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.3	230.0	230.9	230.5	232.3
115°	257.5	258.9	258.4	259.4	259.4
117.5°	284.6	286.4	287.8	287.3	287.3
120°	312.0	313.9	313.4	314.3	313.4
122.5°	337.7	338.6	339.5	340.0	339.1
125°	362.0	363.8	362.9	364.3	364.7
127.5°	385.4	385.8	388.1	387.7	387.2
130°	407.8	408.3	409.7	410.1	410.1
132.5°	428.4	429.4	431.2	431.6	431.2
135°	449.1	448.6	450.4	451.3	452.3
137.5°	467.4	467.4	469.7	470.6	470.1
140°	485.3	486.2	487.1	488.5	488.9
142.5°	501.3	503.1	503.6	504.5	504.5
145°	517.8	519.2	519.2	519.6	520.5
147.5°	530.6	533.4	532.9	533.4	533.8
150°	544.8	546.7	546.2	546.2	546.7
152.5°	556.7	558.1	557.2	558.1	557.7
155°	567.7	568.2	566.8	568.7	567.3
157.5°	577.4	577.4	575.5	577.8	575.5
160°	585.6	584.2	583.8	586.5	583.8
162.5°	592.9	591.1	590.6	593.4	590.2
165°	598.9	596.6	596.6	600.3	596.1
167.5°	603.9	601.6	601.2	605.3	600.7
170°	608.1	605.3	605.8	609.4	604.9
172.5°	610.8	608.1	608.5	612.2	607.1
175°	612.6	609.9	610.4	614.5	609.0
177.5°	614.0	610.8	611.7	615.4	609.9
180°	612.6	612.6	612.6	612.6	612.6

(END OF REPORT)