

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033456

Luminaire Tested: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033456
REPORT IS A COMBINATION OF REPORTS P997451 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1560UB35-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7058.0 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	26	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	28	21	20	19	19	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	16	16	12
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14	14	14	10
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	15	14	12	12	12	9
7	54	42	35	30	48	38	31	27	29	25	21	22	18	16	14	12	11	11	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	10	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	6
10	43	32	25	20	38	29	23	19	22	18	15	17	14	11	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4553	4553	4553	4553
5°	4542	5224	4569	3926
10°	4509	6095	4542	3444
15°	4455	7027	4486	3082
20°	4397	7620	4429	2763
25°	4313	7532	4354	2527
30°	4230	6225	4282	2407
35°	4115	4639	4160	2333
40°	3980	3495	4018	2297
45°	3774	2805	3821	2248
50°	3528	2363	3580	2225
55°	3240	2057	3290	2199
60°	2958	1811	3045	2163
65°	2694	1559	2720	2072
70°	2385	1282	2436	1909
75°	2081	985	2066	1622
80°	1637	648	1616	1232
85°	1077	291	1011	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5888 cd/sqm

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	0.8
10°-20°	167.8	2.4
20°-30°	266.5	3.8
30°-40°	296.1	4.2
40°-50°	269.3	3.8
50°-60°	220.1	3.1
60°-70°	157.1	2.2
70°-80°	86.4	1.2
80°-90°	27.6	0.4
90°-100°	129.5	1.8
100°-110°	387.9	5.5
110°-120°	659.0	9.3
120°-130°	869.1	12.3
130°-140°	976.1	13.8
140°-150°	959.4	13.6
150°-160°	806.9	11.4
160°-170°	536.9	7.6
170°-180°	188.0	2.7
0°-30°	488.6	6.9
0°-40°	784.7	11.1
0°-60°	1274.1	18.1
0°-90°	1545.2	21.9
90°-120°	1176.4	16.7
90°-150°	3981.0	56.4
90°-180°	5513.0	78.1
0°-180°	7058.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	558	558	558	558	558	
5°	556	655	559	492	556	53
15°	531	900	535	395	531	150
25°	485	955	490	321	485	223
35°	421	565	425	284	421	263
45°	335	317	340	254	335	259
55°	236	207	240	222	236	212
65°	147	133	148	177	147	145
75°	72	67	72	110	72	76
85°	15	14	14	34	15	17
90°	5	46	5	46	5	8
95°	92	121	92	121	92	100
105°	358	375	358	375	358	380
115°	670	664	670	664	670	661
125°	976	968	976	968	976	870
135°	1258	1260	1258	1260	1258	974
145°	1529	1530	1529	1530	1529	957
155°	1752	1750	1752	1750	1752	806
165°	1907	1902	1907	1902	1907	538
175°	1984	1974	1984	1974	1984	188
180°	1987	1987	1987	1987	1987	

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	558.4	564.0	566.3	568.2	574.2	576.0	576.5	579.3	581.6	582.0	582.0
5°	556.1	564.9	571.9	578.3	588.1	592.2	597.3	602.9	610.3	614.9	617.2
7.5°	552.4	565.4	576.0	587.1	600.6	608.9	613.5	628.3	638.5	646.8	657.0
10°	546.9	563.5	578.8	595.0	614.0	624.1	634.3	652.4	666.7	682.9	695.9
12.5°	538.6	560.3	578.8	601.5	625.1	637.1	649.1	680.6	697.3	711.6	734.7
15°	531.2	552.9	579.3	602.4	631.6	649.6	667.2	687.5	713.9	744.9	767.1
17.5°	522.8	550.1	574.6	607.0	639.4	656.5	670.9	702.3	739.4	769.9	790.2
20°	511.3	539.0	571.4	605.6	644.0	657.5	676.4	718.5	751.8	781.9	815.2
22.5°	497.8	530.2	564.5	597.3	637.1	665.3	686.1	723.2	763.4	798.1	835.6
25°	484.9	520.0	550.1	595.0	637.1	656.1	679.7	723.6	767.6	809.7	848.1
27.5°	471.0	503.9	544.6	580.2	627.9	648.7	674.1	722.2	769.0	811.1	852.2
30°	455.7	490.9	524.7	566.8	613.0	639.9	663.5	715.8	763.4	807.4	845.8
32.5°	438.6	471.9	508.0	547.8	596.4	623.7	653.3	707.0	757.9	795.8	825.4
35°	420.6	454.3	485.8	526.5	576.5	603.8	632.5	691.7	742.1	773.1	790.2
37.5°	400.7	432.6	463.6	503.9	553.8	583.0	612.1	669.5	717.1	743.1	738.4
40°	381.7	410.4	439.1	477.0	529.3	560.3	585.7	643.6	685.2	696.3	681.1
42.5°	360.0	384.5	412.2	451.1	502.0	531.2	563.1	615.8	646.8	642.2	616.3
45°	335.4	357.2	384.9	421.5	473.3	503.4	530.2	580.2	602.9	591.3	544.1
47.5°	311.8	333.1	355.8	392.3	442.8	468.2	495.5	540.4	553.4	528.8	481.6
50°	286.4	304.0	327.6	362.3	409.5	436.3	459.0	495.1	499.7	469.6	420.6
52.5°	261.9	276.7	299.4	333.6	377.5	398.8	421.0	453.0	449.3	418.3	371.1
55°	236.0	249.8	270.7	302.1	341.0	361.3	380.3	408.5	400.7	368.8	327.6
57.5°	214.2	223.9	244.3	273.4	305.4	327.6	343.8	366.0	353.9	322.0	283.6
60°	189.2	201.3	218.4	242.0	273.4	288.2	302.6	317.4	309.1	278.5	244.3
62.5°	166.6	175.8	190.6	213.3	237.8	251.2	266.5	275.8	267.4	239.2	210.5
65°	147.1	154.5	166.1	184.6	208.2	219.3	228.1	236.9	229.9	203.6	182.8
67.5°	125.8	132.3	142.0	156.8	176.7	184.6	192.9	199.0	191.1	173.5	153.1
70°	106.9	111.5	120.8	131.9	145.7	153.1	160.1	166.1	159.2	144.4	129.1
72.5°	87.4	91.1	99.5	107.3	119.8	124.9	130.0	134.6	132.3	118.4	106.0
75°	72.2	73.6	79.1	85.6	93.5	99.0	102.7	105.5	103.6	92.5	84.7
77.5°	54.6	56.4	60.6	65.7	72.6	75.9	78.2	81.0	78.7	69.9	64.3
80°	39.8	40.3	42.6	47.2	51.8	52.3	54.6	58.3	56.9	50.9	46.7
82.5°	25.4	26.8	27.8	30.5	33.8	34.7	36.1	37.0	36.6	32.8	31.5
85°	14.8	14.8	15.7	17.6	18.5	19.9	20.4	20.8	21.7	19.4	18.0
87.5°	6.5	6.9	6.9	7.4	8.3	8.3	8.8	9.3	9.7	9.3	7.9
90°	4.6	8.4	12.1	15.9	19.6	21.5	22.9	25.6	28.3	31.1	33.8
92.5°	40.0	44.4	48.8	53.3	57.7	59.9	60.8	62.5	64.2	65.9	67.6
95°	92.2	95.3	98.3	101.4	104.5	106.0	107.2	109.6	112.0	114.4	116.8
97.5°	147.5	150.2	153.0	155.7	158.4	159.8	161.2	163.9	166.6	169.4	172.1
100°	215.1	216.5	217.9	219.2	220.6	221.3	222.8	225.9	229.0	232.0	235.1
102.5°	285.8	286.1	286.5	286.8	287.1	287.3	288.7	291.4	294.1	296.9	299.6
105°	358.0	358.4	358.7	359.1	359.4	359.6	360.3	361.6	363.0	364.3	365.7
107.5°	433.3	433.7	434.0	434.4	434.7	434.9	435.1	435.4	435.7	436.1	436.4
110°	510.2	510.9	511.5	512.2	512.9	513.2	513.0	512.7	512.4	512.0	511.7

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	590.1	590.1	590.1	590.1	590.1	590.1	589.8	589.1	588.4	587.7	587.0
115°	670.0	670.0	670.0	670.0	670.0	670.0	669.7	669.0	668.3	667.6	666.9
117.5°	745.3	745.3	745.3	745.3	745.3	745.3	745.1	744.8	744.4	744.1	743.7
120°	820.6	822.0	823.3	824.7	826.0	826.7	826.2	825.2	824.1	823.1	822.1
122.5°	898.9	899.3	899.6	900.0	900.3	900.5	900.3	900.0	899.6	899.3	898.9
125°	975.7	975.7	975.7	975.7	975.7	975.7	975.5	975.2	974.9	974.5	974.2
127.5°	1044.9	1045.9	1046.9	1048.0	1049.0	1049.5	1049.2	1048.5	1047.8	1047.1	1046.4
130°	1118.7	1119.7	1120.7	1121.8	1122.8	1123.3	1123.3	1123.3	1123.3	1123.3	1123.3
132.5°	1193.9	1194.6	1195.3	1196.0	1196.7	1197.0	1196.8	1196.5	1196.2	1195.8	1195.5
135°	1258.5	1260.5	1262.6	1264.6	1266.7	1267.7	1267.7	1267.7	1267.7	1267.7	1267.7
137.5°	1330.7	1331.7	1332.7	1333.8	1334.8	1335.3	1335.6	1336.3	1337.0	1337.7	1338.4
140°	1402.9	1403.6	1404.3	1405.0	1405.7	1406.0	1406.0	1406.0	1406.0	1406.0	1406.0
142.5°	1469.0	1469.7	1470.4	1471.1	1471.8	1472.1	1471.9	1471.6	1471.2	1470.9	1470.5
145°	1528.9	1530.3	1531.7	1533.0	1534.4	1535.1	1535.3	1535.6	1535.9	1536.3	1536.6
147.5°	1590.4	1592.1	1593.8	1595.5	1597.2	1598.1	1597.9	1597.6	1597.2	1596.9	1596.5
150°	1645.7	1647.1	1648.5	1649.8	1651.2	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
152.5°	1698.0	1698.7	1699.3	1700.0	1700.7	1701.0	1701.2	1701.5	1701.9	1702.2	1702.6
155°	1751.7	1751.7	1751.7	1751.7	1751.7	1751.7	1751.5	1751.2	1750.9	1750.5	1750.2
157.5°	1797.8	1797.1	1796.5	1795.8	1795.1	1794.8	1794.8	1794.8	1794.8	1794.8	1794.8
160°	1837.8	1837.5	1837.1	1836.8	1836.5	1836.3	1836.1	1835.8	1835.4	1835.1	1834.7
162.5°	1874.7	1873.7	1872.7	1871.6	1870.6	1870.1	1869.9	1869.6	1869.2	1868.9	1868.5
165°	1906.9	1905.9	1904.9	1903.8	1902.8	1902.3	1902.0	1901.3	1900.6	1900.0	1899.3
167.5°	1933.1	1931.7	1930.3	1929.0	1927.6	1926.9	1926.9	1926.9	1926.9	1926.9	1926.9
170°	1954.6	1952.9	1951.2	1949.5	1947.8	1946.9	1947.1	1947.4	1947.7	1948.1	1948.4
172.5°	1969.9	1968.5	1967.2	1965.8	1964.5	1963.8	1963.8	1963.8	1963.8	1963.8	1963.8
175°	1983.8	1982.1	1980.4	1978.7	1977.0	1976.1	1975.9	1975.6	1975.2	1974.9	1974.5
177.5°	1989.9	1988.2	1986.5	1984.8	1983.1	1982.2	1982.2	1982.2	1982.2	1982.2	1982.2
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	583.4	591.8	595.5	596.4	601.5	598.2	599.6	599.2	602.9	603.3	603.3
5°	626.0	635.7	639.0	643.6	650.5	652.4	651.0	653.8	658.8	655.1	660.7
7.5°	670.9	681.5	688.9	699.1	701.4	707.4	711.1	714.4	715.3	715.8	716.7
10°	712.5	725.9	736.1	753.2	756.9	760.2	776.4	769.9	778.2	775.4	776.4
12.5°	746.3	772.7	781.0	809.7	812.5	823.6	822.6	832.8	834.7	838.4	834.7
15°	790.7	821.2	834.7	850.9	860.1	873.1	875.4	889.3	894.8	899.9	894.8
17.5°	831.4	847.6	881.9	894.8	900.8	907.8	925.4	930.4	938.8	935.5	944.8
20°	851.8	874.9	911.0	933.2	942.5	948.9	963.8	971.6	974.9	974.9	975.8
22.5°	869.8	903.1	930.0	955.4	963.8	968.4	977.2	983.2	984.6	985.5	986.4
25°	886.0	916.1	937.8	952.2	955.4	955.4	960.5	956.8	950.8	955.4	958.2
27.5°	886.0	907.3	917.0	922.1	922.1	909.6	902.2	886.9	874.0	870.3	878.6
30°	871.2	880.9	867.5	855.0	845.3	837.0	807.8	784.7	780.1	776.8	789.3
32.5°	837.0	824.5	798.1	762.0	747.7	728.7	706.0	688.5	677.8	674.1	671.3
35°	776.4	744.0	709.7	661.2	651.0	626.9	595.9	583.0	565.4	564.9	570.9
37.5°	710.2	660.2	623.2	577.0	562.6	537.2	508.0	494.6	482.6	473.3	484.4
40°	632.9	589.4	533.0	495.1	474.7	461.3	436.8	422.0	416.4	411.8	418.7
42.5°	560.8	513.1	469.2	430.3	413.6	398.4	382.2	367.8	363.7	363.2	368.3
45°	489.0	442.3	401.6	368.3	357.6	348.4	332.7	328.5	321.6	316.9	319.2
47.5°	431.7	383.6	349.8	324.3	315.1	307.2	297.0	290.1	284.1	282.2	285.0
50°	375.2	342.8	308.1	286.9	279.9	272.5	264.7	258.2	255.4	253.5	255.4
52.5°	329.9	295.2	271.6	254.5	247.5	242.0	236.4	233.7	229.9	230.9	232.7
55°	289.2	258.6	238.7	226.2	222.1	219.8	212.8	209.6	208.2	207.3	208.2
57.5°	250.8	228.6	213.8	203.1	197.6	196.2	190.6	190.6	189.2	187.8	188.3
60°	220.2	201.3	186.9	178.6	177.7	175.4	171.7	171.2	168.0	169.3	169.8
62.5°	189.2	174.0	164.2	159.2	155.9	155.0	152.7	152.2	150.8	151.3	150.4
65°	164.7	152.2	142.5	138.3	137.0	136.5	134.6	133.3	132.3	133.3	132.3
67.5°	140.2	131.9	124.5	120.3	118.4	118.0	116.6	115.7	116.1	114.7	115.7
70°	117.1	108.7	104.1	101.8	100.9	99.5	99.5	99.5	99.5	98.5	98.1
72.5°	98.5	90.2	87.0	85.6	84.7	84.2	82.8	83.3	82.8	82.4	84.2
75°	78.2	73.1	69.9	68.5	69.4	68.0	66.6	67.6	66.2	66.6	68.5
77.5°	59.2	56.9	55.1	54.1	53.2	52.3	52.3	51.4	51.4	51.4	51.4
80°	43.0	42.6	39.3	38.9	38.9	37.9	37.9	37.9	37.9	37.5	37.9
82.5°	28.7	28.2	27.3	26.8	25.9	26.4	26.4	25.4	25.4	25.0	25.4
85°	16.7	16.7	15.7	15.3	14.8	15.3	14.3	13.9	14.3	13.9	14.3
87.5°	7.9	6.9	7.4	6.9	6.0	6.5	5.6	6.0	5.6	5.1	6.0
90°	35.8	37.9	39.9	42.0	43.0	43.3	44.0	44.7	45.4	46.1	45.4
92.5°	68.6	69.6	70.7	71.7	72.2	72.4	72.7	73.1	73.4	73.8	73.4
95°	117.8	118.8	119.9	120.9	121.4	121.4	121.4	121.4	121.4	121.4	121.4
97.5°	173.5	174.8	176.2	177.5	178.2	178.2	178.2	178.2	178.2	178.2	178.2
100°	235.8	236.5	237.2	237.9	238.2	238.2	238.2	238.2	238.2	238.2	238.2
102.5°	300.6	301.6	302.7	303.7	304.2	304.4	304.7	305.1	305.4	305.8	305.4
105°	366.7	367.7	368.8	369.8	370.3	370.8	371.8	372.9	373.9	374.9	373.9
107.5°	437.8	439.1	440.5	441.8	442.5	442.3	442.0	441.7	441.3	441.0	441.3
110°	511.0	510.3	509.6	508.9	508.6	509.1	510.1	511.2	512.2	513.2	512.2

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0
115°	666.6	666.2	665.9	665.6	665.4	665.2	664.9	664.5	664.2	663.8	664.2
117.5°	742.7	741.7	740.6	739.6	739.1	738.6	737.6	736.5	735.5	734.5	735.5
120°	820.4	818.7	817.0	815.3	814.4	814.7	815.4	816.1	816.8	817.5	816.8
122.5°	897.9	896.9	895.8	894.8	894.3	893.4	891.7	890.0	888.3	886.6	888.3
125°	973.5	972.8	972.1	971.4	971.1	970.8	970.1	969.4	968.8	968.1	968.8
127.5°	1045.7	1045.1	1044.4	1043.7	1043.4	1043.2	1042.9	1042.5	1042.2	1041.8	1042.2
130°	1122.6	1121.9	1121.2	1120.5	1120.2	1119.5	1118.1	1116.8	1115.4	1114.0	1115.4
132.5°	1194.8	1194.1	1193.4	1192.7	1192.4	1192.2	1191.9	1191.6	1191.2	1190.9	1191.2
135°	1267.0	1266.3	1265.6	1264.9	1264.6	1264.1	1263.1	1262.0	1261.0	1260.0	1261.0
137.5°	1337.4	1336.4	1335.3	1334.3	1333.8	1334.0	1334.3	1334.6	1335.0	1335.3	1335.0
140°	1405.7	1405.3	1405.0	1404.7	1404.5	1404.3	1404.0	1403.6	1403.3	1402.9	1403.3
142.5°	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5
145°	1536.3	1535.9	1535.6	1535.3	1535.1	1534.6	1533.6	1532.5	1531.5	1530.5	1531.5
147.5°	1596.2	1595.8	1595.5	1595.2	1595.0	1594.8	1594.5	1594.2	1593.8	1593.5	1593.8
150°	1651.9	1651.9	1651.9	1651.9	1651.9	1651.7	1651.4	1651.0	1650.7	1650.3	1650.7
152.5°	1703.6	1704.6	1705.7	1706.7	1707.2	1706.7	1705.7	1704.6	1703.6	1702.6	1703.6
155°	1751.6	1752.9	1754.3	1755.6	1756.3	1755.6	1754.3	1752.9	1751.6	1750.2	1751.6
157.5°	1795.8	1796.8	1797.9	1798.9	1799.4	1798.9	1797.9	1796.8	1795.8	1794.8	1795.8
160°	1835.7	1836.7	1837.8	1838.8	1839.3	1838.4	1836.7	1835.0	1833.3	1831.6	1833.3
162.5°	1870.5	1872.6	1874.6	1876.7	1877.7	1876.9	1875.2	1873.5	1871.8	1870.1	1871.8
165°	1901.3	1903.4	1905.4	1907.5	1908.5	1907.8	1906.4	1905.1	1903.7	1902.3	1903.7
167.5°	1928.9	1931.0	1933.0	1935.1	1936.1	1935.1	1933.0	1931.0	1928.9	1926.9	1928.9
170°	1950.4	1952.5	1954.5	1956.6	1957.6	1956.4	1954.0	1951.7	1949.3	1946.9	1949.3
172.5°	1966.2	1968.6	1970.9	1973.3	1974.5	1973.3	1970.9	1968.6	1966.2	1963.8	1966.2
175°	1976.9	1979.3	1981.7	1984.1	1985.3	1984.1	1981.7	1979.3	1976.9	1974.5	1976.9
177.5°	1984.6	1987.0	1989.4	1991.8	1993.0	1991.6	1988.9	1986.2	1983.4	1980.7	1983.4
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	602.4	601.0	599.2	599.2	596.9	596.9	593.1	586.7	581.1	579.3	580.2
5°	653.8	654.2	651.4	649.1	645.0	641.7	635.7	624.1	620.4	613.0	608.0
7.5°	712.5	710.7	705.6	701.9	701.0	693.6	680.6	666.7	655.6	648.2	637.6
10°	778.7	771.3	763.9	761.6	756.0	743.5	728.7	713.4	698.2	682.0	663.9
12.5°	834.2	819.9	819.4	813.8	803.2	796.3	778.7	756.9	730.6	712.5	692.2
15°	893.9	880.5	869.4	859.2	854.1	833.7	818.9	791.6	760.2	740.7	726.9
17.5°	936.5	930.4	911.5	906.8	899.9	876.3	852.7	825.9	798.6	771.3	733.8
20°	970.7	967.0	954.5	948.0	936.9	918.4	889.7	858.7	827.3	788.4	753.2
22.5°	985.5	980.9	970.7	965.1	958.2	942.5	917.9	882.8	841.6	806.9	769.4
25°	956.3	964.7	961.9	959.6	956.8	947.6	929.1	898.1	857.8	818.5	771.7
27.5°	890.6	905.0	918.9	920.7	925.4	929.1	921.6	899.4	865.7	824.0	772.7
30°	802.3	808.8	837.0	845.3	851.8	875.4	889.3	883.7	857.8	820.3	773.1
32.5°	688.9	706.0	734.7	754.6	772.2	798.6	834.7	849.0	839.8	809.2	762.5
35°	581.6	601.9	635.3	660.7	678.3	715.8	758.3	789.3	800.9	785.6	744.0
37.5°	493.7	518.2	547.8	557.5	577.9	624.1	682.9	725.9	754.2	755.5	723.2
40°	427.5	440.0	463.6	478.4	498.3	537.2	594.5	651.4	694.0	708.4	691.2
42.5°	371.5	381.2	398.8	416.9	434.9	464.5	517.3	570.5	627.9	656.5	656.1
45°	327.1	337.3	349.3	364.1	376.6	408.5	450.2	504.8	554.3	598.7	609.8
47.5°	288.2	297.0	311.8	318.3	326.6	356.7	392.8	443.7	495.1	546.0	558.9
50°	259.6	267.0	277.1	281.3	290.6	312.8	342.4	383.6	440.5	487.2	511.3
52.5°	233.7	239.2	247.1	250.3	256.8	273.4	300.3	332.7	379.9	428.0	461.7
55°	211.4	215.1	220.7	224.4	229.0	243.8	263.7	292.9	333.6	375.2	408.1
57.5°	190.6	193.4	199.0	200.8	204.5	216.1	229.9	254.5	291.9	329.0	360.9
60°	171.2	173.0	176.3	180.4	183.2	191.1	204.0	224.4	254.5	288.2	314.2
62.5°	152.7	155.5	156.4	158.2	160.5	168.0	178.1	192.9	219.3	247.1	274.4
65°	133.7	136.0	137.9	138.3	140.7	146.2	155.5	168.4	185.5	209.6	235.0
67.5°	116.1	117.5	118.4	120.3	122.6	125.4	132.8	142.5	158.2	177.7	198.0
70°	99.9	99.9	101.3	101.8	104.6	107.8	111.0	120.3	134.2	149.9	163.8
72.5°	82.4	84.7	84.2	86.5	86.1	88.4	92.5	98.5	108.7	121.2	134.6
75°	67.1	68.5	68.5	68.5	69.4	71.3	73.6	79.1	87.0	97.2	105.0
77.5°	52.3	53.2	53.2	53.2	53.7	55.5	57.8	61.5	67.1	73.1	77.7
80°	37.5	38.4	38.4	39.3	39.3	39.8	42.1	44.0	46.7	51.4	56.0
82.5°	25.4	25.9	26.8	26.8	26.4	27.3	27.8	29.6	32.4	33.3	36.6
85°	13.9	14.3	14.8	14.8	15.3	16.2	15.7	17.6	17.6	19.4	20.4
87.5°	5.6	6.5	6.5	6.0	6.5	6.5	6.5	7.4	7.9	8.3	7.9
90°	44.7	44.0	43.3	43.0	42.0	39.9	37.9	35.8	33.8	31.1	28.3
92.5°	73.1	72.7	72.4	72.2	71.7	70.7	69.6	68.6	67.6	65.9	64.2
95°	121.4	121.4	121.4	121.4	120.9	119.9	118.8	117.8	116.8	114.4	112.0
97.5°	178.2	178.2	178.2	178.2	177.5	176.2	174.8	173.5	172.1	169.4	166.6
100°	238.2	238.2	238.2	238.2	237.9	237.2	236.5	235.8	235.1	232.0	229.0
102.5°	305.1	304.7	304.4	304.2	303.7	302.7	301.6	300.6	299.6	296.9	294.1
105°	372.9	371.8	370.8	370.3	369.8	368.8	367.7	366.7	365.7	364.3	363.0
107.5°	441.7	442.0	442.3	442.5	441.8	440.5	439.1	437.8	436.4	436.1	435.7
110°	511.2	510.1	509.1	508.6	508.9	509.6	510.3	511.0	511.7	512.0	512.4

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.7	588.4
115°	664.5	664.9	665.2	665.4	665.6	665.9	666.2	666.6	666.9	667.6	668.3
117.5°	736.5	737.6	738.6	739.1	739.6	740.6	741.7	742.7	743.7	744.1	744.4
120°	816.1	815.4	814.7	814.4	815.3	817.0	818.7	820.4	822.1	823.1	824.1
122.5°	890.0	891.7	893.4	894.3	894.8	895.8	896.9	897.9	898.9	899.3	899.6
125°	969.4	970.1	970.8	971.1	971.4	972.1	972.8	973.5	974.2	974.5	974.9
127.5°	1042.5	1042.9	1043.2	1043.4	1043.7	1044.4	1045.1	1045.7	1046.4	1047.1	1047.8
130°	1116.8	1118.1	1119.5	1120.2	1120.5	1121.2	1121.9	1122.6	1123.3	1123.3	1123.3
132.5°	1191.6	1191.9	1192.2	1192.4	1192.7	1193.4	1194.1	1194.8	1195.5	1195.8	1196.2
135°	1262.0	1263.1	1264.1	1264.6	1264.9	1265.6	1266.3	1267.0	1267.7	1267.7	1267.7
137.5°	1334.6	1334.3	1334.0	1333.8	1334.3	1335.3	1336.4	1337.4	1338.4	1337.7	1337.0
140°	1403.6	1404.0	1404.3	1404.5	1404.7	1405.0	1405.3	1405.7	1406.0	1406.0	1406.0
142.5°	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.9	1471.2
145°	1532.5	1533.6	1534.6	1535.1	1535.3	1535.6	1535.9	1536.3	1536.6	1536.3	1535.9
147.5°	1594.2	1594.5	1594.8	1595.0	1595.2	1595.5	1595.8	1596.2	1596.5	1596.9	1597.2
150°	1651.0	1651.4	1651.7	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
152.5°	1704.6	1705.7	1706.7	1707.2	1706.7	1705.7	1704.6	1703.6	1702.6	1702.2	1701.9
155°	1752.9	1754.3	1755.6	1756.3	1755.6	1754.3	1752.9	1751.6	1750.2	1750.5	1750.9
157.5°	1796.8	1797.9	1798.9	1799.4	1798.9	1797.9	1796.8	1795.8	1794.8	1794.8	1794.8
160°	1835.0	1836.7	1838.4	1839.3	1838.8	1837.8	1836.7	1835.7	1834.7	1835.1	1835.4
162.5°	1873.5	1875.2	1876.9	1877.7	1876.7	1874.6	1872.6	1870.5	1868.5	1868.9	1869.2
165°	1905.1	1906.4	1907.8	1908.5	1907.5	1905.4	1903.4	1901.3	1899.3	1900.0	1900.6
167.5°	1931.0	1933.0	1935.1	1936.1	1935.1	1933.0	1931.0	1928.9	1926.9	1926.9	1926.9
170°	1951.7	1954.0	1956.4	1957.6	1956.6	1954.5	1952.5	1950.4	1948.4	1948.1	1947.7
172.5°	1968.6	1970.9	1973.3	1974.5	1973.3	1970.9	1968.6	1966.2	1963.8	1963.8	1963.8
175°	1979.3	1981.7	1984.1	1985.3	1984.1	1981.7	1979.3	1976.9	1974.5	1974.9	1975.2
177.5°	1986.2	1988.9	1991.6	1993.0	1991.8	1989.4	1987.0	1984.6	1982.2	1982.2	1982.2
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	576.0	574.2	572.8	572.8	568.6	564.5	562.2	561.2	560.3	556.6	551.5
5°	599.6	593.6	589.4	585.3	578.3	570.9	563.5	559.4	553.4	545.0	539.0
7.5°	626.0	611.7	607.0	601.9	588.1	575.6	565.4	556.6	546.9	536.2	525.6
10°	648.2	632.9	622.8	614.0	595.9	579.3	564.0	551.0	538.6	524.7	511.7
12.5°	669.5	647.7	637.1	624.1	605.2	581.1	561.2	545.0	526.5	512.2	496.5
15°	699.1	662.6	645.0	636.6	611.2	583.0	558.9	534.9	519.6	497.8	484.0
17.5°	703.7	674.1	662.6	641.3	610.7	578.8	551.0	527.0	503.9	484.4	466.4
20°	719.9	681.1	662.6	649.1	608.9	576.5	546.0	515.0	492.7	471.9	451.6
22.5°	730.1	686.1	666.7	645.4	607.0	568.2	532.1	505.2	477.9	456.7	440.5
25°	727.3	683.4	661.6	641.7	595.0	556.1	523.7	489.5	464.1	440.9	419.6
27.5°	725.9	676.4	653.3	631.1	587.1	546.4	505.7	477.9	449.7	422.9	407.2
30°	722.2	667.6	640.8	616.7	570.9	528.4	493.7	461.3	433.1	408.5	387.7
32.5°	709.7	652.8	626.9	601.0	553.4	510.8	475.6	445.6	417.3	391.9	372.0
35°	693.1	635.3	607.0	579.7	532.1	489.0	456.7	425.2	398.8	374.3	355.3
37.5°	676.4	614.9	588.5	557.1	513.1	468.2	434.9	406.7	382.2	356.7	335.9
40°	652.4	590.8	561.7	534.9	483.5	441.4	410.9	385.4	361.3	337.3	319.7
42.5°	619.5	564.5	534.4	504.8	456.7	415.0	385.4	362.7	340.1	320.2	300.7
45°	586.2	532.5	505.7	479.3	427.0	387.7	360.4	339.6	320.6	298.9	283.2
47.5°	546.0	500.6	473.8	447.9	398.4	359.0	334.1	314.6	297.0	279.0	264.2
50°	504.8	465.5	440.9	414.1	366.9	331.3	306.8	290.6	276.2	259.1	247.1
52.5°	460.4	426.1	405.3	379.4	337.8	304.9	279.9	263.7	251.7	239.2	228.6
55°	413.2	388.2	366.0	345.2	305.8	276.2	254.0	239.7	231.3	219.8	210.5
57.5°	370.6	346.5	333.1	309.5	275.3	246.1	228.6	216.5	206.8	199.9	192.5
60°	326.2	306.8	291.9	274.8	244.8	220.2	201.7	194.8	184.6	179.5	176.3
62.5°	283.6	269.7	255.9	242.9	216.1	192.9	179.1	170.3	164.2	159.2	156.4
65°	243.4	230.4	220.7	209.1	186.9	168.4	155.5	148.5	142.5	141.1	137.9
67.5°	204.0	198.5	187.8	178.6	159.6	145.3	135.6	126.8	123.5	122.1	119.4
70°	170.7	164.2	155.9	148.1	133.7	121.2	112.4	109.2	104.6	104.1	100.9
72.5°	140.7	132.8	126.8	120.8	110.1	99.0	94.4	89.8	87.4	85.6	84.2
75°	111.5	106.0	101.8	96.7	87.4	80.0	73.6	71.7	70.3	69.9	68.9
77.5°	83.3	79.6	77.7	72.6	66.2	59.7	56.9	54.1	54.1	53.2	53.7
80°	59.2	56.9	54.6	51.8	46.3	43.5	41.2	39.3	38.4	37.9	38.4
82.5°	37.5	36.1	35.6	33.8	30.1	28.7	26.8	25.4	25.4	25.4	25.4
85°	20.8	20.8	20.8	18.0	16.7	15.3	14.3	13.9	13.9	13.9	14.3
87.5°	8.8	8.8	7.4	7.4	6.9	6.0	5.6	5.6	6.0	6.0	6.5
90°	25.6	22.9	21.5	19.6	15.9	12.1	8.4	4.6	8.4	12.1	15.9
92.5°	62.5	60.8	59.9	57.7	53.3	48.8	44.4	40.0	44.4	48.8	53.3
95°	109.6	107.2	106.0	104.5	101.4	98.3	95.3	92.2	95.3	98.3	101.4
97.5°	163.9	161.2	159.8	158.4	155.7	153.0	150.2	147.5	150.2	153.0	155.7
100°	225.9	222.8	221.3	220.6	219.2	217.9	216.5	215.1	216.5	217.9	219.2
102.5°	291.4	288.7	287.3	287.1	286.8	286.5	286.1	285.8	286.1	286.5	286.8
105°	361.6	360.3	359.6	359.4	359.1	358.7	358.4	358.0	358.4	358.7	359.1
107.5°	435.4	435.1	434.9	434.7	434.4	434.0	433.7	433.3	433.7	434.0	434.4
110°	512.7	513.0	513.2	512.9	512.2	511.5	510.9	510.2	510.9	511.5	512.2

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	589.1	589.8	590.1	590.1	590.1	590.1	590.1	590.1	590.1	590.1	590.1
115°	669.0	669.7	670.0	670.0	670.0	670.0	670.0	670.0	670.0	670.0	670.0
117.5°	744.8	745.1	745.3	745.3	745.3	745.3	745.3	745.3	745.3	745.3	745.3
120°	825.2	826.2	826.7	826.0	824.7	823.3	822.0	820.6	822.0	823.3	824.7
122.5°	900.0	900.3	900.5	900.3	900.0	899.6	899.3	898.9	899.3	899.6	900.0
125°	975.2	975.5	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7	975.7
127.5°	1048.5	1049.2	1049.5	1049.0	1048.0	1046.9	1045.9	1044.9	1045.9	1046.9	1048.0
130°	1123.3	1123.3	1123.3	1122.8	1121.8	1120.7	1119.7	1118.7	1119.7	1120.7	1121.8
132.5°	1196.5	1196.8	1197.0	1196.7	1196.0	1195.3	1194.6	1193.9	1194.6	1195.3	1196.0
135°	1267.7	1267.7	1267.7	1266.7	1264.6	1262.6	1260.5	1258.5	1260.5	1262.6	1264.6
137.5°	1336.3	1335.6	1335.3	1334.8	1333.8	1332.7	1331.7	1330.7	1331.7	1332.7	1333.8
140°	1406.0	1406.0	1406.0	1405.7	1405.0	1404.3	1403.6	1402.9	1403.6	1404.3	1405.0
142.5°	1471.6	1471.9	1472.1	1471.8	1471.1	1470.4	1469.7	1469.0	1469.7	1470.4	1471.1
145°	1535.6	1535.3	1535.1	1534.4	1533.0	1531.7	1530.3	1528.9	1530.3	1531.7	1533.0
147.5°	1597.6	1597.9	1598.1	1597.2	1595.5	1593.8	1592.1	1590.4	1592.1	1593.8	1595.5
150°	1651.9	1651.9	1651.9	1651.2	1649.8	1648.5	1647.1	1645.7	1647.1	1648.5	1649.8
152.5°	1701.5	1701.2	1701.0	1700.7	1700.0	1699.3	1698.7	1698.0	1698.7	1699.3	1700.0
155°	1751.2	1751.5	1751.7	1751.7	1751.7	1751.7	1751.7	1751.7	1751.7	1751.7	1751.7
157.5°	1794.8	1794.8	1794.8	1795.1	1795.8	1796.5	1797.1	1797.8	1797.1	1796.5	1795.8
160°	1835.8	1836.1	1836.3	1836.5	1836.8	1837.1	1837.5	1837.8	1837.5	1837.1	1836.8
162.5°	1869.6	1869.9	1870.1	1870.6	1871.6	1872.7	1873.7	1874.7	1873.7	1872.7	1871.6
165°	1901.3	1902.0	1902.3	1902.8	1903.8	1904.9	1905.9	1906.9	1905.9	1904.9	1903.8
167.5°	1926.9	1926.9	1926.9	1927.6	1929.0	1930.3	1931.7	1933.1	1931.7	1930.3	1929.0
170°	1947.4	1947.1	1946.9	1947.8	1949.5	1951.2	1952.9	1954.6	1952.9	1951.2	1949.5
172.5°	1963.8	1963.8	1963.8	1964.5	1965.8	1967.2	1968.5	1969.9	1968.5	1967.2	1965.8
175°	1975.6	1975.9	1976.1	1977.0	1978.7	1980.4	1982.1	1983.8	1982.1	1980.4	1978.7
177.5°	1982.2	1982.2	1982.2	1983.1	1984.8	1986.5	1988.2	1989.9	1988.2	1986.5	1984.8
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	550.1	548.3	549.2	544.6	540.4	534.4	529.3	528.4	527.4	530.2	528.4
5°	534.4	532.1	529.8	524.2	515.9	510.8	503.4	502.9	500.2	496.0	496.9
7.5°	517.3	515.9	512.6	503.9	496.5	487.7	481.6	476.6	474.2	470.5	469.2
10°	503.4	498.3	495.5	485.8	477.0	467.8	459.9	456.2	452.0	448.8	446.5
12.5°	484.4	483.0	475.2	467.3	459.9	449.3	443.2	432.6	427.0	429.8	428.9
15°	471.9	465.5	463.6	452.5	440.0	433.1	422.0	415.0	412.7	408.5	403.5
17.5°	455.3	451.1	444.6	434.5	420.1	410.4	402.5	396.1	393.3	387.7	383.6
20°	439.5	432.6	427.5	418.3	404.4	391.9	382.2	378.0	371.1	366.4	364.1
22.5°	425.2	420.1	412.7	398.8	386.8	374.8	363.2	357.2	350.7	347.9	344.2
25°	407.6	399.3	394.2	378.9	366.0	356.3	345.6	337.8	334.1	329.4	328.5
27.5°	390.5	382.6	376.6	363.2	347.5	335.0	328.5	322.9	316.5	316.5	314.2
30°	373.4	367.8	358.6	345.6	330.8	318.8	311.4	306.3	304.0	302.1	301.7
32.5°	356.3	348.9	343.3	325.7	314.6	303.5	298.0	293.8	291.0	290.6	291.0
35°	338.7	330.4	324.8	309.1	298.0	287.8	285.5	281.8	280.4	279.9	282.2
37.5°	320.2	313.7	306.8	293.8	281.3	275.3	270.7	269.3	268.8	271.6	272.5
40°	303.1	297.5	291.0	277.1	267.9	261.4	259.1	257.7	259.6	262.3	263.7
42.5°	286.9	279.0	273.9	261.4	253.1	249.4	246.6	246.6	248.5	251.7	254.0
45°	269.7	263.7	258.6	247.5	240.1	236.0	235.5	236.0	238.3	240.6	243.4
47.5°	253.1	247.1	241.5	232.3	225.8	223.5	223.0	223.5	227.2	230.4	233.7
50°	237.8	231.3	226.2	217.5	212.4	209.6	210.1	212.4	215.1	219.8	223.9
52.5°	219.8	215.1	210.5	202.7	198.0	196.2	197.6	199.4	204.5	207.7	212.8
55°	202.2	198.0	194.3	188.3	184.6	183.2	184.1	186.9	191.1	196.6	202.7
57.5°	186.0	181.4	177.7	173.5	169.3	169.8	170.3	174.0	179.1	184.1	191.1
60°	168.0	165.2	161.9	156.8	155.0	155.0	156.4	160.5	165.2	173.5	179.5
62.5°	151.8	148.1	145.7	142.5	139.7	140.2	143.4	147.1	152.7	159.6	167.5
65°	135.1	130.9	129.1	126.3	125.4	125.8	128.2	133.7	139.7	145.7	153.1
67.5°	116.6	115.2	113.4	110.6	111.5	112.0	114.3	118.9	125.4	131.4	139.7
70°	100.9	98.1	97.6	95.3	95.3	96.7	101.3	104.6	110.6	117.1	125.8
72.5°	84.2	81.9	81.9	80.0	81.4	82.8	85.1	89.8	95.3	101.8	109.2
75°	67.1	66.2	67.1	66.2	66.2	68.5	71.3	75.0	81.0	87.9	93.9
77.5°	51.8	51.8	51.4	52.7	52.7	54.1	57.8	61.5	66.2	71.7	78.2
80°	37.9	37.9	37.9	39.3	40.7	40.7	43.0	47.7	51.8	55.5	61.5
82.5°	25.9	25.9	25.9	26.8	28.7	28.7	31.5	34.2	38.9	42.1	44.9
85°	15.7	15.7	15.3	16.2	16.7	18.0	20.4	22.2	24.5	27.3	30.1
87.5°	6.9	6.9	7.4	7.9	8.3	9.3	10.2	11.1	13.4	14.3	15.7
90°	19.6	21.5	22.9	25.6	28.3	31.1	33.8	35.8	37.9	39.9	42.0
92.5°	57.7	59.9	60.8	62.5	64.2	65.9	67.6	68.6	69.6	70.7	71.7
95°	104.5	106.0	107.2	109.6	112.0	114.4	116.8	117.8	118.8	119.9	120.9
97.5°	158.4	159.8	161.2	163.9	166.6	169.4	172.1	173.5	174.8	176.2	177.5
100°	220.6	221.3	222.8	225.9	229.0	232.0	235.1	235.8	236.5	237.2	237.9
102.5°	287.1	287.3	288.7	291.4	294.1	296.9	299.6	300.6	301.6	302.7	303.7
105°	359.4	359.6	360.3	361.6	363.0	364.3	365.7	366.7	367.7	368.8	369.8
107.5°	434.7	434.9	435.1	435.4	435.7	436.1	436.4	437.8	439.1	440.5	441.8
110°	512.9	513.2	513.0	512.7	512.4	512.0	511.7	511.0	510.3	509.6	508.9

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	590.1	590.1	589.8	589.1	588.4	587.7	587.0	587.0	587.0	587.0	587.0
115°	670.0	670.0	669.7	669.0	668.3	667.6	666.9	666.6	666.2	665.9	665.6
117.5°	745.3	745.3	745.1	744.8	744.4	744.1	743.7	742.7	741.7	740.6	739.6
120°	826.0	826.7	826.2	825.2	824.1	823.1	822.1	820.4	818.7	817.0	815.3
122.5°	900.3	900.5	900.3	900.0	899.6	899.3	898.9	897.9	896.9	895.8	894.8
125°	975.7	975.7	975.5	975.2	974.9	974.5	974.2	973.5	972.8	972.1	971.4
127.5°	1049.0	1049.5	1049.2	1048.5	1047.8	1047.1	1046.4	1045.7	1045.1	1044.4	1043.7
130°	1122.8	1123.3	1123.3	1123.3	1123.3	1123.3	1123.3	1122.6	1121.9	1121.2	1120.5
132.5°	1196.7	1197.0	1196.8	1196.5	1196.2	1195.8	1195.5	1194.8	1194.1	1193.4	1192.7
135°	1266.7	1267.7	1267.7	1267.7	1267.7	1267.7	1267.7	1267.0	1266.3	1265.6	1264.9
137.5°	1334.8	1335.3	1335.6	1336.3	1337.0	1337.7	1338.4	1337.4	1336.4	1335.3	1334.3
140°	1405.7	1406.0	1406.0	1406.0	1406.0	1406.0	1406.0	1405.7	1405.3	1405.0	1404.7
142.5°	1471.8	1472.1	1471.9	1471.6	1471.2	1470.9	1470.5	1470.5	1470.5	1470.5	1470.5
145°	1534.4	1535.1	1535.3	1535.6	1535.9	1536.3	1536.6	1536.3	1535.9	1535.6	1535.3
147.5°	1597.2	1598.1	1597.9	1597.6	1597.2	1596.9	1596.5	1596.2	1595.8	1595.5	1595.2
150°	1651.2	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9
152.5°	1700.7	1701.0	1701.2	1701.5	1701.9	1702.2	1702.6	1703.6	1704.6	1705.7	1706.7
155°	1751.7	1751.7	1751.5	1751.2	1750.9	1750.5	1750.2	1751.6	1752.9	1754.3	1755.6
157.5°	1795.1	1794.8	1794.8	1794.8	1794.8	1794.8	1794.8	1795.8	1796.8	1797.9	1798.9
160°	1836.5	1836.3	1836.1	1835.8	1835.4	1835.1	1834.7	1835.7	1836.7	1837.8	1838.8
162.5°	1870.6	1870.1	1869.9	1869.6	1869.2	1868.9	1868.5	1870.5	1872.6	1874.6	1876.7
165°	1902.8	1902.3	1902.0	1901.3	1900.6	1900.0	1899.3	1901.3	1903.4	1905.4	1907.5
167.5°	1927.6	1926.9	1926.9	1926.9	1926.9	1926.9	1926.9	1928.9	1931.0	1933.0	1935.1
170°	1947.8	1946.9	1947.1	1947.4	1947.7	1948.1	1948.4	1950.4	1952.5	1954.5	1956.6
172.5°	1964.5	1963.8	1963.8	1963.8	1963.8	1963.8	1963.8	1966.2	1968.6	1970.9	1973.3
175°	1977.0	1976.1	1975.9	1975.6	1975.2	1974.9	1974.5	1976.9	1979.3	1981.7	1984.1
177.5°	1983.1	1982.2	1982.2	1982.2	1982.2	1982.2	1982.2	1984.6	1987.0	1989.4	1991.8
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	527.0	526.5	524.2	525.1	522.4	523.3	524.7	525.1	527.0	525.6	525.1
5°	494.6	493.7	492.3	490.9	490.4	492.3	489.0	490.0	490.9	492.3	494.1
7.5°	468.2	467.8	466.4	464.1	463.1	462.2	462.7	465.9	465.5	465.0	468.2
10°	444.2	444.6	441.9	441.4	438.6	438.2	438.6	439.5	440.9	442.8	443.2
12.5°	419.2	425.2	420.1	418.3	414.1	416.4	417.3	413.2	415.5	416.9	423.8
15°	403.5	400.7	397.4	397.4	395.6	394.7	392.3	395.6	397.4	400.2	399.3
17.5°	381.7	377.1	375.2	373.4	373.8	375.7	370.6	378.0	378.0	379.4	377.1
20°	362.7	359.0	356.7	355.8	354.4	353.5	353.0	354.9	357.6	358.6	360.9
22.5°	342.8	342.8	339.1	337.8	336.8	335.4	337.8	336.4	338.2	340.1	343.8
25°	326.2	326.2	324.8	322.9	321.6	320.6	322.0	321.6	322.9	325.3	326.2
27.5°	312.8	311.4	310.9	310.5	310.0	310.5	310.0	311.4	312.8	313.2	312.3
30°	301.2	299.8	300.3	300.3	300.7	300.3	299.8	301.2	301.7	300.7	301.2
32.5°	290.6	290.6	291.5	291.9	291.9	292.4	292.9	291.9	292.4	291.0	291.5
35°	281.8	282.7	283.6	284.1	284.5	284.1	285.0	284.5	283.6	282.7	282.2
37.5°	273.0	273.9	275.8	276.2	277.6	278.1	277.1	277.1	276.7	274.8	273.9
40°	263.7	264.7	267.0	268.4	269.3	270.7	269.7	269.7	267.9	266.0	264.7
42.5°	254.9	256.8	259.1	260.5	262.3	262.3	262.3	261.4	259.1	257.2	255.9
45°	246.1	246.6	249.8	252.2	254.0	254.0	254.0	252.6	251.2	247.5	245.7
47.5°	236.4	237.8	241.5	243.8	245.7	246.1	246.1	244.8	242.0	238.7	236.4
50°	225.8	228.1	232.3	235.5	237.8	238.7	237.4	236.4	233.2	229.5	226.7
52.5°	215.6	218.4	223.5	226.2	229.5	229.9	229.5	228.1	224.4	219.3	217.0
55°	205.4	207.7	213.3	217.9	220.7	221.6	220.7	218.4	213.8	208.7	206.4
57.5°	194.3	197.6	203.6	208.2	211.4	211.9	211.0	208.7	205.0	198.5	195.2
60°	182.8	186.9	192.9	197.6	201.7	202.2	201.3	198.0	193.4	186.9	184.1
62.5°	171.2	174.4	181.4	186.5	189.7	192.0	190.2	186.9	182.3	175.8	171.7
65°	157.8	162.4	168.4	173.0	176.7	177.2	176.3	173.5	168.4	161.5	158.2
67.5°	144.8	148.1	154.1	160.1	161.5	162.9	161.5	158.7	154.5	148.5	143.9
70°	129.1	131.9	139.3	143.4	145.3	146.7	145.7	143.0	139.3	133.7	130.0
72.5°	113.4	115.7	122.6	125.8	129.5	129.1	128.6	126.8	121.7	118.0	115.7
75°	96.7	99.5	104.1	108.3	109.7	109.7	109.7	108.3	105.0	99.0	96.7
77.5°	81.4	82.8	86.5	88.8	90.2	90.7	90.2	87.9	86.1	81.9	80.5
80°	62.5	66.2	68.9	69.4	71.3	71.3	71.3	70.3	68.5	64.3	63.8
82.5°	47.2	48.1	50.9	52.3	53.2	52.7	52.7	50.9	50.4	48.1	47.2
85°	31.9	33.3	32.8	34.7	35.2	34.2	34.2	35.2	32.8	33.3	31.9
87.5°	17.6	17.6	18.5	18.0	19.9	19.9	19.0	19.4	18.5	18.0	17.6
90°	43.0	43.3	44.0	44.7	45.4	46.1	45.4	44.7	44.0	43.3	43.0
92.5°	72.2	72.4	72.7	73.1	73.4	73.8	73.4	73.1	72.7	72.4	72.2
95°	121.4	121.4	121.4	121.4	121.4	121.4	121.4	121.4	121.4	121.4	121.4
97.5°	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2	178.2
100°	238.2	238.2	238.2	238.2	238.2	238.2	238.2	238.2	238.2	238.2	238.2
102.5°	304.2	304.4	304.7	305.1	305.4	305.8	305.4	305.1	304.7	304.4	304.2
105°	370.3	370.8	371.8	372.9	373.9	374.9	373.9	372.9	371.8	370.8	370.3
107.5°	442.5	442.3	442.0	441.7	441.3	441.0	441.3	441.7	442.0	442.3	442.5
110°	508.6	509.1	510.1	511.2	512.2	513.2	512.2	511.2	510.1	509.1	508.6

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0	587.0
115°	665.4	665.2	664.9	664.5	664.2	663.8	664.2	664.5	664.9	665.2	665.4
117.5°	739.1	738.6	737.6	736.5	735.5	734.5	735.5	736.5	737.6	738.6	739.1
120°	814.4	814.7	815.4	816.1	816.8	817.5	816.8	816.1	815.4	814.7	814.4
122.5°	894.3	893.4	891.7	890.0	888.3	886.6	888.3	890.0	891.7	893.4	894.3
125°	971.1	970.8	970.1	969.4	968.8	968.1	968.8	969.4	970.1	970.8	971.1
127.5°	1043.4	1043.2	1042.9	1042.5	1042.2	1041.8	1042.2	1042.5	1042.9	1043.2	1043.4
130°	1120.2	1119.5	1118.1	1116.8	1115.4	1114.0	1115.4	1116.8	1118.1	1119.5	1120.2
132.5°	1192.4	1192.2	1191.9	1191.6	1191.2	1190.9	1191.2	1191.6	1191.9	1192.2	1192.4
135°	1264.6	1264.1	1263.1	1262.0	1261.0	1260.0	1261.0	1262.0	1263.1	1264.1	1264.6
137.5°	1333.8	1334.0	1334.3	1334.6	1335.0	1335.3	1335.0	1334.6	1334.3	1334.0	1333.8
140°	1404.5	1404.3	1404.0	1403.6	1403.3	1402.9	1403.3	1403.6	1404.0	1404.3	1404.5
142.5°	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5	1470.5
145°	1535.1	1534.6	1533.6	1532.5	1531.5	1530.5	1531.5	1532.5	1533.6	1534.6	1535.1
147.5°	1595.0	1594.8	1594.5	1594.2	1593.8	1593.5	1593.8	1594.2	1594.5	1594.8	1595.0
150°	1651.9	1651.7	1651.4	1651.0	1650.7	1650.3	1650.7	1651.0	1651.4	1651.7	1651.9
152.5°	1707.2	1706.7	1705.7	1704.6	1703.6	1702.6	1703.6	1704.6	1705.7	1706.7	1707.2
155°	1756.3	1755.6	1754.3	1752.9	1751.6	1750.2	1751.6	1752.9	1754.3	1755.6	1756.3
157.5°	1799.4	1798.9	1797.9	1796.8	1795.8	1794.8	1795.8	1796.8	1797.9	1798.9	1799.4
160°	1839.3	1838.4	1836.7	1835.0	1833.3	1831.6	1833.3	1835.0	1836.7	1838.4	1839.3
162.5°	1877.7	1876.9	1875.2	1873.5	1871.8	1870.1	1871.8	1873.5	1875.2	1876.9	1877.7
165°	1908.5	1907.8	1906.4	1905.1	1903.7	1902.3	1903.7	1905.1	1906.4	1907.8	1908.5
167.5°	1936.1	1935.1	1933.0	1931.0	1928.9	1926.9	1928.9	1931.0	1933.0	1935.1	1936.1
170°	1957.6	1956.4	1954.0	1951.7	1949.3	1946.9	1949.3	1951.7	1954.0	1956.4	1957.6
172.5°	1974.5	1973.3	1970.9	1968.6	1966.2	1963.8	1966.2	1968.6	1970.9	1973.3	1974.5
175°	1985.3	1984.1	1981.7	1979.3	1976.9	1974.5	1976.9	1979.3	1981.7	1984.1	1985.3
177.5°	1993.0	1991.6	1988.9	1986.2	1983.4	1980.7	1983.4	1986.2	1988.9	1991.6	1993.0
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4	558.4
2.5°	525.1	527.9	525.1	527.0	527.9	530.2	531.2	535.3	536.7	539.9	539.9
5°	493.7	495.1	495.5	497.4	499.2	503.9	507.1	513.1	520.0	521.0	525.1
7.5°	468.2	470.5	474.2	472.9	476.1	483.0	487.2	494.6	501.5	505.2	510.3
10°	445.6	448.3	449.7	451.1	457.1	463.1	469.6	474.7	484.0	489.5	493.7
12.5°	427.0	424.7	427.5	432.6	439.5	443.2	452.0	459.9	466.8	472.9	476.6
15°	403.0	404.8	407.6	416.4	418.3	427.5	430.8	439.5	452.5	458.0	462.7
17.5°	379.9	385.9	391.4	394.7	400.2	407.6	416.9	426.6	434.9	441.4	446.9
20°	361.3	367.4	370.6	372.9	378.5	388.6	397.4	409.5	420.1	425.2	432.6
22.5°	346.5	346.5	351.2	358.1	361.3	371.1	378.5	391.4	403.0	409.5	416.4
25°	328.0	330.8	334.5	340.5	345.2	353.0	363.7	374.8	387.3	392.8	401.6
27.5°	312.8	316.0	321.1	322.5	327.1	334.1	345.2	357.2	370.1	376.2	383.6
30°	301.2	303.1	304.9	307.7	311.8	317.9	327.1	337.8	353.5	358.1	367.4
32.5°	291.0	291.9	292.9	295.2	297.5	303.5	310.9	322.5	335.4	342.4	350.7
35°	281.8	280.8	281.3	282.7	285.0	287.3	295.2	304.9	316.9	325.3	331.7
37.5°	273.0	271.1	270.7	270.7	271.6	274.4	280.4	288.7	301.7	308.6	315.1
40°	263.3	261.4	260.5	260.0	259.6	261.4	266.0	274.4	284.5	291.0	298.4
42.5°	254.0	252.2	249.8	249.4	248.5	249.4	252.6	260.5	269.3	275.8	281.8
45°	244.8	241.5	238.7	236.9	237.4	236.0	238.3	244.3	254.5	258.6	264.7
47.5°	234.6	230.9	227.2	225.3	223.5	224.4	225.3	230.4	239.2	243.4	249.4
50°	224.9	219.8	215.6	213.3	211.9	211.0	211.9	217.0	223.5	227.2	232.3
52.5°	213.8	208.7	204.5	200.8	199.0	197.6	198.0	202.7	208.7	212.4	217.5
55°	203.6	197.1	191.5	186.9	185.5	185.1	184.6	187.8	192.9	196.6	200.8
57.5°	192.0	185.5	179.5	174.0	171.2	170.7	170.7	171.7	178.1	180.9	183.2
60°	180.4	173.5	167.0	161.9	157.8	156.4	155.9	157.8	161.0	163.8	167.0
62.5°	167.5	160.5	152.7	148.1	143.9	140.2	141.6	142.0	146.7	148.1	150.8
65°	155.0	147.1	140.7	133.3	128.6	126.3	125.4	126.3	130.0	130.5	132.3
67.5°	140.7	133.3	125.4	120.3	116.1	112.0	111.0	111.0	112.9	114.3	116.6
70°	126.8	119.4	110.6	105.0	100.9	97.2	95.8	95.3	96.7	97.6	99.9
72.5°	110.6	103.2	96.7	90.7	85.6	82.8	81.4	80.5	81.9	82.8	83.3
75°	93.5	87.4	81.0	75.0	71.7	68.9	67.1	65.7	66.6	66.6	66.6
77.5°	77.3	71.3	66.2	62.0	57.8	54.6	53.2	51.8	52.3	52.3	53.2
80°	60.1	56.0	51.8	48.1	44.4	41.6	40.7	39.3	38.4	37.9	37.9
82.5°	44.4	41.2	37.5	34.2	32.4	29.6	28.7	26.8	26.8	26.4	26.4
85°	29.6	27.8	24.1	21.7	20.4	19.0	18.0	17.1	15.7	15.7	15.3
87.5°	15.7	14.8	13.9	11.1	11.1	9.7	9.3	8.8	7.4	7.9	7.9
90°	42.0	39.9	37.9	35.8	33.8	31.1	28.3	25.6	22.9	21.5	19.6
92.5°	71.7	70.7	69.6	68.6	67.6	65.9	64.2	62.5	60.8	59.9	57.7
95°	120.9	119.9	118.8	117.8	116.8	114.4	112.0	109.6	107.2	106.0	104.5
97.5°	177.5	176.2	174.8	173.5	172.1	169.4	166.6	163.9	161.2	159.8	158.4
100°	237.9	237.2	236.5	235.8	235.1	232.0	229.0	225.9	222.8	221.3	220.6
102.5°	303.7	302.7	301.6	300.6	299.6	296.9	294.1	291.4	288.7	287.3	287.1
105°	369.8	368.8	367.7	366.7	365.7	364.3	363.0	361.6	360.3	359.6	359.4
107.5°	441.8	440.5	439.1	437.8	436.4	436.1	435.7	435.4	435.1	434.9	434.7
110°	508.9	509.6	510.3	511.0	511.7	512.0	512.4	512.7	513.0	513.2	512.9

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	587.0	587.0	587.0	587.0	587.0	587.7	588.4	589.1	589.8	590.1	590.1
115°	665.6	665.9	666.2	666.6	666.9	667.6	668.3	669.0	669.7	670.0	670.0
117.5°	739.6	740.6	741.7	742.7	743.7	744.1	744.4	744.8	745.1	745.3	745.3
120°	815.3	817.0	818.7	820.4	822.1	823.1	824.1	825.2	826.2	826.7	826.0
122.5°	894.8	895.8	896.9	897.9	898.9	899.3	899.6	900.0	900.3	900.5	900.3
125°	971.4	972.1	972.8	973.5	974.2	974.5	974.9	975.2	975.5	975.7	975.7
127.5°	1043.7	1044.4	1045.1	1045.7	1046.4	1047.1	1047.8	1048.5	1049.2	1049.5	1049.0
130°	1120.5	1121.2	1121.9	1122.6	1123.3	1123.3	1123.3	1123.3	1123.3	1123.3	1122.8
132.5°	1192.7	1193.4	1194.1	1194.8	1195.5	1195.8	1196.2	1196.5	1196.8	1197.0	1196.7
135°	1264.9	1265.6	1266.3	1267.0	1267.7	1267.7	1267.7	1267.7	1267.7	1267.7	1266.7
137.5°	1334.3	1335.3	1336.4	1337.4	1338.4	1337.7	1337.0	1336.3	1335.6	1335.3	1334.8
140°	1404.7	1405.0	1405.3	1405.7	1406.0	1406.0	1406.0	1406.0	1406.0	1406.0	1405.7
142.5°	1470.5	1470.5	1470.5	1470.5	1470.5	1470.9	1471.2	1471.6	1471.9	1472.1	1471.8
145°	1535.3	1535.6	1535.9	1536.3	1536.6	1536.3	1535.9	1535.6	1535.3	1535.1	1534.4
147.5°	1595.2	1595.5	1595.8	1596.2	1596.5	1596.9	1597.2	1597.6	1597.9	1598.1	1597.2
150°	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.9	1651.2
152.5°	1706.7	1705.7	1704.6	1703.6	1702.6	1702.2	1701.9	1701.5	1701.2	1701.0	1700.7
155°	1755.6	1754.3	1752.9	1751.6	1750.2	1750.5	1750.9	1751.2	1751.5	1751.7	1751.7
157.5°	1798.9	1797.9	1796.8	1795.8	1794.8	1794.8	1794.8	1794.8	1794.8	1794.8	1795.1
160°	1838.8	1837.8	1836.7	1835.7	1834.7	1835.1	1835.4	1835.8	1836.1	1836.3	1836.5
162.5°	1876.7	1874.6	1872.6	1870.5	1868.5	1868.9	1869.2	1869.6	1869.9	1870.1	1870.6
165°	1907.5	1905.4	1903.4	1901.3	1899.3	1900.0	1900.6	1901.3	1902.0	1902.3	1902.8
167.5°	1935.1	1933.0	1931.0	1928.9	1926.9	1926.9	1926.9	1926.9	1926.9	1926.9	1927.6
170°	1956.6	1954.5	1952.5	1950.4	1948.4	1948.1	1947.7	1947.4	1947.1	1946.9	1947.8
172.5°	1973.3	1970.9	1968.6	1966.2	1963.8	1963.8	1963.8	1963.8	1963.8	1963.8	1964.5
175°	1984.1	1981.7	1979.3	1976.9	1974.5	1974.9	1975.2	1975.6	1975.9	1976.1	1977.0
177.5°	1991.8	1989.4	1987.0	1984.6	1982.2	1982.2	1982.2	1982.2	1982.2	1982.2	1983.1
180°	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8	1986.8

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	558.4	558.4	558.4	558.4
2.5°	543.2	547.8	552.0	558.4
5°	531.2	537.6	546.4	556.1
7.5°	517.3	527.4	539.0	552.4
10°	504.3	515.9	530.7	546.9
12.5°	490.9	504.8	521.0	538.6
15°	475.6	489.5	507.6	531.2
17.5°	461.7	478.4	497.8	522.8
20°	445.6	461.3	482.6	511.3
22.5°	431.2	449.3	472.9	497.8
25°	415.5	431.2	454.8	484.9
27.5°	399.8	419.2	441.9	471.0
30°	384.5	400.7	425.2	455.7
32.5°	367.8	387.3	409.9	438.6
35°	349.8	368.3	389.6	420.6
37.5°	333.6	351.6	373.4	400.7
40°	315.5	334.5	354.4	381.7
42.5°	298.0	315.1	335.0	360.0
45°	280.8	295.6	313.7	335.4
47.5°	263.3	275.8	292.4	311.8
50°	244.3	257.7	270.2	286.4
52.5°	226.7	238.3	248.5	261.9
55°	209.6	217.5	225.8	236.0
57.5°	191.5	197.6	203.6	214.2
60°	173.5	179.1	182.3	189.2
62.5°	155.9	158.2	162.4	166.6
65°	136.5	139.7	142.0	147.1
67.5°	118.9	120.3	122.6	125.8
70°	100.4	103.6	104.6	106.9
72.5°	84.7	86.1	87.0	87.4
75°	67.1	68.5	69.4	72.2
77.5°	52.7	52.3	54.1	54.6
80°	38.9	37.5	37.9	39.8
82.5°	25.4	25.9	25.4	25.4
85°	15.7	15.3	14.3	14.8
87.5°	6.9	6.9	6.5	6.5
90°	15.9	12.1	8.4	4.6
92.5°	53.3	48.8	44.4	40.0
95°	101.4	98.3	95.3	92.2
97.5°	155.7	153.0	150.2	147.5
100°	219.2	217.9	216.5	215.1
102.5°	286.8	286.5	286.1	285.8
105°	359.1	358.7	358.4	358.0
107.5°	434.4	434.0	433.7	433.3
110°	512.2	511.5	510.9	510.2

TEST NUMBER: P1033456

CATALOG NUMBER: S124DIW-B350D1560UB35-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	590.1	590.1	590.1	590.1
115°	670.0	670.0	670.0	670.0
117.5°	745.3	745.3	745.3	745.3
120°	824.7	823.3	822.0	820.6
122.5°	900.0	899.6	899.3	898.9
125°	975.7	975.7	975.7	975.7
127.5°	1048.0	1046.9	1045.9	1044.9
130°	1121.8	1120.7	1119.7	1118.7
132.5°	1196.0	1195.3	1194.6	1193.9
135°	1264.6	1262.6	1260.5	1258.5
137.5°	1333.8	1332.7	1331.7	1330.7
140°	1405.0	1404.3	1403.6	1402.9
142.5°	1471.1	1470.4	1469.7	1469.0
145°	1533.0	1531.7	1530.3	1528.9
147.5°	1595.5	1593.8	1592.1	1590.4
150°	1649.8	1648.5	1647.1	1645.7
152.5°	1700.0	1699.3	1698.7	1698.0
155°	1751.7	1751.7	1751.7	1751.7
157.5°	1795.8	1796.5	1797.1	1797.8
160°	1836.8	1837.1	1837.5	1837.8
162.5°	1871.6	1872.7	1873.7	1874.7
165°	1903.8	1904.9	1905.9	1906.9
167.5°	1929.0	1930.3	1931.7	1933.1
170°	1949.5	1951.2	1952.9	1954.6
172.5°	1965.8	1967.2	1968.5	1969.9
175°	1978.7	1980.4	1982.1	1983.8
177.5°	1984.8	1986.5	1988.2	1989.9
180°	1986.8	1986.8	1986.8	1986.8

(END OF REPORT)