

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033505

Luminaire Tested: S124DIW-B350D770UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033505
REPORT IS A COMBINATION OF REPORTS P997550 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D770UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4150.0 lumens
Efficiency: N/A
Efficacy: 114.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033505

CATALOG NUMBER: S124DIW-B350D770UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033505

CATALOG NUMBER: S124DIW-B350D770UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	94	90	86	83	85	82	78	76	66	64	62	51	50	48	38	37	36
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	32	30
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26
4	72	61	53	48	65	56	49	44	45	40	36	35	32	29	26	24	22
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	24	21	19
6	60	49	41	35	54	44	37	32	36	31	27	29	25	22	21	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4648	4648	4648
5°	4652	4514	4520
10°	4612	4389	4359
15°	4546	4240	4176
20°	4461	4079	3988
25°	4367	3909	3784
30°	4252	3724	3561
35°	4134	3536	3346
40°	4010	3333	3116
45°	3879	3129	2902
50°	3736	2932	2665
55°	3580	2702	2429
60°	3420	2450	2184
65°	3238	2189	1907
70°	3025	1876	1611
75°	2712	1511	1289
80°	2311	1093	907
85°	1797	607	488

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3879 cd/sqm

TEST NUMBER: P1033505

CATALOG NUMBER: S124DIW-B350D770UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.7	1.3
10°-20°	151.4	3.6
20°-30°	222.8	5.4
30°-40°	258.9	6.2
40°-50°	258.9	6.2
50°-60°	226.5	5.5
60°-70°	168.1	4.1
70°-80°	95.4	2.3
80°-90°	29.4	0.7
90°-100°	63.1	1.5
100°-110°	188.9	4.6
110°-120°	321.0	7.7
120°-130°	423.3	10.2
130°-140°	475.4	11.5
140°-150°	467.3	11.3
150°-160°	393.0	9.5
160°-170°	261.5	6.3
170°-180°	91.6	2.2
0°-30°	427.8	10.3
0°-40°	686.8	16.5
0°-60°	1172.2	28.2
0°-90°	1465.1	35.3
90°-120°	572.9	13.8
90°-150°	1938.9	46.7
90°-180°	2685.0	64.7
0°-180°	4150.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	570	570	570	570	570	
5°	570	568	563	568	567	54
15°	542	540	534	536	535	153
25°	491	488	481	482	480	226
35°	422	419	413	410	407	264
45°	345	342	334	329	328	266
55°	261	259	253	248	245	234
65°	177	174	170	165	163	175
75°	94	92	90	88	87	100
85°	25	25	24	24	23	27
90°	2	10	16	21	22	5
95°	45	52	57	59	59	49
105°	174	175	178	180	183	185
115°	326	326	325	324	323	322
125°	475	475	474	473	472	424
135°	613	617	617	616	614	474
145°	745	748	748	748	745	466
155°	853	853	852	855	852	393
165°	929	926	925	930	926	262
175°	966	962	962	967	962	92
180°	968	968	968	968	968	

TEST NUMBER: P1033505

CATALOG NUMBER: S124DIW-B350D770UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	570.0	570.0	570.0	570.0	570.0
2.5°	571.8	570.5	565.4	570.0	569.5
5°	569.5	567.7	562.7	567.7	566.8
7.5°	565.4	563.6	558.1	562.2	561.8
10°	559.5	557.7	551.7	555.4	554.5
12.5°	551.7	549.9	543.5	547.6	546.2
15°	542.1	540.3	533.5	536.2	534.8
17.5°	531.2	528.9	522.5	524.3	523.4
20°	518.8	516.6	509.7	511.1	510.2
22.5°	505.6	502.4	495.5	498.3	496.5
25°	491.0	487.8	481.4	481.8	480.0
27.5°	474.5	471.3	465.4	464.5	462.2
30°	458.1	454.4	448.5	446.7	444.4
32.5°	440.7	437.5	431.1	428.9	426.6
35°	422.5	419.3	412.9	409.7	407.4
37.5°	403.3	400.5	393.7	390.5	387.3
40°	384.6	380.9	374.1	369.5	367.2
42.5°	364.5	362.6	354.9	349.4	348.0
45°	344.8	341.6	334.3	329.3	327.9
47.5°	324.3	322.0	315.1	309.7	306.0
50°	303.3	301.4	295.0	288.7	285.9
52.5°	282.7	280.4	273.6	268.1	264.4
55°	260.8	259.4	253.0	247.5	244.8
57.5°	240.2	238.9	232.5	227.0	224.3
60°	218.8	216.5	210.6	206.4	204.2
62.5°	197.8	195.9	189.5	185.9	183.6
65°	176.8	174.5	169.9	165.3	163.1
67.5°	155.3	153.5	148.9	144.3	143.9
70°	135.6	132.5	128.8	125.1	123.8
72.5°	114.6	111.4	108.7	106.0	104.6
75°	94.1	91.8	89.5	87.7	87.2
77.5°	74.0	73.1	70.8	70.3	69.0
80°	56.2	54.8	53.9	53.0	52.5
82.5°	38.8	38.4	38.4	37.9	37.5
85°	24.7	24.7	23.7	23.7	23.3
87.5°	11.9	11.4	11.0	11.0	11.0
90°	2.2	10.5	16.5	21.0	22.5
92.5°	19.5	29.2	32.9	35.2	35.9
95°	44.9	51.6	56.9	59.1	59.1
97.5°	71.8	77.8	83.8	86.8	86.8
100°	104.8	107.8	114.5	116.0	116.0
102.5°	139.2	139.9	145.9	148.2	148.9
105°	174.4	175.1	178.1	180.4	182.6
107.5°	211.0	211.8	212.5	215.5	214.8
110°	248.5	250.0	249.2	247.7	250.0

TEST NUMBER: P1033505

CATALOG NUMBER: S124DIW-B350D770UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	287.4	287.4	285.9	285.9	285.9
115°	326.3	326.3	324.8	324.1	323.3
117.5°	363.0	363.0	362.2	360.0	357.7
120°	399.6	402.6	400.4	396.6	398.1
122.5°	437.8	438.6	437.8	435.6	431.8
125°	475.2	475.2	474.5	473.0	471.5
127.5°	508.9	511.2	509.7	508.2	507.4
130°	544.8	547.1	547.1	545.6	542.6
132.5°	581.5	583.0	582.2	580.8	580.0
135°	612.9	617.4	617.4	615.9	613.7
137.5°	648.1	650.4	651.8	649.6	650.4
140°	683.3	684.8	684.8	684.0	683.3
142.5°	715.5	717.0	716.2	716.2	716.2
145°	744.7	747.6	748.4	747.6	745.4
147.5°	774.6	778.3	777.6	776.8	776.1
150°	801.5	804.5	804.5	804.5	803.8
152.5°	827.0	828.5	829.2	831.5	829.2
155°	853.2	853.2	852.4	855.4	852.4
157.5°	875.6	874.1	874.1	876.4	874.1
160°	895.1	894.3	893.6	895.8	892.1
162.5°	913.0	910.8	910.0	914.5	910.8
165°	928.8	926.5	925.0	929.5	926.5
167.5°	941.5	938.5	938.5	943.0	938.5
170°	952.0	948.2	949.0	953.5	948.2
172.5°	959.4	956.4	956.4	961.7	956.4
175°	966.2	962.4	961.7	966.9	961.7
177.5°	969.2	965.4	965.4	970.7	964.7
180°	967.7	967.7	967.7	967.7	967.7

(END OF REPORT)