

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033007

Luminaire Tested: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033007
REPORT IS A COMBINATION OF REPORTS P1000540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7744.1 lumens
Efficiency: N/A
Efficacy: 117.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 66.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033007

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1033007

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	55	55	55	38	38	38
1	94	89	86	82	84	80	77	75	64	62	60	48	47	46	34	33	32
2	85	78	72	67	76	70	66	61	56	52	50	42	40	38	30	29	28
3	78	69	62	56	70	62	56	51	49	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	30	28	24	22	20
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	17	16
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14
8	51	40	32	27	46	36	29	25	29	24	21	23	19	17	16	14	13
9	48	36	29	24	43	33	26	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8290	8290	8290
5°	8291	8044	8044
10°	8221	7790	7698
15°	8108	7474	7287
20°	7959	7114	6820
25°	7775	6724	6364
30°	7594	6328	5852
35°	7394	5926	5350
40°	7159	5493	4836
45°	6936	5064	4326
50°	6684	4596	3809
55°	6412	4115	3275
60°	6109	3604	2748
65°	5816	3019	2240
70°	5401	2403	1712
75°	4867	1748	1198
80°	4068	1073	860
85°	3056	618	474

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6936 cd/sqm

TEST NUMBER: P1033007

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.6	1.2
10°-20°	266.5	3.4
20°-30°	384.8	5.0
30°-40°	436.1	5.6
40°-50°	421.1	5.4
50°-60°	350.1	4.5
60°-70°	241.6	3.1
70°-80°	122.1	1.6
80°-90°	34.6	0.4
90°-100°	57.8	0.7
100°-110°	380.9	4.9
110°-120°	727.3	9.4
120°-130°	923.3	11.9
130°-140°	987.7	12.8
140°-150°	923.6	11.9
150°-160°	744.8	9.6
160°-170°	480.4	6.2
170°-180°	165.5	2.1
0°-30°	747.0	9.6
0°-40°	1183.1	15.3
0°-60°	1954.3	25.2
0°-90°	2352.6	30.4
90°-120°	1166.1	15.1
90°-150°	4000.7	51.7
90°-180°	5391.0	69.6
0°-180°	7744.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1017	1017	1017	1017	1017	
5°	1015	1012	1003	1010	1009	96
15°	967	960	940	939	933	272
25°	874	860	828	815	807	403
35°	756	731	692	666	652	472
45°	616	588	541	503	489	475
55°	467	436	385	345	330	418
65°	318	284	234	201	192	314
75°	169	140	104	86	81	178
85°	42	26	24	23	23	46
90°	4	18	29	36	39	6
95°	72	27	29	36	38	88
105°	392	400	407	418	371	411
115°	732	736	735	738	738	721
125°	1030	1035	1032	1036	1037	919
135°	1277	1276	1281	1284	1286	984
145°	1473	1476	1476	1478	1480	920
155°	1615	1616	1612	1617	1613	744
165°	1703	1697	1697	1707	1695	481
175°	1742	1734	1736	1748	1732	166
180°	1742	1742	1742	1742	1742	

TEST NUMBER: P1033007

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1019.7	1016.6	1008.1	1016.6	1015.8
5°	1015.1	1011.9	1002.6	1010.4	1008.8
7.5°	1008.1	1004.9	993.3	998.7	996.4
10°	997.2	993.3	979.3	982.4	979.3
12.5°	983.1	978.5	961.3	962.9	958.2
15°	966.8	959.8	940.3	938.8	933.3
17.5°	948.1	938.0	915.4	911.5	903.7
20°	925.5	915.4	889.0	882.7	872.6
22.5°	900.6	889.0	860.2	850.0	842.3
25°	874.2	860.2	828.2	815.0	807.2
27.5°	846.9	829.8	796.3	780.8	769.9
30°	818.1	798.7	762.1	742.6	730.2
32.5°	787.8	765.2	727.0	703.7	692.0
35°	755.8	730.9	692.0	665.5	651.5
37.5°	722.4	696.7	653.9	625.1	611.1
40°	686.6	660.9	616.5	583.8	569.8
42.5°	652.3	625.1	578.4	544.9	530.1
45°	616.5	587.7	541.0	502.9	488.8
47.5°	579.9	550.3	502.1	462.4	446.8
50°	542.6	512.2	462.4	423.5	408.7
52.5°	504.4	474.8	423.5	383.8	368.2
55°	467.1	435.9	385.3	344.8	330.1
57.5°	430.5	397.8	348.0	306.7	295.8
60°	390.8	359.6	309.8	269.3	256.9
62.5°	355.0	322.3	270.9	234.3	225.0
65°	317.6	284.1	234.3	200.8	191.5
67.5°	278.7	246.8	200.1	170.5	159.6
70°	242.1	209.4	165.0	139.3	131.6
72.5°	203.2	174.4	133.1	112.1	105.1
75°	168.9	140.1	103.5	85.6	81.0
77.5°	133.1	108.2	77.1	64.6	63.1
80°	98.9	76.3	52.9	50.6	49.8
82.5°	69.3	49.0	38.1	36.6	35.8
85°	42.0	26.5	24.1	22.6	22.6
87.5°	17.9	11.7	10.9	10.1	10.9
90°	3.9	18.2	28.7	36.5	39.1
92.5°	19.5	16.9	27.4	35.2	35.2
95°	71.7	27.4	28.7	36.5	37.8
97.5°	136.8	165.5	28.7	35.2	36.5
100°	213.7	237.2	57.3	35.2	36.5
102.5°	299.7	315.4	331.0	37.8	37.8
105°	392.3	400.1	406.6	418.3	371.4
107.5°	477.0	480.9	490.0	496.5	501.7
110°	563.0	566.9	574.7	577.3	581.2

TEST NUMBER: P1033007

CATALOG NUMBER: S124RDIW-B575D1340UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	646.4	654.2	656.8	655.5	660.7
115°	732.4	736.3	735.0	737.6	737.6
117.5°	809.3	814.5	818.4	817.1	817.1
120°	887.5	892.7	891.4	894.0	891.4
122.5°	960.4	963.0	965.6	967.0	964.3
125°	1029.5	1034.7	1032.1	1036.0	1037.3
127.5°	1096.0	1097.3	1103.8	1102.5	1101.2
130°	1159.8	1161.1	1165.0	1166.3	1166.3
132.5°	1218.5	1221.1	1226.3	1227.6	1226.3
135°	1277.1	1275.8	1281.0	1283.6	1286.2
137.5°	1329.2	1329.2	1335.7	1338.4	1337.1
140°	1380.1	1382.7	1385.3	1389.2	1390.5
142.5°	1425.7	1430.9	1432.2	1434.8	1434.8
145°	1472.6	1476.5	1476.5	1477.8	1480.4
147.5°	1509.1	1516.9	1515.6	1516.9	1518.2
150°	1549.5	1554.7	1553.4	1553.4	1554.7
152.5°	1583.3	1587.3	1584.7	1587.3	1586.0
155°	1614.6	1615.9	1612.0	1617.2	1613.3
157.5°	1642.0	1642.0	1636.8	1643.3	1636.8
160°	1665.4	1661.5	1660.2	1668.1	1660.2
162.5°	1686.3	1681.1	1679.8	1687.6	1678.5
165°	1703.2	1696.7	1696.7	1707.2	1695.4
167.5°	1717.6	1711.1	1709.8	1721.5	1708.5
170°	1729.3	1721.5	1722.8	1733.2	1720.2
172.5°	1737.1	1729.3	1730.6	1741.0	1726.7
175°	1742.3	1734.5	1735.8	1747.5	1731.9
177.5°	1746.2	1737.1	1739.7	1750.2	1734.5
180°	1742.3	1742.3	1742.3	1742.3	1742.3

(END OF REPORT)