

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033026

Luminaire Tested: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033026
REPORT IS A COMBINATION OF REPORTS P1000627 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4236.0 lumens
Efficiency: N/A
Efficacy: 113.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033026

CATALOG NUMBER: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033026

CATALOG NUMBER: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55		
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	54	53	52	47		
2	91	83	77	72	84	78	72	68	67	63	60	57	54	52	48	46	44	40		
3	83	73	66	60	77	69	62	57	59	55	51	51	47	44	43	40	38	34		
4	76	65	57	51	70	61	54	49	53	48	43	45	41	38	39	36	33	30		
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26		
6	64	52	44	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23		
7	60	47	39	34	55	45	37	32	39	33	29	34	29	26	29	26	23	20		
8	55	43	35	30	51	41	34	29	36	30	26	31	27	23	27	23	21	18		
9	52	39	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17		
10	48	36	29	24	45	34	28	23	30	25	21	26	22	19	23	19	17	15		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6907 cd/sqm

TEST NUMBER: P1033026

CATALOG NUMBER: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	2.2
10°-20°	265.4	6.3
20°-30°	383.2	9.0
30°-40°	434.3	10.3
40°-50°	419.3	9.9
50°-60°	348.6	8.2
60°-70°	240.6	5.7
70°-80°	121.6	2.9
80°-90°	32.1	0.8
90°-100°	20.3	0.5
100°-110°	133.9	3.2
110°-120°	255.7	6.0
120°-130°	324.6	7.7
130°-140°	347.3	8.2
140°-150°	324.8	7.7
150°-160°	261.9	6.2
160°-170°	168.9	4.0
170°-180°	58.2	1.4
0°-30°	743.8	17.6
0°-40°	1178.0	27.8
0°-60°	1945.9	45.9
0°-90°	2340.2	55.2
90°-120°	410.0	9.7
90°-150°	1406.7	33.2
90°-180°	1896.0	44.8
0°-180°	4236.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	1	6	10	13	14	4
95°	25	10	10	13	13	31
105°	138	141	143	147	131	144
115°	258	259	258	259	259	253
125°	362	364	363	364	365	323
135°	449	449	450	451	452	346
145°	518	519	519	520	520	324
155°	568	568	567	569	567	262
165°	599	597	597	600	596	169
175°	613	610	610	614	609	58
180°	613	613	613	613	613	

TEST NUMBER: P1033026

CATALOG NUMBER: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	1.4	6.4	10.1	12.8	13.7
92.5°	6.9	6.0	9.6	12.4	12.4
95°	25.2	9.6	10.1	12.8	13.3
97.5°	48.1	58.2	10.1	12.4	12.8
100°	75.1	83.4	20.2	12.4	12.8
102.5°	105.4	110.9	116.4	13.3	13.3
105°	137.9	140.7	143.0	147.1	130.6
107.5°	167.7	169.1	172.3	174.6	176.4
110°	198.0	199.3	202.1	203.0	204.4



TEST NUMBER: P1033026

CATALOG NUMBER: S124RDIW-B575D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	227.3	230.0	230.9	230.5	232.3
115°	257.5	258.9	258.4	259.4	259.4
117.5°	284.6	286.4	287.8	287.3	287.3
120°	312.0	313.9	313.4	314.3	313.4
122.5°	337.7	338.6	339.5	340.0	339.1
125°	362.0	363.8	362.9	364.3	364.7
127.5°	385.4	385.8	388.1	387.7	387.2
130°	407.8	408.3	409.7	410.1	410.1
132.5°	428.4	429.4	431.2	431.6	431.2
135°	449.1	448.6	450.4	451.3	452.3
137.5°	467.4	467.4	469.7	470.6	470.1
140°	485.3	486.2	487.1	488.5	488.9
142.5°	501.3	503.1	503.6	504.5	504.5
145°	517.8	519.2	519.2	519.6	520.5
147.5°	530.6	533.4	532.9	533.4	533.8
150°	544.8	546.7	546.2	546.2	546.7
152.5°	556.7	558.1	557.2	558.1	557.7
155°	567.7	568.2	566.8	568.7	567.3
157.5°	577.4	577.4	575.5	577.8	575.5
160°	585.6	584.2	583.8	586.5	583.8
162.5°	592.9	591.1	590.6	593.4	590.2
165°	598.9	596.6	596.6	600.3	596.1
167.5°	603.9	601.6	601.2	605.3	600.7
170°	608.1	605.3	605.8	609.4	604.9
172.5°	610.8	608.1	608.5	612.2	607.1
175°	612.6	609.9	610.4	614.5	609.0
177.5°	614.0	610.8	611.7	615.4	609.9
180°	612.6	612.6	612.6	612.6	612.6

(END OF REPORT)