

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033031

Luminaire Tested: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033031
REPORT IS A COMBINATION OF REPORTS P1000664 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5557.0 lumens
Efficiency: N/A
Efficacy: 117.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	50	50	50			44
1	97	93	89	86	88	85	82	79	71	68	66	57	56	55	45	44	43			38
2	88	81	76	71	81	75	70	65	62	59	56	51	48	46	40	39	37			32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32			28
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28			24
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	24			21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22			19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	22	19			17
8	54	42	34	29	49	39	32	28	33	28	24	28	24	21	22	20	17			15
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	21	18	16			14
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7842	7842	7842	7842
5°	7842	8861	7855	6773
10°	7800	10214	7794	5890
15°	7708	11496	7708	4932
20°	7611	12465	7570	4342
25°	7491	12517	7457	3922
30°	7365	10644	7308	3633
35°	7187	8031	7096	3417
40°	6989	5820	6851	3249
45°	6661	4423	6495	3100
50°	6272	3575	6100	2882
55°	5850	2960	5660	2591
60°	5427	2503	5185	2155
65°	4895	2040	4739	1713
70°	4408	1654	4201	1391
75°	3864	1192	3596	1020
80°	3187	789	2900	750
85°	2314	407	1914	407

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 9817 cd/sqm

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.1	1.7
10°-20°	281.2	5.1
20°-30°	440.5	7.9
30°-40°	489.1	8.8
40°-50°	433.5	7.8
50°-60°	337.8	6.1
60°-70°	221.0	4.0
70°-80°	108.4	2.0
80°-90°	28.5	0.5
90°-100°	33.5	0.6
100°-110°	220.7	4.0
110°-120°	421.4	7.6
120°-130°	535.0	9.6
130°-140°	572.3	10.3
140°-150°	535.2	9.6
150°-160°	431.6	7.8
160°-170°	278.3	5.0
170°-180°	95.9	1.7
0°-30°	814.8	14.7
0°-40°	1304.0	23.5
0°-60°	2075.2	37.3
0°-90°	2433.1	43.8
90°-120°	675.6	12.2
90°-150°	2318.1	41.7
90°-180°	3124.0	56.2
0°-180°	5557.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	962	962	962	962	962	
5°	960	1111	962	849	960	91
15°	919	1472	919	632	919	259
25°	842	1588	838	498	842	388
35°	735	978	725	416	735	459
45°	592	500	577	350	592	457
55°	426	298	412	261	426	381
65°	267	174	259	146	267	267
75°	134	81	125	69	134	142
85°	32	19	26	19	32	36
90°	2	23	2	23	2	4
95°	42	22	42	22	42	51
105°	227	215	227	215	227	238
115°	424	427	424	427	424	418
125°	596	601	596	601	596	533
135°	740	745	740	745	740	570
145°	853	858	853	858	853	533
155°	936	935	936	935	936	431
165°	987	982	987	982	987	279
175°	1010	1004	1010	1004	1010	96
180°	1010	1010	1010	1010	1010	

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	963.2	971.7	976.4	980.3	988.0	991.1	997.3	998.9	1005.1	1004.3	1002.0
5°	960.1	974.8	985.7	997.3	1011.3	1019.0	1027.5	1039.9	1046.1	1054.7	1060.1
7.5°	954.7	974.8	992.7	1010.5	1033.0	1045.4	1056.2	1075.6	1091.9	1105.8	1121.3
10°	946.2	971.7	998.1	1022.1	1053.1	1067.8	1084.1	1112.8	1135.3	1154.6	1179.4
12.5°	933.0	968.6	998.1	1030.6	1070.2	1090.3	1112.0	1146.1	1172.5	1204.2	1235.2
15°	919.1	958.6	997.3	1039.9	1084.9	1108.1	1129.8	1175.6	1215.8	1252.3	1286.4
17.5°	903.6	947.0	989.6	1036.8	1091.1	1119.8	1145.3	1200.3	1244.5	1291.8	1325.9
20°	885.0	932.2	981.0	1033.7	1095.0	1126.7	1155.4	1218.2	1267.0	1318.1	1360.8
22.5°	864.8	916.0	969.4	1026.8	1090.3	1125.2	1158.5	1225.9	1282.5	1329.8	1387.1
25°	842.3	896.6	951.6	1012.0	1083.3	1121.3	1155.4	1222.0	1282.5	1344.5	1400.3
27.5°	819.1	874.9	932.2	995.8	1068.6	1105.8	1144.6	1208.9	1279.4	1346.8	1403.4
30°	793.5	847.8	908.2	968.6	1046.1	1083.3	1122.9	1192.6	1269.3	1336.7	1398.0
32.5°	765.6	821.4	878.8	941.5	1017.5	1057.8	1094.2	1173.2	1251.5	1318.1	1375.5
35°	734.6	787.3	841.6	905.9	981.0	1017.5	1060.9	1143.0	1222.0	1292.6	1329.8
37.5°	701.3	751.7	802.0	865.6	937.7	981.8	1024.4	1107.4	1191.1	1238.3	1257.7
40°	670.3	714.5	758.6	819.9	892.7	938.4	981.8	1067.8	1141.5	1177.9	1163.2
42.5°	630.8	676.5	716.0	772.6	846.2	888.8	933.0	1022.1	1081.8	1096.5	1060.1
45°	592.0	630.0	668.0	723.0	800.5	836.9	884.2	967.1	1016.7	1003.5	950.1
47.5°	554.1	585.1	620.7	674.2	743.9	787.3	831.5	903.6	938.4	919.8	845.4
50°	509.1	540.1	577.3	623.8	691.2	733.1	767.9	834.6	860.9	815.2	725.3
52.5°	466.5	493.6	525.4	568.8	633.1	671.1	709.1	766.4	774.9	722.2	627.7
55°	426.2	447.9	481.2	516.1	575.0	615.3	641.6	690.5	688.1	622.3	540.9
57.5°	384.4	404.5	427.0	463.4	519.2	549.4	578.1	620.7	598.2	542.4	461.9
60°	347.2	358.8	381.3	416.1	463.4	489.7	512.2	535.5	516.1	455.7	393.7
62.5°	306.1	319.3	335.5	363.4	405.3	430.1	446.4	456.4	436.3	389.8	333.2
65°	267.3	279.0	296.0	320.8	352.6	371.2	379.7	386.7	375.8	323.1	278.2
67.5°	232.5	240.2	255.7	272.0	306.1	310.7	322.4	325.5	303.8	263.5	227.8
70°	197.6	205.4	212.3	231.7	247.2	255.7	258.0	258.0	236.4	210.0	180.6
72.5°	165.1	169.7	176.7	189.9	198.4	204.6	207.7	203.8	183.7	162.0	140.3
75°	134.1	136.4	142.6	151.1	158.1	155.8	155.0	150.3	135.6	120.1	107.7
77.5°	103.1	104.6	111.6	113.9	113.9	116.2	113.1	108.5	96.1	84.5	79.0
80°	77.5	79.8	80.6	82.1	80.6	80.6	78.3	70.5	64.3	58.9	55.0
82.5°	53.5	55.0	55.8	53.5	55.0	52.7	48.8	43.4	39.5	38.7	37.2
85°	31.8	32.5	31.8	31.8	29.4	28.7	25.6	24.8	23.2	23.2	22.5
87.5°	15.5	14.7	13.2	11.6	11.6	10.8	11.6	10.1	11.6	10.8	10.1
90°	2.3	4.1	6.0	7.8	9.7	10.6	11.3	12.6	13.9	15.3	16.6
92.5°	11.3	11.0	10.6	10.3	10.0	9.8	10.5	11.8	13.2	14.5	15.9
95°	41.5	35.8	30.1	24.4	18.7	15.9	16.0	16.1	16.3	16.4	16.6
97.5°	79.3	83.0	86.7	90.4	94.1	95.9	87.1	69.5	51.8	34.2	16.6
100°	123.8	126.8	129.8	132.9	135.9	137.4	125.8	102.7	79.5	56.4	33.2
102.5°	173.7	175.7	177.7	179.7	181.7	182.7	183.7	185.7	187.8	189.8	191.8
105°	227.3	228.3	229.3	230.3	231.3	231.8	232.2	233.1	233.9	234.8	235.6
107.5°	276.4	276.9	277.4	277.9	278.4	278.6	279.2	280.4	281.5	282.7	283.9
110°	326.2	326.7	327.2	327.7	328.2	328.5	329.0	330.0	331.0	332.0	333.0

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	374.5	375.5	376.5	377.6	378.6	379.1	379.3	379.6	379.9	380.3	380.6
115°	424.4	424.9	425.4	425.9	426.4	426.6	426.5	426.4	426.2	426.1	425.9
117.5°	468.9	469.6	470.2	470.9	471.6	471.9	472.2	472.7	473.2	473.7	474.2
120°	514.2	514.9	515.5	516.2	516.9	517.2	517.1	517.0	516.8	516.7	516.5
122.5°	556.5	556.8	557.2	557.5	557.8	558.0	558.2	558.5	558.8	559.2	559.5
125°	596.5	597.2	597.8	598.5	599.2	599.5	599.3	599.0	598.7	598.3	598.0
127.5°	635.0	635.2	635.4	635.5	635.7	635.8	636.2	637.1	637.9	638.8	639.6
130°	672.0	672.2	672.4	672.5	672.7	672.8	673.0	673.5	674.0	674.5	675.0
132.5°	706.0	706.3	706.7	707.0	707.3	707.5	707.8	708.5	709.2	709.8	710.5
135°	740.0	739.8	739.6	739.5	739.3	739.2	739.5	740.2	740.9	741.6	742.3
137.5°	770.2	770.2	770.2	770.2	770.2	770.2	770.6	771.5	772.3	773.2	774.0
140°	799.6	799.9	800.3	800.6	800.9	801.1	801.3	801.6	802.0	802.3	802.7
142.5°	826.1	826.8	827.4	828.1	828.8	829.1	829.2	829.3	829.5	829.6	829.8
145°	853.3	853.8	854.3	854.8	855.3	855.5	855.5	855.5	855.5	855.5	855.5
147.5°	874.4	875.4	876.4	877.4	878.4	878.9	878.8	878.7	878.5	878.4	878.2
150°	897.8	898.5	899.1	899.8	900.5	900.8	900.7	900.6	900.4	900.3	900.1
152.5°	917.4	917.9	918.4	918.9	919.4	919.7	919.5	919.2	918.9	918.5	918.2
155°	935.6	935.8	935.9	936.1	936.2	936.3	936.0	935.5	935.0	934.5	934.0
157.5°	951.4	951.4	951.4	951.4	951.4	951.4	951.1	950.4	949.7	949.1	948.4
160°	965.0	964.5	964.0	963.5	963.0	962.7	962.6	962.5	962.3	962.2	962.0
162.5°	977.1	976.4	975.8	975.1	974.4	974.1	974.0	973.8	973.7	973.5	973.3
165°	986.9	986.1	985.2	984.4	983.5	983.1	983.1	983.1	983.1	983.1	983.1
167.5°	995.2	994.4	993.5	992.7	991.8	991.4	991.3	991.2	991.0	990.9	990.7
170°	1002.0	1001.0	1000.0	999.0	998.0	997.5	997.6	997.7	997.9	998.0	998.2
172.5°	1006.5	1005.5	1004.5	1003.5	1002.5	1002.0	1002.1	1002.3	1002.4	1002.6	1002.8
175°	1009.6	1008.6	1007.6	1006.5	1005.5	1005.0	1005.1	1005.3	1005.4	1005.6	1005.8
177.5°	1011.8	1010.6	1009.4	1008.3	1007.1	1006.5	1006.7	1007.0	1007.3	1007.7	1008.0
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	1008.2	1016.7	1017.5	1025.2	1022.9	1019.0	1026.0	1021.3	1030.6	1027.5	1031.4
5°	1067.1	1078.7	1088.8	1095.0	1105.8	1103.5	1115.1	1111.2	1119.8	1111.2	1122.1
7.5°	1136.0	1155.4	1165.5	1181.8	1186.4	1187.2	1201.1	1204.2	1209.6	1204.2	1210.4
10°	1203.4	1226.7	1249.9	1263.1	1271.6	1283.3	1295.7	1301.1	1305.0	1299.5	1303.4
12.5°	1264.7	1301.1	1326.7	1353.0	1359.2	1369.3	1382.5	1380.9	1396.4	1393.3	1400.3
15°	1321.2	1361.5	1392.5	1413.5	1430.5	1439.0	1463.8	1465.4	1464.6	1472.3	1467.7
17.5°	1371.6	1405.7	1449.9	1477.0	1497.9	1497.9	1511.9	1540.5	1538.2	1537.4	1542.1
20°	1412.7	1451.4	1492.5	1538.2	1555.3	1558.4	1577.7	1592.5	1594.8	1594.8	1594.8
22.5°	1443.7	1489.4	1533.6	1566.1	1579.3	1590.1	1607.2	1616.5	1619.6	1618.0	1619.6
25°	1459.2	1502.6	1547.5	1577.0	1584.7	1590.9	1592.5	1597.9	1597.1	1587.8	1593.2
27.5°	1462.3	1504.1	1533.6	1541.3	1537.4	1533.6	1508.8	1511.1	1504.1	1490.2	1495.6
30°	1448.3	1470.8	1470.0	1446.0	1439.0	1422.8	1400.3	1367.0	1339.8	1328.2	1332.1
32.5°	1398.0	1398.0	1370.1	1315.8	1291.8	1262.3	1222.0	1191.8	1156.2	1148.4	1163.2
35°	1328.2	1288.7	1237.5	1166.3	1129.8	1108.1	1038.4	1016.7	986.5	977.9	984.9
37.5°	1219.7	1153.9	1079.5	1012.8	981.8	943.1	881.9	850.9	829.2	814.4	821.4
40°	1098.1	1018.2	940.8	858.6	824.5	792.7	747.0	719.1	684.3	685.8	688.1
42.5°	981.8	888.1	801.3	725.3	692.8	666.4	634.7	600.6	588.2	584.3	580.4
45°	858.6	758.6	677.3	620.7	591.3	566.5	537.0	517.6	502.9	499.8	503.7
47.5°	742.4	657.9	580.4	527.7	503.7	491.3	468.1	450.2	440.9	433.2	437.8
50°	637.0	557.9	495.9	451.8	434.7	426.2	404.5	395.2	385.9	383.6	382.8
52.5°	550.2	482.8	429.3	393.7	380.5	375.8	359.6	346.4	338.6	341.0	342.5
55°	471.2	413.8	372.0	343.3	332.4	327.0	315.4	306.1	300.7	298.3	299.9
57.5°	401.4	351.8	321.6	298.3	289.8	287.5	275.1	272.0	268.1	265.8	265.8
60°	337.9	303.0	275.1	261.9	252.6	250.3	241.0	237.1	236.4	234.0	232.5
62.5°	284.4	255.7	236.4	222.4	218.5	217.8	211.6	206.9	204.6	203.0	203.0
65°	237.9	217.0	200.7	190.6	187.5	186.0	179.0	177.5	175.9	174.4	173.6
67.5°	198.4	179.8	168.2	161.2	157.3	158.1	154.2	151.1	151.1	150.3	149.6
70°	160.4	148.8	138.7	134.8	133.3	131.7	130.2	127.9	127.1	127.1	127.1
72.5°	126.3	118.6	113.1	110.8	109.3	107.7	106.2	106.2	106.2	105.4	105.4
75°	96.9	93.8	89.9	87.6	87.6	89.1	86.8	84.5	82.1	80.6	81.4
77.5°	72.8	71.3	69.0	65.1	65.9	64.3	64.3	62.8	63.5	63.5	62.0
80°	53.5	51.1	50.4	48.0	48.8	48.0	47.3	47.3	45.7	45.7	45.7
82.5°	37.2	34.9	34.9	34.1	33.3	33.3	32.5	32.5	33.3	31.8	31.8
85°	22.5	21.7	21.7	20.1	20.1	20.1	20.1	20.9	20.1	19.4	19.4
87.5°	10.1	10.8	10.1	9.3	9.3	9.3	8.5	8.5	7.7	8.5	8.5
90°	17.6	18.6	19.6	20.6	21.1	21.3	21.6	22.0	22.3	22.7	22.3
92.5°	16.9	17.9	18.9	19.9	20.4	20.4	20.4	20.4	20.4	20.4	20.4
95°	17.6	18.6	19.6	20.6	21.1	21.2	21.4	21.5	21.7	21.9	21.7
97.5°	17.4	18.3	19.1	20.0	20.4	20.5	20.6	20.8	20.9	21.1	20.9
100°	30.4	27.5	24.7	21.8	20.4	20.5	20.6	20.8	20.9	21.1	20.9
102.5°	154.0	116.3	78.5	40.8	21.9	21.9	21.9	21.9	21.9	21.9	21.9
105°	237.1	238.6	240.1	241.6	242.4	239.4	233.3	227.3	221.2	215.2	221.2
107.5°	284.7	285.6	286.4	287.3	287.7	288.0	288.7	289.4	290.0	290.7	290.0
110°	333.3	333.7	334.0	334.3	334.5	334.8	335.3	335.8	336.3	336.8	336.3

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	380.4	380.2	380.1	379.9	379.8	380.1	380.8	381.5	382.1	382.8	382.1
115°	426.2	426.6	426.9	427.2	427.4	427.4	427.4	427.4	427.4	427.4	427.4
117.5°	474.0	473.8	473.7	473.5	473.4	473.4	473.4	473.4	473.4	473.4	473.4
120°	516.8	517.2	517.5	517.8	518.0	517.8	517.5	517.2	516.8	516.5	516.8
122.5°	559.7	559.9	560.0	560.2	560.3	560.1	559.8	559.5	559.1	558.8	559.1
125°	598.5	599.0	599.5	600.0	600.3	600.4	600.6	600.7	600.9	601.1	600.9
127.5°	639.4	639.2	639.1	638.9	638.8	638.7	638.6	638.4	638.3	638.1	638.3
130°	675.2	675.4	675.5	675.7	675.8	675.8	675.8	675.8	675.8	675.8	675.8
132.5°	710.7	710.9	711.0	711.2	711.3	711.2	711.0	710.9	710.7	710.5	710.7
135°	742.6	743.0	743.3	743.6	743.8	744.0	744.3	744.6	745.0	745.3	745.0
137.5°	774.3	774.7	775.0	775.3	775.5	775.4	775.2	775.1	774.9	774.7	774.9
140°	803.2	803.7	804.2	804.7	804.9	805.0	805.2	805.3	805.5	805.7	805.5
142.5°	830.2	830.5	830.9	831.2	831.4	831.4	831.4	831.4	831.4	831.4	831.4
145°	855.7	855.9	856.0	856.2	856.3	856.5	856.8	857.1	857.5	857.8	857.5
147.5°	878.4	878.5	878.7	878.8	878.9	879.0	879.2	879.3	879.5	879.7	879.5
150°	900.1	900.1	900.1	900.1	900.1	900.2	900.3	900.5	900.6	900.8	900.6
152.5°	918.5	918.9	919.2	919.5	919.7	919.6	919.4	919.3	919.1	918.9	919.1
155°	934.7	935.4	936.1	936.8	937.1	936.8	936.3	935.8	935.3	934.8	935.3
157.5°	949.2	950.1	950.9	951.8	952.2	951.8	950.9	950.1	949.2	948.4	949.2
160°	963.0	964.0	965.0	966.0	966.5	966.0	965.0	964.0	963.0	962.0	963.0
162.5°	974.3	975.3	976.3	977.3	977.8	977.2	976.1	974.9	973.8	972.6	973.8
165°	984.5	985.8	987.2	988.5	989.2	988.4	986.9	985.4	983.9	982.4	983.9
167.5°	992.2	993.7	995.2	996.7	997.5	996.7	995.0	993.3	991.6	989.9	991.6
170°	999.6	1000.9	1002.3	1003.6	1004.3	1003.5	1001.8	1000.1	998.4	996.7	998.4
172.5°	1004.1	1005.5	1006.8	1008.1	1008.8	1007.9	1006.0	1004.2	1002.3	1000.5	1002.3
175°	1007.3	1008.8	1010.3	1011.8	1012.6	1011.6	1009.6	1007.5	1005.5	1003.5	1005.5
177.5°	1009.4	1010.7	1012.1	1013.4	1014.1	1013.1	1011.1	1009.0	1007.0	1005.0	1007.0
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	1033.7	1028.3	1027.5	1027.5	1019.0	1023.7	1014.4	1004.3	999.6	999.6	991.1
5°	1119.8	1114.3	1108.9	1100.4	1100.4	1095.7	1081.0	1066.3	1055.4	1046.1	1036.1
7.5°	1208.1	1202.7	1187.2	1178.7	1183.3	1174.0	1154.6	1129.8	1111.2	1096.5	1075.6
10°	1304.2	1289.5	1281.7	1277.1	1260.8	1250.7	1228.2	1191.8	1168.6	1149.2	1122.1
12.5°	1382.5	1387.1	1357.7	1360.0	1343.7	1329.8	1294.9	1260.0	1225.1	1198.0	1157.7
15°	1466.9	1453.0	1435.1	1421.2	1415.8	1398.7	1369.3	1322.8	1284.8	1242.2	1196.5
17.5°	1533.6	1522.7	1505.7	1492.5	1480.9	1439.8	1415.0	1373.9	1322.0	1280.2	1224.4
20°	1590.1	1580.1	1556.0	1547.5	1526.6	1497.1	1461.5	1398.0	1351.5	1305.7	1251.5
22.5°	1614.2	1604.1	1583.2	1572.3	1559.1	1530.5	1496.4	1435.9	1378.6	1321.2	1263.9
25°	1594.0	1594.0	1583.9	1580.1	1568.4	1542.9	1508.0	1456.8	1395.6	1333.6	1265.4
27.5°	1496.4	1515.7	1522.7	1526.6	1526.6	1527.4	1503.3	1453.7	1394.1	1333.6	1262.3
30°	1355.3	1387.9	1416.6	1425.1	1439.8	1456.1	1466.1	1442.1	1388.7	1325.1	1253.8
32.5°	1177.9	1219.7	1273.2	1286.4	1306.5	1355.3	1382.5	1392.5	1363.1	1307.3	1231.3
35°	1001.2	1053.9	1086.4	1126.7	1145.3	1217.4	1277.8	1314.3	1307.3	1274.0	1205.0
37.5°	847.0	877.2	916.7	959.3	996.5	1065.5	1140.7	1211.2	1239.9	1223.6	1171.7
40°	699.0	734.6	781.9	816.8	842.3	911.3	1004.3	1081.0	1143.8	1153.9	1122.1
42.5°	594.4	630.0	658.7	696.7	716.8	783.4	865.6	961.7	1036.1	1075.6	1061.6
45°	513.8	535.5	558.7	580.4	605.2	664.1	740.0	845.4	929.1	984.9	990.3
47.5°	443.3	462.6	482.8	502.9	516.9	562.6	632.3	718.3	809.8	886.5	916.7
50°	393.7	403.0	417.7	429.3	445.6	485.1	540.9	615.3	712.2	795.1	834.6
52.5°	344.8	356.5	368.1	378.2	389.0	416.9	468.1	532.4	616.1	701.3	750.1
55°	303.8	313.1	323.9	330.9	337.1	361.9	400.6	450.2	522.3	602.9	663.3
57.5°	270.4	274.3	283.6	287.5	294.5	314.6	342.5	386.7	444.8	523.1	572.7
60°	234.0	241.8	248.7	251.8	257.3	271.2	290.6	331.7	382.0	439.4	495.9
62.5°	204.6	207.7	213.1	217.0	220.9	235.6	251.8	282.8	320.8	368.9	420.8
65°	177.5	179.0	182.1	187.5	189.9	200.7	210.0	232.5	268.1	304.5	356.5
67.5°	149.6	151.1	155.0	158.1	160.4	167.4	177.5	193.7	213.1	253.4	282.1
70°	127.9	127.9	130.2	131.7	134.1	137.2	142.6	155.0	172.8	198.4	224.7
72.5°	106.9	106.9	106.9	109.3	109.3	111.6	114.7	123.2	135.6	155.8	172.8
75°	82.9	83.7	85.2	85.2	86.0	89.1	91.4	93.8	100.0	113.1	128.6
77.5°	62.8	64.3	65.1	63.5	65.1	65.1	68.2	71.3	74.4	78.3	89.9
80°	46.5	47.3	45.7	46.5	46.5	48.0	49.6	48.8	50.4	55.0	58.1
82.5°	31.0	31.8	31.8	31.8	31.8	34.1	34.1	33.3	34.1	34.9	35.6
85°	19.4	18.6	18.6	19.4	18.6	18.6	19.4	20.1	19.4	20.1	20.9
87.5°	8.5	8.5	8.5	8.5	7.7	7.7	8.5	7.7	8.5	7.7	7.0
90°	22.0	21.6	21.3	21.1	20.6	19.6	18.6	17.6	16.6	15.3	13.9
92.5°	20.4	20.4	20.4	20.4	19.9	18.9	17.9	16.9	15.9	14.5	13.2
95°	21.5	21.4	21.2	21.1	20.6	19.6	18.6	17.6	16.6	16.4	16.3
97.5°	20.8	20.6	20.5	20.4	20.0	19.1	18.3	17.4	16.6	34.2	51.8
100°	20.8	20.6	20.5	20.4	21.8	24.7	27.5	30.4	33.2	56.4	79.5
102.5°	21.9	21.9	21.9	21.9	40.8	78.5	116.3	154.0	191.8	189.8	187.8
105°	227.3	233.3	239.4	242.4	241.6	240.1	238.6	237.1	235.6	234.8	233.9
107.5°	289.4	288.7	288.0	287.7	287.3	286.4	285.6	284.7	283.9	282.7	281.5
110°	335.8	335.3	334.8	334.5	334.3	334.0	333.7	333.3	333.0	332.0	331.0



TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	381.5	380.8	380.1	379.8	379.9	380.1	380.2	380.4	380.6	380.3	379.9
115°	427.4	427.4	427.4	427.4	427.2	426.9	426.6	426.2	425.9	426.1	426.2
117.5°	473.4	473.4	473.4	473.4	473.5	473.7	473.8	474.0	474.2	473.7	473.2
120°	517.2	517.5	517.8	518.0	517.8	517.5	517.2	516.8	516.5	516.7	516.8
122.5°	559.5	559.8	560.1	560.3	560.2	560.0	559.9	559.7	559.5	559.2	558.8
125°	600.7	600.6	600.4	600.3	600.0	599.5	599.0	598.5	598.0	598.3	598.7
127.5°	638.4	638.6	638.7	638.8	638.9	639.1	639.2	639.4	639.6	638.8	637.9
130°	675.8	675.8	675.8	675.8	675.7	675.5	675.4	675.2	675.0	674.5	674.0
132.5°	710.9	711.0	711.2	711.3	711.2	711.0	710.9	710.7	710.5	709.8	709.2
135°	744.6	744.3	744.0	743.8	743.6	743.3	743.0	742.6	742.3	741.6	740.9
137.5°	775.1	775.2	775.4	775.5	775.3	775.0	774.7	774.3	774.0	773.2	772.3
140°	805.3	805.2	805.0	804.9	804.7	804.2	803.7	803.2	802.7	802.3	802.0
142.5°	831.4	831.4	831.4	831.4	831.2	830.9	830.5	830.2	829.8	829.6	829.5
145°	857.1	856.8	856.5	856.3	856.2	856.0	855.9	855.7	855.5	855.5	855.5
147.5°	879.3	879.2	879.0	878.9	878.8	878.7	878.5	878.4	878.2	878.4	878.5
150°	900.5	900.3	900.2	900.1	900.1	900.1	900.1	900.1	900.1	900.3	900.4
152.5°	919.3	919.4	919.6	919.7	919.5	919.2	918.9	918.5	918.2	918.5	918.9
155°	935.8	936.3	936.8	937.1	936.8	936.1	935.4	934.7	934.0	934.5	935.0
157.5°	950.1	950.9	951.8	952.2	951.8	950.9	950.1	949.2	948.4	949.1	949.7
160°	964.0	965.0	966.0	966.5	966.0	965.0	964.0	963.0	962.0	962.2	962.3
162.5°	974.9	976.1	977.2	977.8	977.3	976.3	975.3	974.3	973.3	973.5	973.7
165°	985.4	986.9	988.4	989.2	988.5	987.2	985.8	984.5	983.1	983.1	983.1
167.5°	993.3	995.0	996.7	997.5	996.7	995.2	993.7	992.2	990.7	990.9	991.0
170°	1000.1	1001.8	1003.5	1004.3	1003.6	1002.3	1000.9	999.6	998.2	998.0	997.9
172.5°	1004.2	1006.0	1007.9	1008.8	1008.1	1006.8	1005.5	1004.1	1002.8	1002.6	1002.4
175°	1007.5	1009.6	1011.6	1012.6	1011.8	1010.3	1008.8	1007.3	1005.8	1005.6	1005.4
177.5°	1009.0	1011.1	1013.1	1014.1	1013.4	1012.1	1010.7	1009.4	1008.0	1007.7	1007.3
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	986.5	982.6	980.3	979.5	972.5	968.6	966.3	964.8	962.4	956.2	950.8
5°	1023.7	1012.8	1007.4	1001.2	990.3	977.9	967.9	961.7	953.9	941.5	929.9
7.5°	1058.5	1042.3	1031.4	1022.9	1004.3	984.1	967.9	954.7	940.0	922.9	906.7
10°	1095.0	1068.6	1054.7	1041.5	1014.4	988.0	964.8	945.4	924.5	902.0	884.2
12.5°	1123.6	1088.8	1073.3	1054.7	1021.3	990.3	960.9	934.6	907.4	883.4	857.8
15°	1157.0	1113.6	1095.7	1071.7	1026.0	985.7	947.7	919.1	891.2	855.5	828.4
17.5°	1176.3	1126.0	1100.4	1079.5	1029.9	981.0	936.9	901.2	868.7	833.0	804.4
20°	1195.7	1138.4	1109.7	1080.2	1021.3	969.4	922.9	880.3	846.2	807.5	778.0
22.5°	1201.9	1135.3	1105.0	1077.9	1015.9	957.8	904.3	860.9	821.4	782.7	749.3
25°	1201.9	1134.5	1098.8	1064.0	998.9	939.2	885.7	838.5	794.3	755.5	722.2
27.5°	1189.5	1119.0	1081.8	1050.0	982.6	918.3	863.3	811.3	768.7	730.0	692.0
30°	1174.0	1096.5	1059.3	1021.3	956.2	895.0	835.4	787.3	742.4	698.2	664.1
32.5°	1154.6	1072.5	1031.4	992.7	923.7	860.2	805.1	757.9	715.3	669.5	631.6
35°	1126.7	1036.8	991.1	957.0	890.4	824.5	771.8	725.3	684.3	637.0	595.9
37.5°	1091.1	1004.3	957.8	916.0	847.0	786.5	736.9	692.0	651.7	608.3	562.6
40°	1049.2	958.6	918.3	874.1	801.3	743.9	697.4	657.1	616.8	575.8	531.6
42.5°	1002.0	912.1	867.1	824.5	754.8	698.2	654.8	618.4	581.2	543.2	495.9
45°	945.4	860.9	817.5	777.2	709.8	651.7	612.2	577.3	545.5	506.8	465.0
47.5°	881.9	808.2	764.1	720.7	654.8	604.4	565.7	536.2	509.1	470.4	432.4
50°	819.9	747.0	711.4	667.2	606.8	559.5	520.0	495.2	474.3	436.3	402.2
52.5°	741.6	686.6	652.5	614.5	556.4	508.3	477.4	455.7	430.9	401.4	371.2
55°	672.6	621.5	594.4	558.7	501.4	458.8	432.4	412.3	392.9	366.5	342.5
57.5°	594.4	562.6	535.5	504.5	447.9	411.5	388.2	371.2	353.4	331.7	312.3
60°	512.2	497.5	471.2	446.4	398.3	366.5	347.2	331.7	314.6	296.8	280.5
62.5°	439.4	430.9	415.4	396.0	351.0	323.9	304.5	292.9	280.5	264.2	248.7
65°	370.4	366.5	351.8	337.9	306.9	282.8	265.8	258.8	244.9	232.5	218.5
67.5°	309.2	304.5	296.0	289.8	263.5	241.0	232.5	223.2	211.6	202.3	190.6
70°	247.2	246.4	241.0	233.3	219.3	203.0	194.5	188.3	176.7	169.7	161.2
72.5°	192.2	196.1	191.4	188.3	179.0	167.4	159.6	155.8	146.5	141.0	134.8
75°	143.4	146.5	148.8	143.4	141.0	135.6	128.6	124.8	120.1	112.4	110.0
77.5°	97.6	104.6	104.6	106.2	106.9	103.8	98.4	95.3	89.9	88.3	85.2
80°	64.3	70.5	71.3	72.8	75.2	75.2	71.3	70.5	65.1	64.3	62.0
82.5°	37.2	42.6	45.7	48.0	47.3	50.4	47.3	46.5	43.4	43.4	41.8
85°	20.1	20.9	22.5	24.0	25.6	27.1	27.1	26.3	25.6	24.8	23.2
87.5°	7.7	7.7	8.5	7.7	8.5	10.1	10.8	10.8	10.1	9.3	7.7
90°	12.6	11.3	10.6	9.7	7.8	6.0	4.1	2.3	4.1	6.0	7.8
92.5°	11.8	10.5	9.8	10.0	10.3	10.6	11.0	11.3	11.0	10.6	10.3
95°	16.1	16.0	15.9	18.7	24.4	30.1	35.8	41.5	35.8	30.1	24.4
97.5°	69.5	87.1	95.9	94.1	90.4	86.7	83.0	79.3	83.0	86.7	90.4
100°	102.7	125.8	137.4	135.9	132.9	129.8	126.8	123.8	126.8	129.8	132.9
102.5°	185.7	183.7	182.7	181.7	179.7	177.7	175.7	173.7	175.7	177.7	179.7
105°	233.1	232.2	231.8	231.3	230.3	229.3	228.3	227.3	228.3	229.3	230.3
107.5°	280.4	279.2	278.6	278.4	277.9	277.4	276.9	276.4	276.9	277.4	277.9
110°	330.0	329.0	328.5	328.2	327.7	327.2	326.7	326.2	326.7	327.2	327.7

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	379.6	379.3	379.1	378.6	377.6	376.5	375.5	374.5	375.5	376.5	377.6
115°	426.4	426.5	426.6	426.4	425.9	425.4	424.9	424.4	424.9	425.4	425.9
117.5°	472.7	472.2	471.9	471.6	470.9	470.2	469.6	468.9	469.6	470.2	470.9
120°	517.0	517.1	517.2	516.9	516.2	515.5	514.9	514.2	514.9	515.5	516.2
122.5°	558.5	558.2	558.0	557.8	557.5	557.2	556.8	556.5	556.8	557.2	557.5
125°	599.0	599.3	599.5	599.2	598.5	597.8	597.2	596.5	597.2	597.8	598.5
127.5°	637.1	636.2	635.8	635.7	635.5	635.4	635.2	635.0	635.2	635.4	635.5
130°	673.5	673.0	672.8	672.7	672.5	672.4	672.2	672.0	672.2	672.4	672.5
132.5°	708.5	707.8	707.5	707.3	707.0	706.7	706.3	706.0	706.3	706.7	707.0
135°	740.2	739.5	739.2	739.3	739.5	739.6	739.8	740.0	739.8	739.6	739.5
137.5°	771.5	770.6	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2	770.2
140°	801.6	801.3	801.1	800.9	800.6	800.3	799.9	799.6	799.9	800.3	800.6
142.5°	829.3	829.2	829.1	828.8	828.1	827.4	826.8	826.1	826.8	827.4	828.1
145°	855.5	855.5	855.5	855.3	854.8	854.3	853.8	853.3	853.8	854.3	854.8
147.5°	878.7	878.8	878.9	878.4	877.4	876.4	875.4	874.4	875.4	876.4	877.4
150°	900.6	900.7	900.8	900.5	899.8	899.1	898.5	897.8	898.5	899.1	899.8
152.5°	919.2	919.5	919.7	919.4	918.9	918.4	917.9	917.4	917.9	918.4	918.9
155°	935.5	936.0	936.3	936.2	936.1	935.9	935.8	935.6	935.8	935.9	936.1
157.5°	950.4	951.1	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4	951.4
160°	962.5	962.6	962.7	963.0	963.5	964.0	964.5	965.0	964.5	964.0	963.5
162.5°	973.8	974.0	974.1	974.4	975.1	975.8	976.4	977.1	976.4	975.8	975.1
165°	983.1	983.1	983.1	983.5	984.4	985.2	986.1	986.9	986.1	985.2	984.4
167.5°	991.2	991.3	991.4	991.8	992.7	993.5	994.4	995.2	994.4	993.5	992.7
170°	997.7	997.6	997.5	998.0	999.0	1000.0	1001.0	1002.0	1001.0	1000.0	999.0
172.5°	1002.3	1002.1	1002.0	1002.5	1003.5	1004.5	1005.5	1006.5	1005.5	1004.5	1003.5
175°	1005.3	1005.1	1005.0	1005.5	1006.5	1007.6	1008.6	1009.6	1008.6	1007.6	1006.5
177.5°	1007.0	1006.7	1006.5	1007.1	1008.3	1009.4	1010.6	1011.8	1010.6	1009.4	1008.3
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	946.2	944.6	943.1	936.9	931.5	922.2	914.4	911.3	910.5	911.3	909.0
5°	919.1	918.3	912.9	902.0	891.9	881.1	873.3	865.6	860.9	860.9	855.5
7.5°	893.5	888.1	883.4	869.5	857.8	843.1	831.5	824.5	820.6	812.1	812.1
10°	866.4	858.6	852.4	839.2	822.2	807.5	792.7	784.2	777.2	771.0	768.7
12.5°	839.2	833.0	821.4	807.5	790.4	771.8	756.3	750.1	733.8	720.7	721.4
15°	813.7	799.7	794.3	774.1	754.0	736.2	713.7	695.9	682.7	674.2	663.3
17.5°	785.0	771.0	761.0	743.9	717.6	689.7	668.0	644.0	630.8	616.1	609.1
20°	753.2	741.6	733.8	706.7	675.0	641.6	617.6	602.9	588.2	577.3	571.1
22.5°	726.1	711.4	702.1	665.7	630.8	597.5	578.9	566.5	554.1	544.8	541.7
25°	691.2	682.7	660.2	628.5	585.8	563.4	547.1	530.8	523.8	517.6	510.7
27.5°	662.6	641.6	626.1	584.3	557.9	532.4	516.1	503.7	495.2	489.0	483.5
30°	626.9	607.5	585.8	551.0	526.9	502.9	488.2	478.1	468.8	465.0	460.3
32.5°	589.7	571.9	551.0	523.1	493.6	475.0	463.4	452.6	446.4	442.5	437.1
35°	556.4	533.9	520.0	493.6	469.6	448.7	437.8	428.5	421.6	420.0	419.2
37.5°	520.7	503.7	490.5	463.4	443.3	425.4	415.4	405.3	401.4	400.6	397.5
40°	489.7	475.0	462.6	437.1	415.4	399.1	391.3	385.1	381.3	381.3	380.5
42.5°	462.6	447.1	434.7	411.5	392.1	377.4	368.9	362.7	361.1	361.9	361.1
45°	432.4	419.2	406.8	382.8	366.5	355.7	346.4	343.3	341.0	341.7	342.5
47.5°	403.7	392.9	380.5	361.1	342.5	330.9	325.5	322.4	322.4	322.4	323.9
50°	378.2	365.8	354.9	334.8	317.7	308.4	303.8	299.9	300.7	301.4	302.2
52.5°	347.9	337.1	329.3	309.2	296.8	285.2	279.7	280.5	279.7	279.7	281.3
55°	321.6	310.7	303.0	284.4	272.0	264.2	259.6	257.3	258.0	256.5	259.6
57.5°	292.1	282.8	277.4	259.6	248.7	241.8	237.9	234.0	235.6	234.8	234.0
60°	266.6	255.7	247.2	234.8	225.5	217.0	214.7	210.8	212.3	210.8	210.0
62.5°	237.1	228.6	222.4	210.0	202.3	195.3	189.9	187.5	186.8	184.4	182.1
65°	207.7	203.0	196.8	184.4	176.7	171.3	168.2	165.8	165.1	158.9	151.9
67.5°	180.6	177.5	171.3	162.0	155.0	149.6	144.9	141.0	136.4	131.7	127.9
70°	155.0	150.3	146.5	137.9	131.7	126.3	121.7	117.0	114.7	110.0	108.5
72.5°	130.2	125.5	121.7	113.9	108.5	103.1	101.5	96.1	93.8	93.0	93.0
75°	104.6	100.7	98.4	91.4	86.8	82.9	80.6	79.0	77.5	75.9	73.6
77.5°	79.8	77.5	75.9	71.3	67.4	65.1	64.3	58.9	57.3	55.8	54.2
80°	58.1	57.3	55.8	51.9	50.4	44.9	44.9	43.4	42.6	42.6	42.6
82.5°	39.5	38.0	37.2	33.3	32.5	31.8	31.0	30.2	31.0	30.2	31.0
85°	20.9	20.1	19.4	19.4	19.4	19.4	19.4	19.4	19.4	18.6	19.4
87.5°	7.7	7.7	7.7	7.7	7.0	7.7	7.7	7.0	7.7	7.7	7.7
90°	9.7	10.6	11.3	12.6	13.9	15.3	16.6	17.6	18.6	19.6	20.6
92.5°	10.0	9.8	10.5	11.8	13.2	14.5	15.9	16.9	17.9	18.9	19.9
95°	18.7	15.9	16.0	16.1	16.3	16.4	16.6	17.6	18.6	19.6	20.6
97.5°	94.1	95.9	87.1	69.5	51.8	34.2	16.6	17.4	18.3	19.1	20.0
100°	135.9	137.4	125.8	102.7	79.5	56.4	33.2	30.4	27.5	24.7	21.8
102.5°	181.7	182.7	183.7	185.7	187.8	189.8	191.8	154.0	116.3	78.5	40.8
105°	231.3	231.8	232.2	233.1	233.9	234.8	235.6	237.1	238.6	240.1	241.6
107.5°	278.4	278.6	279.2	280.4	281.5	282.7	283.9	284.7	285.6	286.4	287.3
110°	328.2	328.5	329.0	330.0	331.0	332.0	333.0	333.3	333.7	334.0	334.3

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	378.6	379.1	379.3	379.6	379.9	380.3	380.6	380.4	380.2	380.1	379.9
115°	426.4	426.6	426.5	426.4	426.2	426.1	425.9	426.2	426.6	426.9	427.2
117.5°	471.6	471.9	472.2	472.7	473.2	473.7	474.2	474.0	473.8	473.7	473.5
120°	516.9	517.2	517.1	517.0	516.8	516.7	516.5	516.8	517.2	517.5	517.8
122.5°	557.8	558.0	558.2	558.5	558.8	559.2	559.5	559.7	559.9	560.0	560.2
125°	599.2	599.5	599.3	599.0	598.7	598.3	598.0	598.5	599.0	599.5	600.0
127.5°	635.7	635.8	636.2	637.1	637.9	638.8	639.6	639.4	639.2	639.1	638.9
130°	672.7	672.8	673.0	673.5	674.0	674.5	675.0	675.2	675.4	675.5	675.7
132.5°	707.3	707.5	707.8	708.5	709.2	709.8	710.5	710.7	710.9	711.0	711.2
135°	739.3	739.2	739.5	740.2	740.9	741.6	742.3	742.6	743.0	743.3	743.6
137.5°	770.2	770.2	770.6	771.5	772.3	773.2	774.0	774.3	774.7	775.0	775.3
140°	800.9	801.1	801.3	801.6	802.0	802.3	802.7	803.2	803.7	804.2	804.7
142.5°	828.8	829.1	829.2	829.3	829.5	829.6	829.8	830.2	830.5	830.9	831.2
145°	855.3	855.5	855.5	855.5	855.5	855.5	855.5	855.7	855.9	856.0	856.2
147.5°	878.4	878.9	878.8	878.7	878.5	878.4	878.2	878.4	878.5	878.7	878.8
150°	900.5	900.8	900.7	900.6	900.4	900.3	900.1	900.1	900.1	900.1	900.1
152.5°	919.4	919.7	919.5	919.2	918.9	918.5	918.2	918.5	918.9	919.2	919.5
155°	936.2	936.3	936.0	935.5	935.0	934.5	934.0	934.7	935.4	936.1	936.8
157.5°	951.4	951.4	951.1	950.4	949.7	949.1	948.4	949.2	950.1	950.9	951.8
160°	963.0	962.7	962.6	962.5	962.3	962.2	962.0	963.0	964.0	965.0	966.0
162.5°	974.4	974.1	974.0	973.8	973.7	973.5	973.3	974.3	975.3	976.3	977.3
165°	983.5	983.1	983.1	983.1	983.1	983.1	983.1	984.5	985.8	987.2	988.5
167.5°	991.8	991.4	991.3	991.2	991.0	990.9	990.7	992.2	993.7	995.2	996.7
170°	998.0	997.5	997.6	997.7	997.9	998.0	998.2	999.6	1000.9	1002.3	1003.6
172.5°	1002.5	1002.0	1002.1	1002.3	1002.4	1002.6	1002.8	1004.1	1005.5	1006.8	1008.1
175°	1005.5	1005.0	1005.1	1005.3	1005.4	1005.6	1005.8	1007.3	1008.8	1010.3	1011.8
177.5°	1007.1	1006.5	1006.7	1007.0	1007.3	1007.7	1008.0	1009.4	1010.7	1012.1	1013.4
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	909.0	912.1	908.2	910.5	905.1	904.3	905.1	905.1	905.9	906.7	907.4
5°	857.8	857.1	852.4	849.3	847.0	849.3	850.9	852.4	850.9	852.4	853.2
7.5°	809.8	807.5	805.1	799.7	801.3	799.7	804.4	802.0	802.0	805.9	809.0
10°	767.2	762.5	761.0	754.8	750.1	749.3	754.8	757.1	759.4	761.0	767.2
12.5°	712.2	705.2	699.8	702.1	688.9	694.3	695.9	692.8	702.1	712.9	706.7
15°	653.3	654.0	643.2	639.3	628.5	631.6	632.3	640.1	647.8	647.1	656.4
17.5°	609.9	605.2	595.9	595.1	590.5	592.8	592.0	598.2	595.9	599.8	607.5
20°	569.6	566.5	558.7	555.6	557.2	555.6	556.4	557.2	559.5	568.0	566.5
22.5°	537.8	533.9	533.9	530.0	525.4	523.8	527.7	530.0	533.1	534.7	538.6
25°	509.9	506.8	502.9	500.6	496.7	497.5	499.8	502.9	505.2	508.3	511.4
27.5°	481.2	481.2	477.4	476.6	475.0	474.3	477.4	478.9	478.9	481.2	484.3
30°	458.8	458.8	454.9	454.1	453.3	453.3	455.7	456.4	457.2	459.5	461.1
32.5°	437.1	436.3	434.7	435.5	434.7	435.5	435.5	436.3	437.8	438.6	441.7
35°	416.9	417.7	416.1	416.1	415.4	416.1	417.7	418.5	419.2	420.8	420.8
37.5°	397.5	399.1	398.3	400.6	400.6	400.6	400.6	402.2	402.2	402.2	401.4
40°	380.5	380.5	379.7	381.3	382.8	382.8	383.6	383.6	384.4	384.4	383.6
42.5°	361.1	362.7	365.0	365.8	367.3	366.5	368.9	368.1	368.9	367.3	365.8
45°	343.3	343.3	346.4	349.5	350.3	350.3	350.3	351.8	350.3	347.9	347.2
47.5°	323.9	325.5	327.0	330.9	331.7	331.7	331.7	331.7	330.1	330.1	330.1
50°	304.5	305.3	306.1	307.6	310.0	309.2	309.2	309.2	312.3	309.2	310.0
52.5°	281.3	282.1	282.8	285.9	285.2	285.2	285.9	285.9	288.3	287.5	285.9
55°	258.0	258.0	259.6	259.6	259.6	261.1	261.9	263.5	262.7	263.5	264.2
57.5°	234.8	233.3	232.5	232.5	234.8	234.0	234.8	234.8	237.9	239.4	240.2
60°	207.7	207.7	206.9	202.3	202.3	201.5	203.8	205.4	206.9	213.9	213.1
62.5°	179.8	176.7	173.6	174.4	169.7	172.0	170.5	172.0	176.7	182.1	182.9
65°	151.9	149.6	146.5	145.7	144.1	146.5	145.7	146.5	148.8	151.9	155.8
67.5°	127.1	126.3	124.8	124.0	124.0	124.0	125.5	125.5	126.3	128.6	131.0
70°	108.5	107.7	108.5	106.9	107.7	106.9	107.7	108.5	109.3	110.0	112.4
72.5°	91.4	91.4	91.4	89.9	91.4	90.7	90.7	91.4	92.2	93.0	94.5
75°	72.8	71.3	69.7	68.2	67.4	69.0	69.7	69.0	71.3	74.4	74.4
77.5°	55.0	54.2	54.2	54.2	55.0	54.2	55.8	55.0	55.8	55.8	57.3
80°	42.6	41.8	42.6	42.6	41.8	43.4	42.6	42.6	43.4	44.2	43.4
82.5°	31.0	31.8	31.0	31.0	31.0	32.5	31.0	31.0	31.0	31.8	31.8
85°	19.4	19.4	19.4	19.4	20.1	19.4	20.1	19.4	20.9	20.1	20.1
87.5°	7.0	7.7	8.5	8.5	8.5	8.5	7.7	8.5	9.3	8.5	9.3
90°	21.1	21.3	21.6	22.0	22.3	22.7	22.3	22.0	21.6	21.3	21.1
92.5°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4
95°	21.1	21.2	21.4	21.5	21.7	21.9	21.7	21.5	21.4	21.2	21.1
97.5°	20.4	20.5	20.6	20.8	20.9	21.1	20.9	20.8	20.6	20.5	20.4
100°	20.4	20.5	20.6	20.8	20.9	21.1	20.9	20.8	20.6	20.5	20.4
102.5°	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9	21.9
105°	242.4	239.4	233.3	227.3	221.2	215.2	221.2	227.3	233.3	239.4	242.4
107.5°	287.7	288.0	288.7	289.4	290.0	290.7	290.0	289.4	288.7	288.0	287.7
110°	334.5	334.8	335.3	335.8	336.3	336.8	336.3	335.8	335.3	334.8	334.5

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	379.8	380.1	380.8	381.5	382.1	382.8	382.1	381.5	380.8	380.1	379.8
115°	427.4	427.4	427.4	427.4	427.4	427.4	427.4	427.4	427.4	427.4	427.4
117.5°	473.4	473.4	473.4	473.4	473.4	473.4	473.4	473.4	473.4	473.4	473.4
120°	518.0	517.8	517.5	517.2	516.8	516.5	516.8	517.2	517.5	517.8	518.0
122.5°	560.3	560.1	559.8	559.5	559.1	558.8	559.1	559.5	559.8	560.1	560.3
125°	600.3	600.4	600.6	600.7	600.9	601.1	600.9	600.7	600.6	600.4	600.3
127.5°	638.8	638.7	638.6	638.4	638.3	638.1	638.3	638.4	638.6	638.7	638.8
130°	675.8	675.8	675.8	675.8	675.8	675.8	675.8	675.8	675.8	675.8	675.8
132.5°	711.3	711.2	711.0	710.9	710.7	710.5	710.7	710.9	711.0	711.2	711.3
135°	743.8	744.0	744.3	744.6	745.0	745.3	745.0	744.6	744.3	744.0	743.8
137.5°	775.5	775.4	775.2	775.1	774.9	774.7	774.9	775.1	775.2	775.4	775.5
140°	804.9	805.0	805.2	805.3	805.5	805.7	805.5	805.3	805.2	805.0	804.9
142.5°	831.4	831.4	831.4	831.4	831.4	831.4	831.4	831.4	831.4	831.4	831.4
145°	856.3	856.5	856.8	857.1	857.5	857.8	857.5	857.1	856.8	856.5	856.3
147.5°	878.9	879.0	879.2	879.3	879.5	879.7	879.5	879.3	879.2	879.0	878.9
150°	900.1	900.2	900.3	900.5	900.6	900.8	900.6	900.5	900.3	900.2	900.1
152.5°	919.7	919.6	919.4	919.3	919.1	918.9	919.1	919.3	919.4	919.6	919.7
155°	937.1	936.8	936.3	935.8	935.3	934.8	935.3	935.8	936.3	936.8	937.1
157.5°	952.2	951.8	950.9	950.1	949.2	948.4	949.2	950.1	950.9	951.8	952.2
160°	966.5	966.0	965.0	964.0	963.0	962.0	963.0	964.0	965.0	966.0	966.5
162.5°	977.8	977.2	976.1	974.9	973.8	972.6	973.8	974.9	976.1	977.2	977.8
165°	989.2	988.4	986.9	985.4	983.9	982.4	983.9	985.4	986.9	988.4	989.2
167.5°	997.5	996.7	995.0	993.3	991.6	989.9	991.6	993.3	995.0	996.7	997.5
170°	1004.3	1003.5	1001.8	1000.1	998.4	996.7	998.4	1000.1	1001.8	1003.5	1004.3
172.5°	1008.8	1007.9	1006.0	1004.2	1002.3	1000.5	1002.3	1004.2	1006.0	1007.9	1008.8
175°	1012.6	1011.6	1009.6	1007.5	1005.5	1003.5	1005.5	1007.5	1009.6	1011.6	1012.6
177.5°	1014.1	1013.1	1011.1	1009.0	1007.0	1005.0	1007.0	1009.0	1011.1	1013.1	1014.1
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7	961.7
2.5°	910.5	914.4	912.9	907.4	909.8	914.4	919.1	925.3	929.1	932.2	933.8
5°	857.1	864.0	862.5	862.5	865.6	873.3	881.1	894.3	898.9	904.3	912.1
7.5°	809.8	815.2	819.9	821.4	826.1	836.1	846.2	860.9	872.6	878.8	883.4
10°	767.9	771.8	778.8	782.7	787.3	799.7	814.4	829.9	841.6	852.4	858.6
12.5°	714.5	730.0	739.3	745.5	751.7	770.3	781.9	798.9	812.9	823.0	832.3
15°	654.8	673.4	678.8	702.9	718.3	733.1	750.9	771.0	784.2	795.8	808.2
17.5°	604.4	617.6	623.8	649.4	662.6	685.8	711.4	736.9	757.1	765.6	778.0
20°	572.7	579.6	592.0	600.6	614.5	641.6	669.5	700.5	730.7	739.3	751.7
22.5°	540.1	549.4	557.9	569.6	580.4	599.0	626.9	661.0	693.6	709.1	723.8
25°	510.7	520.0	525.4	537.8	547.9	566.5	585.8	620.7	659.5	672.6	695.9
27.5°	487.4	492.8	502.1	507.6	519.2	536.2	554.1	580.4	618.4	640.9	663.3
30°	464.2	468.1	475.8	483.5	492.1	503.7	523.8	549.4	584.3	603.7	626.1
32.5°	440.9	447.1	451.8	457.2	466.5	480.4	494.4	519.2	547.1	568.8	591.3
35°	421.6	423.9	430.1	436.3	442.5	454.9	469.6	493.6	518.4	535.5	555.6
37.5°	400.6	404.5	409.2	411.5	421.6	429.3	444.8	463.4	492.8	503.7	523.8
40°	384.4	383.6	388.2	392.1	396.8	409.2	418.5	438.6	461.9	478.9	491.3
42.5°	364.2	364.2	365.8	370.4	376.6	384.4	395.2	412.3	436.3	448.7	463.4
45°	347.9	345.6	346.4	349.5	353.4	361.1	372.0	386.7	410.7	420.8	436.3
47.5°	328.6	326.2	326.2	329.3	332.4	337.9	346.4	363.4	382.8	396.0	407.6
50°	306.9	307.6	306.9	309.2	310.7	316.2	325.5	339.4	357.2	368.1	381.3
52.5°	286.7	285.2	284.4	285.9	289.0	292.9	303.0	315.4	332.4	343.3	354.9
55°	261.9	263.5	263.5	263.5	268.1	269.7	277.4	289.8	306.9	315.4	326.2
57.5°	239.4	238.7	240.2	239.4	243.3	248.7	254.9	264.2	281.3	289.8	299.9
60°	214.7	215.4	216.2	216.2	219.3	224.7	231.7	240.2	254.2	262.7	272.0
62.5°	184.4	188.3	192.2	193.7	198.4	202.3	206.9	216.2	228.6	234.8	243.3
65°	155.8	161.2	166.6	170.5	173.6	177.5	183.7	192.2	202.3	208.5	217.0
67.5°	131.0	134.8	141.8	145.7	151.9	156.5	160.4	167.4	179.8	182.1	189.1
70°	113.1	114.7	117.8	120.9	127.9	131.7	136.4	143.4	152.7	158.1	162.0
72.5°	95.3	96.1	97.6	100.7	103.8	108.5	113.9	120.1	128.6	131.0	136.4
75°	75.9	80.6	80.6	82.9	85.2	87.6	92.2	98.4	103.8	107.7	110.8
77.5°	56.6	58.9	60.4	64.3	67.4	69.7	72.8	77.5	80.6	83.7	86.0
80°	44.2	44.9	45.7	45.7	47.3	50.4	53.5	56.6	60.4	62.0	64.3
82.5°	32.5	32.5	32.5	34.1	34.9	35.6	35.6	37.2	41.1	42.6	44.9
85°	20.9	20.9	20.9	20.9	21.7	22.5	23.2	24.0	24.0	24.0	25.6
87.5°	8.5	10.1	9.3	10.1	10.1	10.1	10.1	10.8	10.8	11.6	11.6
90°	20.6	19.6	18.6	17.6	16.6	15.3	13.9	12.6	11.3	10.6	9.7
92.5°	19.9	18.9	17.9	16.9	15.9	14.5	13.2	11.8	10.5	9.8	10.0
95°	20.6	19.6	18.6	17.6	16.6	16.4	16.3	16.1	16.0	15.9	18.7
97.5°	20.0	19.1	18.3	17.4	16.6	34.2	51.8	69.5	87.1	95.9	94.1
100°	21.8	24.7	27.5	30.4	33.2	56.4	79.5	102.7	125.8	137.4	135.9
102.5°	40.8	78.5	116.3	154.0	191.8	189.8	187.8	185.7	183.7	182.7	181.7
105°	241.6	240.1	238.6	237.1	235.6	234.8	233.9	233.1	232.2	231.8	231.3
107.5°	287.3	286.4	285.6	284.7	283.9	282.7	281.5	280.4	279.2	278.6	278.4
110°	334.3	334.0	333.7	333.3	333.0	332.0	331.0	330.0	329.0	328.5	328.2

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	379.9	380.1	380.2	380.4	380.6	380.3	379.9	379.6	379.3	379.1	378.6
115°	427.2	426.9	426.6	426.2	425.9	426.1	426.2	426.4	426.5	426.6	426.4
117.5°	473.5	473.7	473.8	474.0	474.2	473.7	473.2	472.7	472.2	471.9	471.6
120°	517.8	517.5	517.2	516.8	516.5	516.7	516.8	517.0	517.1	517.2	516.9
122.5°	560.2	560.0	559.9	559.7	559.5	559.2	558.8	558.5	558.2	558.0	557.8
125°	600.0	599.5	599.0	598.5	598.0	598.3	598.7	599.0	599.3	599.5	599.2
127.5°	638.9	639.1	639.2	639.4	639.6	638.8	637.9	637.1	636.2	635.8	635.7
130°	675.7	675.5	675.4	675.2	675.0	674.5	674.0	673.5	673.0	672.8	672.7
132.5°	711.2	711.0	710.9	710.7	710.5	709.8	709.2	708.5	707.8	707.5	707.3
135°	743.6	743.3	743.0	742.6	742.3	741.6	740.9	740.2	739.5	739.2	739.3
137.5°	775.3	775.0	774.7	774.3	774.0	773.2	772.3	771.5	770.6	770.2	770.2
140°	804.7	804.2	803.7	803.2	802.7	802.3	802.0	801.6	801.3	801.1	800.9
142.5°	831.2	830.9	830.5	830.2	829.8	829.6	829.5	829.3	829.2	829.1	828.8
145°	856.2	856.0	855.9	855.7	855.5	855.5	855.5	855.5	855.5	855.5	855.3
147.5°	878.8	878.7	878.5	878.4	878.2	878.4	878.5	878.7	878.8	878.9	878.4
150°	900.1	900.1	900.1	900.1	900.1	900.3	900.4	900.6	900.7	900.8	900.5
152.5°	919.5	919.2	918.9	918.5	918.2	918.5	918.9	919.2	919.5	919.7	919.4
155°	936.8	936.1	935.4	934.7	934.0	934.5	935.0	935.5	936.0	936.3	936.2
157.5°	951.8	950.9	950.1	949.2	948.4	949.1	949.7	950.4	951.1	951.4	951.4
160°	966.0	965.0	964.0	963.0	962.0	962.2	962.3	962.5	962.6	962.7	963.0
162.5°	977.3	976.3	975.3	974.3	973.3	973.5	973.7	973.8	974.0	974.1	974.4
165°	988.5	987.2	985.8	984.5	983.1	983.1	983.1	983.1	983.1	983.1	983.5
167.5°	996.7	995.2	993.7	992.2	990.7	990.9	991.0	991.2	991.3	991.4	991.8
170°	1003.6	1002.3	1000.9	999.6	998.2	998.0	997.9	997.7	997.6	997.5	998.0
172.5°	1008.1	1006.8	1005.5	1004.1	1002.8	1002.6	1002.4	1002.3	1002.1	1002.0	1002.5
175°	1011.8	1010.3	1008.8	1007.3	1005.8	1005.6	1005.4	1005.3	1005.1	1005.0	1005.5
177.5°	1013.4	1012.1	1010.7	1009.4	1008.0	1007.7	1007.3	1007.0	1006.7	1006.5	1007.1
180°	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6	1009.6

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	961.7	961.7	961.7	961.7
2.5°	940.0	944.6	952.4	963.2
5°	918.3	931.5	943.9	960.1
7.5°	898.9	914.4	931.5	954.7
10°	876.4	895.8	917.5	946.2
12.5°	850.1	877.2	902.0	933.0
15°	830.7	850.9	882.6	919.1
17.5°	803.6	830.7	862.5	903.6
20°	778.0	806.7	842.3	885.0
22.5°	750.9	783.4	819.1	864.8
25°	723.0	757.9	793.5	842.3
27.5°	697.4	729.2	769.5	819.1
30°	666.4	702.9	741.6	793.5
32.5°	636.2	674.2	713.7	765.6
35°	603.7	641.6	685.0	734.6
37.5°	571.9	613.7	653.3	701.3
40°	537.0	580.4	621.5	670.3
42.5°	502.9	547.9	588.9	630.8
45°	471.2	515.3	552.5	592.0
47.5°	440.9	480.4	518.4	554.1
50°	411.5	444.8	479.7	509.1
52.5°	380.5	412.3	440.2	466.5
55°	352.6	377.4	402.2	426.2
57.5°	319.3	344.1	365.8	384.4
60°	291.4	306.9	327.8	347.2
62.5°	259.6	277.4	293.7	306.1
65°	228.6	244.1	256.5	267.3
67.5°	202.3	211.6	220.9	232.5
70°	170.5	178.2	189.1	197.6
72.5°	143.4	149.6	155.0	165.1
75°	116.2	121.7	124.8	134.1
77.5°	89.9	95.3	97.6	103.1
80°	69.0	69.7	72.8	77.5
82.5°	47.3	48.8	49.6	53.5
85°	27.1	31.0	30.2	31.8
87.5°	11.6	12.4	13.9	15.5
90°	7.8	6.0	4.1	2.3
92.5°	10.3	10.6	11.0	11.3
95°	24.4	30.1	35.8	41.5
97.5°	90.4	86.7	83.0	79.3
100°	132.9	129.8	126.8	123.8
102.5°	179.7	177.7	175.7	173.7
105°	230.3	229.3	228.3	227.3
107.5°	277.9	277.4	276.9	276.4
110°	327.7	327.2	326.7	326.2

TEST NUMBER: P1033031

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	377.6	376.5	375.5	374.5
115°	425.9	425.4	424.9	424.4
117.5°	470.9	470.2	469.6	468.9
120°	516.2	515.5	514.9	514.2
122.5°	557.5	557.2	556.8	556.5
125°	598.5	597.8	597.2	596.5
127.5°	635.5	635.4	635.2	635.0
130°	672.5	672.4	672.2	672.0
132.5°	707.0	706.7	706.3	706.0
135°	739.5	739.6	739.8	740.0
137.5°	770.2	770.2	770.2	770.2
140°	800.6	800.3	799.9	799.6
142.5°	828.1	827.4	826.8	826.1
145°	854.8	854.3	853.8	853.3
147.5°	877.4	876.4	875.4	874.4
150°	899.8	899.1	898.5	897.8
152.5°	918.9	918.4	917.9	917.4
155°	936.1	935.9	935.8	935.6
157.5°	951.4	951.4	951.4	951.4
160°	963.5	964.0	964.5	965.0
162.5°	975.1	975.8	976.4	977.1
165°	984.4	985.2	986.1	986.9
167.5°	992.7	993.5	994.4	995.2
170°	999.0	1000.0	1001.0	1002.0
172.5°	1003.5	1004.5	1005.5	1006.5
175°	1006.5	1007.6	1008.6	1009.6
177.5°	1008.3	1009.4	1010.6	1011.8
180°	1009.6	1009.6	1009.6	1009.6

(END OF REPORT)