

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033522

Luminaire Tested: S124DIW-B350D770UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033522
REPORT IS A COMBINATION OF REPORTS P997597 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D770UB40-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4576.0 lumens
Efficiency: N/A
Efficacy: 126.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033522

CATALOG NUMBER: S124DIW-B350D770UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033522

CATALOG NUMBER: S124DIW-B350D770UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33
2	85	78	72	67	77	71	65	61	56	53	50	43	41	39	31	29	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4668	4530	4535
10°	4628	4404	4373
15°	4562	4255	4191
20°	4477	4092	4001
25°	4382	3922	3797
30°	4267	3737	3573
35°	4147	3548	3357
40°	4023	3344	3127
45°	3893	3141	2912
50°	3749	2943	2674
55°	3592	2711	2437
60°	3431	2458	2191
65°	3249	2197	1913
70°	3036	1881	1616
75°	2720	1517	1294
80°	2320	1097	910
85°	1797	610	490

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3893 cd/sqm

TEST NUMBER: P1033522

CATALOG NUMBER: S124DIW-B350D770UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	1.2
10°-20°	151.9	3.3
20°-30°	223.5	4.9
30°-40°	259.8	5.7
40°-50°	259.8	5.7
50°-60°	227.2	5.0
60°-70°	168.7	3.7
70°-80°	95.7	2.1
80°-90°	29.5	0.6
90°-100°	33.3	0.7
100°-110°	219.4	4.8
110°-120°	419.0	9.2
120°-130°	531.9	11.6
130°-140°	569.0	12.4
140°-150°	532.1	11.6
150°-160°	429.1	9.4
160°-170°	276.7	6.0
170°-180°	95.4	2.1
0°-30°	429.3	9.4
0°-40°	689.1	15.1
0°-60°	1176.2	25.7
0°-90°	1470.1	32.1
90°-120°	671.8	14.7
90°-150°	2304.8	50.4
90°-180°	3106.0	67.9
0°-180°	4576.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	572	572	572	572	572	
5°	572	570	565	570	569	54
15°	544	542	535	538	537	153
25°	493	490	483	484	482	227
35°	424	421	414	411	409	265
45°	346	343	336	330	329	267
55°	262	260	254	248	246	234
65°	177	175	170	166	164	176
75°	94	92	90	88	88	100
85°	25	25	24	24	23	27
90°	2	10	16	21	22	4
95°	41	16	16	21	22	51
105°	226	230	234	241	214	237
115°	422	424	423	425	425	415
125°	593	596	595	597	598	530
135°	736	735	738	740	741	567
145°	848	851	851	851	853	530
155°	930	931	929	932	929	429
165°	981	978	978	984	977	277
175°	1004	999	1000	1007	998	96
180°	1004	1004	1004	1004	1004	

TEST NUMBER: P1033522

CATALOG NUMBER: S124DIW-B350D770UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	571.9	571.9	571.9	571.9	571.9
2.5°	573.8	572.4	567.4	571.9	571.5
5°	571.5	569.7	564.6	569.7	568.7
7.5°	567.4	565.5	560.0	564.2	563.7
10°	561.4	559.6	553.6	557.3	556.4
12.5°	553.6	551.8	545.4	549.5	548.1
15°	544.0	542.2	535.3	538.0	536.7
17.5°	533.0	530.7	524.3	526.1	525.2
20°	520.6	518.3	511.4	512.8	511.9
22.5°	507.3	504.1	497.2	500.0	498.2
25°	492.7	489.5	483.0	483.5	481.7
27.5°	476.2	473.0	467.0	466.1	463.8
30°	459.7	456.0	450.0	448.2	445.9
32.5°	442.2	439.0	432.6	430.3	428.0
35°	423.9	420.7	414.3	411.1	408.8
37.5°	404.7	401.9	395.0	391.8	388.6
40°	385.9	382.2	375.3	370.8	368.5
42.5°	365.7	363.9	356.1	350.6	349.2
45°	346.0	342.8	335.5	330.4	329.0
47.5°	325.4	323.1	316.2	310.7	307.1
50°	304.3	302.5	296.1	289.6	286.9
52.5°	283.7	281.4	274.5	269.0	265.3
55°	261.7	260.3	253.9	248.4	245.6
57.5°	241.1	239.7	233.3	227.8	225.0
60°	219.5	217.2	211.3	207.1	204.9
62.5°	198.4	196.6	190.2	186.5	184.2
65°	177.4	175.1	170.5	165.9	163.6
67.5°	155.8	154.0	149.4	144.8	144.4
70°	136.1	132.9	129.2	125.6	124.2
72.5°	115.0	111.8	109.1	106.3	104.9
75°	94.4	92.1	89.8	88.0	87.5
77.5°	74.2	73.3	71.0	70.6	69.2
80°	56.4	55.0	54.1	53.2	52.7
82.5°	39.0	38.5	38.5	38.0	37.6
85°	24.7	24.7	23.8	23.8	23.4
87.5°	11.9	11.5	11.0	11.0	11.0
90°	2.3	10.5	16.5	21.0	22.5
92.5°	11.3	9.8	15.8	20.3	20.3
95°	41.3	15.8	16.5	21.0	21.8
97.5°	78.8	95.3	16.5	20.3	21.0
100°	123.1	136.6	33.0	20.3	21.0
102.5°	172.7	181.7	190.7	21.8	21.8
105°	226.0	230.5	234.2	241.0	214.0
107.5°	274.8	277.0	282.3	286.0	289.0
110°	324.3	326.6	331.1	332.6	334.8

TEST NUMBER: P1033522

CATALOG NUMBER: S124DIW-B350D770UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.4	376.9	378.4	377.6	380.6
115°	421.9	424.2	423.4	424.9	424.9
117.5°	466.2	469.2	471.5	470.7	470.7
120°	511.3	514.3	513.5	515.0	513.5
122.5°	553.3	554.8	556.3	557.0	555.5
125°	593.1	596.1	594.6	596.8	597.6
127.5°	631.4	632.1	635.9	635.1	634.4
130°	668.2	668.9	671.2	671.9	671.9
132.5°	701.9	703.4	706.4	707.2	706.4
135°	735.7	735.0	738.0	739.5	741.0
137.5°	765.8	765.8	769.5	771.0	770.3
140°	795.0	796.5	798.0	800.3	801.0
142.5°	821.3	824.3	825.1	826.6	826.6
145°	848.3	850.6	850.6	851.3	852.8
147.5°	869.4	873.9	873.1	873.9	874.6
150°	892.6	895.6	894.9	894.9	895.6
152.5°	912.2	914.4	912.9	914.4	913.7
155°	930.2	930.9	928.7	931.7	929.4
157.5°	945.9	945.9	942.9	946.7	942.9
160°	959.4	957.2	956.4	960.9	956.4
162.5°	971.5	968.5	967.7	972.2	967.0
165°	981.2	977.5	977.5	983.5	976.7
167.5°	989.5	985.7	985.0	991.7	984.2
170°	996.2	991.7	992.5	998.5	991.0
172.5°	1000.7	996.2	997.0	1003.0	994.7
175°	1003.7	999.2	1000.0	1006.7	997.7
177.5°	1006.0	1000.7	1002.2	1008.2	999.2
180°	1003.7	1003.7	1003.7	1003.7	1003.7

(END OF REPORT)