

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033035

Luminaire Tested: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033035
REPORT IS A COMBINATION OF REPORTS P1000670 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5417.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033035

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1033035

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43		
1	96	92	88	85	88	84	81	78	70	68	66	56	55	54	44	43	42	37		
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36	31		
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	26		
4	74	63	55	50	67	58	51	46	48	43	39	40	36	33	31	29	27	23		
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23	20		
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18		
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	23	21	18	16		
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17	14		
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15	13		
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8181	8181	8181
5°	8182	7938	7938
10°	8112	7687	7595
15°	8000	7375	7191
20°	7854	7020	6730
25°	7672	6636	6280
30°	7493	6245	5774
35°	7298	5848	5280
40°	7064	5421	4772
45°	6845	4998	4269
50°	6596	4535	3759
55°	6327	4060	3232
60°	6028	3557	2711
65°	5739	2979	2210
70°	5330	2371	1689
75°	4804	1726	1181
80°	4014	1059	850
85°	3020	610	467

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6845 cd/sqm

TEST NUMBER: P1033035

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.3	1.7
10°-20°	263.0	4.9
20°-30°	379.7	7.0
30°-40°	430.4	7.9
40°-50°	415.5	7.7
50°-60°	345.5	6.4
60°-70°	238.4	4.4
70°-80°	120.5	2.2
80°-90°	32.7	0.6
90°-100°	33.2	0.6
100°-110°	218.8	4.0
110°-120°	417.8	7.7
120°-130°	530.4	9.8
130°-140°	567.4	10.5
140°-150°	530.5	9.8
150°-160°	427.8	7.9
160°-170°	275.9	5.1
170°-180°	95.1	1.8
0°-30°	737.1	13.6
0°-40°	1167.5	21.6
0°-60°	1928.5	35.6
0°-90°	2320.1	42.8
90°-120°	669.8	12.4
90°-150°	2298.1	42.4
90°-180°	3097.0	57.2
0°-180°	5417.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1003	1003	1003	1003	1003	
5°	1002	999	989	997	996	95
15°	954	947	928	926	921	269
25°	863	849	817	804	797	397
35°	746	721	683	657	643	466
45°	608	580	534	496	482	469
55°	461	430	380	340	326	412
65°	313	280	231	198	189	309
75°	167	138	102	84	80	176
85°	42	26	24	22	22	46
90°	2	10	16	21	22	5
95°	41	16	16	21	22	51
105°	225	230	234	240	213	236
115°	421	423	422	424	424	414
125°	591	594	593	595	596	528
135°	734	733	736	737	739	565
145°	846	848	848	849	850	529
155°	928	928	926	929	927	428
165°	978	975	975	981	974	276
175°	1001	996	997	1004	995	95
180°	1001	1001	1001	1001	1001	

TEST NUMBER: P1033035

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1003.2	1003.2	1003.2	1003.2	1003.2
2.5°	1006.3	1003.2	994.8	1003.2	1002.4
5°	1001.7	998.6	989.4	997.1	995.5
7.5°	994.8	991.7	980.2	985.5	983.2
10°	984.0	980.2	966.3	969.4	966.3
12.5°	970.2	965.6	948.7	950.2	945.6
15°	954.0	947.1	927.9	926.4	921.0
17.5°	935.6	925.6	903.3	899.5	891.8
20°	913.3	903.3	877.2	871.1	861.1
22.5°	888.7	877.2	848.8	838.8	831.1
25°	862.6	848.8	817.3	804.2	796.6
27.5°	835.7	818.8	785.8	770.5	759.7
30°	807.3	788.1	752.0	732.8	720.5
32.5°	777.4	755.1	717.4	694.4	682.9
35°	745.9	721.3	682.9	656.8	642.9
37.5°	712.8	687.5	645.2	616.8	603.0
40°	677.5	652.2	608.4	576.1	562.3
42.5°	643.7	616.8	570.7	537.7	523.1
45°	608.4	580.0	533.9	496.2	482.4
47.5°	572.3	543.1	495.5	456.3	440.9
50°	535.4	505.4	456.3	417.9	403.3
52.5°	497.8	468.6	417.9	378.7	363.3
55°	460.9	430.2	380.2	340.3	325.7
57.5°	424.8	392.5	343.4	302.6	291.9
60°	385.6	354.9	305.7	265.8	253.5
62.5°	350.3	318.0	267.3	231.2	222.0
65°	313.4	280.4	231.2	198.2	189.0
67.5°	275.0	243.5	197.4	168.2	157.5
70°	238.9	206.6	162.8	137.5	129.8
72.5°	200.5	172.1	131.4	110.6	103.7
75°	166.7	138.3	102.2	84.5	79.9
77.5°	131.4	106.8	76.0	63.8	62.2
80°	97.6	75.3	52.2	49.9	49.2
82.5°	68.4	48.4	37.6	36.1	35.3
85°	41.5	26.1	23.8	22.3	22.3
87.5°	17.7	11.5	10.8	10.0	10.8
90°	2.2	10.5	16.5	21.0	22.5
92.5°	11.2	9.7	15.7	20.2	20.2
95°	41.2	15.7	16.5	21.0	21.7
97.5°	78.6	95.1	16.5	20.2	21.0
100°	122.8	136.2	32.9	20.2	21.0
102.5°	172.2	181.2	190.1	21.7	21.7
105°	225.3	229.8	233.6	240.3	213.3
107.5°	274.0	276.2	281.5	285.2	288.2
110°	323.4	325.6	330.1	331.6	333.9

TEST NUMBER: P1033035

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	375.8	377.3	376.5	379.5
115°	420.7	422.9	422.2	423.7	423.7
117.5°	464.9	467.9	470.1	469.4	469.4
120°	509.8	512.8	512.0	513.5	512.0
122.5°	551.7	553.2	554.7	555.4	553.9
125°	591.4	594.4	592.9	595.1	595.9
127.5°	629.5	630.3	634.0	633.3	632.5
130°	666.2	667.0	669.2	670.0	670.0
132.5°	699.9	701.4	704.4	705.2	704.4
135°	733.6	732.8	735.8	737.3	738.8
137.5°	763.5	763.5	767.3	768.8	768.0
140°	792.7	794.2	795.7	798.0	798.7
142.5°	818.9	821.9	822.7	824.2	824.2
145°	845.9	848.1	848.1	848.9	850.4
147.5°	866.8	871.3	870.6	871.3	872.1
150°	890.0	893.0	892.3	892.3	893.0
152.5°	909.5	911.8	910.3	911.8	911.0
155°	927.5	928.2	926.0	929.0	926.7
157.5°	943.2	943.2	940.2	943.9	940.2
160°	956.7	954.4	953.7	958.2	953.7
162.5°	968.6	965.7	964.9	969.4	964.2
165°	978.4	974.6	974.6	980.6	973.9
167.5°	986.6	982.9	982.1	988.9	981.4
170°	993.3	988.9	989.6	995.6	988.1
172.5°	997.8	993.3	994.1	1000.1	991.9
175°	1000.8	996.3	997.1	1003.8	994.8
177.5°	1003.1	997.8	999.3	1005.3	996.3
180°	1000.8	1000.8	1000.8	1000.8	1000.8

(END OF REPORT)