

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033036

Luminaire Tested: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033036
REPORT IS A COMBINATION OF REPORTS P1000671 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5465.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033036

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033036

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	68	66	56	55	54	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31
4	74	63	55	50	67	58	51	46	48	43	39	40	36	33	31	29	27
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	28	26	23
6	62	50	43	37	57	47	40	34	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	35	30	26	29	25	22	23	21	18
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	25	45	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8255	8255	8255
5°	8255	8009	8010
10°	8185	7757	7665
15°	8073	7442	7257
20°	7925	7084	6791
25°	7741	6696	6337
30°	7561	6301	5826
35°	7363	5901	5328
40°	7127	5470	4815
45°	6907	5043	4308
50°	6655	4576	3792
55°	6384	4098	3261
60°	6082	3589	2736
65°	5791	3006	2230
70°	5379	2393	1704
75°	4847	1741	1192
80°	4047	1069	857
85°	3049	615	472

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6907 cd/sqm

TEST NUMBER: P1033036

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.2	1.7
10°-20°	265.4	4.9
20°-30°	383.2	7.0
30°-40°	434.3	7.9
40°-50°	419.3	7.7
50°-60°	348.6	6.4
60°-70°	240.6	4.4
70°-80°	121.6	2.2
80°-90°	33.0	0.6
90°-100°	33.5	0.6
100°-110°	220.7	4.0
110°-120°	421.4	7.7
120°-130°	535.0	9.8
130°-140°	572.3	10.5
140°-150°	535.2	9.8
150°-160°	431.6	7.9
160°-170°	278.3	5.1
170°-180°	95.9	1.8
0°-30°	743.8	13.6
0°-40°	1178.0	21.6
0°-60°	1945.9	35.6
0°-90°	2341.1	42.8
90°-120°	675.6	12.4
90°-150°	2318.1	42.4
90°-180°	3124.0	57.2
0°-180°	5465.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1012	1012	1012	1012	1012	
5°	1011	1008	998	1006	1004	96
15°	963	956	936	935	929	271
25°	870	856	825	812	804	401
35°	753	728	689	663	649	470
45°	614	585	539	501	487	473
55°	465	434	384	343	329	416
65°	316	283	233	200	191	312
75°	168	140	103	85	81	177
85°	42	26	24	22	22	46
90°	2	11	17	21	23	5
95°	42	16	17	21	22	51
105°	227	232	236	242	215	238
115°	424	427	426	427	427	418
125°	596	600	598	600	601	533
135°	740	739	742	744	745	570
145°	853	856	856	856	858	533
155°	936	936	934	937	935	431
165°	987	983	983	989	982	279
175°	1010	1005	1006	1013	1004	96
180°	1010	1010	1010	1010	1010	

TEST NUMBER: P1033036

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1012.3	1012.3	1012.3	1012.3	1012.3
2.5°	1015.4	1012.3	1003.8	1012.3	1011.5
5°	1010.7	1007.6	998.3	1006.1	1004.5
7.5°	1003.8	1000.7	989.0	994.5	992.1
10°	992.9	989.0	975.1	978.2	975.1
12.5°	979.0	974.3	957.3	958.8	954.2
15°	962.7	955.7	936.3	934.8	929.4
17.5°	944.1	934.0	911.5	907.6	899.9
20°	921.6	911.5	885.2	879.0	868.9
22.5°	896.8	885.2	856.5	846.4	838.7
25°	870.4	856.5	824.7	811.5	803.8
27.5°	843.3	826.3	792.9	777.4	766.6
30°	814.6	795.3	758.8	739.5	727.0
32.5°	784.4	761.9	723.9	700.7	689.1
35°	752.6	727.8	689.1	662.7	648.8
37.5°	719.3	693.7	651.1	622.4	608.5
40°	683.6	658.1	613.9	581.3	567.4
42.5°	649.5	622.4	575.9	542.6	527.8
45°	613.9	585.2	538.7	500.7	486.8
47.5°	577.5	548.0	499.9	460.4	444.9
50°	540.2	510.0	460.4	421.7	406.9
52.5°	502.3	472.8	421.7	382.1	366.6
55°	465.1	434.1	383.7	343.4	328.6
57.5°	428.6	396.1	346.5	305.4	294.5
60°	389.1	358.1	308.5	268.2	255.8
62.5°	353.4	320.9	269.7	233.3	224.0
65°	316.2	282.9	233.3	200.0	190.7
67.5°	277.5	245.7	199.2	169.7	158.9
70°	241.1	208.5	164.3	138.7	131.0
72.5°	202.3	173.6	132.5	111.6	104.6
75°	168.2	139.5	103.1	85.3	80.6
77.5°	132.5	107.7	76.7	64.3	62.8
80°	98.4	76.0	52.7	50.4	49.6
82.5°	69.0	48.8	38.0	36.4	35.7
85°	41.9	26.4	24.0	22.5	22.5
87.5°	17.8	11.6	10.9	10.1	10.9
90°	2.3	10.6	16.6	21.1	22.7
92.5°	11.3	9.8	15.9	20.4	20.4
95°	41.5	15.9	16.6	21.1	21.9
97.5°	79.3	95.9	16.6	20.4	21.1
100°	123.8	137.4	33.2	20.4	21.1
102.5°	173.7	182.7	191.8	21.9	21.9
105°	227.3	231.8	235.6	242.4	215.2
107.5°	276.4	278.6	283.9	287.7	290.7
110°	326.2	328.5	333.0	334.5	336.8



TEST NUMBER: P1033036

CATALOG NUMBER: S124RDIW-B575D770UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.5	379.1	380.6	379.8	382.8
115°	424.4	426.6	425.9	427.4	427.4
117.5°	468.9	471.9	474.2	473.4	473.4
120°	514.2	517.2	516.5	518.0	516.5
122.5°	556.5	558.0	559.5	560.3	558.8
125°	596.5	599.5	598.0	600.3	601.1
127.5°	635.0	635.8	639.6	638.8	638.1
130°	672.0	672.8	675.0	675.8	675.8
132.5°	706.0	707.5	710.5	711.3	710.5
135°	740.0	739.2	742.3	743.8	745.3
137.5°	770.2	770.2	774.0	775.5	774.7
140°	799.6	801.1	802.7	804.9	805.7
142.5°	826.1	829.1	829.8	831.4	831.4
145°	853.3	855.5	855.5	856.3	857.8
147.5°	874.4	878.9	878.2	878.9	879.7
150°	897.8	900.8	900.1	900.1	900.8
152.5°	917.4	919.7	918.2	919.7	918.9
155°	935.6	936.3	934.0	937.1	934.8
157.5°	951.4	951.4	948.4	952.2	948.4
160°	965.0	962.7	962.0	966.5	962.0
162.5°	977.1	974.1	973.3	977.8	972.6
165°	986.9	983.1	983.1	989.2	982.4
167.5°	995.2	991.4	990.7	997.5	989.9
170°	1002.0	997.5	998.2	1004.3	996.7
172.5°	1006.5	1002.0	1002.8	1008.8	1000.5
175°	1009.6	1005.0	1005.8	1012.6	1003.5
177.5°	1011.8	1006.5	1008.0	1014.1	1005.0
180°	1009.6	1009.6	1009.6	1009.6	1009.6

(END OF REPORT)