

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033046

Luminaire Tested: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033046
REPORT IS A COMBINATION OF REPORTS P1000715 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7481.0 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033046

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1033046

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1033046

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	1.8
10°-20°	366.2	4.9
20°-30°	528.7	7.1
30°-40°	599.1	8.0
40°-50°	578.5	7.7
50°-60°	480.9	6.4
60°-70°	331.9	4.4
70°-80°	167.7	2.2
80°-90°	45.4	0.6
90°-100°	45.6	0.6
100°-110°	300.3	4.0
110°-120°	573.5	7.7
120°-130°	728.0	9.7
130°-140°	778.8	10.4
140°-150°	728.3	9.7
150°-160°	587.3	7.9
160°-170°	378.8	5.1
170°-180°	130.5	1.7
0°-30°	1026.2	13.7
0°-40°	1625.3	21.7
0°-60°	2684.7	35.9
0°-90°	3229.8	43.2
90°-120°	919.4	12.3
90°-150°	3154.6	42.2
90°-180°	4251.0	56.8
0°-180°	7481.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	3	14	23	29	31	6
95°	56	22	23	29	30	70
105°	309	316	321	330	293	324
115°	578	581	580	582	582	568
125°	812	816	814	817	818	725
135°	1007	1006	1010	1012	1014	776
145°	1161	1164	1164	1165	1167	726
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1346	1337	380
175°	1374	1368	1369	1378	1366	131
180°	1374	1374	1374	1374	1374	

TEST NUMBER: P1033046

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	3.1	14.4	22.6	28.8	30.8
92.5°	15.4	13.4	21.6	27.7	27.7
95°	56.5	21.6	22.6	28.8	29.8
97.5°	107.9	130.5	22.6	27.7	28.8
100°	168.5	187.0	45.2	27.7	28.8
102.5°	236.3	248.7	261.0	29.8	29.8
105°	309.3	315.5	320.6	329.8	292.9
107.5°	376.1	379.2	386.4	391.5	395.6
110°	443.9	447.0	453.2	455.2	458.3

TEST NUMBER: P1033046

CATALOG NUMBER: S124RDIW-B795D1050UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	509.7	515.8	517.9	516.9	521.0
115°	577.5	580.6	579.5	581.6	581.6
117.5°	638.1	642.2	645.3	644.3	644.3
120°	699.8	703.9	702.8	704.9	702.8
122.5°	757.3	759.4	761.4	762.4	760.4
125°	811.8	815.9	813.8	816.9	817.9
127.5°	864.2	865.2	870.3	869.3	868.3
130°	914.5	915.6	918.6	919.7	919.7
132.5°	960.8	962.8	966.9	968.0	966.9
135°	1007.0	1006.0	1010.1	1012.1	1014.2
137.5°	1048.1	1048.1	1053.2	1055.3	1054.3
140°	1088.2	1090.2	1092.3	1095.4	1096.4
142.5°	1124.1	1128.3	1129.3	1131.3	1131.3
145°	1161.1	1164.2	1164.2	1165.3	1167.3
147.5°	1189.9	1196.1	1195.1	1196.1	1197.1
150°	1221.8	1225.9	1224.8	1224.8	1225.9
152.5°	1248.5	1251.6	1249.5	1251.6	1250.5
155°	1273.1	1274.2	1271.1	1275.2	1272.1
157.5°	1294.7	1294.7	1290.6	1295.8	1290.6
160°	1313.2	1310.1	1309.1	1315.3	1309.1
162.5°	1329.7	1325.6	1324.5	1330.7	1323.5
165°	1343.0	1337.9	1337.9	1346.1	1336.9
167.5°	1354.3	1349.2	1348.2	1357.4	1347.1
170°	1363.6	1357.4	1358.4	1366.7	1356.4
172.5°	1369.7	1363.6	1364.6	1372.8	1361.5
175°	1373.8	1367.7	1368.7	1378.0	1365.6
177.5°	1376.9	1369.7	1371.8	1380.0	1367.7
180°	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)