

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033553

Luminaire Tested: S124DIW-B575D1050UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033553
REPORT IS A COMBINATION OF REPORTS P997664 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1050UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6136.0 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033553

CATALOG NUMBER: S124DIW-B575D1050UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033553

CATALOG NUMBER: S124DIW-B575D1050UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	40
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	40	40	34
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	28
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	24
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	25	25	21
5	67	55	47	41	60	50	43	38	42	37	32	34	30	27	26	23	21	21	21	18
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	16
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	14
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13	13	13	11
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7848	7615	7625
10°	7781	7404	7353
15°	7669	7153	7045
20°	7527	6880	6726
25°	7367	6594	6384
30°	7173	6283	6008
35°	6973	5965	5644
40°	6763	5623	5258
45°	6545	5280	4896
50°	6302	4947	4495
55°	6038	4558	4098
60°	5770	4133	3683
65°	5461	3693	3217
70°	5104	3164	2717
75°	4573	2550	2176
80°	3899	1844	1530
85°	3027	1028	824

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6545 cd/sqm

TEST NUMBER: P1033553

CATALOG NUMBER: S124DIW-B575D1050UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.5
10°-20°	255.3	4.2
20°-30°	375.8	6.1
30°-40°	436.8	7.1
40°-50°	436.8	7.1
50°-60°	382.0	6.2
60°-70°	283.6	4.6
70°-80°	160.9	2.6
80°-90°	48.9	0.8
90°-100°	86.1	1.4
100°-110°	257.9	4.2
110°-120°	438.1	7.1
120°-130°	577.8	9.4
130°-140°	649.0	10.6
140°-150°	637.9	10.4
150°-160°	536.5	8.7
160°-170°	356.9	5.8
170°-180°	125.0	2.0
0°-30°	721.7	11.8
0°-40°	1158.6	18.9
0°-60°	1977.4	32.2
0°-90°	2470.8	40.3
90°-120°	782.1	12.7
90°-150°	2646.7	43.1
90°-180°	3665.0	59.7
0°-180°	6136.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	45
90°	3	14	22	29	31	7
95°	61	70	78	81	81	66
105°	238	239	243	246	249	252
115°	445	445	443	442	441	439
125°	649	649	648	646	644	578
135°	837	843	843	841	838	647
145°	1016	1021	1022	1021	1018	636
155°	1165	1165	1164	1168	1164	536
165°	1268	1265	1263	1269	1265	357
175°	1319	1314	1313	1320	1313	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1033553

CATALOG NUMBER: S124DIW-B575D1050UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	3.1	14.3	22.5	28.6	30.6
92.5°	26.6	39.8	45.0	48.0	49.0
95°	61.3	70.5	77.6	80.7	80.7
97.5°	98.1	106.2	114.4	118.5	118.5
100°	143.0	147.1	156.3	158.4	158.4
102.5°	190.0	191.0	199.2	202.3	203.3
105°	238.0	239.1	243.1	246.2	249.3
107.5°	288.1	289.1	290.1	294.2	293.2
110°	339.2	341.2	340.2	338.2	341.2

TEST NUMBER: P1033553

CATALOG NUMBER: S124DIW-B575D1050UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	392.3	390.3	390.3	390.3
115°	445.4	445.4	443.4	442.4	441.3
117.5°	495.5	495.5	494.5	491.4	488.3
120°	545.5	549.6	546.6	541.5	543.5
122.5°	597.6	598.7	597.6	594.6	589.5
125°	648.7	648.7	647.7	645.7	643.6
127.5°	694.7	697.8	695.7	693.7	692.7
130°	743.7	746.8	746.8	744.8	740.7
132.5°	793.8	795.8	794.8	792.8	791.8
135°	836.7	842.8	842.8	840.8	837.7
137.5°	884.7	887.8	889.8	886.8	887.8
140°	932.7	934.8	934.8	933.8	932.7
142.5°	976.7	978.7	977.7	977.7	977.7
145°	1016.5	1020.6	1021.6	1020.6	1017.5
147.5°	1057.4	1062.5	1061.5	1060.4	1059.4
150°	1094.2	1098.2	1098.2	1098.2	1097.2
152.5°	1128.9	1130.9	1132.0	1135.0	1132.0
155°	1164.7	1164.7	1163.6	1167.7	1163.6
157.5°	1195.3	1193.3	1193.3	1196.3	1193.3
160°	1221.9	1220.8	1219.8	1222.9	1217.8
162.5°	1246.4	1243.3	1242.3	1248.4	1243.3
165°	1267.8	1264.8	1262.7	1268.9	1264.8
167.5°	1285.2	1281.1	1281.1	1287.2	1281.1
170°	1299.5	1294.4	1295.4	1301.5	1294.4
172.5°	1309.7	1305.6	1305.6	1312.8	1305.6
175°	1318.9	1313.8	1312.8	1319.9	1312.8
177.5°	1323.0	1317.9	1317.9	1325.0	1316.9
180°	1321.0	1321.0	1321.0	1321.0	1321.0

(END OF REPORT)