

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033675

Luminaire Tested: S124DIW-B575D770UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033675
REPORT IS A COMBINATION OF REPORTS P997936 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D770UB50-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5393.0 lumens
Efficiency: N/A
Efficacy: 114.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033675

CATALOG NUMBER: S124DIW-B575D770UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033675

CATALOG NUMBER: S124DIW-B575D770UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			44
1	96	92	88	85	88	85	81	78	70	68	66	57	55	54	45	44	43			37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	40	38	36			31
3	80	71	63	58	73	65	59	54	54	50	46	44	41	38	35	33	31			26
4	73	63	55	49	67	58	51	45	48	43	39	39	36	33	31	29	26			23
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	28	25	23			20
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	26	23	20			17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18			15
8	53	41	33	28	48	38	31	26	32	27	23	27	22	19	21	18	16			14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15			12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1033675

CATALOG NUMBER: S124DIW-B575D770UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.6
10°-20°	247.0	4.6
20°-30°	363.4	6.7
30°-40°	422.5	7.8
40°-50°	422.5	7.8
50°-60°	369.5	6.9
60°-70°	274.3	5.1
70°-80°	155.6	2.9
80°-90°	46.6	0.9
90°-100°	32.2	0.6
100°-110°	212.2	3.9
110°-120°	405.3	7.5
120°-130°	514.5	9.5
130°-140°	550.4	10.2
140°-150°	514.6	9.5
150°-160°	415.0	7.7
160°-170°	267.6	5.0
170°-180°	92.2	1.7
0°-30°	698.1	12.9
0°-40°	1120.5	20.8
0°-60°	1912.5	35.5
0°-90°	2389.0	44.3
90°-120°	649.7	12.0
90°-150°	2229.1	41.3
90°-180°	3004.0	55.7
0°-180°	5393.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	2	10	16	20	22	5
95°	40	15	16	20	21	49
105°	219	223	226	233	207	229
115°	408	410	410	411	411	402
125°	574	576	575	577	578	512
135°	712	711	714	715	717	548
145°	820	823	823	823	825	513
155°	900	900	898	901	899	415
165°	949	945	945	951	945	268
175°	971	966	967	974	965	92
180°	971	971	971	971	971	

TEST NUMBER: P1033675

CATALOG NUMBER: S124DIW-B575D770UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	2.2	10.2	16.0	20.3	21.8
92.5°	10.9	9.4	15.2	19.6	19.6
95°	39.9	15.2	16.0	20.3	21.1
97.5°	76.2	92.2	16.0	19.6	20.3
100°	119.1	132.2	31.9	19.6	20.3
102.5°	167.0	175.7	184.4	21.1	21.1
105°	218.6	222.9	226.5	233.1	206.9
107.5°	265.8	267.9	273.0	276.6	279.5
110°	313.7	315.9	320.2	321.7	323.8

TEST NUMBER: P1033675

CATALOG NUMBER: S124DIW-B575D770UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	360.1	364.5	366.0	365.2	368.1
115°	408.1	410.2	409.5	411.0	411.0
117.5°	450.9	453.8	456.0	455.3	455.3
120°	494.5	497.4	496.7	498.1	496.7
122.5°	535.1	536.6	538.0	538.8	537.3
125°	573.6	576.5	575.1	577.3	578.0
127.5°	610.7	611.4	615.0	614.3	613.6
130°	646.2	647.0	649.1	649.9	649.9
132.5°	678.9	680.4	683.3	684.0	683.3
135°	711.6	710.9	713.8	715.2	716.7
137.5°	740.6	740.6	744.3	745.7	745.0
140°	768.9	770.4	771.8	774.0	774.8
142.5°	794.4	797.3	798.0	799.4	799.4
145°	820.5	822.7	822.7	823.4	824.9
147.5°	840.8	845.2	844.5	845.2	845.9
150°	863.3	866.2	865.5	865.5	866.2
152.5°	882.2	884.4	882.9	884.4	883.7
155°	899.6	900.4	898.2	901.1	898.9
157.5°	914.9	914.9	912.0	915.6	912.0
160°	928.0	925.8	925.1	929.4	925.1
162.5°	939.6	936.7	935.9	940.3	935.2
165°	949.0	945.4	945.4	951.2	944.7
167.5°	957.0	953.4	952.6	959.2	951.9
170°	963.5	959.2	959.9	965.7	958.5
172.5°	967.9	963.5	964.3	970.1	962.1
175°	970.8	966.4	967.2	973.7	965.0
177.5°	973.0	967.9	969.3	975.2	966.4
180°	970.8	970.8	970.8	970.8	970.8

(END OF REPORT)