

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033763

Luminaire Tested: S124DIW-B795D1560UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033763
REPORT IS A COMBINATION OF REPORTS P998135 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1560UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8575.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033763

CATALOG NUMBER: S124DIW-B795D1560UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033763

CATALOG NUMBER: S124DIW-B795D1560UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	38		
1	95	91	87	84	86	83	79	77	67	65	63	53	52	50	40	39	38	32		
2	87	79	73	68	78	72	67	63	59	55	52	47	44	42	35	34	32	27		
3	79	70	63	57	71	64	57	52	52	47	44	41	38	35	31	29	27	23		
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24	20		
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17		
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15		
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16	13		
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14	12		
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11		
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1033763

CATALOG NUMBER: S124DIW-B795D1560UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	1.4
10°-20°	340.7	4.0
20°-30°	501.4	5.8
30°-40°	582.8	6.8
40°-50°	582.8	6.8
50°-60°	509.7	5.9
60°-70°	378.4	4.4
70°-80°	214.7	2.5
80°-90°	65.6	0.8
90°-100°	124.0	1.4
100°-110°	371.4	4.3
110°-120°	630.9	7.4
120°-130°	832.1	9.7
130°-140°	934.5	10.9
140°-150°	918.5	10.7
150°-160°	772.5	9.0
160°-170°	514.0	6.0
170°-180°	180.0	2.1
0°-30°	963.0	11.2
0°-40°	1545.9	18.0
0°-60°	2638.4	30.8
0°-90°	3297.1	38.4
90°-120°	1126.3	13.1
90°-150°	3811.4	44.4
90°-180°	5278.0	61.6
0°-180°	8575.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	4	21	32	41	44	10
95°	88	102	112	116	116	96
105°	343	344	350	354	359	363
115°	641	641	638	637	636	633
125°	934	934	933	930	927	833
135°	1205	1214	1214	1211	1206	932
145°	1464	1470	1471	1470	1465	916
155°	1677	1677	1676	1682	1676	772
165°	1826	1821	1818	1827	1821	515
175°	1899	1892	1890	1901	1890	180
180°	1902	1902	1902	1902	1902	

TEST NUMBER: P1033763

CATALOG NUMBER: S124DIW-B795D1560UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	4.4	20.6	32.4	41.2	44.1
92.5°	38.3	57.4	64.7	69.1	70.6
95°	88.3	101.5	111.8	116.2	116.2
97.5°	141.2	153.0	164.8	170.7	170.7
100°	206.0	211.8	225.1	228.0	228.0
102.5°	273.6	275.1	286.9	291.3	292.8
105°	342.8	344.3	350.1	354.5	359.0
107.5°	414.9	416.3	417.8	423.7	422.2
110°	488.4	491.4	489.9	487.0	491.4

TEST NUMBER: P1033763

CATALOG NUMBER: S124DIW-B795D1560UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	564.9	564.9	562.0	562.0	562.0
115°	641.4	641.4	638.5	637.0	635.5
117.5°	713.5	713.5	712.0	707.6	703.2
120°	785.6	791.5	787.1	779.7	782.7
122.5°	860.6	862.1	860.6	856.2	848.9
125°	934.2	934.2	932.7	929.8	926.8
127.5°	1000.4	1004.8	1001.9	998.9	997.4
130°	1071.0	1075.4	1075.4	1072.5	1066.6
132.5°	1143.1	1146.0	1144.6	1141.6	1140.1
135°	1204.9	1213.7	1213.7	1210.8	1206.4
137.5°	1274.0	1278.4	1281.4	1277.0	1278.4
140°	1343.2	1346.1	1346.1	1344.6	1343.2
142.5°	1406.4	1409.4	1407.9	1407.9	1407.9
145°	1463.8	1469.7	1471.2	1469.7	1465.3
147.5°	1522.7	1530.0	1528.5	1527.1	1525.6
150°	1575.6	1581.5	1581.5	1581.5	1580.0
152.5°	1625.6	1628.6	1630.0	1634.5	1630.0
155°	1677.1	1677.1	1675.7	1681.5	1675.7
157.5°	1721.3	1718.3	1718.3	1722.7	1718.3
160°	1759.5	1758.0	1756.6	1761.0	1753.6
162.5°	1794.8	1790.4	1788.9	1797.8	1790.4
165°	1825.7	1821.3	1818.4	1827.2	1821.3
167.5°	1850.7	1844.8	1844.8	1853.7	1844.8
170°	1871.3	1864.0	1865.4	1874.3	1864.0
172.5°	1886.0	1880.1	1880.1	1890.4	1880.1
175°	1899.3	1891.9	1890.4	1900.7	1890.4
177.5°	1905.2	1897.8	1897.8	1908.1	1896.3
180°	1902.2	1902.2	1902.2	1902.2	1902.2

(END OF REPORT)