

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033246

Luminaire Tested: S124DIW-B1195D1050UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033246
REPORT IS A COMBINATION OF REPORTS P996985 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1050UB30-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9380.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 92.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033246

CATALOG NUMBER: S124DIW-B1195D1050UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033246

CATALOG NUMBER: S124DIW-B1195D1050UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16299	15817	15836
10°	16161	15378	15270
15°	15929	14856	14632
20°	15633	14291	13971
25°	15300	13695	13259
30°	14899	13050	12478
35°	14482	12389	11722
40°	14048	11678	10919
45°	13593	10965	10169
50°	13090	10275	9337
55°	12542	9467	8511
60°	11982	8583	7650
65°	11341	7671	6681
70°	10604	6572	5643
75°	9501	5298	4518
80°	8094	3829	3178
85°	6287	2132	1710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13593 cd/sqm

TEST NUMBER: P1033246

CATALOG NUMBER: S124DIW-B1195D1050UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.2	2.0
10°-20°	530.3	5.7
20°-30°	780.5	8.3
30°-40°	907.3	9.7
40°-50°	907.2	9.7
50°-60°	793.4	8.5
60°-70°	589.1	6.3
70°-80°	334.2	3.6
80°-90°	98.5	1.1
90°-100°	45.6	0.5
100°-110°	300.3	3.2
110°-120°	573.5	6.1
120°-130°	728.0	7.8
130°-140°	778.8	8.3
140°-150°	728.3	7.8
150°-160°	587.3	6.3
160°-170°	378.8	4.0
170°-180°	130.5	1.4
0°-30°	1499.1	16.0
0°-40°	2406.3	25.7
0°-60°	4107.0	43.8
0°-90°	5128.8	54.7
90°-120°	919.4	9.8
90°-150°	3154.6	33.6
90°-180°	4251.0	45.3
0°-180°	9380.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1997	1997	1997	1997	1997	
5°	1996	1989	1972	1989	1986	189
15°	1900	1893	1869	1879	1874	535
25°	1720	1709	1687	1688	1682	792
35°	1480	1469	1447	1435	1427	926
45°	1208	1197	1171	1154	1149	931
55°	914	909	886	867	858	818
65°	619	611	595	579	571	613
75°	330	322	314	307	306	350
85°	86	86	83	83	82	93
90°	3	14	23	29	31	9
95°	56	22	23	29	30	70
105°	309	316	321	330	293	324
115°	578	581	580	582	582	568
125°	812	816	814	817	818	725
135°	1007	1006	1010	1012	1014	776
145°	1161	1164	1164	1165	1167	726
155°	1273	1274	1271	1275	1272	587
165°	1343	1338	1338	1346	1337	380
175°	1374	1368	1369	1378	1366	131
180°	1374	1374	1374	1374	1374	

TEST NUMBER: P1033246

CATALOG NUMBER: S124DIW-B1195D1050UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1997.1	1997.1	1997.1	1997.1	1997.1
2.5°	2003.5	1998.7	1981.1	1997.1	1995.5
5°	1995.5	1989.1	1971.5	1989.1	1985.9
7.5°	1981.1	1974.7	1955.5	1969.9	1968.3
10°	1960.3	1953.9	1933.1	1945.9	1942.7
12.5°	1933.1	1926.7	1904.3	1918.7	1913.9
15°	1899.5	1893.1	1869.1	1878.7	1873.9
17.5°	1861.1	1853.1	1830.7	1837.1	1833.9
20°	1817.9	1809.9	1785.9	1790.7	1787.5
22.5°	1771.5	1760.3	1736.3	1745.9	1739.5
25°	1720.3	1709.1	1686.7	1688.3	1681.9
27.5°	1662.7	1651.5	1630.7	1627.5	1619.5
30°	1605.1	1592.3	1571.5	1565.1	1557.1
32.5°	1544.2	1533.0	1510.6	1502.6	1494.6
35°	1480.2	1469.0	1446.6	1435.4	1427.4
37.5°	1413.0	1403.4	1379.4	1368.2	1357.0
40°	1347.4	1334.6	1310.6	1294.6	1286.6
42.5°	1277.0	1270.6	1243.4	1224.2	1219.4
45°	1208.2	1197.0	1171.4	1153.8	1149.0
47.5°	1136.2	1128.2	1104.2	1085.0	1072.2
50°	1062.6	1056.2	1033.8	1011.4	1001.8
52.5°	990.6	982.6	958.6	939.4	926.5
55°	913.7	908.9	886.5	867.3	857.7
57.5°	841.7	836.9	814.5	795.3	785.7
60°	766.5	758.5	737.7	723.3	715.3
62.5°	692.9	686.5	664.1	651.3	643.3
65°	619.3	611.3	595.3	579.3	571.3
67.5°	544.1	537.7	521.7	505.7	504.1
70°	475.3	464.1	451.3	438.5	433.7
72.5°	401.7	390.5	380.9	371.3	366.5
75°	329.7	321.7	313.7	307.2	305.6
77.5°	259.2	256.0	248.0	246.4	241.6
80°	196.8	192.0	188.8	185.6	184.0
82.5°	136.0	134.4	134.4	132.8	131.2
85°	86.4	86.4	83.2	83.2	81.6
87.5°	41.6	40.0	38.4	38.4	38.4
90°	3.1	14.4	22.6	28.8	30.8
92.5°	15.4	13.4	21.6	27.7	27.7
95°	56.5	21.6	22.6	28.8	29.8
97.5°	107.9	130.5	22.6	27.7	28.8
100°	168.5	187.0	45.2	27.7	28.8
102.5°	236.3	248.7	261.0	29.8	29.8
105°	309.3	315.5	320.6	329.8	292.9
107.5°	376.1	379.2	386.4	391.5	395.6
110°	443.9	447.0	453.2	455.2	458.3

TEST NUMBER: P1033246

CATALOG NUMBER: S124DIW-B1195D1050UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	509.7	515.8	517.9	516.9	521.0
115°	577.5	580.6	579.5	581.6	581.6
117.5°	638.1	642.2	645.3	644.3	644.3
120°	699.8	703.9	702.8	704.9	702.8
122.5°	757.3	759.4	761.4	762.4	760.4
125°	811.8	815.9	813.8	816.9	817.9
127.5°	864.2	865.2	870.3	869.3	868.3
130°	914.5	915.6	918.6	919.7	919.7
132.5°	960.8	962.8	966.9	968.0	966.9
135°	1007.0	1006.0	1010.1	1012.1	1014.2
137.5°	1048.1	1048.1	1053.2	1055.3	1054.3
140°	1088.2	1090.2	1092.3	1095.4	1096.4
142.5°	1124.1	1128.3	1129.3	1131.3	1131.3
145°	1161.1	1164.2	1164.2	1165.3	1167.3
147.5°	1189.9	1196.1	1195.1	1196.1	1197.1
150°	1221.8	1225.9	1224.8	1224.8	1225.9
152.5°	1248.5	1251.6	1249.5	1251.6	1250.5
155°	1273.1	1274.2	1271.1	1275.2	1272.1
157.5°	1294.7	1294.7	1290.6	1295.8	1290.6
160°	1313.2	1310.1	1309.1	1315.3	1309.1
162.5°	1329.7	1325.6	1324.5	1330.7	1323.5
165°	1343.0	1337.9	1337.9	1346.1	1336.9
167.5°	1354.3	1349.2	1348.2	1357.4	1347.1
170°	1363.6	1357.4	1358.4	1366.7	1356.4
172.5°	1369.7	1363.6	1364.6	1372.8	1361.5
175°	1373.8	1367.7	1368.7	1378.0	1365.6
177.5°	1376.9	1369.7	1371.8	1380.0	1367.7
180°	1373.8	1373.8	1373.8	1373.8	1373.8

(END OF REPORT)