

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033271

Luminaire Tested: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033271
REPORT IS A COMBINATION OF REPORTS P997022 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9700.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033271

CATALOG NUMBER: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033271

CATALOG NUMBER: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	52	50	49
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16146	16146	16146
5°	16159	15681	15700
10°	16022	15246	15139
15°	15792	14729	14506
20°	15499	14169	13850
25°	15168	13577	13145
30°	14770	12938	12371
35°	14357	12282	11622
40°	13928	11578	10826
45°	13476	10871	10081
50°	12977	10186	9257
55°	12435	9386	8438
60°	11879	8510	7585
65°	11244	7605	6624
70°	10512	6515	5593
75°	9418	5252	4480
80°	8024	3797	3151
85°	6236	2114	1696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13476 cd/sqm

TEST NUMBER: P1033271

CATALOG NUMBER: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.6	1.9
10°-20°	525.8	5.4
20°-30°	773.8	8.0
30°-40°	899.5	9.3
40°-50°	899.4	9.3
50°-60°	786.6	8.1
60°-70°	584.0	6.0
70°-80°	331.4	3.4
80°-90°	98.5	1.0
90°-100°	108.4	1.1
100°-110°	324.7	3.3
110°-120°	551.6	5.7
120°-130°	727.5	7.5
130°-140°	817.1	8.4
140°-150°	803.1	8.3
150°-160°	675.4	7.0
160°-170°	449.4	4.6
170°-180°	157.4	1.6
0°-30°	1486.2	15.3
0°-40°	2385.7	24.6
0°-60°	4071.7	42.0
0°-90°	5085.6	52.4
90°-120°	984.7	10.2
90°-150°	3332.3	34.4
90°-180°	4614.0	47.6
0°-180°	9700.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1980	1980	1980	1980	1980	
5°	1978	1972	1955	1972	1969	188
15°	1883	1877	1853	1863	1858	531
25°	1706	1694	1672	1674	1667	785
35°	1468	1456	1434	1423	1415	918
45°	1198	1187	1161	1144	1139	923
55°	906	901	879	860	850	811
65°	614	606	590	574	566	608
75°	327	319	311	305	303	347
85°	86	86	82	82	81	92
90°	4	18	28	36	39	11
95°	77	89	98	102	102	84
105°	300	301	306	310	314	318
115°	561	561	558	557	556	553
125°	817	817	816	813	810	728
135°	1053	1061	1061	1059	1055	815
145°	1280	1285	1286	1285	1281	801
155°	1466	1466	1465	1470	1465	675
165°	1596	1592	1590	1598	1592	450
175°	1660	1654	1653	1662	1653	158
180°	1663	1663	1663	1663	1663	

TEST NUMBER: P1033271

CATALOG NUMBER: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1980.0	1980.0	1980.0	1980.0	1980.0
2.5°	1986.3	1981.6	1964.1	1980.0	1978.4
5°	1978.4	1972.0	1954.6	1972.0	1968.9
7.5°	1964.1	1957.8	1938.7	1953.0	1951.4
10°	1943.5	1937.1	1916.5	1929.2	1926.0
12.5°	1916.5	1910.2	1888.0	1902.2	1897.5
15°	1883.2	1876.9	1853.1	1862.6	1857.8
17.5°	1845.1	1837.2	1815.0	1821.3	1818.2
20°	1802.3	1794.4	1770.6	1775.3	1772.1
22.5°	1756.3	1745.2	1721.4	1730.9	1724.5
25°	1705.5	1694.4	1672.2	1673.8	1667.4
27.5°	1648.4	1637.3	1616.7	1613.5	1605.6
30°	1591.3	1578.6	1558.0	1551.6	1543.7
32.5°	1531.0	1519.9	1497.7	1489.7	1481.8
35°	1467.5	1456.4	1434.2	1423.1	1415.2
37.5°	1400.9	1391.4	1367.6	1356.5	1345.4
40°	1335.9	1323.2	1299.4	1283.5	1275.6
42.5°	1266.0	1259.7	1232.7	1213.7	1208.9
45°	1197.8	1186.7	1161.3	1143.9	1139.1
47.5°	1126.4	1118.5	1094.7	1075.7	1063.0
50°	1053.4	1047.1	1024.9	1002.7	993.2
52.5°	982.1	974.1	950.3	931.3	918.6
55°	905.9	901.1	878.9	859.9	850.4
57.5°	834.5	829.8	807.5	788.5	779.0
60°	759.9	752.0	731.4	717.1	709.2
62.5°	687.0	680.6	658.4	645.7	637.8
65°	614.0	606.1	590.2	574.3	566.4
67.5°	539.4	533.1	517.2	501.3	499.8
70°	471.2	460.1	447.4	434.7	429.9
72.5°	398.2	387.1	377.6	368.1	363.3
75°	326.8	318.9	311.0	304.6	303.0
77.5°	257.0	253.8	245.9	244.3	239.6
80°	195.1	190.4	187.2	184.0	182.4
82.5°	134.9	133.3	133.3	131.7	130.1
85°	85.7	85.7	82.5	82.5	80.9
87.5°	41.2	39.7	38.1	38.1	38.1
90°	3.9	18.0	28.3	36.0	38.6
92.5°	33.4	50.2	56.6	60.5	61.7
95°	77.2	88.7	97.8	101.6	101.6
97.5°	123.5	133.8	144.1	149.2	149.2
100°	180.1	185.2	196.8	199.4	199.4
102.5°	239.2	240.5	250.8	254.7	256.0
105°	299.7	301.0	306.1	310.0	313.8
107.5°	362.7	364.0	365.3	370.4	369.1
110°	427.0	429.6	428.3	425.7	429.6

TEST NUMBER: P1033271

CATALOG NUMBER: S124DIW-B1195D1340UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	493.9	493.9	491.3	491.3	491.3
115°	560.8	560.8	558.2	556.9	555.6
117.5°	623.8	623.8	622.5	618.7	614.8
120°	686.8	692.0	688.1	681.7	684.3
122.5°	752.4	753.7	752.4	748.6	742.1
125°	816.8	816.8	815.5	812.9	810.3
127.5°	874.6	878.5	875.9	873.3	872.1
130°	936.4	940.2	940.2	937.7	932.5
132.5°	999.4	1002.0	1000.7	998.1	996.8
135°	1053.4	1061.1	1061.1	1058.6	1054.7
137.5°	1113.9	1117.7	1120.3	1116.4	1117.7
140°	1174.3	1176.9	1176.9	1175.6	1174.3
142.5°	1229.6	1232.2	1230.9	1230.9	1230.9
145°	1279.8	1284.9	1286.2	1284.9	1281.1
147.5°	1331.2	1337.7	1336.4	1335.1	1333.8
150°	1377.5	1382.7	1382.7	1382.7	1381.4
152.5°	1421.3	1423.8	1425.1	1429.0	1425.1
155°	1466.3	1466.3	1465.0	1470.2	1465.0
157.5°	1504.9	1502.3	1502.3	1506.2	1502.3
160°	1538.3	1537.0	1535.7	1539.6	1533.2
162.5°	1569.2	1565.3	1564.0	1571.8	1565.3
165°	1596.2	1592.3	1589.8	1597.5	1592.3
167.5°	1618.1	1612.9	1612.9	1620.6	1612.9
170°	1636.1	1629.6	1630.9	1638.6	1629.6
172.5°	1648.9	1643.8	1643.8	1652.8	1643.8
175°	1660.5	1654.1	1652.8	1661.8	1652.8
177.5°	1665.7	1659.2	1659.2	1668.2	1657.9
180°	1663.1	1663.1	1663.1	1663.1	1663.1

(END OF REPORT)