

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033277

Luminaire Tested: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033277
REPORT IS A COMBINATION OF REPORTS P997052 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9784.0 lumens
Efficiency: N/A
Efficacy: 94.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033277

CATALOG NUMBER: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033277

CATALOG NUMBER: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58
1	98	94	90	86	91	87	84	81	74	72	69	62	61	59	52	50	49
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16285	16285	16285
5°	16299	15817	15836
10°	16161	15378	15270
15°	15929	14856	14632
20°	15633	14291	13971
25°	15300	13695	13259
30°	14899	13050	12478
35°	14482	12389	11722
40°	14048	11678	10919
45°	13593	10965	10169
50°	13090	10275	9337
55°	12542	9467	8511
60°	11982	8583	7650
65°	11341	7671	6681
70°	10604	6572	5643
75°	9501	5298	4518
80°	8094	3829	3178
85°	6287	2132	1710

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13593 cd/sqm

TEST NUMBER: P1033277

CATALOG NUMBER: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.2	1.9
10°-20°	530.3	5.4
20°-30°	780.5	8.0
30°-40°	907.3	9.3
40°-50°	907.2	9.3
50°-60°	793.4	8.1
60°-70°	589.1	6.0
70°-80°	334.2	3.4
80°-90°	99.3	1.0
90°-100°	109.3	1.1
100°-110°	327.5	3.3
110°-120°	556.4	5.7
120°-130°	733.8	7.5
130°-140°	824.1	8.4
140°-150°	810.0	8.3
150°-160°	681.3	7.0
160°-170°	453.3	4.6
170°-180°	158.7	1.6
0°-30°	1499.1	15.3
0°-40°	2406.3	24.6
0°-60°	4107.0	42.0
0°-90°	5129.6	52.4
90°-120°	993.2	10.2
90°-150°	3361.1	34.4
90°-180°	4654.0	47.6
0°-180°	9784.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1997	1997	1997	1997	1997	
5°	1996	1989	1972	1989	1986	189
15°	1900	1893	1869	1879	1874	535
25°	1720	1709	1687	1688	1682	792
35°	1480	1469	1447	1435	1427	926
45°	1208	1197	1171	1154	1149	931
55°	914	909	886	867	858	818
65°	619	611	595	579	571	613
75°	330	322	314	307	306	350
85°	86	86	83	83	82	93
90°	4	18	28	36	39	11
95°	78	90	99	102	102	84
105°	302	304	309	313	317	321
115°	566	566	563	562	560	558
125°	824	824	822	820	817	734
135°	1062	1070	1070	1068	1064	822
145°	1291	1296	1297	1296	1292	808
155°	1479	1479	1478	1483	1478	681
165°	1610	1606	1604	1611	1606	454
175°	1675	1668	1667	1676	1667	159
180°	1678	1678	1678	1678	1678	

TEST NUMBER: P1033277

CATALOG NUMBER: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1997.1	1997.1	1997.1	1997.1	1997.1
2.5°	2003.5	1998.7	1981.1	1997.1	1995.5
5°	1995.5	1989.1	1971.5	1989.1	1985.9
7.5°	1981.1	1974.7	1955.5	1969.9	1968.3
10°	1960.3	1953.9	1933.1	1945.9	1942.7
12.5°	1933.1	1926.7	1904.3	1918.7	1913.9
15°	1899.5	1893.1	1869.1	1878.7	1873.9
17.5°	1861.1	1853.1	1830.7	1837.1	1833.9
20°	1817.9	1809.9	1785.9	1790.7	1787.5
22.5°	1771.5	1760.3	1736.3	1745.9	1739.5
25°	1720.3	1709.1	1686.7	1688.3	1681.9
27.5°	1662.7	1651.5	1630.7	1627.5	1619.5
30°	1605.1	1592.3	1571.5	1565.1	1557.1
32.5°	1544.2	1533.0	1510.6	1502.6	1494.6
35°	1480.2	1469.0	1446.6	1435.4	1427.4
37.5°	1413.0	1403.4	1379.4	1368.2	1357.0
40°	1347.4	1334.6	1310.6	1294.6	1286.6
42.5°	1277.0	1270.6	1243.4	1224.2	1219.4
45°	1208.2	1197.0	1171.4	1153.8	1149.0
47.5°	1136.2	1128.2	1104.2	1085.0	1072.2
50°	1062.6	1056.2	1033.8	1011.4	1001.8
52.5°	990.6	982.6	958.6	939.4	926.5
55°	913.7	908.9	886.5	867.3	857.7
57.5°	841.7	836.9	814.5	795.3	785.7
60°	766.5	758.5	737.7	723.3	715.3
62.5°	692.9	686.5	664.1	651.3	643.3
65°	619.3	611.3	595.3	579.3	571.3
67.5°	544.1	537.7	521.7	505.7	504.1
70°	475.3	464.1	451.3	438.5	433.7
72.5°	401.7	390.5	380.9	371.3	366.5
75°	329.7	321.7	313.7	307.2	305.6
77.5°	259.2	256.0	248.0	246.4	241.6
80°	196.8	192.0	188.8	185.6	184.0
82.5°	136.0	134.4	134.4	132.8	131.2
85°	86.4	86.4	83.2	83.2	81.6
87.5°	41.6	40.0	38.4	38.4	38.4
90°	3.9	18.2	28.5	36.3	38.9
92.5°	33.7	50.6	57.1	61.0	62.3
95°	77.8	89.5	98.6	102.5	102.5
97.5°	124.5	134.9	145.3	150.5	150.5
100°	181.6	186.8	198.5	201.1	201.1
102.5°	241.3	242.6	253.0	256.9	258.2
105°	302.3	303.6	308.8	312.7	316.6
107.5°	365.9	367.2	368.5	373.6	372.3
110°	430.7	433.3	432.0	429.4	433.3

TEST NUMBER: P1033277

CATALOG NUMBER: S124DIW-B1195D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.2	498.2	495.6	495.6	495.6
115°	565.6	565.6	563.1	561.8	560.5
117.5°	629.2	629.2	627.9	624.0	620.1
120°	692.8	698.0	694.1	687.6	690.2
122.5°	759.0	760.3	759.0	755.1	748.6
125°	823.8	823.8	822.5	819.9	817.3
127.5°	882.2	886.1	883.5	880.9	879.6
130°	944.5	948.4	948.4	945.8	940.6
132.5°	1008.0	1010.6	1009.3	1006.8	1005.5
135°	1062.5	1070.3	1070.3	1067.7	1063.8
137.5°	1123.5	1127.4	1130.0	1126.1	1127.4
140°	1184.5	1187.1	1187.1	1185.8	1184.5
142.5°	1240.3	1242.9	1241.6	1241.6	1241.6
145°	1290.9	1296.1	1297.4	1296.1	1292.2
147.5°	1342.8	1349.3	1348.0	1346.7	1345.4
150°	1389.5	1394.7	1394.7	1394.7	1393.4
152.5°	1433.6	1436.2	1437.5	1441.4	1437.5
155°	1479.0	1479.0	1477.7	1482.9	1477.7
157.5°	1517.9	1515.3	1515.3	1519.2	1515.3
160°	1551.6	1550.3	1549.0	1552.9	1546.5
162.5°	1582.8	1578.9	1577.6	1585.4	1578.9
165°	1610.0	1606.1	1603.5	1611.3	1606.1
167.5°	1632.1	1626.9	1626.9	1634.7	1626.9
170°	1650.2	1643.8	1645.1	1652.8	1643.8
172.5°	1663.2	1658.0	1658.0	1667.1	1658.0
175°	1674.9	1668.4	1667.1	1676.2	1667.1
177.5°	1680.1	1673.6	1673.6	1682.7	1672.3
180°	1677.5	1677.5	1677.5	1677.5	1677.5

(END OF REPORT)