

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033282

Luminaire Tested: S124DIW-B1195D1340UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033282
REPORT IS A COMBINATION OF REPORTS P997060 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1340UB35-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10543.1 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033282

CATALOG NUMBER: S124DIW-B1195D1340UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033282

CATALOG NUMBER: S124DIW-B1195D1340UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	47	46
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39
3	81	71	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	31	27	25
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	28	24	30	25	21	26	22	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1033282

CATALOG NUMBER: S124DIW-B1195D1340UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	1.8
10°-20°	532.6	5.1
20°-30°	783.8	7.4
30°-40°	911.2	8.6
40°-50°	911.1	8.6
50°-60°	796.9	7.6
60°-70°	591.6	5.6
70°-80°	335.7	3.2
80°-90°	99.7	0.9
90°-100°	57.8	0.5
100°-110°	380.9	3.6
110°-120°	727.3	6.9
120°-130°	923.3	8.8
130°-140°	987.7	9.4
140°-150°	923.6	8.8
150°-160°	744.8	7.1
160°-170°	480.4	4.6
170°-180°	165.5	1.6
0°-30°	1505.5	14.3
0°-40°	2416.7	22.9
0°-60°	4124.6	39.1
0°-90°	5151.6	48.9
90°-120°	1166.1	11.1
90°-150°	4000.7	37.9
90°-180°	5391.0	51.1
0°-180°	10543.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	4	18	29	36	39	9
95°	72	27	29	36	38	88
105°	392	400	407	418	371	411
115°	732	736	735	738	738	721
125°	1030	1035	1032	1036	1037	919
135°	1277	1276	1281	1284	1286	984
145°	1473	1476	1476	1478	1480	920
155°	1615	1616	1612	1617	1613	744
165°	1703	1697	1697	1707	1695	481
175°	1742	1734	1736	1748	1732	166
180°	1742	1742	1742	1742	1742	

TEST NUMBER: P1033282

CATALOG NUMBER: S124DIW-B1195D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	3.9	18.2	28.7	36.5	39.1
92.5°	19.5	16.9	27.4	35.2	35.2
95°	71.7	27.4	28.7	36.5	37.8
97.5°	136.8	165.5	28.7	35.2	36.5
100°	213.7	237.2	57.3	35.2	36.5
102.5°	299.7	315.4	331.0	37.8	37.8
105°	392.3	400.1	406.6	418.3	371.4
107.5°	477.0	480.9	490.0	496.5	501.7
110°	563.0	566.9	574.7	577.3	581.2



TEST NUMBER: P1033282

CATALOG NUMBER: S124DIW-B1195D1340UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	646.4	654.2	656.8	655.5	660.7
115°	732.4	736.3	735.0	737.6	737.6
117.5°	809.3	814.5	818.4	817.1	817.1
120°	887.5	892.7	891.4	894.0	891.4
122.5°	960.4	963.0	965.6	967.0	964.3
125°	1029.5	1034.7	1032.1	1036.0	1037.3
127.5°	1096.0	1097.3	1103.8	1102.5	1101.2
130°	1159.8	1161.1	1165.0	1166.3	1166.3
132.5°	1218.5	1221.1	1226.3	1227.6	1226.3
135°	1277.1	1275.8	1281.0	1283.6	1286.2
137.5°	1329.2	1329.2	1335.7	1338.4	1337.1
140°	1380.1	1382.7	1385.3	1389.2	1390.5
142.5°	1425.7	1430.9	1432.2	1434.8	1434.8
145°	1472.6	1476.5	1476.5	1477.8	1480.4
147.5°	1509.1	1516.9	1515.6	1516.9	1518.2
150°	1549.5	1554.7	1553.4	1553.4	1554.7
152.5°	1583.3	1587.3	1584.7	1587.3	1586.0
155°	1614.6	1615.9	1612.0	1617.2	1613.3
157.5°	1642.0	1642.0	1636.8	1643.3	1636.8
160°	1665.4	1661.5	1660.2	1668.1	1660.2
162.5°	1686.3	1681.1	1679.8	1687.6	1678.5
165°	1703.2	1696.7	1696.7	1707.2	1695.4
167.5°	1717.6	1711.1	1709.8	1721.5	1708.5
170°	1729.3	1721.5	1722.8	1733.2	1720.2
172.5°	1737.1	1729.3	1730.6	1741.0	1726.7
175°	1742.3	1734.5	1735.8	1747.5	1731.9
177.5°	1746.2	1737.1	1739.7	1750.2	1734.5
180°	1742.3	1742.3	1742.3	1742.3	1742.3

(END OF REPORT)