

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033313

Luminaire Tested: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033313
REPORT IS A COMBINATION OF REPORTS P997127 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10665.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033313

CATALOG NUMBER: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033313

CATALOG NUMBER: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16355	16355	16355
5°	16369	15885	15904
10°	16230	15444	15336
15°	15998	14919	14694
20°	15700	14353	14031
25°	15366	13753	13316
30°	14962	13105	12531
35°	14544	12442	11773
40°	14109	11728	10966
45°	13652	11012	10212
50°	13146	10318	9377
55°	12597	9508	8547
60°	12034	8620	7684
65°	11391	7704	6709
70°	10648	6599	5666
75°	9542	5320	4539
80°	8131	3845	3192
85°	6316	2142	1719

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13652 cd/sqm

TEST NUMBER: P1033313

CATALOG NUMBER: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	1.8
10°-20°	532.6	5.0
20°-30°	783.8	7.3
30°-40°	911.2	8.5
40°-50°	911.1	8.5
50°-60°	796.9	7.5
60°-70°	591.6	5.5
70°-80°	335.7	3.1
80°-90°	100.4	0.9
90°-100°	129.5	1.2
100°-110°	387.9	3.6
110°-120°	659.0	6.2
120°-130°	869.1	8.1
130°-140°	976.1	9.2
140°-150°	959.4	9.0
150°-160°	806.9	7.6
160°-170°	536.9	5.0
170°-180°	188.0	1.8
0°-30°	1505.5	14.1
0°-40°	2416.7	22.7
0°-60°	4124.6	38.7
0°-90°	5152.3	48.3
90°-120°	1176.4	11.0
90°-150°	3981.0	37.3
90°-180°	5513.0	51.7
0°-180°	10665.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2006	2006	2006	2006	2006	
5°	2004	1998	1980	1998	1994	190
15°	1908	1901	1877	1887	1882	538
25°	1728	1716	1694	1696	1689	795
35°	1487	1475	1453	1442	1434	930
45°	1213	1202	1176	1159	1154	935
55°	918	913	890	871	861	822
65°	622	614	598	582	574	616
75°	331	323	315	309	307	351
85°	87	87	84	84	82	93
90°	5	22	34	43	46	12
95°	92	106	117	121	121	100
105°	358	360	366	370	375	380
115°	670	670	667	665	664	661
125°	976	976	974	971	968	870
135°	1258	1268	1268	1265	1260	974
145°	1529	1535	1537	1535	1530	957
155°	1752	1752	1750	1756	1750	806
165°	1907	1902	1899	1908	1902	538
175°	1984	1976	1974	1985	1974	188
180°	1987	1987	1987	1987	1987	

TEST NUMBER: P1033313

CATALOG NUMBER: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2005.7	2005.7	2005.7	2005.7	2005.7
2.5°	2012.1	2007.3	1989.6	2005.7	2004.1
5°	2004.1	1997.7	1980.0	1997.7	1994.4
7.5°	1989.6	1983.2	1963.9	1978.4	1976.8
10°	1968.7	1962.3	1941.4	1954.3	1951.1
12.5°	1941.4	1935.0	1912.5	1926.9	1922.1
15°	1907.7	1901.2	1877.1	1886.8	1881.9
17.5°	1869.1	1861.1	1838.6	1845.0	1841.8
20°	1825.7	1817.7	1793.6	1798.4	1795.2
22.5°	1779.1	1767.8	1743.7	1753.4	1746.9
25°	1727.7	1716.4	1693.9	1695.5	1689.1
27.5°	1669.8	1658.6	1637.7	1634.4	1626.4
30°	1611.9	1599.1	1578.2	1571.8	1563.7
32.5°	1550.9	1539.6	1517.1	1509.1	1501.1
35°	1486.6	1475.3	1452.8	1441.6	1433.6
37.5°	1419.1	1409.4	1385.3	1374.1	1362.8
40°	1353.2	1340.3	1316.2	1300.2	1292.1
42.5°	1282.5	1276.1	1248.7	1229.5	1224.6
45°	1213.4	1202.1	1176.4	1158.7	1153.9
47.5°	1141.1	1133.0	1108.9	1089.6	1076.8
50°	1067.1	1060.7	1038.2	1015.7	1006.1
52.5°	994.8	986.8	962.7	943.4	930.5
55°	917.7	912.8	890.3	871.1	861.4
57.5°	845.3	840.5	818.0	798.7	789.1
60°	769.8	761.8	740.9	726.4	718.4
62.5°	695.9	689.5	667.0	654.1	646.1
65°	622.0	613.9	597.9	581.8	573.7
67.5°	546.4	540.0	523.9	507.9	506.2
70°	477.3	466.1	453.2	440.4	435.5
72.5°	403.4	392.1	382.5	372.9	368.0
75°	331.1	323.0	315.0	308.6	307.0
77.5°	260.4	257.1	249.1	247.5	242.7
80°	197.7	192.9	189.6	186.4	184.8
82.5°	136.6	135.0	135.0	133.4	131.8
85°	86.8	86.8	83.6	83.6	82.0
87.5°	41.8	40.2	38.6	38.6	38.6
90°	4.6	21.5	33.8	43.0	46.1
92.5°	40.0	59.9	67.6	72.2	73.8
95°	92.2	106.0	116.8	121.4	121.4
97.5°	147.5	159.8	172.1	178.2	178.2
100°	215.1	221.3	235.1	238.2	238.2
102.5°	285.8	287.3	299.6	304.2	305.8
105°	358.0	359.6	365.7	370.3	374.9
107.5°	433.3	434.9	436.4	442.5	441.0
110°	510.2	513.2	511.7	508.6	513.2

TEST NUMBER: P1033313

CATALOG NUMBER: S124DIW-B1195D1560UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	590.1	590.1	587.0	587.0	587.0
115°	670.0	670.0	666.9	665.4	663.8
117.5°	745.3	745.3	743.7	739.1	734.5
120°	820.6	826.7	822.1	814.4	817.5
122.5°	898.9	900.5	898.9	894.3	886.6
125°	975.7	975.7	974.2	971.1	968.1
127.5°	1044.9	1049.5	1046.4	1043.4	1041.8
130°	1118.7	1123.3	1123.3	1120.2	1114.0
132.5°	1193.9	1197.0	1195.5	1192.4	1190.9
135°	1258.5	1267.7	1267.7	1264.6	1260.0
137.5°	1330.7	1335.3	1338.4	1333.8	1335.3
140°	1402.9	1406.0	1406.0	1404.5	1402.9
142.5°	1469.0	1472.1	1470.5	1470.5	1470.5
145°	1528.9	1535.1	1536.6	1535.1	1530.5
147.5°	1590.4	1598.1	1596.5	1595.0	1593.5
150°	1645.7	1651.9	1651.9	1651.9	1650.3
152.5°	1698.0	1701.0	1702.6	1707.2	1702.6
155°	1751.7	1751.7	1750.2	1756.3	1750.2
157.5°	1797.8	1794.8	1794.8	1799.4	1794.8
160°	1837.8	1836.3	1834.7	1839.3	1831.6
162.5°	1874.7	1870.1	1868.5	1877.7	1870.1
165°	1906.9	1902.3	1899.3	1908.5	1902.3
167.5°	1933.1	1926.9	1926.9	1936.1	1926.9
170°	1954.6	1946.9	1948.4	1957.6	1946.9
172.5°	1969.9	1963.8	1963.8	1974.5	1963.8
175°	1983.8	1976.1	1974.5	1985.3	1974.5
177.5°	1989.9	1982.2	1982.2	1993.0	1980.7
180°	1986.8	1986.8	1986.8	1986.8	1986.8

(END OF REPORT)