

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033423

Luminaire Tested: S124DIW-B350D1340UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033423
REPORT IS A COMBINATION OF REPORTS P997381 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1340UB30-4F0-XX-W2A-F
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6848.0 lumens
Efficiency: N/A
Efficacy: 124.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033423

CATALOG NUMBER: S124DIW-B350D1340UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1033423

CATALOG NUMBER: S124DIW-B350D1340UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25
2	83	76	70	65	73	68	63	59	52	48	46	37	35	33	23	22	21
3	76	67	60	54	67	59	54	49	45	41	38	33	30	28	21	19	18
4	69	59	51	46	61	53	46	41	40	36	32	29	26	24	18	17	16
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	13
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12
7	54	42	34	29	47	38	31	26	29	24	21	21	18	16	14	12	10
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	11	9
9	46	34	27	23	41	31	25	20	24	20	16	18	15	12	11	10	8
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4690	4690	4690
5°	4693	4555	4560
10°	4654	4428	4397
15°	4587	4278	4213
20°	4502	4115	4023
25°	4405	3944	3818
30°	4290	3758	3593
35°	4170	3567	3375
40°	4045	3363	3144
45°	3914	3157	2928
50°	3770	2959	2689
55°	3612	2726	2451
60°	3450	2471	2203
65°	3265	2209	1924
70°	3054	1892	1625
75°	2735	1525	1301
80°	2332	1103	916
85°	1812	615	493

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3914 cd/sqm

TEST NUMBER: P1033423

CATALOG NUMBER: S124DIW-B350D1340UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	0.8
10°-20°	152.7	2.2
20°-30°	224.7	3.3
30°-40°	261.2	3.8
40°-50°	261.2	3.8
50°-60°	228.5	3.3
60°-70°	169.6	2.5
70°-80°	96.2	1.4
80°-90°	31.2	0.5
90°-100°	57.6	0.8
100°-110°	379.3	5.5
110°-120°	724.2	10.6
120°-130°	919.4	13.4
130°-140°	983.6	14.4
140°-150°	919.7	13.4
150°-160°	741.6	10.8
160°-170°	478.3	7.0
170°-180°	164.8	2.4
0°-30°	431.6	6.3
0°-40°	692.9	10.1
0°-60°	1182.6	17.3
0°-90°	1479.6	21.6
90°-120°	1161.0	17.0
90°-150°	3983.6	58.2
90°-180°	5368.0	78.4
0°-180°	6848.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	575	575	575	575	575	
5°	575	573	568	573	572	55
15°	547	545	538	541	540	154
25°	495	492	486	486	484	228
35°	426	423	416	413	411	267
45°	348	345	337	332	331	268
55°	263	262	255	250	247	236
65°	178	176	171	167	164	176
75°	95	93	90	88	88	101
85°	25	25	24	24	24	27
90°	4	18	28	36	39	5
95°	71	27	28	36	38	88
105°	391	398	405	416	370	409
115°	729	733	732	734	734	718
125°	1025	1030	1028	1032	1033	915
135°	1272	1270	1276	1278	1281	980
145°	1466	1470	1470	1472	1474	916
155°	1608	1609	1605	1610	1606	741
165°	1696	1690	1690	1700	1688	479
175°	1735	1727	1728	1740	1724	165
180°	1735	1735	1735	1735	1735	

TEST NUMBER: P1033423

CATALOG NUMBER: S124DIW-B350D1340UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	575.1	575.1	575.1	575.1	575.1
2.5°	576.9	575.5	570.5	575.1	574.6
5°	574.6	572.8	567.7	572.8	571.8
7.5°	570.5	568.6	563.1	567.2	566.8
10°	564.5	562.6	556.6	560.3	559.4
12.5°	556.6	554.8	548.3	552.5	551.1
15°	547.0	545.1	538.2	541.0	539.6
17.5°	535.9	533.6	527.1	529.0	528.1
20°	523.5	521.1	514.2	515.6	514.7
22.5°	510.1	506.9	500.0	502.7	500.9
25°	495.3	492.1	485.7	486.1	484.3
27.5°	478.8	475.5	469.5	468.6	466.3
30°	462.2	458.5	452.5	450.6	448.3
32.5°	444.7	441.4	435.0	432.7	430.4
35°	426.2	423.0	416.5	413.3	411.0
37.5°	406.9	404.1	397.2	394.0	390.7
40°	388.0	384.3	377.4	372.8	370.5
42.5°	367.7	365.9	358.0	352.5	351.1
45°	347.9	344.7	337.3	332.2	330.8
47.5°	327.2	324.9	317.9	312.4	308.7
50°	306.0	304.1	297.7	291.2	288.5
52.5°	285.2	282.9	276.0	270.5	266.8
55°	263.1	261.7	255.3	249.7	247.0
57.5°	242.4	241.0	234.5	229.0	226.2
60°	220.7	218.4	212.4	208.3	206.0
62.5°	199.5	197.7	191.2	187.5	185.2
65°	178.3	176.0	171.4	166.8	164.5
67.5°	156.7	154.8	150.2	145.6	145.1
70°	136.9	133.6	129.9	126.3	124.9
72.5°	115.7	112.4	109.7	106.9	105.5
75°	94.9	92.6	90.3	88.5	88.0
77.5°	74.6	73.7	71.4	71.0	69.6
80°	56.7	55.3	54.4	53.5	53.0
82.5°	39.2	38.7	38.7	38.2	37.8
85°	24.9	24.9	24.0	24.0	23.5
87.5°	12.0	11.5	11.1	11.1	11.1
90°	3.9	18.2	28.5	36.3	38.9
92.5°	19.5	16.9	27.2	35.0	35.0
95°	71.4	27.2	28.5	36.3	37.6
97.5°	136.2	164.8	28.5	35.0	36.3
100°	212.8	236.2	57.1	35.0	36.3
102.5°	298.5	314.0	329.6	37.6	37.6
105°	390.6	398.4	404.9	416.5	369.8
107.5°	474.9	478.8	487.9	494.4	499.6
110°	560.6	564.5	572.2	574.8	578.7

TEST NUMBER: P1033423

CATALOG NUMBER: S124DIW-B350D1340UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	643.6	651.4	654.0	652.7	657.9
115°	729.3	733.2	731.9	734.4	734.4
117.5°	805.8	811.0	814.9	813.6	813.6
120°	883.7	888.9	887.6	890.2	887.6
122.5°	956.3	958.9	961.5	962.8	960.2
125°	1025.1	1030.3	1027.7	1031.6	1032.9
127.5°	1091.3	1092.6	1099.1	1097.8	1096.5
130°	1154.9	1156.2	1160.1	1161.4	1161.4
132.5°	1213.3	1215.9	1221.1	1222.4	1221.1
135°	1271.7	1270.4	1275.6	1278.1	1280.7
137.5°	1323.6	1323.6	1330.1	1332.6	1331.4
140°	1374.2	1376.8	1379.4	1383.3	1384.6
142.5°	1419.6	1424.8	1426.1	1428.7	1428.7
145°	1466.3	1470.2	1470.2	1471.5	1474.1
147.5°	1502.6	1510.4	1509.1	1510.4	1511.7
150°	1542.9	1548.1	1546.8	1546.8	1548.1
152.5°	1576.6	1580.5	1577.9	1580.5	1579.2
155°	1607.7	1609.0	1605.1	1610.3	1606.4
157.5°	1635.0	1635.0	1629.8	1636.3	1629.8
160°	1658.3	1654.5	1653.2	1660.9	1653.2
162.5°	1679.1	1673.9	1672.6	1680.4	1671.3
165°	1696.0	1689.5	1689.5	1699.9	1688.2
167.5°	1710.3	1703.8	1702.5	1714.1	1701.2
170°	1721.9	1714.1	1715.4	1725.8	1712.8
172.5°	1729.7	1721.9	1723.2	1733.6	1719.3
175°	1734.9	1727.1	1728.4	1740.1	1724.5
177.5°	1738.8	1729.7	1732.3	1742.7	1727.1
180°	1734.9	1734.9	1734.9	1734.9	1734.9

(END OF REPORT)