

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033461

Luminaire Tested: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033461
REPORT IS A COMBINATION OF REPORTS P997460 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1560UB40-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6988.0 lumens
Efficiency: N/A
Efficacy: 107.2 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	30	30	22
1	92	87	84	80	81	78	75	72	59	57	55	42	41	40	27	26	26	26	26	19
2	83	76	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22	22	22	16
3	76	67	60	55	67	60	54	49	46	42	39	33	31	28	21	20	19	19	19	13
4	70	59	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16	16	16	12
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14	14	14	10
6	59	47	39	34	52	42	36	31	33	28	25	24	21	18	15	14	12	12	12	9
7	54	42	35	30	48	38	31	27	29	25	21	22	18	16	14	12	11	11	11	8
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10	10	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	9	9	6
10	43	32	25	20	38	29	23	19	22	18	15	17	14	11	11	9	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4509	4509	4509	4509
5°	4498	5174	4524	3887
10°	4465	6036	4499	3411
15°	4411	6958	4441	3051
20°	4354	7545	4385	2736
25°	4271	7459	4311	2503
30°	4189	6165	4240	2383
35°	4075	4594	4120	2310
40°	3941	3461	3980	2274
45°	3738	2777	3784	2226
50°	3494	2340	3544	2203
55°	3208	2037	3257	2178
60°	2929	1794	3015	2141
65°	2668	1544	2694	2052
70°	2360	1270	2412	1889
75°	2060	976	2046	1606
80°	1620	641	1600	1220
85°	1070	287	997	711

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5831 cd/sqm

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	0.8
10°-20°	166.1	2.4
20°-30°	263.9	3.8
30°-40°	293.2	4.2
40°-50°	266.7	3.8
50°-60°	217.9	3.1
60°-70°	155.6	2.2
70°-80°	85.6	1.2
80°-90°	27.3	0.4
90°-100°	128.2	1.8
100°-110°	384.0	5.5
110°-120°	652.4	9.3
120°-130°	860.4	12.3
130°-140°	966.4	13.8
140°-150°	949.8	13.6
150°-160°	798.9	11.4
160°-170°	531.5	7.6
170°-180°	186.1	2.7
0°-30°	483.9	6.9
0°-40°	777.1	11.1
0°-60°	1261.7	18.1
0°-90°	1530.2	21.9
90°-120°	1164.7	16.7
90°-150°	3941.3	56.4
90°-180°	5458.0	78.1
0°-180°	6988.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	553	553	553	553	553	
5°	551	649	554	488	551	52
15°	526	891	530	391	526	148
25°	480	946	485	318	480	221
35°	416	559	421	281	416	260
45°	332	314	336	252	332	256
55°	234	205	237	220	234	210
65°	146	132	147	176	146	144
75°	72	66	71	109	72	75
85°	15	14	14	34	15	17
90°	5	46	5	46	5	8
95°	91	120	91	120	91	99
105°	354	371	354	371	354	376
115°	663	657	663	657	663	654
125°	966	958	966	958	966	861
135°	1246	1248	1246	1248	1246	964
145°	1514	1515	1514	1515	1514	947
155°	1734	1733	1734	1733	1734	798
165°	1888	1883	1888	1883	1888	532
175°	1964	1955	1964	1955	1964	186
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	553.0	558.5	560.8	562.6	568.6	570.4	570.9	573.6	575.9	576.4	576.4
5°	550.7	559.4	566.3	572.7	582.3	586.5	591.5	597.0	604.3	608.9	611.2
7.5°	547.1	559.9	570.4	581.4	594.7	603.0	607.5	622.2	632.3	640.5	650.6
10°	541.6	558.1	573.2	589.2	608.0	618.1	628.2	646.0	660.2	676.3	689.1
12.5°	533.3	554.8	573.2	595.6	619.0	630.9	642.8	674.0	690.5	704.7	727.6
15°	526.0	547.5	573.6	596.5	625.4	643.3	660.7	680.8	707.0	737.7	759.6
17.5°	517.7	544.8	569.0	601.1	633.2	650.1	664.3	695.5	732.2	762.4	782.6
20°	506.3	533.8	565.8	599.7	637.8	651.1	669.8	711.5	744.5	774.3	807.3
22.5°	493.0	525.1	559.0	591.5	630.9	658.9	679.5	716.1	756.0	790.3	827.5
25°	480.2	515.0	544.8	589.2	630.9	649.7	673.1	716.6	760.1	801.8	839.8
27.5°	466.4	498.9	539.3	574.5	621.7	642.4	667.6	715.2	761.5	803.2	844.0
30°	451.3	486.1	519.6	561.3	607.1	633.7	657.0	708.8	756.0	799.5	837.5
32.5°	434.3	467.3	503.1	542.5	590.6	617.6	646.9	700.1	750.5	788.1	817.4
35°	416.5	449.9	481.1	521.4	570.9	597.9	626.3	685.0	734.9	765.6	782.6
37.5°	396.8	428.4	459.1	498.9	548.4	577.3	606.2	663.0	710.2	735.8	731.2
40°	378.0	406.4	434.8	472.4	524.1	554.8	580.0	637.3	678.6	689.5	674.4
42.5°	356.5	380.7	408.2	446.7	497.1	526.0	557.6	609.8	640.5	635.9	610.3
45°	332.2	353.7	381.2	417.4	468.7	498.5	525.1	574.5	597.0	585.5	538.8
47.5°	308.8	329.9	352.3	388.5	438.5	463.7	490.7	535.1	548.0	523.7	477.0
50°	283.6	301.0	324.4	358.7	405.5	432.1	454.5	490.2	494.8	465.0	416.5
52.5°	259.3	274.0	296.4	330.3	373.9	394.9	416.9	448.6	444.9	414.2	367.5
55°	233.7	247.4	268.0	299.2	337.7	357.8	376.6	404.6	396.8	365.2	324.4
57.5°	212.1	221.8	241.9	270.8	302.4	324.4	340.4	362.4	350.5	318.9	280.9
60°	187.4	199.3	216.3	239.6	270.8	285.4	299.6	314.3	306.1	275.8	241.9
62.5°	164.9	174.1	188.8	211.2	235.5	248.8	263.9	273.1	264.8	236.9	208.5
65°	145.7	153.0	164.5	182.8	206.2	217.2	225.9	234.6	227.7	201.6	181.0
67.5°	124.6	131.0	140.7	155.3	175.0	182.8	191.1	197.0	189.2	171.8	151.7
70°	105.8	110.4	119.6	130.6	144.3	151.7	158.5	164.5	157.6	142.9	127.8
72.5°	86.6	90.3	98.5	106.3	118.7	123.7	128.7	133.3	131.0	117.3	104.9
75°	71.5	72.8	78.3	84.8	92.6	98.0	101.7	104.5	102.6	91.6	83.8
77.5°	54.1	55.9	60.0	65.1	71.9	75.1	77.4	80.2	77.9	69.2	63.7
80°	39.4	39.9	42.2	46.7	51.3	51.8	54.1	57.7	56.4	50.4	46.3
82.5°	25.2	26.6	27.5	30.2	33.4	34.4	35.7	36.7	36.2	32.5	31.2
85°	14.7	14.7	15.6	17.4	18.3	19.7	20.2	20.6	21.5	19.2	17.9
87.5°	6.4	6.9	6.9	7.3	8.2	8.2	8.7	9.2	9.6	9.2	7.8
90°	4.6	8.3	12.0	15.7	19.4	21.3	22.7	25.4	28.1	30.8	33.5
92.5°	39.6	44.0	48.4	52.7	57.1	59.3	60.1	61.8	63.5	65.2	66.9
95°	91.3	94.3	97.4	100.4	103.5	105.0	106.2	108.5	110.9	113.2	115.6
97.5°	146.0	148.7	151.4	154.1	156.8	158.2	159.6	162.3	165.0	167.7	170.4
100°	213.0	214.4	215.7	217.1	218.4	219.1	220.6	223.7	226.7	229.8	232.8
102.5°	283.0	283.3	283.7	284.0	284.3	284.5	285.9	288.6	291.3	294.0	296.7
105°	354.5	354.8	355.2	355.5	355.8	356.0	356.7	358.0	359.4	360.7	362.1
107.5°	429.0	429.3	429.7	430.0	430.3	430.5	430.7	431.0	431.3	431.7	432.0
110°	505.1	505.8	506.4	507.1	507.8	508.1	507.9	507.6	507.3	506.9	506.6

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	584.2	584.2	584.2	584.2	584.2	584.2	583.9	583.2	582.5	581.8	581.1
115°	663.3	663.3	663.3	663.3	663.3	663.3	663.0	662.3	661.6	660.9	660.2
117.5°	737.8	737.8	737.8	737.8	737.8	737.8	737.6	737.3	737.0	736.6	736.3
120°	812.4	813.8	815.1	816.5	817.8	818.5	818.0	817.0	815.9	814.9	813.9
122.5°	890.0	890.3	890.7	891.0	891.3	891.5	891.3	891.0	890.7	890.3	890.0
125°	966.0	966.0	966.0	966.0	966.0	966.0	965.8	965.5	965.2	964.8	964.5
127.5°	1034.5	1035.5	1036.5	1037.5	1038.5	1039.0	1038.7	1038.0	1037.3	1036.7	1036.0
130°	1107.5	1108.5	1109.5	1110.6	1111.6	1112.1	1112.1	1112.1	1112.1	1112.1	1112.1
132.5°	1182.0	1182.7	1183.4	1184.1	1184.8	1185.1	1184.9	1184.6	1184.3	1183.9	1183.6
135°	1245.9	1247.9	1250.0	1252.0	1254.1	1255.1	1255.1	1255.1	1255.1	1255.1	1255.1
137.5°	1317.4	1318.4	1319.4	1320.5	1321.5	1322.0	1322.3	1323.0	1323.7	1324.3	1325.0
140°	1388.9	1389.6	1390.3	1391.0	1391.7	1392.0	1392.0	1392.0	1392.0	1392.0	1392.0
142.5°	1454.4	1455.1	1455.7	1456.4	1457.1	1457.4	1457.2	1456.9	1456.6	1456.2	1455.9
145°	1513.7	1515.1	1516.4	1517.8	1519.1	1519.8	1520.0	1520.3	1520.6	1521.0	1521.3
147.5°	1574.5	1576.2	1577.9	1579.6	1581.3	1582.1	1581.9	1581.6	1581.3	1580.9	1580.6
150°	1629.3	1630.7	1632.0	1633.4	1634.7	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4
152.5°	1681.0	1681.7	1682.4	1683.1	1683.8	1684.1	1684.3	1684.6	1684.9	1685.3	1685.6
155°	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.1	1733.8	1733.5	1733.1	1732.8
157.5°	1779.9	1779.2	1778.6	1777.9	1777.2	1776.9	1776.9	1776.9	1776.9	1776.9	1776.9
160°	1819.5	1819.1	1818.8	1818.4	1818.1	1817.9	1817.7	1817.4	1817.1	1816.7	1816.4
162.5°	1856.0	1855.0	1854.0	1852.9	1851.9	1851.4	1851.2	1850.9	1850.6	1850.2	1849.9
165°	1887.9	1886.9	1885.9	1884.9	1883.9	1883.4	1883.1	1882.4	1881.7	1881.0	1880.3
167.5°	1913.8	1912.4	1911.1	1909.7	1908.4	1907.7	1907.7	1907.7	1907.7	1907.7	1907.7
170°	1935.1	1933.4	1931.7	1930.0	1928.3	1927.5	1927.7	1928.0	1928.3	1928.7	1929.0
172.5°	1950.3	1948.9	1947.6	1946.2	1944.9	1944.2	1944.2	1944.2	1944.2	1944.2	1944.2
175°	1964.0	1962.3	1960.6	1958.9	1957.2	1956.4	1956.2	1955.9	1955.6	1955.2	1954.9
177.5°	1970.1	1968.4	1966.7	1965.0	1963.3	1962.5	1962.5	1962.5	1962.5	1962.5	1962.5
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	577.8	586.0	589.7	590.6	595.6	592.4	593.8	593.3	597.0	597.5	597.5
5°	619.9	629.5	632.7	637.3	644.2	646.0	644.6	647.4	652.4	648.8	654.3
7.5°	664.3	674.9	682.2	692.3	694.6	700.5	704.2	707.4	708.3	708.8	709.7
10°	705.6	718.9	729.0	745.9	749.6	752.8	768.8	762.4	770.6	767.9	768.8
12.5°	739.0	765.1	773.4	801.8	804.5	815.5	814.6	824.7	826.5	830.2	826.5
15°	783.0	813.3	826.5	842.6	851.7	864.6	866.9	880.6	886.1	891.1	886.1
17.5°	823.3	839.4	873.3	886.1	892.1	898.9	916.3	921.4	929.6	926.4	935.6
20°	843.5	866.4	902.1	924.1	933.3	939.7	954.4	962.2	965.4	965.4	966.3
22.5°	861.4	894.4	920.9	946.1	954.4	959.0	967.7	973.6	975.0	975.9	976.8
25°	877.4	907.2	928.7	942.9	946.1	946.1	951.2	947.5	941.5	946.1	948.9
27.5°	877.4	898.5	908.1	913.1	913.1	900.8	893.4	878.3	865.5	861.8	870.1
30°	862.7	872.4	859.1	846.7	837.1	828.8	800.0	777.1	772.5	769.3	781.6
32.5°	828.8	816.5	790.3	754.6	740.4	721.6	699.2	681.8	671.2	667.6	664.8
35°	768.8	736.7	702.8	654.7	644.6	620.8	590.1	577.3	559.9	559.4	565.4
37.5°	703.3	653.8	617.2	571.3	557.1	531.9	503.1	489.8	477.9	468.7	479.7
40°	626.8	583.7	527.8	490.2	470.1	456.8	432.5	417.9	412.4	407.8	414.6
42.5°	555.3	508.1	464.6	426.1	409.6	394.5	378.4	364.2	360.1	359.7	364.7
45°	484.3	438.0	397.7	364.7	354.2	345.0	329.4	325.3	318.4	313.8	316.1
47.5°	427.5	379.8	346.4	321.2	312.0	304.2	294.1	287.3	281.3	279.5	282.2
50°	371.6	339.5	305.1	284.1	277.2	269.9	262.1	255.7	252.9	251.1	252.9
52.5°	326.7	292.3	268.9	252.0	245.1	239.6	234.1	231.4	227.7	228.6	230.5
55°	286.4	256.1	236.4	224.0	219.9	217.6	210.8	207.6	206.2	205.3	206.2
57.5°	248.3	226.3	211.7	201.1	195.6	194.3	188.8	188.8	187.4	186.0	186.5
60°	218.1	199.3	185.1	176.9	175.9	173.6	170.0	169.5	166.3	167.7	168.1
62.5°	187.4	172.3	162.7	157.6	154.4	153.5	151.2	150.7	149.4	149.8	148.9
65°	163.1	150.7	141.1	137.0	135.6	135.2	133.3	132.0	131.0	132.0	131.0
67.5°	138.8	130.6	123.2	119.1	117.3	116.8	115.5	114.5	115.0	113.6	114.5
70°	115.9	107.7	103.1	100.8	99.9	98.5	98.5	98.5	98.5	97.6	97.1
72.5°	97.6	89.3	86.1	84.8	83.8	83.4	82.0	82.5	82.0	81.6	83.4
75°	77.4	72.4	69.2	67.8	68.7	67.4	66.0	66.9	65.5	66.0	67.8
77.5°	58.6	56.4	54.5	53.6	52.7	51.8	51.8	50.9	50.9	50.9	50.9
80°	42.6	42.2	38.9	38.5	38.5	37.6	37.6	37.6	37.6	37.1	37.6
82.5°	28.4	27.9	27.0	26.6	25.7	26.1	26.1	25.2	25.2	24.7	25.2
85°	16.5	16.5	15.6	15.1	14.7	15.1	14.2	13.7	14.2	13.7	14.2
87.5°	7.8	6.9	7.3	6.9	6.0	6.4	5.5	6.0	5.5	5.0	6.0
90°	35.5	37.5	39.6	41.6	42.6	42.9	43.6	44.3	44.9	45.6	44.9
92.5°	67.9	68.9	70.0	71.0	71.5	71.7	72.0	72.3	72.7	73.0	72.7
95°	116.6	117.6	118.7	119.7	120.2	120.2	120.2	120.2	120.2	120.2	120.2
97.5°	171.8	173.1	174.5	175.8	176.5	176.5	176.5	176.5	176.5	176.5	176.5
100°	233.5	234.1	234.8	235.5	235.8	235.8	235.8	235.8	235.8	235.8	235.8
102.5°	297.7	298.7	299.7	300.7	301.2	301.4	301.7	302.0	302.4	302.7	302.4
105°	363.1	364.1	365.1	366.1	366.6	367.1	368.1	369.2	370.2	371.2	370.2
107.5°	433.4	434.7	436.1	437.4	438.1	437.9	437.6	437.3	436.9	436.6	436.9
110°	505.9	505.2	504.5	503.8	503.5	504.0	505.0	506.1	507.1	508.1	507.1

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1
115°	659.9	659.5	659.2	658.9	658.7	658.5	658.2	657.9	657.5	657.2	657.5
117.5°	735.3	734.3	733.2	732.2	731.7	731.2	730.2	729.2	728.2	727.2	728.2
120°	812.2	810.5	808.8	807.1	806.3	806.6	807.3	808.0	808.6	809.3	808.6
122.5°	889.0	888.0	886.9	885.9	885.4	884.6	882.9	881.2	879.5	877.8	879.5
125°	963.8	963.2	962.5	961.8	961.5	961.2	960.5	959.8	959.1	958.4	959.1
127.5°	1035.3	1034.7	1034.0	1033.3	1033.0	1032.8	1032.5	1032.1	1031.8	1031.4	1031.8
130°	1111.4	1110.7	1110.0	1109.3	1109.0	1108.3	1107.0	1105.6	1104.3	1102.9	1104.3
132.5°	1182.9	1182.2	1181.5	1180.8	1180.5	1180.3	1180.0	1179.7	1179.3	1179.0	1179.3
135°	1254.4	1253.7	1253.0	1252.3	1252.0	1251.5	1250.5	1249.5	1248.5	1247.5	1248.5
137.5°	1324.0	1323.0	1322.0	1321.0	1320.5	1320.7	1321.0	1321.3	1321.7	1322.0	1321.7
140°	1391.7	1391.3	1391.0	1390.7	1390.5	1390.3	1390.0	1389.6	1389.3	1388.9	1389.3
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9
145°	1521.0	1520.6	1520.3	1520.0	1519.8	1519.3	1518.3	1517.2	1516.2	1515.2	1516.2
147.5°	1580.3	1579.9	1579.6	1579.3	1579.1	1578.9	1578.6	1578.3	1577.9	1577.6	1577.9
150°	1635.4	1635.4	1635.4	1635.4	1635.4	1635.2	1634.9	1634.6	1634.2	1633.9	1634.2
152.5°	1686.6	1687.6	1688.7	1689.7	1690.2	1689.7	1688.7	1687.6	1686.6	1685.6	1686.6
155°	1734.1	1735.5	1736.8	1738.1	1738.8	1738.1	1736.8	1735.5	1734.1	1732.8	1734.1
157.5°	1777.9	1778.9	1779.9	1780.9	1781.4	1780.9	1779.9	1778.9	1777.9	1776.9	1777.9
160°	1817.4	1818.4	1819.5	1820.5	1821.0	1820.2	1818.5	1816.8	1815.1	1813.4	1815.1
162.5°	1851.9	1853.9	1856.0	1858.0	1859.0	1858.2	1856.5	1854.8	1853.1	1851.4	1853.1
165°	1882.3	1884.3	1886.4	1888.4	1889.4	1888.7	1887.4	1886.1	1884.7	1883.4	1884.7
167.5°	1909.7	1911.7	1913.8	1915.8	1916.8	1915.8	1913.8	1911.7	1909.7	1907.7	1909.7
170°	1931.0	1933.0	1935.1	1937.1	1938.1	1936.9	1934.6	1932.2	1929.9	1927.5	1929.9
172.5°	1946.6	1949.0	1951.3	1953.7	1954.9	1953.7	1951.3	1949.0	1946.6	1944.2	1946.6
175°	1957.3	1959.6	1962.0	1964.3	1965.5	1964.3	1962.0	1959.6	1957.3	1954.9	1957.3
177.5°	1964.9	1967.2	1969.6	1971.9	1973.1	1971.7	1969.0	1966.3	1963.6	1960.9	1963.6
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	596.5	595.2	593.3	593.3	591.0	591.0	587.4	581.0	575.5	573.6	574.5
5°	647.4	647.9	645.1	642.8	638.7	635.5	629.5	618.1	614.4	607.1	602.0
7.5°	705.6	703.8	698.7	695.0	694.1	686.8	674.0	660.2	649.2	641.9	631.4
10°	771.1	763.8	756.4	754.2	748.7	736.3	721.6	706.5	691.4	675.3	657.5
12.5°	826.1	811.9	811.4	805.9	795.4	788.5	771.1	749.6	723.5	705.6	685.4
15°	885.2	871.9	860.9	850.8	845.8	825.6	811.0	783.9	752.8	733.5	719.8
17.5°	927.3	921.4	902.6	898.0	891.1	867.8	844.4	817.8	790.8	763.8	726.7
20°	961.2	957.6	945.2	938.8	927.8	909.5	881.1	850.4	819.2	780.7	745.9
22.5°	975.9	971.3	961.2	955.7	948.9	933.3	909.0	874.2	833.4	799.1	761.9
25°	947.0	955.3	952.5	950.2	947.5	938.3	920.0	889.3	849.5	810.5	764.2
27.5°	882.0	896.2	909.9	911.8	916.3	920.0	912.7	890.7	857.2	816.0	765.1
30°	794.5	800.9	828.8	837.1	843.5	866.9	880.6	875.1	849.5	812.3	765.6
32.5°	682.2	699.2	727.6	747.3	764.7	790.8	826.5	840.7	831.6	801.3	755.1
35°	575.9	596.1	629.1	654.3	671.7	708.8	750.9	781.6	793.1	778.0	736.7
37.5°	488.9	513.2	542.5	552.1	572.3	618.1	676.3	718.9	746.8	748.2	716.1
40°	423.4	435.7	459.1	473.7	493.5	531.9	588.8	645.1	687.3	701.5	684.5
42.5°	367.9	377.5	394.9	412.8	430.7	460.0	512.2	564.9	621.7	650.1	649.7
45°	323.9	334.0	345.9	360.6	373.0	404.6	445.8	499.9	548.9	592.9	603.9
47.5°	285.4	294.1	308.8	315.2	323.5	353.3	389.0	439.4	490.2	540.6	553.5
50°	257.0	264.4	274.4	278.6	287.7	309.7	339.0	379.8	436.2	482.5	506.3
52.5°	231.4	236.9	244.7	247.9	254.3	270.8	297.4	329.4	376.2	423.8	457.3
55°	209.4	213.0	218.5	222.2	226.8	241.5	261.2	290.0	330.3	371.6	404.1
57.5°	188.8	191.5	197.0	198.8	202.5	214.0	227.7	252.0	289.1	325.8	357.4
60°	169.5	171.4	174.6	178.7	181.4	189.2	202.1	222.2	252.0	285.4	311.1
62.5°	151.2	153.9	154.9	156.7	159.0	166.3	176.4	191.1	217.2	244.7	271.7
65°	132.4	134.7	136.5	137.0	139.3	144.8	153.9	166.8	183.7	207.6	232.8
67.5°	115.0	116.4	117.3	119.1	121.4	124.2	131.5	141.1	156.7	175.9	196.1
70°	99.0	99.0	100.3	100.8	103.5	106.8	110.0	119.1	132.9	148.4	162.2
72.5°	81.6	83.8	83.4	85.7	85.2	87.5	91.6	97.6	107.7	120.0	133.3
75°	66.4	67.8	67.8	67.8	68.7	70.6	72.8	78.3	86.1	96.2	104.0
77.5°	51.8	52.7	52.7	52.7	53.1	55.0	57.3	60.9	66.4	72.4	77.0
80°	37.1	38.0	38.0	38.9	38.9	39.4	41.7	43.5	46.3	50.9	55.4
82.5°	25.2	25.7	26.6	26.6	26.1	27.0	27.5	29.3	32.1	33.0	36.2
85°	13.7	14.2	14.7	14.7	15.1	16.0	15.6	17.4	17.4	19.2	20.2
87.5°	5.5	6.4	6.4	6.0	6.4	6.4	6.4	7.3	7.8	8.2	7.8
90°	44.3	43.6	42.9	42.6	41.6	39.6	37.5	35.5	33.5	30.8	28.1
92.5°	72.3	72.0	71.7	71.5	71.0	70.0	68.9	67.9	66.9	65.2	63.5
95°	120.2	120.2	120.2	120.2	119.7	118.7	117.6	116.6	115.6	113.2	110.9
97.5°	176.5	176.5	176.5	176.5	175.8	174.5	173.1	171.8	170.4	167.7	165.0
100°	235.8	235.8	235.8	235.8	235.5	234.8	234.1	233.5	232.8	229.8	226.7
102.5°	302.0	301.7	301.4	301.2	300.7	299.7	298.7	297.7	296.7	294.0	291.3
105°	369.2	368.1	367.1	366.6	366.1	365.1	364.1	363.1	362.1	360.7	359.4
107.5°	437.3	437.6	437.9	438.1	437.4	436.1	434.7	433.4	432.0	431.7	431.3
110°	506.1	505.0	504.0	503.5	503.8	504.5	505.2	505.9	506.6	506.9	507.3

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.8	582.5
115°	657.9	658.2	658.5	658.7	658.9	659.2	659.5	659.9	660.2	660.9	661.6
117.5°	729.2	730.2	731.2	731.7	732.2	733.2	734.3	735.3	736.3	736.6	737.0
120°	808.0	807.3	806.6	806.3	807.1	808.8	810.5	812.2	813.9	814.9	815.9
122.5°	881.2	882.9	884.6	885.4	885.9	886.9	888.0	889.0	890.0	890.3	890.7
125°	959.8	960.5	961.2	961.5	961.8	962.5	963.2	963.8	964.5	964.8	965.2
127.5°	1032.1	1032.5	1032.8	1033.0	1033.3	1034.0	1034.7	1035.3	1036.0	1036.7	1037.3
130°	1105.6	1107.0	1108.3	1109.0	1109.3	1110.0	1110.7	1111.4	1112.1	1112.1	1112.1
132.5°	1179.7	1180.0	1180.3	1180.5	1180.8	1181.5	1182.2	1182.9	1183.6	1183.9	1184.3
135°	1249.5	1250.5	1251.5	1252.0	1252.3	1253.0	1253.7	1254.4	1255.1	1255.1	1255.1
137.5°	1321.3	1321.0	1320.7	1320.5	1321.0	1322.0	1323.0	1324.0	1325.0	1324.3	1323.7
140°	1389.6	1390.0	1390.3	1390.5	1390.7	1391.0	1391.3	1391.7	1392.0	1392.0	1392.0
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1456.2	1456.6
145°	1517.2	1518.3	1519.3	1519.8	1520.0	1520.3	1520.6	1521.0	1521.3	1521.0	1520.6
147.5°	1578.3	1578.6	1578.9	1579.1	1579.3	1579.6	1579.9	1580.3	1580.6	1580.9	1581.3
150°	1634.6	1634.9	1635.2	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4
152.5°	1687.6	1688.7	1689.7	1690.2	1689.7	1688.7	1687.6	1686.6	1685.6	1685.3	1684.9
155°	1735.5	1736.8	1738.1	1738.8	1738.1	1736.8	1735.5	1734.1	1732.8	1733.1	1733.5
157.5°	1778.9	1779.9	1780.9	1781.4	1780.9	1779.9	1778.9	1777.9	1776.9	1776.9	1776.9
160°	1816.8	1818.5	1820.2	1821.0	1820.5	1819.5	1818.4	1817.4	1816.4	1816.7	1817.1
162.5°	1854.8	1856.5	1858.2	1859.0	1858.0	1856.0	1853.9	1851.9	1849.9	1850.2	1850.6
165°	1886.1	1887.4	1888.7	1889.4	1888.4	1886.4	1884.3	1882.3	1880.3	1881.0	1881.7
167.5°	1911.7	1913.8	1915.8	1916.8	1915.8	1913.8	1911.7	1909.7	1907.7	1907.7	1907.7
170°	1932.2	1934.6	1936.9	1938.1	1937.1	1935.1	1933.0	1931.0	1929.0	1928.7	1928.3
172.5°	1949.0	1951.3	1953.7	1954.9	1953.7	1951.3	1949.0	1946.6	1944.2	1944.2	1944.2
175°	1959.6	1962.0	1964.3	1965.5	1964.3	1962.0	1959.6	1957.3	1954.9	1955.2	1955.6
177.5°	1966.3	1969.0	1971.7	1973.1	1971.9	1969.6	1967.2	1964.9	1962.5	1962.5	1962.5
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	570.4	568.6	567.2	567.2	563.1	559.0	556.7	555.8	554.8	551.2	546.1
5°	593.8	587.8	583.7	579.6	572.7	565.4	558.1	553.9	548.0	539.7	533.8
7.5°	619.9	605.7	601.1	596.1	582.3	570.0	559.9	551.2	541.6	531.0	520.5
10°	641.9	626.8	616.7	608.0	590.1	573.6	558.5	545.7	533.3	519.6	506.7
12.5°	663.0	641.4	630.9	618.1	599.3	575.5	555.8	539.7	521.4	507.2	491.6
15°	692.3	656.1	638.7	630.4	605.2	577.3	553.5	529.6	514.5	493.0	479.2
17.5°	696.9	667.6	656.1	635.0	604.8	573.2	545.7	521.9	498.9	479.7	461.8
20°	712.9	674.4	656.1	642.8	603.0	570.9	540.6	509.9	488.0	467.3	447.2
22.5°	723.0	679.5	660.2	639.1	601.1	562.6	526.9	500.3	473.3	452.2	436.2
25°	720.2	676.7	655.2	635.5	589.2	550.7	518.7	484.7	459.5	436.6	415.6
27.5°	718.9	669.8	646.9	624.9	581.4	541.1	500.8	473.3	445.3	418.8	403.2
30°	715.2	661.1	634.6	610.7	565.4	523.2	488.9	456.8	428.8	404.6	383.9
32.5°	702.8	646.5	620.8	595.2	548.0	505.8	471.0	441.2	413.3	388.1	368.4
35°	686.3	629.1	601.1	574.1	526.9	484.3	452.2	421.1	394.9	370.7	351.9
37.5°	669.8	608.9	582.8	551.6	508.1	463.7	430.7	402.7	378.4	353.3	332.6
40°	646.0	585.1	556.2	529.6	478.8	437.1	406.9	381.7	357.8	334.0	316.6
42.5°	613.5	559.0	529.2	499.9	452.2	411.0	381.7	359.2	336.8	317.1	297.8
45°	580.5	527.4	500.8	474.7	422.9	383.9	356.9	336.3	317.5	296.0	280.4
47.5°	540.6	495.7	469.2	443.5	394.5	355.5	330.8	311.6	294.1	276.3	261.6
50°	499.9	460.9	436.6	410.1	363.3	328.1	303.8	287.7	273.5	256.6	244.7
52.5°	455.9	422.0	401.4	375.7	334.5	301.9	277.2	261.2	249.2	236.9	226.3
55°	409.1	384.4	362.4	341.8	302.9	273.5	251.5	237.3	229.1	217.6	208.5
57.5°	367.0	343.2	329.9	306.5	272.6	243.7	226.3	214.4	204.8	197.9	190.6
60°	323.0	303.8	289.1	272.2	242.4	218.1	199.8	192.9	182.8	177.8	174.6
62.5°	280.9	267.1	253.4	240.5	214.0	191.1	177.3	168.6	162.7	157.6	154.9
65°	241.0	228.2	218.5	207.1	185.1	166.8	153.9	147.1	141.1	139.7	136.5
67.5°	202.1	196.6	186.0	176.9	158.1	143.9	134.2	125.5	122.3	121.0	118.2
70°	169.1	162.7	154.4	146.6	132.4	120.0	111.3	108.1	103.5	103.1	99.9
72.5°	139.3	131.5	125.5	119.6	109.0	98.0	93.5	88.9	86.6	84.8	83.4
75°	110.4	104.9	100.8	95.8	86.6	79.3	72.8	71.0	69.6	69.2	68.3
77.5°	82.5	78.8	77.0	71.9	65.5	59.1	56.4	53.6	53.6	52.7	53.1
80°	58.6	56.4	54.1	51.3	45.8	43.1	40.8	38.9	38.0	37.6	38.0
82.5°	37.1	35.7	35.3	33.4	29.8	28.4	26.6	25.2	25.2	25.2	25.2
85°	20.6	20.6	20.6	17.9	16.5	15.1	14.2	13.7	13.7	13.7	14.2
87.5°	8.7	8.7	7.3	7.3	6.9	6.0	5.5	5.5	6.0	6.0	6.4
90°	25.4	22.7	21.3	19.4	15.7	12.0	8.3	4.6	8.3	12.0	15.7
92.5°	61.8	60.1	59.3	57.1	52.7	48.4	44.0	39.6	44.0	48.4	52.7
95°	108.5	106.2	105.0	103.5	100.4	97.4	94.3	91.3	94.3	97.4	100.4
97.5°	162.3	159.6	158.2	156.8	154.1	151.4	148.7	146.0	148.7	151.4	154.1
100°	223.7	220.6	219.1	218.4	217.1	215.7	214.4	213.0	214.4	215.7	217.1
102.5°	288.6	285.9	284.5	284.3	284.0	283.7	283.3	283.0	283.3	283.7	284.0
105°	358.0	356.7	356.0	355.8	355.5	355.2	354.8	354.5	354.8	355.2	355.5
107.5°	431.0	430.7	430.5	430.3	430.0	429.7	429.3	429.0	429.3	429.7	430.0
110°	507.6	507.9	508.1	507.8	507.1	506.4	505.8	505.1	505.8	506.4	507.1

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	583.2	583.9	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
115°	662.3	663.0	663.3	663.3	663.3	663.3	663.3	663.3	663.3	663.3	663.3
117.5°	737.3	737.6	737.8	737.8	737.8	737.8	737.8	737.8	737.8	737.8	737.8
120°	817.0	818.0	818.5	817.8	816.5	815.1	813.8	812.4	813.8	815.1	816.5
122.5°	891.0	891.3	891.5	891.3	891.0	890.7	890.3	890.0	890.3	890.7	891.0
125°	965.5	965.8	966.0	966.0	966.0	966.0	966.0	966.0	966.0	966.0	966.0
127.5°	1038.0	1038.7	1039.0	1038.5	1037.5	1036.5	1035.5	1034.5	1035.5	1036.5	1037.5
130°	1112.1	1112.1	1112.1	1111.6	1110.6	1109.5	1108.5	1107.5	1108.5	1109.5	1110.6
132.5°	1184.6	1184.9	1185.1	1184.8	1184.1	1183.4	1182.7	1182.0	1182.7	1183.4	1184.1
135°	1255.1	1255.1	1255.1	1254.1	1252.0	1250.0	1247.9	1245.9	1247.9	1250.0	1252.0
137.5°	1323.0	1322.3	1322.0	1321.5	1320.5	1319.4	1318.4	1317.4	1318.4	1319.4	1320.5
140°	1392.0	1392.0	1392.0	1391.7	1391.0	1390.3	1389.6	1388.9	1389.6	1390.3	1391.0
142.5°	1456.9	1457.2	1457.4	1457.1	1456.4	1455.7	1455.1	1454.4	1455.1	1455.7	1456.4
145°	1520.3	1520.0	1519.8	1519.1	1517.8	1516.4	1515.1	1513.7	1515.1	1516.4	1517.8
147.5°	1581.6	1581.9	1582.1	1581.3	1579.6	1577.9	1576.2	1574.5	1576.2	1577.9	1579.6
150°	1635.4	1635.4	1635.4	1634.7	1633.4	1632.0	1630.7	1629.3	1630.7	1632.0	1633.4
152.5°	1684.6	1684.3	1684.1	1683.8	1683.1	1682.4	1681.7	1681.0	1681.7	1682.4	1683.1
155°	1733.8	1734.1	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3
157.5°	1776.9	1776.9	1776.9	1777.2	1777.9	1778.6	1779.2	1779.9	1779.2	1778.6	1777.9
160°	1817.4	1817.7	1817.9	1818.1	1818.4	1818.8	1819.1	1819.5	1819.1	1818.8	1818.4
162.5°	1850.9	1851.2	1851.4	1851.9	1852.9	1854.0	1855.0	1856.0	1855.0	1854.0	1852.9
165°	1882.4	1883.1	1883.4	1883.9	1884.9	1885.9	1886.9	1887.9	1886.9	1885.9	1884.9
167.5°	1907.7	1907.7	1907.7	1908.4	1909.7	1911.1	1912.4	1913.8	1912.4	1911.1	1909.7
170°	1928.0	1927.7	1927.5	1928.3	1930.0	1931.7	1933.4	1935.1	1933.4	1931.7	1930.0
172.5°	1944.2	1944.2	1944.2	1944.9	1946.2	1947.6	1948.9	1950.3	1948.9	1947.6	1946.2
175°	1955.9	1956.2	1956.4	1957.2	1958.9	1960.6	1962.3	1964.0	1962.3	1960.6	1958.9
177.5°	1962.5	1962.5	1962.5	1963.3	1965.0	1966.7	1968.4	1970.1	1968.4	1966.7	1965.0
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	544.8	542.9	543.8	539.3	535.1	529.2	524.1	523.2	522.3	525.1	523.2
5°	529.2	526.9	524.6	519.1	510.9	505.8	498.5	498.0	495.3	491.2	492.1
7.5°	512.2	510.9	507.7	498.9	491.6	482.9	477.0	471.9	469.6	466.0	464.6
10°	498.5	493.5	490.7	481.1	472.4	463.2	455.4	451.8	447.6	444.4	442.1
12.5°	479.7	478.3	470.5	462.8	455.4	444.9	438.9	428.4	422.9	425.6	424.7
15°	467.3	460.9	459.1	448.1	435.7	428.8	417.9	411.0	408.7	404.6	399.5
17.5°	450.8	446.7	440.3	430.2	416.0	406.4	398.6	392.2	389.4	383.9	379.8
20°	435.3	428.4	423.4	414.2	400.4	388.1	378.4	374.3	367.5	362.9	360.6
22.5°	421.1	416.0	408.7	394.9	383.0	371.1	359.7	353.7	347.3	344.5	340.9
25°	403.6	395.4	390.4	375.2	362.4	352.8	342.3	334.5	330.8	326.2	325.3
27.5°	386.7	378.9	373.0	359.7	344.1	331.7	325.3	319.8	313.4	313.4	311.1
30°	369.7	364.2	355.1	342.3	327.6	315.7	308.3	303.3	301.0	299.2	298.7
32.5°	352.8	345.5	340.0	322.6	311.6	300.6	295.1	290.9	288.2	287.7	288.2
35°	335.4	327.1	321.6	306.1	295.1	285.0	282.7	279.0	277.7	277.2	279.5
37.5°	317.1	310.6	303.8	290.9	278.6	272.6	268.0	266.7	266.2	268.9	269.9
40°	300.1	294.6	288.2	274.4	265.3	258.9	256.6	255.2	257.0	259.8	261.2
42.5°	284.1	276.3	271.2	258.9	250.6	247.0	244.2	244.2	246.0	249.2	251.5
45°	267.1	261.2	256.1	245.1	237.8	233.7	233.2	233.7	236.0	238.2	241.0
47.5°	250.6	244.7	239.2	230.0	223.6	221.3	220.8	221.3	225.0	228.2	231.4
50°	235.5	229.1	224.0	215.3	210.3	207.6	208.0	210.3	213.0	217.6	221.8
52.5°	217.6	213.0	208.5	200.7	196.1	194.3	195.6	197.5	202.5	205.7	210.8
55°	200.2	196.1	192.4	186.5	182.8	181.4	182.4	185.1	189.2	194.7	200.7
57.5°	184.2	179.6	175.9	171.8	167.7	168.1	168.6	172.3	177.3	182.4	189.2
60°	166.3	163.6	160.4	155.3	153.5	153.5	154.9	159.0	163.6	171.8	177.8
62.5°	150.3	146.6	144.3	141.1	138.4	138.8	142.0	145.7	151.2	158.1	165.9
65°	133.8	129.7	127.8	125.1	124.2	124.6	126.9	132.4	138.4	144.3	151.7
67.5°	115.5	114.1	112.3	109.5	110.4	110.9	113.2	117.8	124.2	130.1	138.4
70°	99.9	97.1	96.7	94.4	94.4	95.8	100.3	103.5	109.5	115.9	124.6
72.5°	83.4	81.1	81.1	79.3	80.6	82.0	84.3	88.9	94.4	100.8	108.1
75°	66.4	65.5	66.4	65.5	65.5	67.8	70.6	74.2	80.2	87.1	93.0
77.5°	51.3	51.3	50.9	52.2	52.2	53.6	57.3	60.9	65.5	71.0	77.4
80°	37.6	37.6	37.6	38.9	40.3	40.3	42.6	47.2	51.3	55.0	60.9
82.5°	25.7	25.7	25.7	26.6	28.4	28.4	31.2	33.9	38.5	41.7	44.4
85°	15.6	15.6	15.1	16.0	16.5	17.9	20.2	22.0	24.3	27.0	29.8
87.5°	6.9	6.9	7.3	7.8	8.2	9.2	10.1	11.0	13.3	14.2	15.6
90°	19.4	21.3	22.7	25.4	28.1	30.8	33.5	35.5	37.5	39.6	41.6
92.5°	57.1	59.3	60.1	61.8	63.5	65.2	66.9	67.9	68.9	70.0	71.0
95°	103.5	105.0	106.2	108.5	110.9	113.2	115.6	116.6	117.6	118.7	119.7
97.5°	156.8	158.2	159.6	162.3	165.0	167.7	170.4	171.8	173.1	174.5	175.8
100°	218.4	219.1	220.6	223.7	226.7	229.8	232.8	233.5	234.1	234.8	235.5
102.5°	284.3	284.5	285.9	288.6	291.3	294.0	296.7	297.7	298.7	299.7	300.7
105°	355.8	356.0	356.7	358.0	359.4	360.7	362.1	363.1	364.1	365.1	366.1
107.5°	430.3	430.5	430.7	431.0	431.3	431.7	432.0	433.4	434.7	436.1	437.4
110°	507.8	508.1	507.9	507.6	507.3	506.9	506.6	505.9	505.2	504.5	503.8

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	584.2	584.2	583.9	583.2	582.5	581.8	581.1	581.1	581.1	581.1	581.1
115°	663.3	663.3	663.0	662.3	661.6	660.9	660.2	659.9	659.5	659.2	658.9
117.5°	737.8	737.8	737.6	737.3	737.0	736.6	736.3	735.3	734.3	733.2	732.2
120°	817.8	818.5	818.0	817.0	815.9	814.9	813.9	812.2	810.5	808.8	807.1
122.5°	891.3	891.5	891.3	891.0	890.7	890.3	890.0	889.0	888.0	886.9	885.9
125°	966.0	966.0	965.8	965.5	965.2	964.8	964.5	963.8	963.2	962.5	961.8
127.5°	1038.5	1039.0	1038.7	1038.0	1037.3	1036.7	1036.0	1035.3	1034.7	1034.0	1033.3
130°	1111.6	1112.1	1112.1	1112.1	1112.1	1112.1	1112.1	1111.4	1110.7	1110.0	1109.3
132.5°	1184.8	1185.1	1184.9	1184.6	1184.3	1183.9	1183.6	1182.9	1182.2	1181.5	1180.8
135°	1254.1	1255.1	1255.1	1255.1	1255.1	1255.1	1255.1	1254.4	1253.7	1253.0	1252.3
137.5°	1321.5	1322.0	1322.3	1323.0	1323.7	1324.3	1325.0	1324.0	1323.0	1322.0	1321.0
140°	1391.7	1392.0	1392.0	1392.0	1392.0	1392.0	1392.0	1391.7	1391.3	1391.0	1390.7
142.5°	1457.1	1457.4	1457.2	1456.9	1456.6	1456.2	1455.9	1455.9	1455.9	1455.9	1455.9
145°	1519.1	1519.8	1520.0	1520.3	1520.6	1521.0	1521.3	1521.0	1520.6	1520.3	1520.0
147.5°	1581.3	1582.1	1581.9	1581.6	1581.3	1580.9	1580.6	1580.3	1579.9	1579.6	1579.3
150°	1634.7	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4
152.5°	1683.8	1684.1	1684.3	1684.6	1684.9	1685.3	1685.6	1686.6	1687.6	1688.7	1689.7
155°	1734.3	1734.3	1734.1	1733.8	1733.5	1733.1	1732.8	1734.1	1735.5	1736.8	1738.1
157.5°	1777.2	1776.9	1776.9	1776.9	1776.9	1776.9	1776.9	1777.9	1778.9	1779.9	1780.9
160°	1818.1	1817.9	1817.7	1817.4	1817.1	1816.7	1816.4	1817.4	1818.4	1819.5	1820.5
162.5°	1851.9	1851.4	1851.2	1850.9	1850.6	1850.2	1849.9	1851.9	1853.9	1856.0	1858.0
165°	1883.9	1883.4	1883.1	1882.4	1881.7	1881.0	1880.3	1882.3	1884.3	1886.4	1888.4
167.5°	1908.4	1907.7	1907.7	1907.7	1907.7	1907.7	1907.7	1909.7	1911.7	1913.8	1915.8
170°	1928.3	1927.5	1927.7	1928.0	1928.3	1928.7	1929.0	1931.0	1933.0	1935.1	1937.1
172.5°	1944.9	1944.2	1944.2	1944.2	1944.2	1944.2	1944.2	1946.6	1949.0	1951.3	1953.7
175°	1957.2	1956.4	1956.2	1955.9	1955.6	1955.2	1954.9	1957.3	1959.6	1962.0	1964.3
177.5°	1963.3	1962.5	1962.5	1962.5	1962.5	1962.5	1962.5	1964.9	1967.2	1969.6	1971.9
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	521.9	521.4	519.1	520.0	517.3	518.2	519.6	520.0	521.9	520.5	520.0
5°	489.8	488.9	487.5	486.1	485.7	487.5	484.3	485.2	486.1	487.5	489.3
7.5°	463.7	463.2	461.8	459.5	458.6	457.7	458.2	461.4	460.9	460.5	463.7
10°	439.8	440.3	437.6	437.1	434.3	433.9	434.3	435.3	436.6	438.5	438.9
12.5°	415.1	421.1	416.0	414.2	410.1	412.4	413.3	409.1	411.4	412.8	419.7
15°	399.5	396.8	393.6	393.6	391.7	390.8	388.5	391.7	393.6	396.3	395.4
17.5°	378.0	373.4	371.6	369.7	370.2	372.0	367.0	374.3	374.3	375.7	373.4
20°	359.2	355.5	353.3	352.3	351.0	350.0	349.6	351.4	354.2	355.1	357.4
22.5°	339.5	339.5	335.8	334.5	333.5	332.2	334.5	333.1	334.9	336.8	340.4
25°	323.0	323.0	321.6	319.8	318.4	317.5	318.9	318.4	319.8	322.1	323.0
27.5°	309.7	308.3	307.9	307.4	307.0	307.4	307.0	308.3	309.7	310.2	309.3
30°	298.3	296.9	297.4	297.4	297.8	297.4	296.9	298.3	298.7	297.8	298.3
32.5°	287.7	287.7	288.6	289.1	289.1	289.6	290.0	289.1	289.6	288.2	288.6
35°	279.0	279.9	280.9	281.3	281.8	281.3	282.2	281.8	280.9	279.9	279.5
37.5°	270.3	271.2	273.1	273.5	274.9	275.4	274.4	274.4	274.0	272.2	271.2
40°	261.2	262.1	264.4	265.7	266.7	268.0	267.1	267.1	265.3	263.4	262.1
42.5°	252.5	254.3	256.6	258.0	259.8	259.8	259.8	258.9	256.6	254.7	253.4
45°	243.7	244.2	247.4	249.7	251.5	251.5	251.5	250.2	248.8	245.1	243.3
47.5°	234.1	235.5	239.2	241.5	243.3	243.7	243.7	242.4	239.6	236.4	234.1
50°	223.6	225.9	230.0	233.2	235.5	236.4	235.0	234.1	230.9	227.3	224.5
52.5°	213.5	216.3	221.3	224.0	227.3	227.7	227.3	225.9	222.2	217.2	214.9
55°	203.4	205.7	211.2	215.8	218.5	219.5	218.5	216.3	211.7	206.6	204.3
57.5°	192.4	195.6	201.6	206.2	209.4	209.8	208.9	206.6	203.0	196.6	193.3
60°	181.0	185.1	191.1	195.6	199.8	200.2	199.3	196.1	191.5	185.1	182.4
62.5°	169.5	172.7	179.6	184.6	187.9	190.1	188.3	185.1	180.5	174.1	170.0
65°	156.2	160.8	166.8	171.4	175.0	175.5	174.6	171.8	166.8	159.9	156.7
67.5°	143.4	146.6	152.6	158.5	159.9	161.3	159.9	157.2	153.0	147.1	142.5
70°	127.8	130.6	137.9	142.0	143.9	145.2	144.3	141.6	137.9	132.4	128.7
72.5°	112.3	114.5	121.4	124.6	128.3	127.8	127.4	125.5	120.5	116.8	114.5
75°	95.8	98.5	103.1	107.2	108.6	108.6	108.6	107.2	104.0	98.0	95.8
77.5°	80.6	82.0	85.7	88.0	89.3	89.8	89.3	87.1	85.2	81.1	79.7
80°	61.9	65.5	68.3	68.7	70.6	70.6	70.6	69.6	67.8	63.7	63.2
82.5°	46.7	47.6	50.4	51.8	52.7	52.2	52.2	50.4	49.9	47.6	46.7
85°	31.6	33.0	32.5	34.4	34.8	33.9	33.9	34.8	32.5	33.0	31.6
87.5°	17.4	17.4	18.3	17.9	19.7	19.7	18.8	19.2	18.3	17.9	17.4
90°	42.6	42.9	43.6	44.3	44.9	45.6	44.9	44.3	43.6	42.9	42.6
92.5°	71.5	71.7	72.0	72.3	72.7	73.0	72.7	72.3	72.0	71.7	71.5
95°	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2
97.5°	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5
100°	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
102.5°	301.2	301.4	301.7	302.0	302.4	302.7	302.4	302.0	301.7	301.4	301.2
105°	366.6	367.1	368.1	369.2	370.2	371.2	370.2	369.2	368.1	367.1	366.6
107.5°	438.1	437.9	437.6	437.3	436.9	436.6	436.9	437.3	437.6	437.9	438.1
110°	503.5	504.0	505.0	506.1	507.1	508.1	507.1	506.1	505.0	504.0	503.5

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1
115°	658.7	658.5	658.2	657.9	657.5	657.2	657.5	657.9	658.2	658.5	658.7
117.5°	731.7	731.2	730.2	729.2	728.2	727.2	728.2	729.2	730.2	731.2	731.7
120°	806.3	806.6	807.3	808.0	808.6	809.3	808.6	808.0	807.3	806.6	806.3
122.5°	885.4	884.6	882.9	881.2	879.5	877.8	879.5	881.2	882.9	884.6	885.4
125°	961.5	961.2	960.5	959.8	959.1	958.4	959.1	959.8	960.5	961.2	961.5
127.5°	1033.0	1032.8	1032.5	1032.1	1031.8	1031.4	1031.8	1032.1	1032.5	1032.8	1033.0
130°	1109.0	1108.3	1107.0	1105.6	1104.3	1102.9	1104.3	1105.6	1107.0	1108.3	1109.0
132.5°	1180.5	1180.3	1180.0	1179.7	1179.3	1179.0	1179.3	1179.7	1180.0	1180.3	1180.5
135°	1252.0	1251.5	1250.5	1249.5	1248.5	1247.5	1248.5	1249.5	1250.5	1251.5	1252.0
137.5°	1320.5	1320.7	1321.0	1321.3	1321.7	1322.0	1321.7	1321.3	1321.0	1320.7	1320.5
140°	1390.5	1390.3	1390.0	1389.6	1389.3	1388.9	1389.3	1389.6	1390.0	1390.3	1390.5
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9
145°	1519.8	1519.3	1518.3	1517.2	1516.2	1515.2	1516.2	1517.2	1518.3	1519.3	1519.8
147.5°	1579.1	1578.9	1578.6	1578.3	1577.9	1577.6	1577.9	1578.3	1578.6	1578.9	1579.1
150°	1635.4	1635.2	1634.9	1634.6	1634.2	1633.9	1634.2	1634.6	1634.9	1635.2	1635.4
152.5°	1690.2	1689.7	1688.7	1687.6	1686.6	1685.6	1686.6	1687.6	1688.7	1689.7	1690.2
155°	1738.8	1738.1	1736.8	1735.5	1734.1	1732.8	1734.1	1735.5	1736.8	1738.1	1738.8
157.5°	1781.4	1780.9	1779.9	1778.9	1777.9	1776.9	1777.9	1778.9	1779.9	1780.9	1781.4
160°	1821.0	1820.2	1818.5	1816.8	1815.1	1813.4	1815.1	1816.8	1818.5	1820.2	1821.0
162.5°	1859.0	1858.2	1856.5	1854.8	1853.1	1851.4	1853.1	1854.8	1856.5	1858.2	1859.0
165°	1889.4	1888.7	1887.4	1886.1	1884.7	1883.4	1884.7	1886.1	1887.4	1888.7	1889.4
167.5°	1916.8	1915.8	1913.8	1911.7	1909.7	1907.7	1909.7	1911.7	1913.8	1915.8	1916.8
170°	1938.1	1936.9	1934.6	1932.2	1929.9	1927.5	1929.9	1932.2	1934.6	1936.9	1938.1
172.5°	1954.9	1953.7	1951.3	1949.0	1946.6	1944.2	1946.6	1949.0	1951.3	1953.7	1954.9
175°	1965.5	1964.3	1962.0	1959.6	1957.3	1954.9	1957.3	1959.6	1962.0	1964.3	1965.5
177.5°	1973.1	1971.7	1969.0	1966.3	1963.6	1960.9	1963.6	1966.3	1969.0	1971.7	1973.1
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0	553.0
2.5°	520.0	522.8	520.0	521.9	522.8	525.1	526.0	530.1	531.5	534.7	534.7
5°	488.9	490.2	490.7	492.5	494.4	498.9	502.2	508.1	515.0	515.9	520.0
7.5°	463.7	466.0	469.6	468.3	471.5	478.3	482.5	489.8	496.7	500.3	505.4
10°	441.2	444.0	445.3	446.7	452.7	458.6	465.0	470.1	479.2	484.7	488.9
12.5°	422.9	420.6	423.4	428.4	435.3	438.9	447.6	455.4	462.3	468.3	471.9
15°	399.1	400.9	403.6	412.4	414.2	423.4	426.6	435.3	448.1	453.6	458.2
17.5°	376.2	382.1	387.6	390.8	396.3	403.6	412.8	422.4	430.7	437.1	442.6
20°	357.8	363.8	367.0	369.3	374.8	384.9	393.6	405.5	416.0	421.1	428.4
22.5°	343.2	343.2	347.8	354.6	357.8	367.5	374.8	387.6	399.1	405.5	412.4
25°	324.8	327.6	331.3	337.2	341.8	349.6	360.1	371.1	383.5	389.0	397.7
27.5°	309.7	312.9	318.0	319.3	323.9	330.8	341.8	353.7	366.5	372.5	379.8
30°	298.3	300.1	301.9	304.7	308.8	314.8	323.9	334.5	350.0	354.6	363.8
32.5°	288.2	289.1	290.0	292.3	294.6	300.6	307.9	319.3	332.2	339.0	347.3
35°	279.0	278.1	278.6	279.9	282.2	284.5	292.3	301.9	313.8	322.1	328.5
37.5°	270.3	268.5	268.0	268.0	268.9	271.7	277.7	285.9	298.7	305.6	312.0
40°	260.7	258.9	258.0	257.5	257.0	258.9	263.4	271.7	281.8	288.2	295.5
42.5°	251.5	249.7	247.4	247.0	246.0	247.0	250.2	258.0	266.7	273.1	279.0
45°	242.4	239.2	236.4	234.6	235.0	233.7	236.0	241.9	252.0	256.1	262.1
47.5°	232.3	228.6	225.0	223.1	221.3	222.2	223.1	228.2	236.9	241.0	247.0
50°	222.7	217.6	213.5	211.2	209.8	208.9	209.8	214.9	221.3	225.0	230.0
52.5°	211.7	206.6	202.5	198.8	197.0	195.6	196.1	200.7	206.6	210.3	215.3
55°	201.6	195.2	189.7	185.1	183.7	183.3	182.8	186.0	191.1	194.7	198.8
57.5°	190.1	183.7	177.8	172.3	169.5	169.1	169.1	170.0	176.4	179.1	181.4
60°	178.7	171.8	165.4	160.4	156.2	154.9	154.4	156.2	159.4	162.2	165.4
62.5°	165.9	159.0	151.2	146.6	142.5	138.8	140.2	140.7	145.2	146.6	149.4
65°	153.5	145.7	139.3	132.0	127.4	125.1	124.2	125.1	128.7	129.2	131.0
67.5°	139.3	132.0	124.2	119.1	115.0	110.9	110.0	110.0	111.8	113.2	115.5
70°	125.5	118.2	109.5	104.0	99.9	96.2	94.8	94.4	95.8	96.7	99.0
72.5°	109.5	102.2	95.8	89.8	84.8	82.0	80.6	79.7	81.1	82.0	82.5
75°	92.6	86.6	80.2	74.2	71.0	68.3	66.4	65.1	66.0	66.0	66.0
77.5°	76.5	70.6	65.5	61.4	57.3	54.1	52.7	51.3	51.8	51.8	52.7
80°	59.6	55.4	51.3	47.6	44.0	41.2	40.3	38.9	38.0	37.6	37.6
82.5°	44.0	40.8	37.1	33.9	32.1	29.3	28.4	26.6	26.6	26.1	26.1
85°	29.3	27.5	23.8	21.5	20.2	18.8	17.9	17.0	15.6	15.6	15.1
87.5°	15.6	14.7	13.7	11.0	11.0	9.6	9.2	8.7	7.3	7.8	7.8
90°	41.6	39.6	37.5	35.5	33.5	30.8	28.1	25.4	22.7	21.3	19.4
92.5°	71.0	70.0	68.9	67.9	66.9	65.2	63.5	61.8	60.1	59.3	57.1
95°	119.7	118.7	117.6	116.6	115.6	113.2	110.9	108.5	106.2	105.0	103.5
97.5°	175.8	174.5	173.1	171.8	170.4	167.7	165.0	162.3	159.6	158.2	156.8
100°	235.5	234.8	234.1	233.5	232.8	229.8	226.7	223.7	220.6	219.1	218.4
102.5°	300.7	299.7	298.7	297.7	296.7	294.0	291.3	288.6	285.9	284.5	284.3
105°	366.1	365.1	364.1	363.1	362.1	360.7	359.4	358.0	356.7	356.0	355.8
107.5°	437.4	436.1	434.7	433.4	432.0	431.7	431.3	431.0	430.7	430.5	430.3
110°	503.8	504.5	505.2	505.9	506.6	506.9	507.3	507.6	507.9	508.1	507.8

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	581.1	581.1	581.1	581.1	581.1	581.8	582.5	583.2	583.9	584.2	584.2
115°	658.9	659.2	659.5	659.9	660.2	660.9	661.6	662.3	663.0	663.3	663.3
117.5°	732.2	733.2	734.3	735.3	736.3	736.6	737.0	737.3	737.6	737.8	737.8
120°	807.1	808.8	810.5	812.2	813.9	814.9	815.9	817.0	818.0	818.5	817.8
122.5°	885.9	886.9	888.0	889.0	890.0	890.3	890.7	891.0	891.3	891.5	891.3
125°	961.8	962.5	963.2	963.8	964.5	964.8	965.2	965.5	965.8	966.0	966.0
127.5°	1033.3	1034.0	1034.7	1035.3	1036.0	1036.7	1037.3	1038.0	1038.7	1039.0	1038.5
130°	1109.3	1110.0	1110.7	1111.4	1112.1	1112.1	1112.1	1112.1	1112.1	1112.1	1111.6
132.5°	1180.8	1181.5	1182.2	1182.9	1183.6	1183.9	1184.3	1184.6	1184.9	1185.1	1184.8
135°	1252.3	1253.0	1253.7	1254.4	1255.1	1255.1	1255.1	1255.1	1255.1	1255.1	1254.1
137.5°	1321.0	1322.0	1323.0	1324.0	1325.0	1324.3	1323.7	1323.0	1322.3	1322.0	1321.5
140°	1390.7	1391.0	1391.3	1391.7	1392.0	1392.0	1392.0	1392.0	1392.0	1392.0	1391.7
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1456.2	1456.6	1456.9	1457.2	1457.4	1457.1
145°	1520.0	1520.3	1520.6	1521.0	1521.3	1521.0	1520.6	1520.3	1520.0	1519.8	1519.1
147.5°	1579.3	1579.6	1579.9	1580.3	1580.6	1580.9	1581.3	1581.6	1581.9	1582.1	1581.3
150°	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1634.7
152.5°	1689.7	1688.7	1687.6	1686.6	1685.6	1685.3	1684.9	1684.6	1684.3	1684.1	1683.8
155°	1738.1	1736.8	1735.5	1734.1	1732.8	1733.1	1733.5	1733.8	1734.1	1734.3	1734.3
157.5°	1780.9	1779.9	1778.9	1777.9	1776.9	1776.9	1776.9	1776.9	1776.9	1776.9	1777.2
160°	1820.5	1819.5	1818.4	1817.4	1816.4	1816.7	1817.1	1817.4	1817.7	1817.9	1818.1
162.5°	1858.0	1856.0	1853.9	1851.9	1849.9	1850.2	1850.6	1850.9	1851.2	1851.4	1851.9
165°	1888.4	1886.4	1884.3	1882.3	1880.3	1881.0	1881.7	1882.4	1883.1	1883.4	1883.9
167.5°	1915.8	1913.8	1911.7	1909.7	1907.7	1907.7	1907.7	1907.7	1907.7	1907.7	1908.4
170°	1937.1	1935.1	1933.0	1931.0	1929.0	1928.7	1928.3	1928.0	1927.7	1927.5	1928.3
172.5°	1953.7	1951.3	1949.0	1946.6	1944.2	1944.2	1944.2	1944.2	1944.2	1944.2	1944.9
175°	1964.3	1962.0	1959.6	1957.3	1954.9	1955.2	1955.6	1955.9	1956.2	1956.4	1957.2
177.5°	1971.9	1969.6	1967.2	1964.9	1962.5	1962.5	1962.5	1962.5	1962.5	1962.5	1963.3
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	553.0	553.0	553.0	553.0
2.5°	537.9	542.5	546.6	553.0
5°	526.0	532.4	541.1	550.7
7.5°	512.2	522.3	533.8	547.1
10°	499.4	510.9	525.5	541.6
12.5°	486.1	499.9	515.9	533.3
15°	471.0	484.7	502.6	526.0
17.5°	457.3	473.7	493.0	517.7
20°	441.2	456.8	477.9	506.3
22.5°	427.0	444.9	468.3	493.0
25°	411.4	427.0	450.4	480.2
27.5°	395.9	415.1	437.6	466.4
30°	380.7	396.8	421.1	451.3
32.5°	364.2	383.5	405.9	434.3
35°	346.4	364.7	385.8	416.5
37.5°	330.3	348.2	369.7	396.8
40°	312.5	331.3	351.0	378.0
42.5°	295.1	312.0	331.7	356.5
45°	278.1	292.8	310.6	332.2
47.5°	260.7	273.1	289.6	308.8
50°	241.9	255.2	267.6	283.6
52.5°	224.5	236.0	246.0	259.3
55°	207.6	215.3	223.6	233.7
57.5°	189.7	195.6	201.6	212.1
60°	171.8	177.3	180.5	187.4
62.5°	154.4	156.7	160.8	164.9
65°	135.2	138.4	140.7	145.7
67.5°	117.8	119.1	121.4	124.6
70°	99.4	102.6	103.5	105.8
72.5°	83.8	85.2	86.1	86.6
75°	66.4	67.8	68.7	71.5
77.5°	52.2	51.8	53.6	54.1
80°	38.5	37.1	37.6	39.4
82.5°	25.2	25.7	25.2	25.2
85°	15.6	15.1	14.2	14.7
87.5°	6.9	6.9	6.4	6.4
90°	15.7	12.0	8.3	4.6
92.5°	52.7	48.4	44.0	39.6
95°	100.4	97.4	94.3	91.3
97.5°	154.1	151.4	148.7	146.0
100°	217.1	215.7	214.4	213.0
102.5°	284.0	283.7	283.3	283.0
105°	355.5	355.2	354.8	354.5
107.5°	430.0	429.7	429.3	429.0
110°	507.1	506.4	505.8	505.1

TEST NUMBER: P1033461

CATALOG NUMBER: S124DIW-B350D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	584.2	584.2	584.2	584.2
115°	663.3	663.3	663.3	663.3
117.5°	737.8	737.8	737.8	737.8
120°	816.5	815.1	813.8	812.4
122.5°	891.0	890.7	890.3	890.0
125°	966.0	966.0	966.0	966.0
127.5°	1037.5	1036.5	1035.5	1034.5
130°	1110.6	1109.5	1108.5	1107.5
132.5°	1184.1	1183.4	1182.7	1182.0
135°	1252.0	1250.0	1247.9	1245.9
137.5°	1320.5	1319.4	1318.4	1317.4
140°	1391.0	1390.3	1389.6	1388.9
142.5°	1456.4	1455.7	1455.1	1454.4
145°	1517.8	1516.4	1515.1	1513.7
147.5°	1579.6	1577.9	1576.2	1574.5
150°	1633.4	1632.0	1630.7	1629.3
152.5°	1683.1	1682.4	1681.7	1681.0
155°	1734.3	1734.3	1734.3	1734.3
157.5°	1777.9	1778.6	1779.2	1779.9
160°	1818.4	1818.8	1819.1	1819.5
162.5°	1852.9	1854.0	1855.0	1856.0
165°	1884.9	1885.9	1886.9	1887.9
167.5°	1909.7	1911.1	1912.4	1913.8
170°	1930.0	1931.7	1933.4	1935.1
172.5°	1946.2	1947.6	1948.9	1950.3
175°	1958.9	1960.6	1962.3	1964.0
177.5°	1965.0	1966.7	1968.4	1970.1
180°	1967.0	1967.0	1967.0	1967.0

(END OF REPORT)