

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034112

Luminaire Tested: S124RDIW-B350D770UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034112
REPORT IS A COMBINATION OF REPORTS P1000470 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B350D770UB40-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4491.0 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034112

CATALOG NUMBER: S124RDIW-B350D770UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034112

CATALOG NUMBER: S124RDIW-B350D770UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	94	90	86	82	84	81	77	75	64	62	60	48	47	46	34	34	33
2	85	78	72	68	76	71	66	61	56	53	50	43	40	39	30	29	28
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24
4	71	61	53	48	64	55	49	44	44	39	36	34	31	28	24	22	21
5	65	54	46	41	59	49	42	37	39	35	31	30	27	24	22	20	18
6	60	49	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4880	4880	4880
5°	4881	4736	4737
10°	4840	4586	4531
15°	4773	4400	4291
20°	4686	4188	4016
25°	4578	3959	3747
30°	4471	3726	3445
35°	4354	3489	3150
40°	4214	3235	2847
45°	4084	2981	2547
50°	3935	2705	2242
55°	3775	2423	1928
60°	3597	2122	1617
65°	3425	1777	1318
70°	3179	1415	1008
75°	2867	1030	705
80°	2394	633	506
85°	1797	364	279

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4084 cd/sqm

TEST NUMBER: P1034112

CATALOG NUMBER: S124RDIW-B350D770UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.3	1.3
10°-20°	156.9	3.5
20°-30°	226.6	5.0
30°-40°	256.8	5.7
40°-50°	247.9	5.5
50°-60°	206.1	4.6
60°-70°	142.3	3.2
70°-80°	71.9	1.6
80°-90°	20.3	0.5
90°-100°	33.3	0.7
100°-110°	219.4	4.9
110°-120°	419.0	9.3
120°-130°	531.9	11.8
130°-140°	569.0	12.7
140°-150°	532.1	11.8
150°-160°	429.1	9.6
160°-170°	276.7	6.2
170°-180°	95.4	2.1
0°-30°	439.8	9.8
0°-40°	696.6	15.5
0°-60°	1150.6	25.6
0°-90°	1385.1	30.8
90°-120°	671.8	15.0
90°-150°	2304.8	51.3
90°-180°	3106.0	69.2
0°-180°	4491.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	598	598	598	598	598	
5°	598	596	590	595	594	57
15°	569	565	554	553	550	160
25°	515	506	488	480	475	237
35°	445	430	407	392	384	278
45°	363	346	318	296	288	280
55°	275	257	227	203	194	246
65°	187	167	138	118	113	185
75°	100	82	61	50	48	105
85°	25	16	14	13	13	27
90°	2	10	16	21	22	4
95°	41	16	16	21	22	51
105°	226	230	234	241	214	237
115°	422	424	423	425	425	415
125°	593	596	595	597	598	530
135°	736	735	738	740	741	567
145°	848	851	851	851	853	530
155°	930	931	929	932	929	429
165°	981	978	978	984	977	277
175°	1004	999	1000	1007	998	96
180°	1004	1004	1004	1004	1004	

TEST NUMBER: P1034112

CATALOG NUMBER: S124RDIW-B350D770UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	598.5	598.5	598.5	598.5	598.5
2.5°	600.4	598.5	593.5	598.5	598.1
5°	597.6	595.8	590.3	594.9	594.0
7.5°	593.5	591.7	584.8	588.0	586.6
10°	587.1	584.8	576.5	578.4	576.5
12.5°	578.8	576.1	566.0	566.9	564.2
15°	569.2	565.1	553.6	552.7	549.5
17.5°	558.2	552.3	539.0	536.7	532.1
20°	544.9	539.0	523.4	519.7	513.8
22.5°	530.3	523.4	506.4	500.5	495.9
25°	514.7	506.4	487.6	479.8	475.3
27.5°	498.6	488.6	468.8	459.7	453.3
30°	481.7	470.2	448.7	437.2	429.9
32.5°	463.8	450.5	428.1	414.3	407.4
35°	445.0	430.3	407.4	391.8	383.6
37.5°	425.3	410.2	385.0	368.0	359.8
40°	404.2	389.1	363.0	343.7	335.5
42.5°	384.1	368.0	340.5	320.8	312.1
45°	363.0	346.0	318.5	296.1	287.8
47.5°	341.4	324.0	295.6	272.2	263.1
50°	319.4	301.6	272.2	249.3	240.6
52.5°	297.0	279.6	249.3	225.9	216.8
55°	275.0	256.6	226.9	203.0	194.3
57.5°	253.4	234.2	204.9	180.6	174.2
60°	230.1	211.7	182.4	158.6	151.2
62.5°	209.0	189.7	159.5	137.9	132.4
65°	187.0	167.3	137.9	118.2	112.7
67.5°	164.1	145.3	117.8	100.4	94.0
70°	142.5	123.3	97.2	82.0	77.5
72.5°	119.6	102.7	78.4	66.0	61.9
75°	99.5	82.5	61.0	50.4	47.7
77.5°	78.4	63.7	45.4	38.0	37.1
80°	58.2	44.9	31.2	29.8	29.3
82.5°	40.8	28.9	22.5	21.5	21.1
85°	24.7	15.6	14.2	13.3	13.3
87.5°	10.5	6.9	6.4	6.0	6.4
90°	2.3	10.5	16.5	21.0	22.5
92.5°	11.3	9.8	15.8	20.3	20.3
95°	41.3	15.8	16.5	21.0	21.8
97.5°	78.8	95.3	16.5	20.3	21.0
100°	123.1	136.6	33.0	20.3	21.0
102.5°	172.7	181.7	190.7	21.8	21.8
105°	226.0	230.5	234.2	241.0	214.0
107.5°	274.8	277.0	282.3	286.0	289.0
110°	324.3	326.6	331.1	332.6	334.8

TEST NUMBER: P1034112

CATALOG NUMBER: S124RDIW-B350D770UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.4	376.9	378.4	377.6	380.6
115°	421.9	424.2	423.4	424.9	424.9
117.5°	466.2	469.2	471.5	470.7	470.7
120°	511.3	514.3	513.5	515.0	513.5
122.5°	553.3	554.8	556.3	557.0	555.5
125°	593.1	596.1	594.6	596.8	597.6
127.5°	631.4	632.1	635.9	635.1	634.4
130°	668.2	668.9	671.2	671.9	671.9
132.5°	701.9	703.4	706.4	707.2	706.4
135°	735.7	735.0	738.0	739.5	741.0
137.5°	765.8	765.8	769.5	771.0	770.3
140°	795.0	796.5	798.0	800.3	801.0
142.5°	821.3	824.3	825.1	826.6	826.6
145°	848.3	850.6	850.6	851.3	852.8
147.5°	869.4	873.9	873.1	873.9	874.6
150°	892.6	895.6	894.9	894.9	895.6
152.5°	912.2	914.4	912.9	914.4	913.7
155°	930.2	930.9	928.7	931.7	929.4
157.5°	945.9	945.9	942.9	946.7	942.9
160°	959.4	957.2	956.4	960.9	956.4
162.5°	971.5	968.5	967.7	972.2	967.0
165°	981.2	977.5	977.5	983.5	976.7
167.5°	989.5	985.7	985.0	991.7	984.2
170°	996.2	991.7	992.5	998.5	991.0
172.5°	1000.7	996.2	997.0	1003.0	994.7
175°	1003.7	999.2	1000.0	1006.7	997.7
177.5°	1006.0	1000.7	1002.2	1008.2	999.2
180°	1003.7	1003.7	1003.7	1003.7	1003.7

(END OF REPORT)