

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033466

Luminaire Tested: S124DIW-B350D1560UB50-4F0-XX-W2A-D

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033466
REPORT IS A COMBINATION OF REPORTS P997471 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D1560UB50-4F0-XX-W2A-D
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7440.0 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033466

CATALOG NUMBER: S124DIW-B350D1560UB50-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1033466

CATALOG NUMBER: S124DIW-B350D1560UB50-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	99	99	99	99	87	87	87	87	65	65	65	44	44	44	26	26	26
1	90	86	82	78	79	75	72	69	56	54	52	38	37	36	22	21	21
2	82	75	69	64	72	66	61	57	49	46	43	33	31	30	19	18	17
3	74	65	58	53	65	58	52	47	43	39	36	29	27	25	17	16	15
4	68	58	50	44	59	51	44	40	38	34	30	26	23	21	15	14	12
5	62	51	43	38	54	45	38	34	34	29	26	23	20	18	13	12	11
6	57	45	38	32	50	40	34	29	30	26	22	21	18	16	12	10	9
7	53	41	33	28	46	36	30	25	27	23	19	19	16	14	11	9	8
8	49	37	29	24	42	33	26	22	25	20	17	17	14	12	10	8	7
9	45	33	26	21	39	30	23	19	22	18	15	16	13	11	9	8	6
10	42	30	24	19	37	27	21	17	20	16	13	14	11	10	8	7	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3227	3227	3227
5°	3235	3143	3148
10°	3214	3081	3072
15°	3184	3011	2986
20°	3140	2936	2902
25°	3090	2853	2812
30°	3035	2770	2720
35°	2974	2686	2638
40°	2925	2605	2554
45°	2851	2530	2478
50°	2789	2444	2399
55°	2725	2361	2308
60°	2625	2258	2222
65°	2516	2147	2119
70°	2383	2020	2000
75°	2196	1878	1887
80°	1987	1734	1769
85°	1710	1589	1673

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 90°
Luminance: 3751 cd/sqm

TEST NUMBER: P1033466

CATALOG NUMBER: S124DIW-B350D1560UB50-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.5	0.5
10°-20°	107.4	1.4
20°-30°	162.4	2.2
30°-40°	196.5	2.6
40°-50°	207.7	2.8
50°-60°	195.5	2.6
60°-70°	162.2	2.2
70°-80°	113.8	1.5
80°-90°	68.2	0.9
90°-100°	103.5	1.4
100°-110°	458.3	6.2
110°-120°	840.1	11.3
120°-130°	1053.1	14.2
130°-140°	1119.8	15.1
140°-150°	1043.7	14.0
150°-160°	840.9	11.3
160°-170°	542.3	7.3
170°-180°	186.9	2.5
0°-30°	307.3	4.1
0°-40°	503.8	6.8
0°-60°	907.0	12.2
0°-90°	1251.3	16.8
90°-120°	1402.0	18.8
90°-150°	4618.5	62.1
90°-180°	6189.0	83.2
0°-180°	7440.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	396	396	396	396	396	
5°	396	395	392	395	395	38
15°	380	380	379	383	382	107
25°	347	350	351	356	357	160
35°	304	309	314	320	321	190
45°	253	262	270	278	280	196
55°	198	208	221	230	233	177
65°	137	152	167	178	181	136
75°	76	93	111	124	128	81
85°	24	42	62	75	80	24
90°	12	45	76	98	104	9
95°	87	51	71	92	97	104
105°	447	464	488	513	463	468
115°	830	838	851	863	866	817
125°	1164	1170	1178	1190	1195	1040
135°	1443	1441	1450	1460	1466	1112
145°	1663	1667	1667	1671	1676	1039
155°	1823	1824	1820	1826	1822	841
165°	1923	1916	1916	1927	1914	543
175°	1967	1958	1960	1973	1955	187
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1033466

CATALOG NUMBER: S124DIW-B350D1560UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	395.7	395.7	395.7	395.7	395.7
2.5°	397.4	396.1	392.6	395.7	395.2
5°	396.1	394.8	391.7	395.2	394.8
7.5°	393.5	392.6	389.9	393.9	393.5
10°	389.9	389.5	387.3	391.2	390.8
12.5°	385.0	385.0	383.7	387.3	387.3
15°	379.7	380.2	378.8	382.8	382.4
17.5°	372.6	374.0	373.5	377.5	377.1
20°	365.1	366.4	366.9	371.3	371.3
22.5°	356.7	358.5	359.3	363.8	364.7
25°	347.4	350.0	351.4	356.2	356.7
27.5°	337.2	341.2	342.9	347.4	347.8
30°	327.0	330.5	333.6	338.5	339.4
32.5°	315.9	320.3	323.9	329.7	330.5
35°	304.0	309.3	313.7	319.9	321.2
37.5°	292.0	298.2	303.5	309.7	311.0
40°	280.5	286.2	292.4	299.1	300.9
42.5°	267.2	273.8	281.4	288.9	290.2
45°	253.4	261.9	270.3	277.8	280.0
47.5°	240.6	249.0	258.8	266.3	268.9
50°	226.4	236.2	245.9	254.8	257.4
52.5°	212.2	222.0	233.5	242.4	245.0
55°	198.5	207.8	221.1	230.0	232.6
57.5°	183.0	194.5	207.4	218.0	220.2
60°	167.9	179.4	194.1	204.3	207.8
62.5°	153.3	166.2	180.8	191.0	194.5
65°	137.4	151.5	166.6	177.7	181.2
67.5°	122.3	137.4	153.3	164.4	167.9
70°	106.8	121.8	138.7	150.6	153.7
72.5°	91.7	107.2	125.4	136.9	140.5
75°	76.2	92.6	111.2	123.6	127.6
77.5°	61.6	78.9	98.4	110.8	115.2
80°	48.3	66.0	85.5	98.8	102.4
82.5°	35.0	53.6	73.1	86.8	90.8
85°	23.5	42.1	62.0	75.3	79.8
87.5°	14.6	32.8	52.3	65.1	69.1
90°	11.5	45.4	76.3	97.9	104.4
92.5°	28.7	41.3	72.1	93.3	96.9
95°	86.7	51.3	70.9	91.7	97.2
97.5°	159.8	205.1	68.7	87.6	93.0
100°	246.2	284.2	98.4	85.3	89.9
102.5°	343.3	370.7	405.2	85.7	89.2
105°	446.9	464.5	488.2	512.6	463.2
107.5°	542.5	554.4	580.2	598.7	607.6
110°	639.1	649.7	674.1	687.2	695.2

TEST NUMBER: P1033466

CATALOG NUMBER: S124DIW-B350D1560UB50-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	732.9	747.0	764.5	772.9	782.2
115°	829.6	837.9	850.6	863.3	866.4
117.5°	916.4	924.9	942.6	950.4	954.0
120°	1004.1	1011.3	1022.8	1034.6	1035.2
122.5°	1086.5	1089.5	1104.4	1114.7	1114.9
125°	1164.1	1169.5	1177.7	1190.5	1194.6
127.5°	1239.2	1240.1	1256.4	1262.9	1264.5
130°	1310.7	1311.8	1323.3	1332.8	1335.4
132.5°	1377.0	1379.5	1390.7	1399.7	1400.9
135°	1442.8	1441.3	1450.3	1460.3	1465.9
137.5°	1501.6	1501.1	1510.3	1519.9	1520.6
140°	1559.0	1561.4	1564.9	1575.0	1578.8
142.5°	1610.0	1615.9	1616.9	1624.8	1626.5
145°	1663.0	1667.0	1667.0	1671.1	1675.8
147.5°	1704.2	1712.6	1711.1	1713.0	1716.3
150°	1749.8	1755.2	1753.8	1753.8	1755.2
152.5°	1787.6	1792.0	1789.1	1792.0	1790.6
155°	1822.9	1824.4	1820.0	1825.9	1821.5
157.5°	1853.8	1853.8	1847.9	1855.3	1847.9
160°	1880.3	1875.9	1874.4	1883.2	1874.4
162.5°	1903.8	1898.0	1896.5	1905.3	1895.0
165°	1923.0	1915.6	1915.6	1927.4	1914.1
167.5°	1939.2	1931.8	1930.3	1943.6	1928.9
170°	1952.4	1943.6	1945.0	1956.8	1942.1
172.5°	1961.2	1952.4	1953.9	1965.6	1949.5
175°	1967.1	1958.3	1959.8	1973.0	1955.3
177.5°	1971.5	1961.2	1964.2	1975.9	1958.3
180°	1967.1	1967.1	1967.1	1967.1	1967.1

(END OF REPORT)