

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033525

Luminaire Tested: S124DIW-B350D770UB50-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033525
REPORT IS A COMBINATION OF REPORTS P997601 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B350D770UB50-4F0-XX-W2A-A1
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4082.0 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31
3	79	70	63	57	71	64	57	53	52	47	44	41	38	35	30	29	27
4	72	62	54	48	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	44	37	31	51	41	34	29	34	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	31	25	22	24	21	18	19	16	14
9	49	37	29	25	44	34	27	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	20	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4362	4362	4362	4362
5°	4351	5004	4376	3760
10°	4318	5838	4351	3299
15°	4266	6730	4296	2951
20°	4211	7298	4241	2646
25°	4130	7214	4170	2421
30°	4052	5963	4101	2305
35°	3941	4444	3985	2235
40°	3812	3347	3849	2200
45°	3615	2687	3660	2153
50°	3379	2264	3428	2132
55°	3102	1970	3152	2107
60°	2834	1735	2917	2072
65°	2580	1492	2606	1985
70°	2285	1228	2334	1828
75°	1991	943	1980	1552
80°	1567	620	1551	1178
85°	1033	279	968	688

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 5640 cd/sqm

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	1.3
10°-20°	160.7	3.9
20°-30°	255.3	6.3
30°-40°	283.6	6.9
40°-50°	257.9	6.3
50°-60°	210.8	5.2
60°-70°	150.5	3.7
70°-80°	82.8	2.0
80°-90°	24.4	0.6
90°-100°	61.2	1.5
100°-110°	183.2	4.5
110°-120°	311.3	7.6
120°-130°	410.5	10.1
130°-140°	461.1	11.3
140°-150°	453.2	11.1
150°-160°	381.1	9.3
160°-170°	253.6	6.2
170°-180°	88.8	2.2
0°-30°	468.0	11.5
0°-40°	751.6	18.4
0°-60°	1220.4	29.9
0°-90°	1478.0	36.2
90°-120°	555.7	13.6
90°-150°	1880.4	46.1
90°-180°	2604.0	63.8
0°-180°	4082.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	535	535	535	535	535	
5°	533	628	536	472	533	51
15°	509	862	512	378	509	144
25°	464	915	469	307	464	214
35°	403	541	407	272	403	252
45°	321	304	325	243	321	248
55°	226	198	230	212	226	203
65°	141	128	142	170	141	139
75°	69	64	69	105	69	73
85°	14	13	13	33	14	17
90°	2	22	2	22	2	4
95°	44	57	44	57	44	47
105°	169	177	169	177	169	179
115°	316	314	316	314	316	312
125°	461	457	461	457	461	411
135°	594	595	594	595	594	460
145°	722	723	722	723	722	452
155°	827	827	827	827	827	381
165°	901	899	901	899	901	254
175°	937	933	937	933	937	89
180°	938	938	938	938	938	

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	534.9	540.2	542.4	544.2	550.0	551.7	552.2	554.8	557.1	557.5	557.5
5°	532.7	541.1	547.7	553.9	563.3	567.2	572.1	577.4	584.5	589.0	591.2
7.5°	529.1	541.5	551.7	562.4	575.2	583.2	587.6	601.8	611.6	619.5	629.3
10°	523.8	539.8	554.4	569.9	588.1	597.8	607.6	624.9	638.6	654.1	666.5
12.5°	515.8	536.7	554.4	576.1	598.7	610.2	621.8	651.9	667.8	681.6	703.7
15°	508.7	529.6	554.8	577.0	604.9	622.2	639.0	658.5	683.8	713.5	734.8
17.5°	500.8	526.9	550.4	581.4	612.4	628.8	642.6	672.7	708.2	737.4	756.9
20°	489.7	516.3	547.3	580.1	616.9	629.7	647.9	688.2	720.1	748.9	780.8
22.5°	476.8	507.9	540.7	572.1	610.2	637.3	657.2	692.7	731.2	764.5	800.3
25°	464.4	498.1	526.9	569.9	610.2	628.4	651.0	693.1	735.2	775.5	812.3
27.5°	451.1	482.6	521.6	555.7	601.4	621.3	645.7	691.8	736.5	776.9	816.3
30°	436.5	470.2	502.5	542.9	587.2	612.9	635.5	685.6	731.2	773.3	810.1
32.5°	420.1	452.0	486.6	524.7	571.2	597.4	625.7	677.1	725.9	762.2	790.6
35°	402.8	435.2	465.3	504.3	552.2	578.3	605.8	662.5	710.8	740.5	756.9
37.5°	383.8	414.4	444.0	482.6	530.5	558.4	586.3	641.3	686.9	711.7	707.3
40°	365.6	393.1	420.6	456.9	507.0	536.7	561.0	616.4	656.3	667.0	652.3
42.5°	344.8	368.3	394.9	432.1	480.8	508.7	539.3	589.8	619.5	615.1	590.3
45°	321.3	342.1	368.7	403.7	453.4	482.2	507.9	555.7	577.4	566.4	521.2
47.5°	298.7	319.1	340.8	375.8	424.1	448.5	474.6	517.6	530.0	506.5	461.3
50°	274.3	291.2	313.8	347.0	392.2	417.9	439.6	474.2	478.6	449.8	402.8
52.5°	250.8	265.0	286.7	319.5	361.6	382.0	403.3	433.9	430.3	400.6	355.4
55°	226.0	239.3	259.2	289.4	326.6	346.1	364.3	391.3	383.8	353.2	313.8
57.5°	205.2	214.5	234.0	261.9	292.5	313.8	329.3	350.5	339.0	308.4	271.7
60°	181.3	192.8	209.2	231.8	261.9	276.1	289.8	304.0	296.0	266.8	234.0
62.5°	159.5	168.4	182.6	204.3	227.8	240.6	255.3	264.1	256.1	229.1	201.6
65°	140.9	148.0	159.1	176.8	199.4	210.1	218.5	226.9	220.3	195.0	175.0
67.5°	120.5	126.7	136.0	150.2	169.3	176.8	184.8	190.6	183.0	166.2	146.7
70°	102.4	106.8	115.7	126.3	139.6	146.7	153.3	159.1	152.4	138.3	123.6
72.5°	83.8	87.3	95.3	102.8	114.8	119.7	124.5	129.0	126.7	113.4	101.5
75°	69.1	70.5	75.8	82.0	89.5	94.8	98.4	101.0	99.3	88.6	81.1
77.5°	52.3	54.1	58.1	62.9	69.6	72.7	74.9	77.6	75.3	66.9	61.6
80°	38.1	38.6	40.8	45.2	49.6	50.1	52.3	55.8	54.5	48.7	44.8
82.5°	24.4	25.7	26.6	29.2	32.4	33.2	34.6	35.5	35.0	31.5	30.1
85°	14.2	14.2	15.1	16.8	17.7	19.1	19.5	19.9	20.8	18.6	17.3
87.5°	6.2	6.6	6.6	7.1	8.0	8.0	8.4	8.9	9.3	8.9	7.5
90°	2.2	4.0	5.8	7.5	9.3	10.2	10.8	12.1	13.4	14.7	16.0
92.5°	18.9	21.0	23.1	25.2	27.3	28.3	28.7	29.5	30.3	31.1	31.9
95°	43.5	45.0	46.4	47.9	49.4	50.1	50.7	51.8	52.9	54.1	55.2
97.5°	69.7	71.0	72.3	73.6	74.9	75.5	76.1	77.4	78.7	80.0	81.3
100°	101.6	102.2	102.9	103.5	104.2	104.5	105.2	106.7	108.2	109.6	111.1
102.5°	135.0	135.2	135.3	135.5	135.6	135.7	136.3	137.6	138.9	140.2	141.5
105°	169.1	169.3	169.4	169.6	169.7	169.8	170.1	170.8	171.4	172.1	172.7
107.5°	204.7	204.9	205.0	205.2	205.3	205.4	205.5	205.6	205.8	205.9	206.1
110°	241.0	241.3	241.6	241.9	242.2	242.4	242.3	242.2	242.0	241.9	241.7

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	278.7	278.7	278.7	278.7	278.7	278.7	278.5	278.2	277.9	277.6	277.3
115°	316.5	316.5	316.5	316.5	316.5	316.5	316.3	316.0	315.7	315.3	315.0
117.5°	352.0	352.0	352.0	352.0	352.0	352.0	351.9	351.8	351.6	351.5	351.3
120°	387.6	388.2	388.9	389.5	390.2	390.5	390.3	389.8	389.3	388.8	388.3
122.5°	424.6	424.8	424.9	425.1	425.2	425.3	425.2	425.1	424.9	424.8	424.6
125°	460.9	460.9	460.9	460.9	460.9	460.9	460.8	460.7	460.5	460.4	460.2
127.5°	493.6	494.1	494.5	495.0	495.5	495.7	495.5	495.2	494.9	494.6	494.3
130°	528.4	528.9	529.4	529.9	530.4	530.6	530.6	530.6	530.6	530.6	530.6
132.5°	564.0	564.3	564.6	564.9	565.2	565.4	565.3	565.2	565.0	564.9	564.7
135°	594.5	595.5	596.4	597.4	598.3	598.8	598.8	598.8	598.8	598.8	598.8
137.5°	628.6	629.1	629.5	630.0	630.5	630.7	630.9	631.2	631.5	631.9	632.2
140°	662.7	663.0	663.3	663.6	663.9	664.1	664.1	664.1	664.1	664.1	664.1
142.5°	693.9	694.2	694.5	694.8	695.1	695.3	695.2	695.1	694.9	694.8	694.6
145°	722.2	722.8	723.5	724.1	724.8	725.1	725.2	725.3	725.5	725.6	725.8
147.5°	751.2	752.0	752.8	753.7	754.5	754.9	754.8	754.6	754.5	754.3	754.1
150°	777.4	778.0	778.7	779.3	780.0	780.3	780.3	780.3	780.3	780.3	780.3
152.5°	802.0	802.3	802.7	803.0	803.3	803.5	803.6	803.7	803.9	804.0	804.2
155°	827.4	827.4	827.4	827.4	827.4	827.4	827.3	827.2	827.0	826.9	826.7
157.5°	849.2	848.9	848.6	848.3	848.0	847.8	847.8	847.8	847.8	847.8	847.8
160°	868.1	867.9	867.8	867.6	867.5	867.4	867.3	867.1	867.0	866.8	866.6
162.5°	885.5	885.0	884.5	884.0	883.5	883.3	883.2	883.1	882.9	882.8	882.6
165°	900.8	900.3	899.8	899.3	898.8	898.6	898.4	898.1	897.8	897.4	897.1
167.5°	913.1	912.5	911.8	911.2	910.5	910.2	910.2	910.2	910.2	910.2	910.2
170°	923.3	922.5	921.7	920.8	920.0	919.6	919.7	919.9	920.0	920.2	920.4
172.5°	930.5	929.9	929.2	928.6	927.9	927.6	927.6	927.6	927.6	927.6	927.6
175°	937.0	936.2	935.4	934.6	933.8	933.4	933.3	933.2	933.0	932.9	932.7
177.5°	940.0	939.2	938.4	937.5	936.7	936.3	936.3	936.3	936.3	936.3	936.3
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	558.8	566.8	570.3	571.2	576.1	573.0	574.3	573.9	577.4	577.9	577.9
5°	599.6	608.9	612.0	616.4	623.1	624.9	623.5	626.2	631.1	627.5	632.8
7.5°	642.6	652.8	659.9	669.6	671.8	677.6	681.1	684.2	685.1	685.6	686.5
10°	682.5	695.3	705.1	721.5	725.0	728.1	743.6	737.4	745.4	742.7	743.6
12.5°	714.8	740.1	748.1	775.5	778.2	788.8	787.9	797.7	799.5	803.0	799.5
15°	757.4	786.6	799.5	815.0	823.8	836.2	838.5	851.8	857.1	861.9	857.1
17.5°	796.4	811.9	844.7	857.1	862.8	869.5	886.3	891.2	899.2	896.1	904.9
20°	815.9	838.0	872.6	893.9	902.7	908.9	923.1	930.6	933.7	933.7	934.6
22.5°	833.1	865.0	890.8	915.1	923.1	927.5	936.0	941.7	943.0	943.9	944.8
25°	848.7	877.5	898.3	912.0	915.1	915.1	920.0	916.5	910.7	915.1	917.8
27.5°	848.7	869.0	878.3	883.2	883.2	871.3	864.2	849.5	837.1	833.6	841.6
30°	834.5	843.8	830.9	819.0	809.7	801.7	773.8	751.6	747.2	744.1	756.0
32.5°	801.7	789.7	764.5	729.9	716.1	698.0	676.3	659.4	649.2	645.7	643.0
35°	743.6	712.6	679.8	633.3	623.5	600.5	570.8	558.4	541.5	541.1	546.9
37.5°	680.2	632.4	596.9	552.6	538.9	514.5	486.6	473.7	462.2	453.4	464.0
40°	606.2	564.6	510.5	474.2	454.7	441.8	418.3	404.2	398.8	394.4	401.1
42.5°	537.1	491.5	449.4	412.1	396.2	381.6	366.0	352.3	348.3	347.9	352.8
45°	468.4	423.7	384.7	352.8	342.6	333.7	318.6	314.6	308.0	303.6	305.8
47.5°	413.5	367.4	335.0	310.7	301.8	294.3	284.5	277.9	272.1	270.3	273.0
50°	359.4	328.4	295.1	274.8	268.1	261.0	253.5	247.3	244.6	242.9	244.6
52.5°	316.0	282.7	260.1	243.7	237.1	231.8	226.5	223.8	220.3	221.1	222.9
55°	277.0	247.7	228.7	216.7	212.7	210.5	203.9	200.8	199.4	198.5	199.4
57.5°	240.2	218.9	204.7	194.5	189.2	187.9	182.6	182.6	181.3	179.9	180.4
60°	210.9	192.8	179.0	171.1	170.2	168.0	164.4	164.0	160.9	162.2	162.6
62.5°	181.3	166.6	157.3	152.4	149.3	148.5	146.2	145.8	144.5	144.9	144.0
65°	157.8	145.8	136.5	132.5	131.2	130.7	129.0	127.6	126.7	127.6	126.7
67.5°	134.3	126.3	119.2	115.2	113.4	113.0	111.7	110.8	111.2	109.9	110.8
70°	112.1	104.1	99.7	97.5	96.6	95.3	95.3	95.3	95.3	94.4	93.9
72.5°	94.4	86.4	83.3	82.0	81.1	80.7	79.3	79.8	79.3	78.9	80.7
75°	74.9	70.0	66.9	65.6	66.5	65.1	63.8	64.7	63.4	63.8	65.6
77.5°	56.7	54.5	52.7	51.8	51.0	50.1	50.1	49.2	49.2	49.2	49.2
80°	41.2	40.8	37.7	37.2	37.2	36.3	36.3	36.3	36.3	35.9	36.3
82.5°	27.5	27.0	26.1	25.7	24.8	25.3	25.3	24.4	24.4	23.9	24.4
85°	16.0	16.0	15.1	14.6	14.2	14.6	13.7	13.3	13.7	13.3	13.7
87.5°	7.5	6.6	7.1	6.6	5.8	6.2	5.3	5.8	5.3	4.9	5.8
90°	17.0	17.9	18.9	19.8	20.3	20.5	20.8	21.1	21.5	21.8	21.5
92.5°	32.4	32.9	33.4	33.9	34.1	34.2	34.3	34.5	34.6	34.8	34.6
95°	55.7	56.1	56.6	57.1	57.3	57.3	57.3	57.3	57.3	57.3	57.3
97.5°	81.9	82.6	83.2	83.9	84.2	84.2	84.2	84.2	84.2	84.2	84.2
100°	111.4	111.7	112.0	112.3	112.5	112.5	112.5	112.5	112.5	112.5	112.5
102.5°	142.0	142.5	143.0	143.5	143.7	143.8	143.9	144.1	144.2	144.4	144.2
105°	173.2	173.7	174.2	174.7	174.9	175.1	175.6	176.1	176.6	177.1	176.6
107.5°	206.7	207.4	208.0	208.7	209.0	208.9	208.8	208.6	208.5	208.3	208.5
110°	241.4	241.1	240.8	240.5	240.3	240.5	241.0	241.5	241.9	242.4	241.9

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3
115°	314.8	314.7	314.5	314.4	314.3	314.2	314.1	313.9	313.8	313.6	313.8
117.5°	350.8	350.3	349.8	349.3	349.1	348.9	348.4	347.9	347.4	346.9	347.4
120°	387.5	386.7	385.9	385.1	384.7	384.9	385.2	385.5	385.8	386.1	385.8
122.5°	424.1	423.6	423.1	422.6	422.4	422.0	421.2	420.4	419.6	418.8	419.6
125°	459.9	459.5	459.2	458.9	458.7	458.5	458.2	457.9	457.6	457.3	457.6
127.5°	494.0	493.6	493.3	493.0	492.8	492.7	492.6	492.4	492.3	492.1	492.3
130°	530.3	529.9	529.6	529.3	529.1	528.8	528.1	527.5	526.8	526.2	526.8
132.5°	564.4	564.0	563.7	563.4	563.2	563.1	563.0	562.8	562.7	562.5	562.7
135°	598.5	598.2	597.9	597.6	597.4	597.2	596.7	596.2	595.7	595.2	595.7
137.5°	631.7	631.2	630.7	630.2	630.0	630.1	630.2	630.4	630.5	630.7	630.5
140°	663.9	663.8	663.6	663.5	663.4	663.3	663.2	663.0	662.9	662.7	662.9
142.5°	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6
145°	725.6	725.5	725.3	725.2	725.1	724.9	724.4	723.9	723.4	722.9	723.4
147.5°	753.9	753.8	753.6	753.5	753.4	753.3	753.2	753.0	752.9	752.7	752.9
150°	780.3	780.3	780.3	780.3	780.3	780.2	780.0	779.9	779.7	779.5	779.7
152.5°	804.7	805.2	805.7	806.2	806.4	806.2	805.7	805.2	804.7	804.2	804.7
155°	827.3	828.0	828.6	829.3	829.6	829.3	828.6	828.0	827.3	826.7	827.3
157.5°	848.3	848.7	849.2	849.7	849.9	849.7	849.2	848.7	848.3	847.8	848.3
160°	867.1	867.6	868.1	868.6	868.8	868.4	867.6	866.8	866.0	865.2	866.0
162.5°	883.6	884.6	885.5	886.5	887.0	886.6	885.8	884.9	884.1	883.3	884.1
165°	898.1	899.1	900.0	901.0	901.5	901.2	900.5	899.9	899.2	898.6	899.2
167.5°	911.2	912.1	913.1	914.0	914.5	914.0	913.1	912.1	911.2	910.2	911.2
170°	921.4	922.3	923.3	924.2	924.7	924.1	923.0	921.9	920.7	919.6	920.7
172.5°	928.7	929.9	931.0	932.1	932.7	932.1	931.0	929.9	928.7	927.6	928.7
175°	933.8	935.0	936.1	937.2	937.8	937.2	936.1	935.0	933.8	932.7	933.8
177.5°	937.4	938.6	939.7	940.8	941.4	940.8	939.5	938.2	936.9	935.6	936.9
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	577.0	575.7	573.9	573.9	571.7	571.7	568.1	561.9	556.6	554.8	555.7
5°	626.2	626.6	624.0	621.8	617.8	614.7	608.9	597.8	594.3	587.2	582.3
7.5°	682.5	680.7	675.8	672.3	671.4	664.3	651.9	638.6	628.0	620.9	610.7
10°	745.8	738.7	731.7	729.4	724.1	712.2	698.0	683.4	668.7	653.2	635.9
12.5°	799.0	785.3	784.8	779.5	769.3	762.7	745.8	725.0	699.7	682.5	663.0
15°	856.2	843.3	832.7	822.9	818.1	798.6	784.4	758.2	728.1	709.5	696.2
17.5°	897.0	891.2	873.0	868.6	861.9	839.3	816.7	791.0	764.9	738.7	702.9
20°	929.7	926.2	914.2	908.0	897.4	879.7	852.2	822.5	792.4	755.1	721.5
22.5°	943.9	939.5	929.7	924.4	917.8	902.7	879.2	845.5	806.1	772.9	737.0
25°	916.0	924.0	921.3	919.1	916.5	907.6	889.9	860.2	821.6	783.9	739.2
27.5°	853.1	866.8	880.1	881.9	886.3	889.9	882.8	861.5	829.2	789.3	740.1
30°	768.4	774.6	801.7	809.7	815.9	838.5	851.8	846.4	821.6	785.7	740.5
32.5°	659.9	676.3	703.7	722.8	739.6	764.9	799.5	813.2	804.3	775.1	730.3
35°	557.1	576.6	608.5	632.8	649.7	685.6	726.3	756.0	767.1	752.5	712.6
37.5°	472.9	496.3	524.7	534.0	553.5	597.8	654.1	695.3	722.3	723.7	692.7
40°	409.5	421.4	444.0	458.2	477.3	514.5	569.5	624.0	664.7	678.5	662.1
42.5°	355.9	365.2	382.0	399.3	416.6	444.9	495.5	546.4	601.4	628.8	628.4
45°	313.3	323.1	334.6	348.8	360.7	391.3	431.2	483.5	530.9	573.4	584.1
47.5°	276.1	284.5	298.7	304.9	312.9	341.7	376.2	425.0	474.2	522.9	535.3
50°	248.6	255.7	265.5	269.4	278.3	299.6	327.9	367.4	421.9	466.6	489.7
52.5°	223.8	229.1	236.6	239.7	246.0	261.9	287.6	318.6	363.8	409.9	442.3
55°	202.5	206.1	211.4	214.9	219.4	233.5	252.6	280.5	319.5	359.4	390.9
57.5°	182.6	185.2	190.6	192.3	195.9	207.0	220.3	243.7	279.6	315.1	345.7
60°	164.0	165.7	168.8	172.8	175.5	183.0	195.4	214.9	243.7	276.1	300.9
62.5°	146.2	148.9	149.8	151.6	153.8	160.9	170.6	184.8	210.1	236.6	262.8
65°	128.1	130.3	132.1	132.5	134.7	140.0	148.9	161.3	177.7	200.8	225.1
67.5°	111.2	112.6	113.4	115.2	117.4	120.1	127.2	136.5	151.6	170.2	189.7
70°	95.7	95.7	97.1	97.5	100.2	103.3	106.4	115.2	128.5	143.6	156.9
72.5°	78.9	81.1	80.7	82.9	82.4	84.6	88.6	94.4	104.1	116.1	129.0
75°	64.3	65.6	65.6	65.6	66.5	68.2	70.5	75.8	83.3	93.1	100.6
77.5°	50.1	51.0	51.0	51.0	51.4	53.2	55.4	58.9	64.3	70.0	74.5
80°	35.9	36.8	36.8	37.7	37.7	38.1	40.3	42.1	44.8	49.2	53.6
82.5°	24.4	24.8	25.7	25.7	25.3	26.1	26.6	28.4	31.0	31.9	35.0
85°	13.3	13.7	14.2	14.2	14.6	15.5	15.1	16.8	16.8	18.6	19.5
87.5°	5.3	6.2	6.2	5.8	6.2	6.2	6.2	7.1	7.5	8.0	7.5
90°	21.1	20.8	20.5	20.3	19.8	18.9	17.9	17.0	16.0	14.7	13.4
92.5°	34.5	34.3	34.2	34.1	33.9	33.4	32.9	32.4	31.9	31.1	30.3
95°	57.3	57.3	57.3	57.3	57.1	56.6	56.1	55.7	55.2	54.1	52.9
97.5°	84.2	84.2	84.2	84.2	83.9	83.2	82.6	81.9	81.3	80.0	78.7
100°	112.5	112.5	112.5	112.5	112.3	112.0	111.7	111.4	111.1	109.6	108.2
102.5°	144.1	143.9	143.8	143.7	143.5	143.0	142.5	142.0	141.5	140.2	138.9
105°	176.1	175.6	175.1	174.9	174.7	174.2	173.7	173.2	172.7	172.1	171.4
107.5°	208.6	208.8	208.9	209.0	208.7	208.0	207.4	206.7	206.1	205.9	205.8
110°	241.5	241.0	240.5	240.3	240.5	240.8	241.1	241.4	241.7	241.9	242.0

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.6	277.9
115°	313.9	314.1	314.2	314.3	314.4	314.5	314.7	314.8	315.0	315.3	315.7
117.5°	347.9	348.4	348.9	349.1	349.3	349.8	350.3	350.8	351.3	351.5	351.6
120°	385.5	385.2	384.9	384.7	385.1	385.9	386.7	387.5	388.3	388.8	389.3
122.5°	420.4	421.2	422.0	422.4	422.6	423.1	423.6	424.1	424.6	424.8	424.9
125°	457.9	458.2	458.5	458.7	458.9	459.2	459.5	459.9	460.2	460.4	460.5
127.5°	492.4	492.6	492.7	492.8	493.0	493.3	493.6	494.0	494.3	494.6	494.9
130°	527.5	528.1	528.8	529.1	529.3	529.6	529.9	530.3	530.6	530.6	530.6
132.5°	562.8	563.0	563.1	563.2	563.4	563.7	564.0	564.4	564.7	564.9	565.0
135°	596.2	596.7	597.2	597.4	597.6	597.9	598.2	598.5	598.8	598.8	598.8
137.5°	630.4	630.2	630.1	630.0	630.2	630.7	631.2	631.7	632.2	631.9	631.5
140°	663.0	663.2	663.3	663.4	663.5	663.6	663.8	663.9	664.1	664.1	664.1
142.5°	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.8	694.9
145°	723.9	724.4	724.9	725.1	725.2	725.3	725.5	725.6	725.8	725.6	725.5
147.5°	753.0	753.2	753.3	753.4	753.5	753.6	753.8	753.9	754.1	754.3	754.5
150°	779.9	780.0	780.2	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3
152.5°	805.2	805.7	806.2	806.4	806.2	805.7	805.2	804.7	804.2	804.0	803.9
155°	828.0	828.6	829.3	829.6	829.3	828.6	828.0	827.3	826.7	826.9	827.0
157.5°	848.7	849.2	849.7	849.9	849.7	849.2	848.7	848.3	847.8	847.8	847.8
160°	866.8	867.6	868.4	868.8	868.6	868.1	867.6	867.1	866.6	866.8	867.0
162.5°	884.9	885.8	886.6	887.0	886.5	885.5	884.6	883.6	882.6	882.8	882.9
165°	899.9	900.5	901.2	901.5	901.0	900.0	899.1	898.1	897.1	897.4	897.8
167.5°	912.1	913.1	914.0	914.5	914.0	913.1	912.1	911.2	910.2	910.2	910.2
170°	921.9	923.0	924.1	924.7	924.2	923.3	922.3	921.4	920.4	920.2	920.0
172.5°	929.9	931.0	932.1	932.7	932.1	931.0	929.9	928.7	927.6	927.6	927.6
175°	935.0	936.1	937.2	937.8	937.2	936.1	935.0	933.8	932.7	932.9	933.0
177.5°	938.2	939.5	940.8	941.4	940.8	939.7	938.6	937.4	936.3	936.3	936.3
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	551.7	550.0	548.6	548.6	544.6	540.7	538.4	537.6	536.7	533.1	528.2
5°	574.3	568.6	564.6	560.6	553.9	546.9	539.8	535.8	530.0	522.0	516.3
7.5°	599.6	585.9	581.4	576.6	563.3	551.3	541.5	533.1	523.8	513.6	503.4
10°	620.9	606.2	596.5	588.1	570.8	554.8	540.2	527.8	515.8	502.5	490.1
12.5°	641.3	620.4	610.2	597.8	579.7	556.6	537.6	522.0	504.3	490.6	475.5
15°	669.6	634.6	617.8	609.8	585.4	558.4	535.3	512.3	497.7	476.8	463.5
17.5°	674.0	645.7	634.6	614.2	585.0	554.4	527.8	504.8	482.6	464.0	446.7
20°	689.6	652.3	634.6	621.8	583.2	552.2	522.9	493.2	472.0	452.0	432.5
22.5°	699.3	657.2	638.6	618.2	581.4	544.2	509.6	483.9	457.8	437.4	421.9
25°	696.6	654.5	633.7	614.7	569.9	532.7	501.7	468.9	444.5	422.3	401.9
27.5°	695.3	647.9	625.7	604.5	562.4	523.4	484.4	457.8	430.8	405.0	390.0
30°	691.8	639.5	613.8	590.7	546.9	506.1	472.9	441.8	414.8	391.3	371.4
32.5°	679.8	625.3	600.5	575.7	530.0	489.2	455.6	426.8	399.7	375.4	356.3
35°	663.9	608.5	581.4	555.3	509.6	468.4	437.4	407.3	382.0	358.5	340.3
37.5°	647.9	589.0	563.7	533.6	491.5	448.5	416.6	389.5	366.0	341.7	321.7
40°	624.9	565.9	538.0	512.3	463.1	422.8	393.5	369.2	346.1	323.1	306.2
42.5°	593.4	540.7	511.8	483.5	437.4	397.5	369.2	347.4	325.7	306.7	288.1
45°	561.5	510.1	484.4	459.1	409.0	371.4	345.2	325.3	307.1	286.3	271.2
47.5°	522.9	479.5	453.8	429.0	381.6	343.9	320.0	301.3	284.5	267.2	253.0
50°	483.5	445.8	422.3	396.6	351.4	317.3	293.8	278.3	264.6	248.2	236.6
52.5°	440.9	408.1	388.2	363.4	323.5	292.0	268.1	252.6	241.1	229.1	218.9
55°	395.7	371.8	350.5	330.6	292.9	264.6	243.3	229.6	221.6	210.5	201.6
57.5°	355.0	331.9	319.1	296.5	263.7	235.8	218.9	207.4	198.1	191.4	184.4
60°	312.4	293.8	279.6	263.2	234.4	210.9	193.2	186.6	176.8	171.9	168.8
62.5°	271.7	258.4	245.1	232.7	207.0	184.8	171.5	163.1	157.3	152.4	149.8
65°	233.1	220.7	211.4	200.3	179.0	161.3	148.9	142.3	136.5	135.2	132.1
67.5°	195.4	190.1	179.9	171.1	152.9	139.2	129.8	121.4	118.3	117.0	114.3
70°	163.5	157.3	149.3	141.8	128.1	116.1	107.7	104.6	100.2	99.7	96.6
72.5°	134.7	127.2	121.4	115.7	105.5	94.8	90.4	86.0	83.8	82.0	80.7
75°	106.8	101.5	97.5	92.6	83.8	76.7	70.5	68.7	67.4	66.9	66.0
77.5°	79.8	76.2	74.5	69.6	63.4	57.2	54.5	51.8	51.8	51.0	51.4
80°	56.7	54.5	52.3	49.6	44.3	41.7	39.4	37.7	36.8	36.3	36.8
82.5°	35.9	34.6	34.1	32.4	28.8	27.5	25.7	24.4	24.4	24.4	24.4
85°	19.9	19.9	19.9	17.3	16.0	14.6	13.7	13.3	13.3	13.3	13.7
87.5°	8.4	8.4	7.1	7.1	6.6	5.8	5.3	5.3	5.8	5.8	6.2
90°	12.1	10.8	10.2	9.3	7.5	5.8	4.0	2.2	4.0	5.8	7.5
92.5°	29.5	28.7	28.3	27.3	25.2	23.1	21.0	18.9	21.0	23.1	25.2
95°	51.8	50.7	50.1	49.4	47.9	46.4	45.0	43.5	45.0	46.4	47.9
97.5°	77.4	76.1	75.5	74.9	73.6	72.3	71.0	69.7	71.0	72.3	73.6
100°	106.7	105.2	104.5	104.2	103.5	102.9	102.2	101.6	102.2	102.9	103.5
102.5°	137.6	136.3	135.7	135.6	135.5	135.3	135.2	135.0	135.2	135.3	135.5
105°	170.8	170.1	169.8	169.7	169.6	169.4	169.3	169.1	169.3	169.4	169.6
107.5°	205.6	205.5	205.4	205.3	205.2	205.0	204.9	204.7	204.9	205.0	205.2
110°	242.2	242.3	242.4	242.2	241.9	241.6	241.3	241.0	241.3	241.6	241.9

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	278.2	278.5	278.7	278.7	278.7	278.7	278.7	278.7	278.7	278.7	278.7
115°	316.0	316.3	316.5	316.5	316.5	316.5	316.5	316.5	316.5	316.5	316.5
117.5°	351.8	351.9	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0	352.0
120°	389.8	390.3	390.5	390.2	389.5	388.9	388.2	387.6	388.2	388.9	389.5
122.5°	425.1	425.2	425.3	425.2	425.1	424.9	424.8	424.6	424.8	424.9	425.1
125°	460.7	460.8	460.9	460.9	460.9	460.9	460.9	460.9	460.9	460.9	460.9
127.5°	495.2	495.5	495.7	495.5	495.0	494.5	494.1	493.6	494.1	494.5	495.0
130°	530.6	530.6	530.6	530.4	529.9	529.4	528.9	528.4	528.9	529.4	529.9
132.5°	565.2	565.3	565.4	565.2	564.9	564.6	564.3	564.0	564.3	564.6	564.9
135°	598.8	598.8	598.8	598.3	597.4	596.4	595.5	594.5	595.5	596.4	597.4
137.5°	631.2	630.9	630.7	630.5	630.0	629.5	629.1	628.6	629.1	629.5	630.0
140°	664.1	664.1	664.1	663.9	663.6	663.3	663.0	662.7	663.0	663.3	663.6
142.5°	695.1	695.2	695.3	695.1	694.8	694.5	694.2	693.9	694.2	694.5	694.8
145°	725.3	725.2	725.1	724.8	724.1	723.5	722.8	722.2	722.8	723.5	724.1
147.5°	754.6	754.8	754.9	754.5	753.7	752.8	752.0	751.2	752.0	752.8	753.7
150°	780.3	780.3	780.3	780.0	779.3	778.7	778.0	777.4	778.0	778.7	779.3
152.5°	803.7	803.6	803.5	803.3	803.0	802.7	802.3	802.0	802.3	802.7	803.0
155°	827.2	827.3	827.4	827.4	827.4	827.4	827.4	827.4	827.4	827.4	827.4
157.5°	847.8	847.8	847.8	848.0	848.3	848.6	848.9	849.2	848.9	848.6	848.3
160°	867.1	867.3	867.4	867.5	867.6	867.8	867.9	868.1	867.9	867.8	867.6
162.5°	883.1	883.2	883.3	883.5	884.0	884.5	885.0	885.5	885.0	884.5	884.0
165°	898.1	898.4	898.6	898.8	899.3	899.8	900.3	900.8	900.3	899.8	899.3
167.5°	910.2	910.2	910.2	910.5	911.2	911.8	912.5	913.1	912.5	911.8	911.2
170°	919.9	919.7	919.6	920.0	920.8	921.7	922.5	923.3	922.5	921.7	920.8
172.5°	927.6	927.6	927.6	927.9	928.6	929.2	929.9	930.5	929.9	929.2	928.6
175°	933.2	933.3	933.4	933.8	934.6	935.4	936.2	937.0	936.2	935.4	934.6
177.5°	936.3	936.3	936.3	936.7	937.5	938.4	939.2	940.0	939.2	938.4	937.5
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	526.9	525.1	526.0	521.6	517.6	511.8	507.0	506.1	505.2	507.9	506.1
5°	511.8	509.6	507.4	502.1	494.1	489.2	482.2	481.7	479.1	475.1	476.0
7.5°	495.5	494.1	491.0	482.6	475.5	467.1	461.3	456.5	454.2	450.7	449.4
10°	482.2	477.3	474.6	465.3	456.9	448.0	440.5	437.0	433.0	429.9	427.6
12.5°	464.0	462.7	455.1	447.6	440.5	430.3	424.5	414.4	409.0	411.7	410.8
15°	452.0	445.8	444.0	433.4	421.4	414.8	404.2	397.5	395.3	391.3	386.4
17.5°	436.1	432.1	425.9	416.1	402.4	393.1	385.5	379.3	376.7	371.4	367.4
20°	421.0	414.4	409.5	400.6	387.3	375.4	366.0	362.1	355.4	351.0	348.8
22.5°	407.3	402.4	395.3	382.0	370.5	359.0	347.9	342.1	335.9	333.3	329.7
25°	390.4	382.4	377.6	362.9	350.5	341.2	331.0	323.5	320.0	315.5	314.6
27.5°	374.0	366.5	360.7	347.9	332.8	320.8	314.6	309.3	303.1	303.1	300.9
30°	357.6	352.3	343.4	331.0	316.9	305.3	298.2	293.4	291.2	289.4	288.9
32.5°	341.2	334.1	328.8	312.0	301.3	290.7	285.4	281.4	278.7	278.3	278.7
35°	324.4	316.4	311.1	296.0	285.4	275.6	273.4	269.9	268.6	268.1	270.3
37.5°	306.7	300.5	293.8	281.4	269.4	263.7	259.2	257.9	257.5	260.1	261.0
40°	290.3	285.0	278.7	265.5	256.6	250.4	248.2	246.8	248.6	251.3	252.6
42.5°	274.8	267.2	262.4	250.4	242.4	238.9	236.2	236.2	238.0	241.1	243.3
45°	258.4	252.6	247.7	237.1	230.0	226.0	225.6	226.0	228.2	230.4	233.1
47.5°	242.4	236.6	231.3	222.5	216.3	214.0	213.6	214.0	217.6	220.7	223.8
50°	227.8	221.6	216.7	208.3	203.4	200.8	201.2	203.4	206.1	210.5	214.5
52.5°	210.5	206.1	201.6	194.1	189.7	187.9	189.2	191.0	195.9	199.0	203.9
55°	193.7	189.7	186.1	180.4	176.8	175.5	176.4	179.0	183.0	188.3	194.1
57.5°	178.2	173.7	170.2	166.2	162.2	162.6	163.1	166.6	171.5	176.4	183.0
60°	160.9	158.2	155.1	150.2	148.5	148.5	149.8	153.8	158.2	166.2	171.9
62.5°	145.4	141.8	139.6	136.5	133.8	134.3	137.4	140.9	146.2	152.9	160.4
65°	129.4	125.4	123.6	121.0	120.1	120.5	122.8	128.1	133.8	139.6	146.7
67.5°	111.7	110.3	108.6	105.9	106.8	107.2	109.5	113.9	120.1	125.9	133.8
70°	96.6	93.9	93.5	91.3	91.3	92.6	97.1	100.2	105.9	112.1	120.5
72.5°	80.7	78.4	78.4	76.7	78.0	79.3	81.5	86.0	91.3	97.5	104.6
75°	64.3	63.4	64.3	63.4	63.4	65.6	68.2	71.8	77.6	84.2	90.0
77.5°	49.6	49.6	49.2	50.5	50.5	51.8	55.4	58.9	63.4	68.7	74.9
80°	36.3	36.3	36.3	37.7	39.0	39.0	41.2	45.6	49.6	53.2	58.9
82.5°	24.8	24.8	24.8	25.7	27.5	27.5	30.1	32.8	37.2	40.3	43.0
85°	15.1	15.1	14.6	15.5	16.0	17.3	19.5	21.3	23.5	26.1	28.8
87.5°	6.6	6.6	7.1	7.5	8.0	8.9	9.7	10.6	12.9	13.7	15.1
90°	9.3	10.2	10.8	12.1	13.4	14.7	16.0	17.0	17.9	18.9	19.8
92.5°	27.3	28.3	28.7	29.5	30.3	31.1	31.9	32.4	32.9	33.4	33.9
95°	49.4	50.1	50.7	51.8	52.9	54.1	55.2	55.7	56.1	56.6	57.1
97.5°	74.9	75.5	76.1	77.4	78.7	80.0	81.3	81.9	82.6	83.2	83.9
100°	104.2	104.5	105.2	106.7	108.2	109.6	111.1	111.4	111.7	112.0	112.3
102.5°	135.6	135.7	136.3	137.6	138.9	140.2	141.5	142.0	142.5	143.0	143.5
105°	169.7	169.8	170.1	170.8	171.4	172.1	172.7	173.2	173.7	174.2	174.7
107.5°	205.3	205.4	205.5	205.6	205.8	205.9	206.1	206.7	207.4	208.0	208.7
110°	242.2	242.4	242.3	242.2	242.0	241.9	241.7	241.4	241.1	240.8	240.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	278.7	278.7	278.5	278.2	277.9	277.6	277.3	277.3	277.3	277.3	277.3
115°	316.5	316.5	316.3	316.0	315.7	315.3	315.0	314.8	314.7	314.5	314.4
117.5°	352.0	352.0	351.9	351.8	351.6	351.5	351.3	350.8	350.3	349.8	349.3
120°	390.2	390.5	390.3	389.8	389.3	388.8	388.3	387.5	386.7	385.9	385.1
122.5°	425.2	425.3	425.2	425.1	424.9	424.8	424.6	424.1	423.6	423.1	422.6
125°	460.9	460.9	460.8	460.7	460.5	460.4	460.2	459.9	459.5	459.2	458.9
127.5°	495.5	495.7	495.5	495.2	494.9	494.6	494.3	494.0	493.6	493.3	493.0
130°	530.4	530.6	530.6	530.6	530.6	530.6	530.6	530.3	529.9	529.6	529.3
132.5°	565.2	565.4	565.3	565.2	565.0	564.9	564.7	564.4	564.0	563.7	563.4
135°	598.3	598.8	598.8	598.8	598.8	598.8	598.8	598.5	598.2	597.9	597.6
137.5°	630.5	630.7	630.9	631.2	631.5	631.9	632.2	631.7	631.2	630.7	630.2
140°	663.9	664.1	664.1	664.1	664.1	664.1	664.1	663.9	663.8	663.6	663.5
142.5°	695.1	695.3	695.2	695.1	694.9	694.8	694.6	694.6	694.6	694.6	694.6
145°	724.8	725.1	725.2	725.3	725.5	725.6	725.8	725.6	725.5	725.3	725.2
147.5°	754.5	754.9	754.8	754.6	754.5	754.3	754.1	753.9	753.8	753.6	753.5
150°	780.0	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3
152.5°	803.3	803.5	803.6	803.7	803.9	804.0	804.2	804.7	805.2	805.7	806.2
155°	827.4	827.4	827.3	827.2	827.0	826.9	826.7	827.3	828.0	828.6	829.3
157.5°	848.0	847.8	847.8	847.8	847.8	847.8	847.8	848.3	848.7	849.2	849.7
160°	867.5	867.4	867.3	867.1	867.0	866.8	866.6	867.1	867.6	868.1	868.6
162.5°	883.5	883.3	883.2	883.1	882.9	882.8	882.6	883.6	884.6	885.5	886.5
165°	898.8	898.6	898.4	898.1	897.8	897.4	897.1	898.1	899.1	900.0	901.0
167.5°	910.5	910.2	910.2	910.2	910.2	910.2	910.2	911.2	912.1	913.1	914.0
170°	920.0	919.6	919.7	919.9	920.0	920.2	920.4	921.4	922.3	923.3	924.2
172.5°	927.9	927.6	927.6	927.6	927.6	927.6	927.6	928.7	929.9	931.0	932.1
175°	933.8	933.4	933.3	933.2	933.0	932.9	932.7	933.8	935.0	936.1	937.2
177.5°	936.7	936.3	936.3	936.3	936.3	936.3	936.3	937.4	938.6	939.7	940.8
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	504.8	504.3	502.1	503.0	500.3	501.2	502.5	503.0	504.8	503.4	503.0
5°	473.7	472.9	471.5	470.2	469.7	471.5	468.4	469.3	470.2	471.5	473.3
7.5°	448.5	448.0	446.7	444.5	443.6	442.7	443.2	446.3	445.8	445.4	448.5
10°	425.4	425.9	423.2	422.8	420.1	419.7	420.1	421.0	422.3	424.1	424.5
12.5°	401.5	407.3	402.4	400.6	396.6	398.8	399.7	395.7	398.0	399.3	405.9
15°	386.4	383.8	380.7	380.7	378.9	378.0	375.8	378.9	380.7	383.3	382.4
17.5°	365.6	361.2	359.4	357.6	358.1	359.8	355.0	362.1	362.1	363.4	361.2
20°	347.4	343.9	341.7	340.8	339.5	338.6	338.1	339.9	342.6	343.4	345.7
22.5°	328.4	328.4	324.8	323.5	322.6	321.3	323.5	322.2	323.9	325.7	329.3
25°	312.4	312.4	311.1	309.3	308.0	307.1	308.4	308.0	309.3	311.5	312.4
27.5°	299.6	298.2	297.8	297.4	296.9	297.4	296.9	298.2	299.6	300.0	299.1
30°	288.5	287.2	287.6	287.6	288.1	287.6	287.2	288.5	288.9	288.1	288.5
32.5°	278.3	278.3	279.2	279.6	279.6	280.1	280.5	279.6	280.1	278.7	279.2
35°	269.9	270.8	271.7	272.1	272.5	272.1	273.0	272.5	271.7	270.8	270.3
37.5°	261.5	262.4	264.1	264.6	265.9	266.3	265.5	265.5	265.0	263.2	262.4
40°	252.6	253.5	255.7	257.0	257.9	259.2	258.4	258.4	256.6	254.8	253.5
42.5°	244.2	246.0	248.2	249.5	251.3	251.3	251.3	250.4	248.2	246.4	245.1
45°	235.8	236.2	239.3	241.5	243.3	243.3	243.3	242.0	240.6	237.1	235.3
47.5°	226.5	227.8	231.3	233.5	235.3	235.8	235.8	234.4	231.8	228.7	226.5
50°	216.3	218.5	222.5	225.6	227.8	228.7	227.3	226.5	223.4	219.8	217.1
52.5°	206.5	209.2	214.0	216.7	219.8	220.3	219.8	218.5	214.9	210.1	207.8
55°	196.8	199.0	204.3	208.7	211.4	212.3	211.4	209.2	204.7	199.9	197.6
57.5°	186.1	189.2	195.0	199.4	202.5	203.0	202.1	199.9	196.3	190.1	187.0
60°	175.0	179.0	184.8	189.2	193.2	193.7	192.8	189.7	185.2	179.0	176.4
62.5°	164.0	167.1	173.7	178.6	181.7	183.9	182.1	179.0	174.6	168.4	164.4
65°	151.1	155.5	161.3	165.7	169.3	169.7	168.8	166.2	161.3	154.7	151.6
67.5°	138.7	141.8	147.6	153.3	154.7	156.0	154.7	152.0	148.0	142.3	137.8
70°	123.6	126.3	133.4	137.4	139.2	140.5	139.6	136.9	133.4	128.1	124.5
72.5°	108.6	110.8	117.4	120.5	124.1	123.6	123.2	121.4	116.6	113.0	110.8
75°	92.6	95.3	99.7	103.7	105.0	105.0	105.0	103.7	100.6	94.8	92.6
77.5°	78.0	79.3	82.9	85.1	86.4	86.9	86.4	84.2	82.4	78.4	77.1
80°	59.8	63.4	66.0	66.5	68.2	68.2	68.2	67.4	65.6	61.6	61.2
82.5°	45.2	46.1	48.7	50.1	51.0	50.5	50.5	48.7	48.3	46.1	45.2
85°	30.6	31.9	31.5	33.2	33.7	32.8	32.8	33.7	31.5	31.9	30.6
87.5°	16.8	16.8	17.7	17.3	19.1	19.1	18.2	18.6	17.7	17.3	16.8
90°	20.3	20.5	20.8	21.1	21.5	21.8	21.5	21.1	20.8	20.5	20.3
92.5°	34.1	34.2	34.3	34.5	34.6	34.8	34.6	34.5	34.3	34.2	34.1
95°	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3	57.3
97.5°	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2	84.2
100°	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5	112.5
102.5°	143.7	143.8	143.9	144.1	144.2	144.4	144.2	144.1	143.9	143.8	143.7
105°	174.9	175.1	175.6	176.1	176.6	177.1	176.6	176.1	175.6	175.1	174.9
107.5°	209.0	208.9	208.8	208.6	208.5	208.3	208.5	208.6	208.8	208.9	209.0
110°	240.3	240.5	241.0	241.5	241.9	242.4	241.9	241.5	241.0	240.5	240.3

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3	277.3
115°	314.3	314.2	314.1	313.9	313.8	313.6	313.8	313.9	314.1	314.2	314.3
117.5°	349.1	348.9	348.4	347.9	347.4	346.9	347.4	347.9	348.4	348.9	349.1
120°	384.7	384.9	385.2	385.5	385.8	386.1	385.8	385.5	385.2	384.9	384.7
122.5°	422.4	422.0	421.2	420.4	419.6	418.8	419.6	420.4	421.2	422.0	422.4
125°	458.7	458.5	458.2	457.9	457.6	457.3	457.6	457.9	458.2	458.5	458.7
127.5°	492.8	492.7	492.6	492.4	492.3	492.1	492.3	492.4	492.6	492.7	492.8
130°	529.1	528.8	528.1	527.5	526.8	526.2	526.8	527.5	528.1	528.8	529.1
132.5°	563.2	563.1	563.0	562.8	562.7	562.5	562.7	562.8	563.0	563.1	563.2
135°	597.4	597.2	596.7	596.2	595.7	595.2	595.7	596.2	596.7	597.2	597.4
137.5°	630.0	630.1	630.2	630.4	630.5	630.7	630.5	630.4	630.2	630.1	630.0
140°	663.4	663.3	663.2	663.0	662.9	662.7	662.9	663.0	663.2	663.3	663.4
142.5°	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6	694.6
145°	725.1	724.9	724.4	723.9	723.4	722.9	723.4	723.9	724.4	724.9	725.1
147.5°	753.4	753.3	753.2	753.0	752.9	752.7	752.9	753.0	753.2	753.3	753.4
150°	780.3	780.2	780.0	779.9	779.7	779.5	779.7	779.9	780.0	780.2	780.3
152.5°	806.4	806.2	805.7	805.2	804.7	804.2	804.7	805.2	805.7	806.2	806.4
155°	829.6	829.3	828.6	828.0	827.3	826.7	827.3	828.0	828.6	829.3	829.6
157.5°	849.9	849.7	849.2	848.7	848.3	847.8	848.3	848.7	849.2	849.7	849.9
160°	868.8	868.4	867.6	866.8	866.0	865.2	866.0	866.8	867.6	868.4	868.8
162.5°	887.0	886.6	885.8	884.9	884.1	883.3	884.1	884.9	885.8	886.6	887.0
165°	901.5	901.2	900.5	899.9	899.2	898.6	899.2	899.9	900.5	901.2	901.5
167.5°	914.5	914.0	913.1	912.1	911.2	910.2	911.2	912.1	913.1	914.0	914.5
170°	924.7	924.1	923.0	921.9	920.7	919.6	920.7	921.9	923.0	924.1	924.7
172.5°	932.7	932.1	931.0	929.9	928.7	927.6	928.7	929.9	931.0	932.1	932.7
175°	937.8	937.2	936.1	935.0	933.8	932.7	933.8	935.0	936.1	937.2	937.8
177.5°	941.4	940.8	939.5	938.2	936.9	935.6	936.9	938.2	939.5	940.8	941.4
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9	534.9
2.5°	503.0	505.6	503.0	504.8	505.6	507.9	508.7	512.7	514.1	517.2	517.2
5°	472.9	474.2	474.6	476.4	478.2	482.6	485.7	491.5	498.1	499.0	503.0
7.5°	448.5	450.7	454.2	452.9	456.0	462.7	466.6	473.7	480.4	483.9	488.8
10°	426.8	429.4	430.8	432.1	437.8	443.6	449.8	454.7	463.5	468.9	472.9
12.5°	409.0	406.8	409.5	414.4	421.0	424.5	433.0	440.5	447.1	452.9	456.5
15°	386.0	387.8	390.4	398.8	400.6	409.5	412.6	421.0	433.4	438.7	443.2
17.5°	363.8	369.6	374.9	378.0	383.3	390.4	399.3	408.6	416.6	422.8	428.1
20°	346.1	351.9	355.0	357.2	362.5	372.3	380.7	392.2	402.4	407.3	414.4
22.5°	331.9	331.9	336.4	343.0	346.1	355.4	362.5	374.9	386.0	392.2	398.8
25°	314.2	316.9	320.4	326.2	330.6	338.1	348.3	359.0	370.9	376.2	384.7
27.5°	299.6	302.7	307.6	308.9	313.3	320.0	330.6	342.1	354.5	360.3	367.4
30°	288.5	290.3	292.0	294.7	298.7	304.5	313.3	323.5	338.6	343.0	351.9
32.5°	278.7	279.6	280.5	282.7	285.0	290.7	297.8	308.9	321.3	327.9	335.9
35°	269.9	269.0	269.4	270.8	273.0	275.2	282.7	292.0	303.6	311.5	317.7
37.5°	261.5	259.7	259.2	259.2	260.1	262.8	268.6	276.5	288.9	295.6	301.8
40°	252.2	250.4	249.5	249.1	248.6	250.4	254.8	262.8	272.5	278.7	285.8
42.5°	243.3	241.5	239.3	238.9	238.0	238.9	242.0	249.5	257.9	264.1	269.9
45°	234.4	231.3	228.7	226.9	227.3	226.0	228.2	234.0	243.7	247.7	253.5
47.5°	224.7	221.1	217.6	215.8	214.0	214.9	215.8	220.7	229.1	233.1	238.9
50°	215.4	210.5	206.5	204.3	203.0	202.1	203.0	207.8	214.0	217.6	222.5
52.5°	204.7	199.9	195.9	192.3	190.6	189.2	189.7	194.1	199.9	203.4	208.3
55°	195.0	188.8	183.5	179.0	177.7	177.3	176.8	179.9	184.8	188.3	192.3
57.5°	183.9	177.7	171.9	166.6	164.0	163.5	163.5	164.4	170.6	173.3	175.5
60°	172.8	166.2	160.0	155.1	151.1	149.8	149.3	151.1	154.2	156.9	160.0
62.5°	160.4	153.8	146.2	141.8	137.8	134.3	135.6	136.0	140.5	141.8	144.5
65°	148.5	140.9	134.7	127.6	123.2	121.0	120.1	121.0	124.5	125.0	126.7
67.5°	134.7	127.6	120.1	115.2	111.2	107.2	106.4	106.4	108.1	109.5	111.7
70°	121.4	114.3	105.9	100.6	96.6	93.1	91.7	91.3	92.6	93.5	95.7
72.5°	105.9	98.8	92.6	86.9	82.0	79.3	78.0	77.1	78.4	79.3	79.8
75°	89.5	83.8	77.6	71.8	68.7	66.0	64.3	62.9	63.8	63.8	63.8
77.5°	74.0	68.2	63.4	59.4	55.4	52.3	51.0	49.6	50.1	50.1	51.0
80°	57.6	53.6	49.6	46.1	42.5	39.9	39.0	37.7	36.8	36.3	36.3
82.5°	42.5	39.4	35.9	32.8	31.0	28.4	27.5	25.7	25.7	25.3	25.3
85°	28.4	26.6	23.0	20.8	19.5	18.2	17.3	16.4	15.1	15.1	14.6
87.5°	15.1	14.2	13.3	10.6	10.6	9.3	8.9	8.4	7.1	7.5	7.5
90°	19.8	18.9	17.9	17.0	16.0	14.7	13.4	12.1	10.8	10.2	9.3
92.5°	33.9	33.4	32.9	32.4	31.9	31.1	30.3	29.5	28.7	28.3	27.3
95°	57.1	56.6	56.1	55.7	55.2	54.1	52.9	51.8	50.7	50.1	49.4
97.5°	83.9	83.2	82.6	81.9	81.3	80.0	78.7	77.4	76.1	75.5	74.9
100°	112.3	112.0	111.7	111.4	111.1	109.6	108.2	106.7	105.2	104.5	104.2
102.5°	143.5	143.0	142.5	142.0	141.5	140.2	138.9	137.6	136.3	135.7	135.6
105°	174.7	174.2	173.7	173.2	172.7	172.1	171.4	170.8	170.1	169.8	169.7
107.5°	208.7	208.0	207.4	206.7	206.1	205.9	205.8	205.6	205.5	205.4	205.3
110°	240.5	240.8	241.1	241.4	241.7	241.9	242.0	242.2	242.3	242.4	242.2

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	277.3	277.3	277.3	277.3	277.3	277.6	277.9	278.2	278.5	278.7	278.7
115°	314.4	314.5	314.7	314.8	315.0	315.3	315.7	316.0	316.3	316.5	316.5
117.5°	349.3	349.8	350.3	350.8	351.3	351.5	351.6	351.8	351.9	352.0	352.0
120°	385.1	385.9	386.7	387.5	388.3	388.8	389.3	389.8	390.3	390.5	390.2
122.5°	422.6	423.1	423.6	424.1	424.6	424.8	424.9	425.1	425.2	425.3	425.2
125°	458.9	459.2	459.5	459.9	460.2	460.4	460.5	460.7	460.8	460.9	460.9
127.5°	493.0	493.3	493.6	494.0	494.3	494.6	494.9	495.2	495.5	495.7	495.5
130°	529.3	529.6	529.9	530.3	530.6	530.6	530.6	530.6	530.6	530.6	530.4
132.5°	563.4	563.7	564.0	564.4	564.7	564.9	565.0	565.2	565.3	565.4	565.2
135°	597.6	597.9	598.2	598.5	598.8	598.8	598.8	598.8	598.8	598.8	598.3
137.5°	630.2	630.7	631.2	631.7	632.2	631.9	631.5	631.2	630.9	630.7	630.5
140°	663.5	663.6	663.8	663.9	664.1	664.1	664.1	664.1	664.1	664.1	663.9
142.5°	694.6	694.6	694.6	694.6	694.6	694.8	694.9	695.1	695.2	695.3	695.1
145°	725.2	725.3	725.5	725.6	725.8	725.6	725.5	725.3	725.2	725.1	724.8
147.5°	753.5	753.6	753.8	753.9	754.1	754.3	754.5	754.6	754.8	754.9	754.5
150°	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.3	780.0
152.5°	806.2	805.7	805.2	804.7	804.2	804.0	803.9	803.7	803.6	803.5	803.3
155°	829.3	828.6	828.0	827.3	826.7	826.9	827.0	827.2	827.3	827.4	827.4
157.5°	849.7	849.2	848.7	848.3	847.8	847.8	847.8	847.8	847.8	847.8	848.0
160°	868.6	868.1	867.6	867.1	866.6	866.8	867.0	867.1	867.3	867.4	867.5
162.5°	886.5	885.5	884.6	883.6	882.6	882.8	882.9	883.1	883.2	883.3	883.5
165°	901.0	900.0	899.1	898.1	897.1	897.4	897.8	898.1	898.4	898.6	898.8
167.5°	914.0	913.1	912.1	911.2	910.2	910.2	910.2	910.2	910.2	910.2	910.5
170°	924.2	923.3	922.3	921.4	920.4	920.2	920.0	919.9	919.7	919.6	920.0
172.5°	932.1	931.0	929.9	928.7	927.6	927.6	927.6	927.6	927.6	927.6	927.9
175°	937.2	936.1	935.0	933.8	932.7	932.9	933.0	933.2	933.3	933.4	933.8
177.5°	940.8	939.7	938.6	937.4	936.3	936.3	936.3	936.3	936.3	936.3	936.7
180°	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5	938.5

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	534.9	534.9	534.9	534.9
2.5°	520.3	524.7	528.7	534.9
5°	508.7	515.0	523.4	532.7
7.5°	495.5	505.2	516.3	529.1
10°	483.0	494.1	508.3	523.8
12.5°	470.2	483.5	499.0	515.8
15°	455.6	468.9	486.1	508.7
17.5°	442.3	458.2	476.8	500.8
20°	426.8	441.8	462.2	489.7
22.5°	413.0	430.3	452.9	476.8
25°	398.0	413.0	435.6	464.4
27.5°	382.9	401.5	423.2	451.1
30°	368.3	383.8	407.3	436.5
32.5°	352.3	370.9	392.6	420.1
35°	335.0	352.8	373.1	402.8
37.5°	319.5	336.8	357.6	383.8
40°	302.2	320.4	339.5	365.6
42.5°	285.4	301.8	320.8	344.8
45°	269.0	283.2	300.5	321.3
47.5°	252.2	264.1	280.1	298.7
50°	234.0	246.8	258.8	274.3
52.5°	217.1	228.2	238.0	250.8
55°	200.8	208.3	216.3	226.0
57.5°	183.5	189.2	195.0	205.2
60°	166.2	171.5	174.6	181.3
62.5°	149.3	151.6	155.5	159.5
65°	130.7	133.8	136.0	140.9
67.5°	113.9	115.2	117.4	120.5
70°	96.2	99.3	100.2	102.4
72.5°	81.1	82.4	83.3	83.8
75°	64.3	65.6	66.5	69.1
77.5°	50.5	50.1	51.8	52.3
80°	37.2	35.9	36.3	38.1
82.5°	24.4	24.8	24.4	24.4
85°	15.1	14.6	13.7	14.2
87.5°	6.6	6.6	6.2	6.2
90°	7.5	5.8	4.0	2.2
92.5°	25.2	23.1	21.0	18.9
95°	47.9	46.4	45.0	43.5
97.5°	73.6	72.3	71.0	69.7
100°	103.5	102.9	102.2	101.6
102.5°	135.5	135.3	135.2	135.0
105°	169.6	169.4	169.3	169.1
107.5°	205.2	205.0	204.9	204.7
110°	241.9	241.6	241.3	241.0

TEST NUMBER: P1033525

CATALOG NUMBER: S124DIW-B350D770UB50-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	278.7	278.7	278.7	278.7
115°	316.5	316.5	316.5	316.5
117.5°	352.0	352.0	352.0	352.0
120°	389.5	388.9	388.2	387.6
122.5°	425.1	424.9	424.8	424.6
125°	460.9	460.9	460.9	460.9
127.5°	495.0	494.5	494.1	493.6
130°	529.9	529.4	528.9	528.4
132.5°	564.9	564.6	564.3	564.0
135°	597.4	596.4	595.5	594.5
137.5°	630.0	629.5	629.1	628.6
140°	663.6	663.3	663.0	662.7
142.5°	694.8	694.5	694.2	693.9
145°	724.1	723.5	722.8	722.2
147.5°	753.7	752.8	752.0	751.2
150°	779.3	778.7	778.0	777.4
152.5°	803.0	802.7	802.3	802.0
155°	827.4	827.4	827.4	827.4
157.5°	848.3	848.6	848.9	849.2
160°	867.6	867.8	867.9	868.1
162.5°	884.0	884.5	885.0	885.5
165°	899.3	899.8	900.3	900.8
167.5°	911.2	911.8	912.5	913.1
170°	920.8	921.7	922.5	923.3
172.5°	928.6	929.2	929.9	930.5
175°	934.6	935.4	936.2	937.0
177.5°	937.5	938.4	939.2	940.0
180°	938.5	938.5	938.5	938.5

(END OF REPORT)