

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033559

Luminaire Tested: S124DIW-B575D1050UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033559
REPORT IS A COMBINATION OF REPORTS P997673 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B575D1050UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5934.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033559

CATALOG NUMBER: S124DIW-B575D1050UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033559

CATALOG NUMBER: S124DIW-B575D1050UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	47	47	47
1	96	91	87	84	87	83	80	77	68	66	64	54	53	51	42	41	40	40	40	40
2	87	80	74	69	79	73	68	63	60	56	53	48	45	43	37	35	33	33	33	33
3	79	70	63	57	72	64	58	53	53	48	44	42	39	36	32	30	28	28	28	28
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	29	27	25	25	25	25
5	67	55	47	41	60	50	43	38	42	37	32	34	30	27	26	23	21	21	21	21
6	61	49	41	36	56	45	38	33	38	32	28	30	26	23	24	21	19	19	19	19
7	57	44	37	31	51	41	34	29	34	29	25	28	24	21	22	19	17	17	17	17
8	52	40	33	27	48	37	30	26	31	26	22	25	21	18	20	17	15	15	15	15
9	49	37	29	24	44	34	27	23	28	23	20	23	19	17	18	16	13	13	13	13
10	46	34	27	22	41	31	25	20	26	21	18	21	18	15	17	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7584	7584	7584
5°	7589	7366	7375
10°	7526	7161	7111
15°	7417	6918	6813
20°	7280	6655	6506
25°	7125	6377	6174
30°	6937	6077	5811
35°	6744	5769	5459
40°	6541	5438	5085
45°	6330	5106	4735
50°	6095	4785	4348
55°	5841	4408	3963
60°	5579	3997	3563
65°	5282	3572	3111
70°	4937	3059	2627
75°	4424	2467	2104
80°	3771	1783	1480
85°	2925	992	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6330 cd/sqm

TEST NUMBER: P1033559

CATALOG NUMBER: S124DIW-B575D1050UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.5
10°-20°	247.0	4.2
20°-30°	363.4	6.1
30°-40°	422.5	7.1
40°-50°	422.5	7.1
50°-60°	369.5	6.2
60°-70°	274.3	4.6
70°-80°	155.6	2.6
80°-90°	47.3	0.8
90°-100°	83.3	1.4
100°-110°	249.4	4.2
110°-120°	423.7	7.1
120°-130°	558.7	9.4
130°-140°	627.6	10.6
140°-150°	616.8	10.4
150°-160°	518.8	8.7
160°-170°	345.2	5.8
170°-180°	120.9	2.0
0°-30°	698.1	11.8
0°-40°	1120.5	18.9
0°-60°	1912.5	32.2
0°-90°	2389.7	40.3
90°-120°	756.3	12.7
90°-150°	2559.4	43.1
90°-180°	3544.0	59.7
0°-180°	5934.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	930	930	930	930	930	
5°	929	926	918	926	925	88
15°	884	882	870	875	873	249
25°	801	796	785	786	783	369
35°	689	684	674	668	665	431
45°	563	557	546	537	535	434
55°	426	423	413	404	399	381
65°	288	285	277	270	266	285
75°	154	150	146	143	142	163
85°	40	40	39	39	38	43
90°	3	14	22	28	30	7
95°	59	68	75	78	78	64
105°	230	231	235	238	241	244
115°	431	431	429	428	427	425
125°	627	627	626	624	622	559
135°	809	815	815	813	810	626
145°	983	987	988	987	984	615
155°	1126	1126	1125	1129	1125	518
165°	1226	1223	1221	1227	1223	346
175°	1275	1270	1270	1276	1270	121
180°	1277	1277	1277	1277	1277	

TEST NUMBER: P1033559

CATALOG NUMBER: S124DIW-B575D1050UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	930.0	930.0	930.0	930.0	930.0
2.5°	933.0	930.7	922.5	930.0	929.2
5°	929.2	926.3	918.1	926.3	924.8
7.5°	922.5	919.6	910.6	917.3	916.6
10°	912.9	909.9	900.2	906.1	904.7
12.5°	900.2	897.2	886.8	893.5	891.2
15°	884.5	881.6	870.4	874.8	872.6
17.5°	866.6	862.9	852.5	855.5	854.0
20°	846.5	842.8	831.6	833.9	832.4
22.5°	824.9	819.7	808.5	813.0	810.0
25°	801.1	795.9	785.4	786.2	783.2
27.5°	774.2	769.0	759.3	757.9	754.1
30°	747.4	741.5	731.8	728.8	725.1
32.5°	719.1	713.9	703.5	699.7	696.0
35°	689.3	684.1	673.6	668.4	664.7
37.5°	658.0	653.5	642.3	637.1	631.9
40°	627.4	621.5	610.3	602.9	599.1
42.5°	594.7	591.7	579.0	570.1	567.8
45°	562.6	557.4	545.5	537.3	535.0
47.5°	529.1	525.4	514.2	505.2	499.3
50°	494.8	491.8	481.4	471.0	466.5
52.5°	461.3	457.5	446.4	437.4	431.5
55°	425.5	423.3	412.8	403.9	399.4
57.5°	392.0	389.7	379.3	370.4	365.9
60°	356.9	353.2	343.5	336.8	333.1
62.5°	322.7	319.7	309.3	303.3	299.6
65°	288.4	284.7	277.2	269.8	266.0
67.5°	253.4	250.4	242.9	235.5	234.7
70°	221.3	216.1	210.1	204.2	201.9
72.5°	187.0	181.8	177.4	172.9	170.6
75°	153.5	149.8	146.1	143.1	142.3
77.5°	120.7	119.2	115.5	114.8	112.5
80°	91.7	89.4	87.9	86.4	85.7
82.5°	63.3	62.6	62.6	61.9	61.1
85°	40.2	40.2	38.7	38.7	38.0
87.5°	19.4	18.6	17.9	17.9	17.9
90°	3.0	13.8	21.7	27.7	29.6
92.5°	25.7	38.5	43.5	46.4	47.4
95°	59.3	68.2	75.1	78.0	78.0
97.5°	94.8	102.7	110.6	114.6	114.6
100°	138.3	142.3	151.2	153.1	153.1
102.5°	183.8	184.7	192.6	195.6	196.6
105°	230.2	231.2	235.1	238.1	241.1
107.5°	278.6	279.6	280.6	284.5	283.5
110°	328.0	330.0	329.0	327.0	330.0

TEST NUMBER: P1033559

CATALOG NUMBER: S124DIW-B575D1050UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.4	379.4	377.4	377.4	377.4
115°	430.7	430.7	428.8	427.8	426.8
117.5°	479.1	479.1	478.2	475.2	472.2
120°	527.6	531.5	528.5	523.6	525.6
122.5°	577.9	578.9	577.9	575.0	570.0
125°	627.3	627.3	626.3	624.4	622.4
127.5°	671.8	674.8	672.8	670.8	669.8
130°	719.2	722.2	722.2	720.2	716.2
132.5°	767.6	769.6	768.6	766.6	765.6
135°	809.1	815.0	815.0	813.1	810.1
137.5°	855.5	858.5	860.5	857.5	858.5
140°	902.0	903.9	903.9	903.0	902.0
142.5°	944.5	946.4	945.4	945.4	945.4
145°	983.0	986.9	987.9	986.9	984.0
147.5°	1022.5	1027.4	1026.5	1025.5	1024.5
150°	1058.1	1062.0	1062.0	1062.0	1061.0
152.5°	1091.7	1093.6	1094.6	1097.6	1094.6
155°	1126.2	1126.2	1125.2	1129.2	1125.2
157.5°	1155.9	1153.9	1153.9	1156.9	1153.9
160°	1181.6	1180.6	1179.6	1182.5	1177.6
162.5°	1205.3	1202.3	1201.3	1207.2	1202.3
165°	1226.0	1223.0	1221.1	1227.0	1223.0
167.5°	1242.8	1238.9	1238.9	1244.8	1238.9
170°	1256.6	1251.7	1252.7	1258.6	1251.7
172.5°	1266.5	1262.6	1262.6	1269.5	1262.6
175°	1275.4	1270.5	1269.5	1276.4	1269.5
177.5°	1279.4	1274.4	1274.4	1281.3	1273.4
180°	1277.4	1277.4	1277.4	1277.4	1277.4

(END OF REPORT)