

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034226

Luminaire Tested: S124RDIW-B795D1050UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034226
REPORT IS A COMBINATION OF REPORTS P1000728 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1050UB35-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7513.0 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034226

CATALOG NUMBER: S124RDIW-B795D1050UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034226

CATALOG NUMBER: S124RDIW-B795D1050UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	97	92	89	85	88	85	81	78	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	39	38	36
3	80	71	64	58	73	65	59	54	55	50	46	44	41	39	35	33	31
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	31	29	27
5	68	56	48	43	62	52	45	40	43	38	34	36	32	29	28	26	24
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19
8	53	41	34	29	49	38	32	27	32	27	23	27	23	20	22	19	17
9	50	38	30	26	46	35	28	24	30	25	21	25	21	18	20	17	15
10	46	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11438	11438	11438
5°	11439	11098	11099
10°	11342	10748	10620
15°	11186	10312	10055
20°	10982	9815	9410
25°	10727	9279	8781
30°	10478	8732	8073
35°	10203	8177	7382
40°	9877	7579	6672
45°	9570	6987	5970
50°	9222	6341	5256
55°	8846	5677	4519
60°	8429	4974	3790
65°	8025	4166	3090
70°	7451	3316	2361
75°	6717	2412	1652
80°	5610	1481	1187
85°	4221	853	652

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9570 cd/sqm

TEST NUMBER: P1034226

CATALOG NUMBER: S124RDIW-B795D1050UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.9	1.8
10°-20°	367.8	4.9
20°-30°	530.9	7.1
30°-40°	601.7	8.0
40°-50°	581.0	7.7
50°-60°	483.0	6.4
60°-70°	333.4	4.4
70°-80°	168.5	2.2
80°-90°	45.6	0.6
90°-100°	45.8	0.6
100°-110°	301.6	4.0
110°-120°	575.9	7.7
120°-130°	731.1	9.7
130°-140°	782.1	10.4
140°-150°	731.3	9.7
150°-160°	589.8	7.9
160°-170°	380.4	5.1
170°-180°	131.1	1.7
0°-30°	1030.6	13.7
0°-40°	1632.3	21.7
0°-60°	2696.4	35.9
0°-90°	3243.8	43.2
90°-120°	923.3	12.3
90°-150°	3167.9	42.2
90°-180°	4269.0	56.8
0°-180°	7513.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1403	1403	1403	1403	1403	
5°	1400	1396	1383	1394	1392	133
15°	1334	1324	1297	1295	1288	376
25°	1206	1187	1143	1124	1114	556
35°	1043	1008	955	918	899	652
45°	851	811	746	694	674	656
55°	644	601	532	476	455	576
65°	438	392	323	277	264	433
75°	233	193	143	118	112	246
85°	58	36	33	31	31	64
90°	3	14	23	29	31	6
95°	57	22	23	29	30	70
105°	311	317	322	331	294	325
115°	580	583	582	584	584	571
125°	815	819	817	820	821	728
135°	1011	1010	1014	1016	1018	779
145°	1166	1169	1169	1170	1172	729
155°	1278	1280	1276	1281	1278	590
165°	1349	1344	1344	1352	1342	381
175°	1380	1374	1374	1384	1371	131
180°	1380	1380	1380	1380	1380	

TEST NUMBER: P1034226

CATALOG NUMBER: S124RDIW-B795D1050UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1402.7	1402.7	1402.7	1402.7	1402.7
2.5°	1407.0	1402.7	1390.8	1402.7	1401.6
5°	1400.5	1396.2	1383.3	1394.1	1391.9
7.5°	1390.8	1386.6	1370.4	1378.0	1374.7
10°	1375.8	1370.4	1351.1	1355.4	1351.1
12.5°	1356.5	1350.0	1326.4	1328.6	1322.1
15°	1333.9	1324.3	1297.4	1295.3	1287.7
17.5°	1308.1	1294.2	1263.0	1257.7	1246.9
20°	1277.0	1263.0	1226.5	1217.9	1204.0
22.5°	1242.6	1226.5	1186.8	1172.8	1162.1
25°	1206.1	1186.8	1142.8	1124.5	1113.8
27.5°	1168.5	1144.9	1098.7	1077.2	1062.2
30°	1128.8	1101.9	1051.5	1024.6	1007.4
32.5°	1086.9	1055.8	1003.1	970.9	954.8
35°	1042.9	1008.5	954.8	918.3	898.9
37.5°	996.7	961.2	902.2	862.4	843.1
40°	947.3	911.8	850.6	805.5	786.2
42.5°	900.0	862.4	798.0	751.8	731.4
45°	850.6	810.9	746.4	693.8	674.5
47.5°	800.1	759.3	692.7	638.0	616.5
50°	748.6	706.7	638.0	584.3	563.9
52.5°	696.0	655.1	584.3	529.5	508.0
55°	644.4	601.4	531.6	475.8	455.4
57.5°	593.9	548.8	480.1	423.2	408.1
60°	539.2	496.2	427.5	371.6	354.4
62.5°	489.8	444.6	373.8	323.3	310.4
65°	438.2	392.0	323.3	277.1	264.2
67.5°	384.5	340.5	276.0	235.2	220.2
70°	334.0	288.9	227.7	192.2	181.5
72.5°	280.3	240.6	183.7	154.7	145.0
75°	233.1	193.3	142.8	118.1	111.7
77.5°	183.7	149.3	106.3	89.1	87.0
80°	136.4	105.3	73.0	69.8	68.7
82.5°	95.6	67.7	52.6	50.5	49.4
85°	58.0	36.5	33.3	31.1	31.1
87.5°	24.7	16.1	15.0	14.0	15.0
90°	3.1	14.4	22.7	28.9	31.0
92.5°	15.5	13.4	21.7	27.9	27.9
95°	56.8	21.7	22.7	28.9	29.9
97.5°	108.4	131.1	22.7	27.9	28.9
100°	169.2	187.8	45.4	27.9	28.9
102.5°	237.3	249.7	262.1	29.9	29.9
105°	310.6	316.8	322.0	331.2	294.1
107.5°	377.7	380.8	388.0	393.2	397.3
110°	445.8	448.9	455.1	457.1	460.2



TEST NUMBER: P1034226

CATALOG NUMBER: S124RDIW-B795D1050UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	511.8	518.0	520.1	519.0	523.2
115°	579.9	583.0	582.0	584.1	584.1
117.5°	640.8	644.9	648.0	647.0	647.0
120°	702.7	706.9	705.8	707.9	705.8
122.5°	760.5	762.6	764.6	765.7	763.6
125°	815.2	819.3	817.3	820.4	821.4
127.5°	867.8	868.9	874.0	873.0	872.0
130°	918.4	919.4	922.5	923.6	923.6
132.5°	964.8	966.9	971.0	972.1	971.0
135°	1011.3	1010.2	1014.4	1016.4	1018.5
137.5°	1052.5	1052.5	1057.7	1059.8	1058.7
140°	1092.8	1094.9	1096.9	1100.0	1101.0
142.5°	1128.9	1133.0	1134.1	1136.1	1136.1
145°	1166.1	1169.1	1169.1	1170.2	1172.2
147.5°	1194.9	1201.1	1200.1	1201.1	1202.2
150°	1226.9	1231.1	1230.0	1230.0	1231.1
152.5°	1253.8	1256.9	1254.8	1256.9	1255.8
155°	1278.5	1279.6	1276.5	1280.6	1277.5
157.5°	1300.2	1300.2	1296.1	1301.2	1296.1
160°	1318.8	1315.7	1314.6	1320.8	1314.6
162.5°	1335.3	1331.2	1330.1	1336.3	1329.1
165°	1348.7	1343.5	1343.5	1351.8	1342.5
167.5°	1360.1	1354.9	1353.9	1363.1	1352.8
170°	1369.3	1363.1	1364.2	1372.4	1362.1
172.5°	1375.5	1369.3	1370.4	1378.6	1367.3
175°	1379.7	1373.5	1374.5	1383.8	1371.4
177.5°	1382.8	1375.5	1377.6	1385.9	1373.5
180°	1379.7	1379.7	1379.7	1379.7	1379.7

(END OF REPORT)