

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034242

Luminaire Tested: S124RDIW-B795D1340UB30-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034242
REPORT IS A COMBINATION OF REPORTS P1000766 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1340UB30-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8599.0 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034242

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034242

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	76	76	76	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	63	59	56	52	47	44	42	35	34	32
3	79	70	63	58	72	64	58	53	52	48	44	41	38	36	31	29	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24
5	67	55	48	42	60	51	44	39	42	37	33	33	30	27	25	23	21
6	61	50	42	36	56	45	39	34	37	32	28	30	26	23	23	21	19
7	57	45	37	32	51	41	34	29	34	29	25	27	24	21	21	19	17
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1034242

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	1.5
10°-20°	366.2	4.3
20°-30°	528.7	6.1
30°-40°	599.1	7.0
40°-50°	578.5	6.7
50°-60°	480.9	5.6
60°-70°	331.9	3.9
70°-80°	167.7	2.0
80°-90°	46.2	0.5
90°-100°	57.6	0.7
100°-110°	379.3	4.4
110°-120°	724.2	8.4
120°-130°	919.4	10.7
130°-140°	983.6	11.4
140°-150°	919.7	10.7
150°-160°	741.6	8.6
160°-170°	478.3	5.6
170°-180°	164.8	1.9
0°-30°	1026.2	11.9
0°-40°	1625.3	18.9
0°-60°	2684.7	31.2
0°-90°	3230.6	37.6
90°-120°	1161.0	13.5
90°-150°	3983.6	46.3
90°-180°	5368.0	62.4
0°-180°	8599.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	4	18	28	36	39	7
95°	71	27	28	36	38	88
105°	391	398	405	416	370	409
115°	729	733	732	734	734	718
125°	1025	1030	1028	1032	1033	915
135°	1272	1270	1276	1278	1281	980
145°	1466	1470	1470	1472	1474	916
155°	1608	1609	1605	1610	1606	741
165°	1696	1690	1690	1700	1688	479
175°	1735	1727	1728	1740	1724	165
180°	1735	1735	1735	1735	1735	

TEST NUMBER: P1034242

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	3.9	18.2	28.5	36.3	38.9
92.5°	19.5	16.9	27.2	35.0	35.0
95°	71.4	27.2	28.5	36.3	37.6
97.5°	136.2	164.8	28.5	35.0	36.3
100°	212.8	236.2	57.1	35.0	36.3
102.5°	298.5	314.0	329.6	37.6	37.6
105°	390.6	398.4	404.9	416.5	369.8
107.5°	474.9	478.8	487.9	494.4	499.6
110°	560.6	564.5	572.2	574.8	578.7

TEST NUMBER: P1034242

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	643.6	651.4	654.0	652.7	657.9
115°	729.3	733.2	731.9	734.4	734.4
117.5°	805.8	811.0	814.9	813.6	813.6
120°	883.7	888.9	887.6	890.2	887.6
122.5°	956.3	958.9	961.5	962.8	960.2
125°	1025.1	1030.3	1027.7	1031.6	1032.9
127.5°	1091.3	1092.6	1099.1	1097.8	1096.5
130°	1154.9	1156.2	1160.1	1161.4	1161.4
132.5°	1213.3	1215.9	1221.1	1222.4	1221.1
135°	1271.7	1270.4	1275.6	1278.1	1280.7
137.5°	1323.6	1323.6	1330.1	1332.6	1331.4
140°	1374.2	1376.8	1379.4	1383.3	1384.6
142.5°	1419.6	1424.8	1426.1	1428.7	1428.7
145°	1466.3	1470.2	1470.2	1471.5	1474.1
147.5°	1502.6	1510.4	1509.1	1510.4	1511.7
150°	1542.9	1548.1	1546.8	1546.8	1548.1
152.5°	1576.6	1580.5	1577.9	1580.5	1579.2
155°	1607.7	1609.0	1605.1	1610.3	1606.4
157.5°	1635.0	1635.0	1629.8	1636.3	1629.8
160°	1658.3	1654.5	1653.2	1660.9	1653.2
162.5°	1679.1	1673.9	1672.6	1680.4	1671.3
165°	1696.0	1689.5	1689.5	1699.9	1688.2
167.5°	1710.3	1703.8	1702.5	1714.1	1701.2
170°	1721.9	1714.1	1715.4	1725.8	1712.8
172.5°	1729.7	1721.9	1723.2	1733.6	1719.3
175°	1734.9	1727.1	1728.4	1740.1	1724.5
177.5°	1738.8	1729.7	1732.3	1742.7	1727.1
180°	1734.9	1734.9	1734.9	1734.9	1734.9

(END OF REPORT)