

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034243

Luminaire Tested: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034243
REPORT IS A COMBINATION OF REPORTS P1000767 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7885.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034243

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1034243

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41
2	88	80	74	69	80	74	68	64	61	57	54	49	46	44	38	36	35
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	34	32	30
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26
5	67	56	48	42	61	51	44	39	43	38	34	35	31	28	27	25	23
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16
9	49	38	30	25	45	35	28	24	29	24	21	24	20	17	19	16	14
10	46	34	27	23	42	32	25	21	27	22	19	22	18	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11389	11389	11389
5°	11390	11051	11051
10°	11293	10702	10574
15°	11138	10267	10012
20°	10934	9772	9370
25°	10681	9238	8742
30°	10432	8693	8039
35°	10159	8142	7351
40°	9834	7546	6644
45°	9528	6957	5944
50°	9183	6313	5232
55°	8807	5653	4499
60°	8391	4952	3774
65°	7990	4148	3077
70°	7420	3301	2351
75°	6689	2401	1644
80°	5585	1474	1182
85°	4199	851	650

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9528 cd/sqm

TEST NUMBER: P1034243

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	1.7
10°-20°	366.2	4.6
20°-30°	528.7	6.7
30°-40°	599.1	7.6
40°-50°	578.5	7.3
50°-60°	480.9	6.1
60°-70°	331.9	4.2
70°-80°	167.7	2.1
80°-90°	46.2	0.6
90°-100°	109.3	1.4
100°-110°	327.5	4.2
110°-120°	556.4	7.1
120°-130°	733.8	9.3
130°-140°	824.1	10.5
140°-150°	810.0	10.3
150°-160°	681.3	8.6
160°-170°	453.3	5.7
170°-180°	158.7	2.0
0°-30°	1026.2	13.0
0°-40°	1625.3	20.6
0°-60°	2684.7	34.0
0°-90°	3230.6	41.0
90°-120°	993.2	12.6
90°-150°	3361.1	42.6
90°-180°	4654.0	59.0
0°-180°	7885.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1397	1397	1397	1397	1397	
5°	1394	1390	1377	1388	1386	132
15°	1328	1318	1292	1290	1282	374
25°	1201	1182	1138	1120	1109	553
35°	1038	1004	951	914	895	649
45°	847	807	743	691	672	653
55°	642	599	529	474	453	574
65°	436	390	322	276	263	431
75°	232	192	142	118	111	245
85°	58	36	33	31	31	63
90°	4	18	28	36	39	9
95°	78	90	99	102	102	84
105°	302	304	309	313	317	321
115°	566	566	563	562	560	558
125°	824	824	822	820	817	734
135°	1062	1070	1070	1068	1064	822
145°	1291	1296	1297	1296	1292	808
155°	1479	1479	1478	1483	1478	681
165°	1610	1606	1604	1611	1606	454
175°	1675	1668	1667	1676	1667	159
180°	1678	1678	1678	1678	1678	

TEST NUMBER: P1034243

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1396.6	1396.6	1396.6	1396.6	1396.6
2.5°	1400.9	1396.6	1384.8	1396.6	1395.5
5°	1394.5	1390.2	1377.4	1388.0	1385.9
7.5°	1384.8	1380.6	1364.5	1372.0	1368.8
10°	1369.9	1364.5	1345.3	1349.6	1345.3
12.5°	1350.6	1344.2	1320.7	1322.8	1316.4
15°	1328.2	1318.5	1291.8	1289.7	1282.2
17.5°	1302.5	1288.6	1257.6	1252.2	1241.5
20°	1271.5	1257.6	1221.2	1212.7	1198.8
22.5°	1237.3	1221.2	1181.7	1167.8	1157.1
25°	1200.9	1181.7	1137.8	1119.6	1108.9
27.5°	1163.5	1140.0	1094.0	1072.6	1057.6
30°	1123.9	1097.2	1046.9	1020.2	1003.1
32.5°	1082.2	1051.2	998.8	966.7	950.7
35°	1038.4	1004.1	950.7	914.3	895.1
37.5°	992.4	957.1	898.3	858.7	839.5
40°	943.2	907.9	846.9	802.0	782.8
42.5°	896.1	858.7	794.5	748.6	728.2
45°	846.9	807.4	743.2	690.8	671.6
47.5°	796.7	756.0	689.7	635.2	613.8
50°	745.4	703.6	635.2	581.7	561.4
52.5°	693.0	652.3	581.7	527.2	505.8
55°	641.6	598.8	529.3	473.7	453.4
57.5°	591.4	546.5	478.0	421.3	406.4
60°	536.8	494.1	425.6	370.0	352.9
62.5°	487.6	442.7	372.1	321.9	309.0
65°	436.3	390.3	321.9	275.9	263.1
67.5°	382.8	339.0	274.8	234.2	219.2
70°	332.6	287.7	226.7	191.4	180.7
72.5°	279.1	239.5	182.9	154.0	144.4
75°	232.1	192.5	142.2	117.6	111.2
77.5°	182.9	148.6	105.9	88.8	86.6
80°	135.8	104.8	72.7	69.5	68.4
82.5°	95.2	67.4	52.4	50.3	49.2
85°	57.7	36.4	33.2	31.0	31.0
87.5°	24.6	16.0	15.0	13.9	15.0
90°	3.9	18.2	28.5	36.3	38.9
92.5°	33.7	50.6	57.1	61.0	62.3
95°	77.8	89.5	98.6	102.5	102.5
97.5°	124.5	134.9	145.3	150.5	150.5
100°	181.6	186.8	198.5	201.1	201.1
102.5°	241.3	242.6	253.0	256.9	258.2
105°	302.3	303.6	308.8	312.7	316.6
107.5°	365.9	367.2	368.5	373.6	372.3
110°	430.7	433.3	432.0	429.4	433.3

TEST NUMBER: P1034243

CATALOG NUMBER: S124RDIW-B795D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.2	498.2	495.6	495.6	495.6
115°	565.6	565.6	563.1	561.8	560.5
117.5°	629.2	629.2	627.9	624.0	620.1
120°	692.8	698.0	694.1	687.6	690.2
122.5°	759.0	760.3	759.0	755.1	748.6
125°	823.8	823.8	822.5	819.9	817.3
127.5°	882.2	886.1	883.5	880.9	879.6
130°	944.5	948.4	948.4	945.8	940.6
132.5°	1008.0	1010.6	1009.3	1006.8	1005.5
135°	1062.5	1070.3	1070.3	1067.7	1063.8
137.5°	1123.5	1127.4	1130.0	1126.1	1127.4
140°	1184.5	1187.1	1187.1	1185.8	1184.5
142.5°	1240.3	1242.9	1241.6	1241.6	1241.6
145°	1290.9	1296.1	1297.4	1296.1	1292.2
147.5°	1342.8	1349.3	1348.0	1346.7	1345.4
150°	1389.5	1394.7	1394.7	1394.7	1393.4
152.5°	1433.6	1436.2	1437.5	1441.4	1437.5
155°	1479.0	1479.0	1477.7	1482.9	1477.7
157.5°	1517.9	1515.3	1515.3	1519.2	1515.3
160°	1551.6	1550.3	1549.0	1552.9	1546.5
162.5°	1582.8	1578.9	1577.6	1585.4	1578.9
165°	1610.0	1606.1	1603.5	1611.3	1606.1
167.5°	1632.1	1626.9	1626.9	1634.7	1626.9
170°	1650.2	1643.8	1645.1	1652.8	1643.8
172.5°	1663.2	1658.0	1658.0	1667.1	1658.0
175°	1674.9	1668.4	1667.1	1676.2	1667.1
177.5°	1680.1	1673.6	1673.6	1682.7	1672.3
180°	1677.5	1677.5	1677.5	1677.5	1677.5

(END OF REPORT)