

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034268

Luminaire Tested: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034268
REPORT IS A COMBINATION OF REPORTS P1000820 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8797.0 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

Luminous Intensity Polar Plot



TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	88	84	87	83	80	77	68	65	64	53	52	51	40	40	39	33		
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	34	33	28		
3	80	71	64	58	72	64	59	54	53	49	45	42	39	37	32	30	29	24		
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21		
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18		
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16		
7	57	45	38	32	52	42	35	30	35	29	26	28	24	21	22	19	17	14		
8	53	41	34	28	48	38	31	27	31	26	23	26	22	19	20	17	15	13		
9	49	37	30	25	45	35	28	24	29	24	20	24	20	17	18	16	14	12		
10	46	34	27	23	42	32	25	21	27	22	18	22	18	16	17	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10758	10758	10758	10758
5°	10759	12157	10776	9291
10°	10701	14013	10692	8080
15°	10573	15772	10573	6765
20°	10440	17099	10386	5957
25°	10278	17173	10231	5380
30°	10104	14602	10025	4984
35°	9860	11018	9735	4688
40°	9588	7985	9399	4457
45°	9138	6069	8911	4253
50°	8604	4904	8368	3954
55°	8026	4061	7764	3555
60°	7446	3434	7113	2956
65°	6717	2797	6503	2350
70°	6048	2268	5763	1909
75°	5300	1635	4934	1399
80°	4372	1083	3977	1028
85°	3173	558	2627	558

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 13468 cd/sqm

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	127.7	1.5
10°-20°	385.8	4.4
20°-30°	604.3	6.9
30°-40°	671.0	7.6
40°-50°	594.6	6.8
50°-60°	463.4	5.3
60°-70°	303.1	3.4
70°-80°	148.7	1.7
80°-90°	40.4	0.5
90°-100°	128.2	1.5
100°-110°	384.0	4.4
110°-120°	652.4	7.4
120°-130°	860.4	9.8
130°-140°	966.4	11.0
140°-150°	949.8	10.8
150°-160°	798.9	9.1
160°-170°	531.5	6.0
170°-180°	186.1	2.1
0°-30°	1117.8	12.7
0°-40°	1788.9	20.3
0°-60°	2846.9	32.4
0°-90°	3339.2	38.0
90°-120°	1164.7	13.2
90°-150°	3941.3	44.8
90°-180°	5458.0	62.0
0°-180°	8797.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1319	1319	1319	1319	1319	
5°	1317	1524	1319	1165	1317	125
15°	1261	2020	1261	866	1261	356
25°	1156	2178	1150	682	1156	533
35°	1008	1342	995	571	1008	630
45°	812	686	792	480	812	626
55°	585	409	566	358	585	523
65°	367	239	355	201	367	366
75°	184	111	171	95	184	195
85°	44	27	36	27	44	49
90°	5	46	5	46	5	10
95°	91	120	91	120	91	99
105°	354	371	354	371	354	376
115°	663	657	663	657	663	654
125°	966	958	966	958	966	861
135°	1246	1248	1246	1248	1246	964
145°	1514	1515	1514	1515	1514	947
155°	1734	1733	1734	1733	1734	798
165°	1888	1883	1888	1883	1888	532
175°	1964	1955	1964	1955	1964	186
180°	1967	1967	1967	1967	1967	

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1321.4	1333.1	1339.5	1344.8	1355.4	1359.7	1368.2	1370.3	1378.8	1377.8	1374.6
5°	1317.2	1337.4	1352.2	1368.2	1387.3	1398.0	1409.6	1426.7	1435.2	1446.9	1454.3
7.5°	1309.7	1337.4	1361.8	1386.3	1417.1	1434.1	1449.0	1475.6	1497.9	1517.0	1538.3
10°	1298.0	1333.1	1369.3	1402.2	1444.7	1464.9	1487.3	1526.6	1557.4	1584.0	1618.0
12.5°	1280.0	1328.9	1369.3	1413.9	1468.1	1495.8	1525.5	1572.3	1608.4	1652.0	1694.6
15°	1260.8	1315.0	1368.2	1426.7	1488.3	1520.2	1550.0	1612.7	1668.0	1717.9	1764.7
17.5°	1239.6	1299.1	1357.6	1422.4	1496.8	1536.2	1571.2	1646.7	1707.3	1772.2	1818.9
20°	1214.0	1278.9	1345.9	1418.2	1502.1	1545.7	1585.1	1671.2	1738.1	1808.3	1866.8
22.5°	1186.4	1256.6	1329.9	1408.6	1495.8	1543.6	1589.3	1681.8	1759.4	1824.3	1902.9
25°	1155.6	1230.0	1305.5	1388.4	1486.2	1538.3	1585.1	1676.5	1759.4	1844.4	1921.0
27.5°	1123.7	1200.2	1278.9	1366.1	1466.0	1517.0	1570.2	1658.4	1755.1	1847.6	1925.2
30°	1088.6	1163.0	1245.9	1328.9	1435.2	1486.2	1540.4	1636.1	1741.3	1833.8	1917.8
32.5°	1050.3	1126.9	1205.5	1291.6	1395.8	1451.1	1501.1	1609.5	1716.9	1808.3	1887.0
35°	1007.8	1080.1	1154.5	1242.7	1345.9	1395.8	1455.4	1568.0	1676.5	1773.2	1824.3
37.5°	962.1	1031.2	1100.3	1187.5	1286.3	1346.9	1405.4	1519.1	1634.0	1698.8	1725.4
40°	919.6	980.2	1040.8	1124.7	1224.7	1287.4	1346.9	1464.9	1565.9	1615.9	1595.7
42.5°	865.3	928.1	982.3	1059.9	1160.9	1219.4	1280.0	1402.2	1484.1	1504.3	1454.3
45°	812.2	864.3	916.4	991.9	1098.2	1148.1	1213.0	1326.7	1394.8	1376.7	1303.3
47.5°	760.1	802.6	851.5	924.9	1020.6	1080.1	1140.7	1239.6	1287.4	1261.9	1159.8
50°	698.4	741.0	792.0	855.8	948.3	1005.7	1053.5	1144.9	1181.1	1118.4	995.0
52.5°	640.0	677.2	720.8	780.3	868.5	920.6	972.7	1051.4	1063.1	990.8	861.1
55°	584.7	614.5	660.2	708.0	788.8	844.1	880.2	947.2	944.0	853.7	742.0
57.5°	527.3	554.9	585.8	635.7	712.3	753.7	793.1	851.5	820.7	744.2	633.6
60°	476.3	492.2	523.0	570.9	635.7	671.9	702.7	734.6	708.0	625.1	540.0
62.5°	419.9	438.0	460.3	498.6	556.0	590.0	612.3	626.2	598.5	534.7	457.1
65°	366.8	382.7	406.1	440.1	483.7	509.2	520.9	530.5	515.6	443.3	381.6
67.5°	318.9	329.6	350.8	373.1	419.9	426.3	442.2	446.5	416.7	361.4	312.5
70°	271.1	281.7	291.3	317.9	339.1	350.8	354.0	354.0	324.2	288.1	247.7
72.5°	226.4	232.8	242.4	260.5	272.1	280.7	284.9	279.6	252.0	222.2	192.4
75°	183.9	187.1	195.6	207.3	216.9	213.7	212.6	206.2	186.0	164.8	147.8
77.5°	141.4	143.5	153.1	156.3	156.3	159.5	155.2	148.8	131.8	115.9	108.4
80°	106.3	109.5	110.6	112.7	110.6	110.6	107.4	96.7	88.2	80.8	75.5
82.5°	73.4	75.5	76.5	73.4	75.5	72.3	67.0	59.5	54.2	53.2	51.0
85°	43.6	44.6	43.6	43.6	40.4	39.3	35.1	34.0	31.9	31.9	30.8
87.5°	21.3	20.2	18.1	15.9	15.9	14.9	15.9	13.8	15.9	14.9	13.8
90°	4.6	8.3	12.0	15.7	19.4	21.3	22.7	25.4	28.1	30.8	33.5
92.5°	39.6	44.0	48.4	52.7	57.1	59.3	60.1	61.8	63.5	65.2	66.9
95°	91.3	94.3	97.4	100.4	103.5	105.0	106.2	108.5	110.9	113.2	115.6
97.5°	146.0	148.7	151.4	154.1	156.8	158.2	159.6	162.3	165.0	167.7	170.4
100°	213.0	214.4	215.7	217.1	218.4	219.1	220.6	223.7	226.7	229.8	232.8
102.5°	283.0	283.3	283.7	284.0	284.3	284.5	285.9	288.6	291.3	294.0	296.7
105°	354.5	354.8	355.2	355.5	355.8	356.0	356.7	358.0	359.4	360.7	362.1
107.5°	429.0	429.3	429.7	430.0	430.3	430.5	430.7	431.0	431.3	431.7	432.0
110°	505.1	505.8	506.4	507.1	507.8	508.1	507.9	507.6	507.3	506.9	506.6

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	584.2	584.2	584.2	584.2	584.2	584.2	583.9	583.2	582.5	581.8	581.1
115°	663.3	663.3	663.3	663.3	663.3	663.3	663.0	662.3	661.6	660.9	660.2
117.5°	737.8	737.8	737.8	737.8	737.8	737.8	737.6	737.3	737.0	736.6	736.3
120°	812.4	813.8	815.1	816.5	817.8	818.5	818.0	817.0	815.9	814.9	813.9
122.5°	890.0	890.3	890.7	891.0	891.3	891.5	891.3	891.0	890.7	890.3	890.0
125°	966.0	966.0	966.0	966.0	966.0	966.0	965.8	965.5	965.2	964.8	964.5
127.5°	1034.5	1035.5	1036.5	1037.5	1038.5	1039.0	1038.7	1038.0	1037.3	1036.7	1036.0
130°	1107.5	1108.5	1109.5	1110.6	1111.6	1112.1	1112.1	1112.1	1112.1	1112.1	1112.1
132.5°	1182.0	1182.7	1183.4	1184.1	1184.8	1185.1	1184.9	1184.6	1184.3	1183.9	1183.6
135°	1245.9	1247.9	1250.0	1252.0	1254.1	1255.1	1255.1	1255.1	1255.1	1255.1	1255.1
137.5°	1317.4	1318.4	1319.4	1320.5	1321.5	1322.0	1322.3	1323.0	1323.7	1324.3	1325.0
140°	1388.9	1389.6	1390.3	1391.0	1391.7	1392.0	1392.0	1392.0	1392.0	1392.0	1392.0
142.5°	1454.4	1455.1	1455.7	1456.4	1457.1	1457.4	1457.2	1456.9	1456.6	1456.2	1455.9
145°	1513.7	1515.1	1516.4	1517.8	1519.1	1519.8	1520.0	1520.3	1520.6	1521.0	1521.3
147.5°	1574.5	1576.2	1577.9	1579.6	1581.3	1582.1	1581.9	1581.6	1581.3	1580.9	1580.6
150°	1629.3	1630.7	1632.0	1633.4	1634.7	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4
152.5°	1681.0	1681.7	1682.4	1683.1	1683.8	1684.1	1684.3	1684.6	1684.9	1685.3	1685.6
155°	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.1	1733.8	1733.5	1733.1	1732.8
157.5°	1779.9	1779.2	1778.6	1777.9	1777.2	1776.9	1776.9	1776.9	1776.9	1776.9	1776.9
160°	1819.5	1819.1	1818.8	1818.4	1818.1	1817.9	1817.7	1817.4	1817.1	1816.7	1816.4
162.5°	1856.0	1855.0	1854.0	1852.9	1851.9	1851.4	1851.2	1850.9	1850.6	1850.2	1849.9
165°	1887.9	1886.9	1885.9	1884.9	1883.9	1883.4	1883.1	1882.4	1881.7	1881.0	1880.3
167.5°	1913.8	1912.4	1911.1	1909.7	1908.4	1907.7	1907.7	1907.7	1907.7	1907.7	1907.7
170°	1935.1	1933.4	1931.7	1930.0	1928.3	1927.5	1927.7	1928.0	1928.3	1928.7	1929.0
172.5°	1950.3	1948.9	1947.6	1946.2	1944.9	1944.2	1944.2	1944.2	1944.2	1944.2	1944.2
175°	1964.0	1962.3	1960.6	1958.9	1957.2	1956.4	1956.2	1955.9	1955.6	1955.2	1954.9
177.5°	1970.1	1968.4	1966.7	1965.0	1963.3	1962.5	1962.5	1962.5	1962.5	1962.5	1962.5
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1383.1	1394.8	1395.8	1406.5	1403.3	1398.0	1407.5	1401.1	1413.9	1409.6	1415.0
5°	1463.9	1479.8	1493.6	1502.1	1517.0	1513.8	1529.8	1524.5	1536.2	1524.5	1539.3
7.5°	1558.5	1585.1	1598.9	1621.2	1627.6	1628.6	1647.8	1652.0	1659.5	1652.0	1660.5
10°	1651.0	1682.9	1714.8	1732.8	1744.5	1760.5	1777.5	1784.9	1790.2	1782.8	1788.1
12.5°	1735.0	1784.9	1820.0	1856.1	1864.6	1878.5	1896.5	1894.4	1915.7	1911.4	1921.0
15°	1812.6	1867.8	1910.4	1939.1	1962.5	1974.1	2008.2	2010.3	2009.2	2019.9	2013.5
17.5°	1881.7	1928.4	1989.0	2026.2	2054.9	2054.9	2074.1	2113.4	2110.2	2109.2	2115.5
20°	1938.0	1991.2	2047.5	2110.2	2133.6	2137.9	2164.4	2184.6	2187.8	2187.8	2187.8
22.5°	1980.5	2043.2	2103.8	2148.5	2166.6	2181.4	2204.8	2217.6	2221.8	2219.7	2221.8
25°	2001.8	2061.3	2123.0	2163.4	2174.0	2182.5	2184.6	2192.1	2191.0	2178.3	2185.7
27.5°	2006.0	2063.4	2103.8	2114.5	2109.2	2103.8	2069.8	2073.0	2063.4	2044.3	2051.8
30°	1986.9	2017.7	2016.7	1983.7	1974.1	1951.8	1921.0	1875.3	1838.1	1822.1	1827.4
32.5°	1917.8	1917.8	1879.5	1805.1	1772.2	1731.8	1676.5	1635.0	1586.1	1575.5	1595.7
35°	1822.1	1767.9	1697.7	1599.9	1550.0	1520.2	1424.5	1394.8	1353.3	1341.6	1351.2
37.5°	1673.3	1582.9	1480.9	1389.4	1346.9	1293.8	1209.8	1167.3	1137.5	1117.3	1126.9
40°	1506.4	1396.9	1290.6	1177.9	1131.1	1087.5	1024.8	986.5	938.7	940.8	944.0
42.5°	1346.9	1218.3	1099.2	995.0	950.4	914.3	870.7	823.9	806.9	801.6	796.2
45°	1177.9	1040.8	929.1	851.5	811.1	777.1	736.7	710.1	689.9	685.7	691.0
47.5°	1018.4	902.6	796.2	724.0	691.0	674.0	642.1	617.7	604.9	594.3	600.6
50°	873.9	765.4	680.4	619.8	596.4	584.7	554.9	542.2	529.4	526.2	525.2
52.5°	754.8	662.3	588.9	540.0	522.0	515.6	493.3	475.2	464.6	467.8	469.9
55°	646.4	567.7	510.3	470.9	456.1	448.6	432.7	419.9	412.5	409.3	411.4
57.5°	550.7	482.6	441.2	409.3	397.6	394.4	377.4	373.1	367.8	364.6	364.6
60°	463.5	415.7	377.4	359.3	346.6	343.4	330.6	325.3	324.2	321.1	318.9
62.5°	390.2	350.8	324.2	305.1	299.8	298.7	290.2	283.8	280.7	278.5	278.5
65°	326.4	297.7	275.3	261.5	257.3	255.1	245.6	243.4	241.3	239.2	238.1
67.5°	272.1	246.6	230.7	221.1	215.8	216.9	211.6	207.3	207.3	206.2	205.2
70°	220.1	204.1	190.3	185.0	182.9	180.7	178.6	175.4	174.3	174.3	174.3
72.5°	173.3	162.7	155.2	152.0	149.9	147.8	145.6	145.6	145.6	144.6	144.6
75°	132.9	128.6	123.3	120.1	120.1	122.3	119.1	115.9	112.7	110.6	111.6
77.5°	99.9	97.8	94.6	89.3	90.4	88.2	88.2	86.1	87.2	87.2	85.0
80°	73.4	70.2	69.1	65.9	67.0	65.9	64.8	64.8	62.7	62.7	62.7
82.5°	51.0	47.8	47.8	46.8	45.7	45.7	44.6	44.6	45.7	43.6	43.6
85°	30.8	29.8	29.8	27.6	27.6	27.6	27.6	28.7	27.6	26.6	26.6
87.5°	13.8	14.9	13.8	12.8	12.8	12.8	11.7	11.7	10.6	11.7	11.7
90°	35.5	37.5	39.6	41.6	42.6	42.9	43.6	44.3	44.9	45.6	44.9
92.5°	67.9	68.9	70.0	71.0	71.5	71.7	72.0	72.3	72.7	73.0	72.7
95°	116.6	117.6	118.7	119.7	120.2	120.2	120.2	120.2	120.2	120.2	120.2
97.5°	171.8	173.1	174.5	175.8	176.5	176.5	176.5	176.5	176.5	176.5	176.5
100°	233.5	234.1	234.8	235.5	235.8	235.8	235.8	235.8	235.8	235.8	235.8
102.5°	297.7	298.7	299.7	300.7	301.2	301.4	301.7	302.0	302.4	302.7	302.4
105°	363.1	364.1	365.1	366.1	366.6	367.1	368.1	369.2	370.2	371.2	370.2
107.5°	433.4	434.7	436.1	437.4	438.1	437.9	437.6	437.3	436.9	436.6	436.9
110°	505.9	505.2	504.5	503.8	503.5	504.0	505.0	506.1	507.1	508.1	507.1

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1
115°	659.9	659.5	659.2	658.9	658.7	658.5	658.2	657.9	657.5	657.2	657.5
117.5°	735.3	734.3	733.2	732.2	731.7	731.2	730.2	729.2	728.2	727.2	728.2
120°	812.2	810.5	808.8	807.1	806.3	806.6	807.3	808.0	808.6	809.3	808.6
122.5°	889.0	888.0	886.9	885.9	885.4	884.6	882.9	881.2	879.5	877.8	879.5
125°	963.8	963.2	962.5	961.8	961.5	961.2	960.5	959.8	959.1	958.4	959.1
127.5°	1035.3	1034.7	1034.0	1033.3	1033.0	1032.8	1032.5	1032.1	1031.8	1031.4	1031.8
130°	1111.4	1110.7	1110.0	1109.3	1109.0	1108.3	1107.0	1105.6	1104.3	1102.9	1104.3
132.5°	1182.9	1182.2	1181.5	1180.8	1180.5	1180.3	1180.0	1179.7	1179.3	1179.0	1179.3
135°	1254.4	1253.7	1253.0	1252.3	1252.0	1251.5	1250.5	1249.5	1248.5	1247.5	1248.5
137.5°	1324.0	1323.0	1322.0	1321.0	1320.5	1320.7	1321.0	1321.3	1321.7	1322.0	1321.7
140°	1391.7	1391.3	1391.0	1390.7	1390.5	1390.3	1390.0	1389.6	1389.3	1388.9	1389.3
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9
145°	1521.0	1520.6	1520.3	1520.0	1519.8	1519.3	1518.3	1517.2	1516.2	1515.2	1516.2
147.5°	1580.3	1579.9	1579.6	1579.3	1579.1	1578.9	1578.6	1578.3	1577.9	1577.6	1577.9
150°	1635.4	1635.4	1635.4	1635.4	1635.4	1635.2	1634.9	1634.6	1634.2	1633.9	1634.2
152.5°	1686.6	1687.6	1688.7	1689.7	1690.2	1689.7	1688.7	1687.6	1686.6	1685.6	1686.6
155°	1734.1	1735.5	1736.8	1738.1	1738.8	1738.1	1736.8	1735.5	1734.1	1732.8	1734.1
157.5°	1777.9	1778.9	1779.9	1780.9	1781.4	1780.9	1779.9	1778.9	1777.9	1776.9	1777.9
160°	1817.4	1818.4	1819.5	1820.5	1821.0	1820.2	1818.5	1816.8	1815.1	1813.4	1815.1
162.5°	1851.9	1853.9	1856.0	1858.0	1859.0	1858.2	1856.5	1854.8	1853.1	1851.4	1853.1
165°	1882.3	1884.3	1886.4	1888.4	1889.4	1888.7	1887.4	1886.1	1884.7	1883.4	1884.7
167.5°	1909.7	1911.7	1913.8	1915.8	1916.8	1915.8	1913.8	1911.7	1909.7	1907.7	1909.7
170°	1931.0	1933.0	1935.1	1937.1	1938.1	1936.9	1934.6	1932.2	1929.9	1927.5	1929.9
172.5°	1946.6	1949.0	1951.3	1953.7	1954.9	1953.7	1951.3	1949.0	1946.6	1944.2	1946.6
175°	1957.3	1959.6	1962.0	1964.3	1965.5	1964.3	1962.0	1959.6	1957.3	1954.9	1957.3
177.5°	1964.9	1967.2	1969.6	1971.9	1973.1	1971.7	1969.0	1966.3	1963.6	1960.9	1963.6
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1418.2	1410.7	1409.6	1409.6	1398.0	1404.3	1391.6	1377.8	1371.4	1371.4	1359.7
5°	1536.2	1528.7	1521.3	1509.6	1509.6	1503.2	1483.0	1462.8	1447.9	1435.2	1421.3
7.5°	1657.3	1649.9	1628.6	1616.9	1623.3	1610.6	1584.0	1550.0	1524.5	1504.3	1475.6
10°	1789.2	1769.0	1758.3	1752.0	1729.6	1715.8	1685.0	1635.0	1603.1	1576.6	1539.3
12.5°	1896.5	1902.9	1862.5	1865.7	1843.4	1824.3	1776.4	1728.6	1680.7	1643.5	1588.2
15°	2012.4	1993.3	1968.8	1949.7	1942.3	1918.9	1878.5	1814.7	1762.6	1704.1	1641.4
17.5°	2103.8	2089.0	2065.6	2047.5	2031.6	1975.2	1941.2	1884.8	1813.6	1756.2	1679.7
20°	2181.4	2167.6	2134.7	2123.0	2094.3	2053.9	2005.0	1917.8	1854.0	1791.3	1716.9
22.5°	2214.4	2200.6	2171.9	2157.0	2138.9	2099.6	2052.8	1969.9	1891.2	1812.6	1733.9
25°	2186.8	2186.8	2172.9	2167.6	2151.7	2116.6	2068.8	1998.6	1914.6	1829.6	1736.0
27.5°	2052.8	2079.4	2089.0	2094.3	2094.3	2095.3	2062.4	1994.3	1912.5	1829.6	1731.8
30°	1859.3	1904.0	1943.3	1955.0	1975.2	1997.5	2011.4	1978.4	1905.0	1817.9	1720.1
32.5°	1615.9	1673.3	1746.6	1764.7	1792.4	1859.3	1896.5	1910.4	1870.0	1793.4	1689.2
35°	1373.5	1445.8	1490.4	1545.7	1571.2	1670.1	1753.0	1803.0	1793.4	1747.7	1653.1
37.5°	1161.9	1203.4	1257.6	1316.1	1367.1	1461.7	1564.9	1661.6	1700.9	1678.6	1607.4
40°	958.9	1007.8	1072.7	1120.5	1155.6	1250.2	1377.8	1483.0	1569.1	1582.9	1539.3
42.5°	815.4	864.3	903.6	955.7	983.4	1074.8	1187.5	1319.3	1421.3	1475.6	1456.4
45°	704.8	734.6	766.5	796.2	830.3	911.1	1015.2	1159.8	1274.6	1351.2	1358.6
47.5°	608.1	634.7	662.3	689.9	709.1	771.8	867.5	985.5	1110.9	1216.2	1257.6
50°	540.0	552.8	573.0	588.9	611.3	665.5	742.0	844.1	977.0	1090.7	1144.9
52.5°	473.1	489.0	505.0	518.8	533.7	571.9	642.1	730.3	845.2	962.1	1029.1
55°	416.7	429.5	444.4	453.9	462.4	496.5	549.6	617.7	716.5	827.1	910.0
57.5°	371.0	376.3	389.1	394.4	404.0	431.6	469.9	530.5	610.2	717.6	785.6
60°	321.1	331.7	341.2	345.5	352.9	372.1	398.7	455.0	524.1	602.8	680.4
62.5°	280.7	284.9	292.3	297.7	303.0	323.2	345.5	388.0	440.1	506.0	577.3
65°	243.4	245.6	249.8	257.3	260.5	275.3	288.1	318.9	367.8	417.8	489.0
67.5°	205.2	207.3	212.6	216.9	220.1	229.6	243.4	265.8	292.3	347.6	387.0
70°	175.4	175.4	178.6	180.7	183.9	188.2	195.6	212.6	237.1	272.1	308.3
72.5°	146.7	146.7	146.7	149.9	149.9	153.1	157.3	169.0	186.0	213.7	237.1
75°	113.7	114.8	116.9	116.9	118.0	122.3	125.4	128.6	137.1	155.2	176.5
77.5°	86.1	88.2	89.3	87.2	89.3	89.3	93.6	97.8	102.1	107.4	123.3
80°	63.8	64.8	62.7	63.8	63.8	65.9	68.0	67.0	69.1	75.5	79.7
82.5°	42.5	43.6	43.6	43.6	43.6	46.8	46.8	45.7	46.8	47.8	48.9
85°	26.6	25.5	25.5	26.6	25.5	25.5	26.6	27.6	26.6	27.6	28.7
87.5°	11.7	11.7	11.7	11.7	10.6	10.6	11.7	10.6	11.7	10.6	9.6
90°	44.3	43.6	42.9	42.6	41.6	39.6	37.5	35.5	33.5	30.8	28.1
92.5°	72.3	72.0	71.7	71.5	71.0	70.0	68.9	67.9	66.9	65.2	63.5
95°	120.2	120.2	120.2	120.2	119.7	118.7	117.6	116.6	115.6	113.2	110.9
97.5°	176.5	176.5	176.5	176.5	175.8	174.5	173.1	171.8	170.4	167.7	165.0
100°	235.8	235.8	235.8	235.8	235.5	234.8	234.1	233.5	232.8	229.8	226.7
102.5°	302.0	301.7	301.4	301.2	300.7	299.7	298.7	297.7	296.7	294.0	291.3
105°	369.2	368.1	367.1	366.6	366.1	365.1	364.1	363.1	362.1	360.7	359.4
107.5°	437.3	437.6	437.9	438.1	437.4	436.1	434.7	433.4	432.0	431.7	431.3
110°	506.1	505.0	504.0	503.5	503.8	504.5	505.2	505.9	506.6	506.9	507.3

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.8	582.5
115°	657.9	658.2	658.5	658.7	658.9	659.2	659.5	659.9	660.2	660.9	661.6
117.5°	729.2	730.2	731.2	731.7	732.2	733.2	734.3	735.3	736.3	736.6	737.0
120°	808.0	807.3	806.6	806.3	807.1	808.8	810.5	812.2	813.9	814.9	815.9
122.5°	881.2	882.9	884.6	885.4	885.9	886.9	888.0	889.0	890.0	890.3	890.7
125°	959.8	960.5	961.2	961.5	961.8	962.5	963.2	963.8	964.5	964.8	965.2
127.5°	1032.1	1032.5	1032.8	1033.0	1033.3	1034.0	1034.7	1035.3	1036.0	1036.7	1037.3
130°	1105.6	1107.0	1108.3	1109.0	1109.3	1110.0	1110.7	1111.4	1112.1	1112.1	1112.1
132.5°	1179.7	1180.0	1180.3	1180.5	1180.8	1181.5	1182.2	1182.9	1183.6	1183.9	1184.3
135°	1249.5	1250.5	1251.5	1252.0	1252.3	1253.0	1253.7	1254.4	1255.1	1255.1	1255.1
137.5°	1321.3	1321.0	1320.7	1320.5	1321.0	1322.0	1323.0	1324.0	1325.0	1324.3	1323.7
140°	1389.6	1390.0	1390.3	1390.5	1390.7	1391.0	1391.3	1391.7	1392.0	1392.0	1392.0
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1456.2	1456.6
145°	1517.2	1518.3	1519.3	1519.8	1520.0	1520.3	1520.6	1521.0	1521.3	1521.0	1520.6
147.5°	1578.3	1578.6	1578.9	1579.1	1579.3	1579.6	1579.9	1580.3	1580.6	1580.9	1581.3
150°	1634.6	1634.9	1635.2	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4
152.5°	1687.6	1688.7	1689.7	1690.2	1689.7	1688.7	1687.6	1686.6	1685.6	1685.3	1684.9
155°	1735.5	1736.8	1738.1	1738.8	1738.1	1736.8	1735.5	1734.1	1732.8	1733.1	1733.5
157.5°	1778.9	1779.9	1780.9	1781.4	1780.9	1779.9	1778.9	1777.9	1776.9	1776.9	1776.9
160°	1816.8	1818.5	1820.2	1821.0	1820.5	1819.5	1818.4	1817.4	1816.4	1816.7	1817.1
162.5°	1854.8	1856.5	1858.2	1859.0	1858.0	1856.0	1853.9	1851.9	1849.9	1850.2	1850.6
165°	1886.1	1887.4	1888.7	1889.4	1888.4	1886.4	1884.3	1882.3	1880.3	1881.0	1881.7
167.5°	1911.7	1913.8	1915.8	1916.8	1915.8	1913.8	1911.7	1909.7	1907.7	1907.7	1907.7
170°	1932.2	1934.6	1936.9	1938.1	1937.1	1935.1	1933.0	1931.0	1929.0	1928.7	1928.3
172.5°	1949.0	1951.3	1953.7	1954.9	1953.7	1951.3	1949.0	1946.6	1944.2	1944.2	1944.2
175°	1959.6	1962.0	1964.3	1965.5	1964.3	1962.0	1959.6	1957.3	1954.9	1955.2	1955.6
177.5°	1966.3	1969.0	1971.7	1973.1	1971.9	1969.6	1967.2	1964.9	1962.5	1962.5	1962.5
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1353.3	1348.0	1344.8	1343.7	1334.2	1328.9	1325.7	1323.5	1320.3	1311.8	1304.4
5°	1404.3	1389.4	1382.0	1373.5	1358.6	1341.6	1327.8	1319.3	1308.7	1291.6	1275.7
7.5°	1452.2	1429.8	1415.0	1403.3	1377.8	1350.1	1327.8	1309.7	1289.5	1266.1	1243.8
10°	1502.1	1466.0	1446.9	1428.8	1391.6	1355.4	1323.5	1297.0	1268.3	1237.4	1213.0
12.5°	1541.5	1493.6	1472.4	1446.9	1401.1	1358.6	1318.2	1282.1	1244.9	1211.9	1176.8
15°	1587.2	1527.7	1503.2	1470.2	1407.5	1352.2	1300.2	1260.8	1222.5	1173.6	1136.4
17.5°	1613.8	1544.7	1509.6	1480.9	1412.8	1345.9	1285.3	1236.4	1191.7	1142.8	1103.5
20°	1640.3	1561.7	1522.3	1481.9	1401.1	1329.9	1266.1	1207.7	1160.9	1107.7	1067.3
22.5°	1648.8	1557.4	1516.0	1478.7	1393.7	1314.0	1240.6	1181.1	1126.9	1073.7	1028.0
25°	1648.8	1556.4	1507.5	1459.6	1370.3	1288.5	1215.1	1150.3	1089.7	1036.5	990.8
27.5°	1631.8	1535.1	1484.1	1440.5	1348.0	1259.8	1184.3	1113.0	1054.6	1001.4	949.3
30°	1610.6	1504.3	1453.2	1401.1	1311.8	1227.9	1146.0	1080.1	1018.4	957.8	911.1
32.5°	1584.0	1471.3	1415.0	1361.8	1267.2	1180.0	1104.5	1039.7	981.2	918.5	866.4
35°	1545.7	1422.4	1359.7	1312.9	1221.5	1131.1	1058.8	995.0	938.7	873.9	817.5
37.5°	1496.8	1377.8	1314.0	1256.6	1161.9	1079.0	1011.0	949.3	894.1	834.5	771.8
40°	1439.4	1315.0	1259.8	1199.2	1099.2	1020.6	956.8	901.5	846.2	789.9	729.3
42.5°	1374.6	1251.2	1189.6	1131.1	1035.4	957.8	898.3	848.3	797.3	745.2	680.4
45°	1297.0	1181.1	1121.6	1066.3	973.8	894.1	839.8	792.0	748.4	695.3	637.8
47.5°	1209.8	1108.8	1048.2	988.7	898.3	829.2	776.1	735.7	698.4	645.3	593.2
50°	1124.7	1024.8	975.9	915.3	832.4	767.5	713.3	679.3	650.6	598.5	551.7
52.5°	1017.4	941.9	895.1	843.0	763.3	697.4	654.9	625.1	591.1	550.7	509.2
55°	922.8	852.6	815.4	766.5	687.8	629.3	593.2	565.6	539.0	502.8	469.9
57.5°	815.4	771.8	734.6	692.1	614.5	564.5	532.6	509.2	484.8	455.0	428.4
60°	702.7	682.5	646.4	612.3	546.4	502.8	476.3	455.0	431.6	407.2	384.8
62.5°	602.8	591.1	569.8	543.2	481.6	444.4	417.8	401.8	384.8	362.5	341.2
65°	508.2	502.8	482.6	463.5	421.0	388.0	364.6	355.1	335.9	318.9	299.8
67.5°	424.2	417.8	406.1	397.6	361.4	330.6	318.9	306.2	290.2	277.5	261.5
70°	339.1	338.1	330.6	320.0	300.9	278.5	266.8	258.3	242.4	232.8	221.1
72.5°	263.6	269.0	262.6	258.3	245.6	229.6	219.0	213.7	200.9	193.5	185.0
75°	196.7	200.9	204.1	196.7	193.5	186.0	176.5	171.2	164.8	154.1	151.0
77.5°	133.9	143.5	143.5	145.6	146.7	142.5	135.0	130.8	123.3	121.2	116.9
80°	88.2	96.7	97.8	99.9	103.1	103.1	97.8	96.7	89.3	88.2	85.0
82.5°	51.0	58.5	62.7	65.9	64.8	69.1	64.8	63.8	59.5	59.5	57.4
85°	27.6	28.7	30.8	33.0	35.1	37.2	37.2	36.1	35.1	34.0	31.9
87.5°	10.6	10.6	11.7	10.6	11.7	13.8	14.9	14.9	13.8	12.8	10.6
90°	25.4	22.7	21.3	19.4	15.7	12.0	8.3	4.6	8.3	12.0	15.7
92.5°	61.8	60.1	59.3	57.1	52.7	48.4	44.0	39.6	44.0	48.4	52.7
95°	108.5	106.2	105.0	103.5	100.4	97.4	94.3	91.3	94.3	97.4	100.4
97.5°	162.3	159.6	158.2	156.8	154.1	151.4	148.7	146.0	148.7	151.4	154.1
100°	223.7	220.6	219.1	218.4	217.1	215.7	214.4	213.0	214.4	215.7	217.1
102.5°	288.6	285.9	284.5	284.3	284.0	283.7	283.3	283.0	283.3	283.7	284.0
105°	358.0	356.7	356.0	355.8	355.5	355.2	354.8	354.5	354.8	355.2	355.5
107.5°	431.0	430.7	430.5	430.3	430.0	429.7	429.3	429.0	429.3	429.7	430.0
110°	507.6	507.9	508.1	507.8	507.1	506.4	505.8	505.1	505.8	506.4	507.1

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	583.2	583.9	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2	584.2
115°	662.3	663.0	663.3	663.3	663.3	663.3	663.3	663.3	663.3	663.3	663.3
117.5°	737.3	737.6	737.8	737.8	737.8	737.8	737.8	737.8	737.8	737.8	737.8
120°	817.0	818.0	818.5	817.8	816.5	815.1	813.8	812.4	813.8	815.1	816.5
122.5°	891.0	891.3	891.5	891.3	891.0	890.7	890.3	890.0	890.3	890.7	891.0
125°	965.5	965.8	966.0	966.0	966.0	966.0	966.0	966.0	966.0	966.0	966.0
127.5°	1038.0	1038.7	1039.0	1038.5	1037.5	1036.5	1035.5	1034.5	1035.5	1036.5	1037.5
130°	1112.1	1112.1	1112.1	1111.6	1110.6	1109.5	1108.5	1107.5	1108.5	1109.5	1110.6
132.5°	1184.6	1184.9	1185.1	1184.8	1184.1	1183.4	1182.7	1182.0	1182.7	1183.4	1184.1
135°	1255.1	1255.1	1255.1	1254.1	1252.0	1250.0	1247.9	1245.9	1247.9	1250.0	1252.0
137.5°	1323.0	1322.3	1322.0	1321.5	1320.5	1319.4	1318.4	1317.4	1318.4	1319.4	1320.5
140°	1392.0	1392.0	1392.0	1391.7	1391.0	1390.3	1389.6	1388.9	1389.6	1390.3	1391.0
142.5°	1456.9	1457.2	1457.4	1457.1	1456.4	1455.7	1455.1	1454.4	1455.1	1455.7	1456.4
145°	1520.3	1520.0	1519.8	1519.1	1517.8	1516.4	1515.1	1513.7	1515.1	1516.4	1517.8
147.5°	1581.6	1581.9	1582.1	1581.3	1579.6	1577.9	1576.2	1574.5	1576.2	1577.9	1579.6
150°	1635.4	1635.4	1635.4	1634.7	1633.4	1632.0	1630.7	1629.3	1630.7	1632.0	1633.4
152.5°	1684.6	1684.3	1684.1	1683.8	1683.1	1682.4	1681.7	1681.0	1681.7	1682.4	1683.1
155°	1733.8	1734.1	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3	1734.3
157.5°	1776.9	1776.9	1776.9	1777.2	1777.9	1778.6	1779.2	1779.9	1779.2	1778.6	1777.9
160°	1817.4	1817.7	1817.9	1818.1	1818.4	1818.8	1819.1	1819.5	1819.1	1818.8	1818.4
162.5°	1850.9	1851.2	1851.4	1851.9	1852.9	1854.0	1855.0	1856.0	1855.0	1854.0	1852.9
165°	1882.4	1883.1	1883.4	1883.9	1884.9	1885.9	1886.9	1887.9	1886.9	1885.9	1884.9
167.5°	1907.7	1907.7	1907.7	1908.4	1909.7	1911.1	1912.4	1913.8	1912.4	1911.1	1909.7
170°	1928.0	1927.7	1927.5	1928.3	1930.0	1931.7	1933.4	1935.1	1933.4	1931.7	1930.0
172.5°	1944.2	1944.2	1944.2	1944.9	1946.2	1947.6	1948.9	1950.3	1948.9	1947.6	1946.2
175°	1955.9	1956.2	1956.4	1957.2	1958.9	1960.6	1962.3	1964.0	1962.3	1960.6	1958.9
177.5°	1962.5	1962.5	1962.5	1963.3	1965.0	1966.7	1968.4	1970.1	1968.4	1966.7	1965.0
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1298.0	1295.9	1293.8	1285.3	1277.8	1265.1	1254.4	1250.2	1249.1	1250.2	1247.0
5°	1260.8	1259.8	1252.3	1237.4	1223.6	1208.7	1198.1	1187.5	1181.1	1181.1	1173.6
7.5°	1225.7	1218.3	1211.9	1192.8	1176.8	1156.6	1140.7	1131.1	1125.8	1114.1	1114.1
10°	1188.5	1177.9	1169.4	1151.3	1127.9	1107.7	1087.5	1075.8	1066.3	1057.8	1054.6
12.5°	1151.3	1142.8	1126.9	1107.7	1084.3	1058.8	1037.6	1029.1	1006.7	988.7	989.7
15°	1116.2	1097.1	1089.7	1062.0	1034.4	1009.9	979.1	954.6	936.6	924.9	910.0
17.5°	1076.9	1057.8	1043.9	1020.6	984.4	946.1	916.4	883.4	865.3	845.2	835.6
20°	1033.3	1017.4	1006.7	969.5	925.9	880.2	847.3	827.1	806.9	792.0	783.5
22.5°	996.1	975.9	963.2	913.2	865.3	819.6	794.1	777.1	760.1	747.3	743.1
25°	948.3	936.6	905.7	862.2	803.7	772.9	750.5	728.2	718.6	710.1	700.6
27.5°	908.9	880.2	859.0	801.6	765.4	730.3	708.0	691.0	679.3	670.8	663.4
30°	860.0	833.5	803.7	755.9	722.9	689.9	669.7	655.9	643.2	637.8	631.5
32.5°	809.0	784.6	755.9	717.6	677.2	651.7	635.7	620.8	612.3	607.0	599.6
35°	763.3	732.5	713.3	677.2	644.2	615.5	600.6	587.9	578.3	576.2	575.1
37.5°	714.4	691.0	672.9	635.7	608.1	583.6	569.8	556.0	550.7	549.6	545.4
40°	671.9	651.7	634.7	599.6	569.8	547.5	536.9	528.4	523.0	523.0	522.0
42.5°	634.7	613.4	596.4	564.5	537.9	517.7	506.0	497.5	495.4	496.5	495.4
45°	593.2	575.1	558.1	525.2	502.8	488.0	475.2	470.9	467.8	468.8	469.9
47.5°	553.9	539.0	522.0	495.4	469.9	453.9	446.5	442.2	442.2	442.2	444.4
50°	518.8	501.8	486.9	459.3	435.9	423.1	416.7	411.4	412.5	413.5	414.6
52.5°	477.3	462.4	451.8	424.2	407.2	391.2	383.8	384.8	383.8	383.8	385.9
55°	441.2	426.3	415.7	390.2	373.1	362.5	356.1	352.9	354.0	351.9	356.1
57.5°	400.8	388.0	380.6	356.1	341.2	331.7	326.4	321.1	323.2	322.1	321.1
60°	365.7	350.8	339.1	322.1	309.4	297.7	294.5	289.2	291.3	289.2	288.1
62.5°	325.3	313.6	305.1	288.1	277.5	267.9	260.5	257.3	256.2	253.0	249.8
65°	284.9	278.5	270.0	253.0	242.4	234.9	230.7	227.5	226.4	217.9	208.4
67.5°	247.7	243.4	234.9	222.2	212.6	205.2	198.8	193.5	187.1	180.7	175.4
70°	212.6	206.2	200.9	189.2	180.7	173.3	166.9	160.5	157.3	151.0	148.8
72.5°	178.6	172.2	166.9	156.3	148.8	141.4	139.3	131.8	128.6	127.6	127.6
75°	143.5	138.2	135.0	125.4	119.1	113.7	110.6	108.4	106.3	104.2	101.0
77.5°	109.5	106.3	104.2	97.8	92.5	89.3	88.2	80.8	78.7	76.5	74.4
80°	79.7	78.7	76.5	71.2	69.1	61.7	61.7	59.5	58.5	58.5	58.5
82.5°	54.2	52.1	51.0	45.7	44.6	43.6	42.5	41.5	42.5	41.5	42.5
85°	28.7	27.6	26.6	26.6	26.6	26.6	26.6	26.6	26.6	25.5	26.6
87.5°	10.6	10.6	10.6	10.6	9.6	10.6	10.6	9.6	10.6	10.6	10.6
90°	19.4	21.3	22.7	25.4	28.1	30.8	33.5	35.5	37.5	39.6	41.6
92.5°	57.1	59.3	60.1	61.8	63.5	65.2	66.9	67.9	68.9	70.0	71.0
95°	103.5	105.0	106.2	108.5	110.9	113.2	115.6	116.6	117.6	118.7	119.7
97.5°	156.8	158.2	159.6	162.3	165.0	167.7	170.4	171.8	173.1	174.5	175.8
100°	218.4	219.1	220.6	223.7	226.7	229.8	232.8	233.5	234.1	234.8	235.5
102.5°	284.3	284.5	285.9	288.6	291.3	294.0	296.7	297.7	298.7	299.7	300.7
105°	355.8	356.0	356.7	358.0	359.4	360.7	362.1	363.1	364.1	365.1	366.1
107.5°	430.3	430.5	430.7	431.0	431.3	431.7	432.0	433.4	434.7	436.1	437.4
110°	507.8	508.1	507.9	507.6	507.3	506.9	506.6	505.9	505.2	504.5	503.8

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	584.2	584.2	583.9	583.2	582.5	581.8	581.1	581.1	581.1	581.1	581.1
115°	663.3	663.3	663.0	662.3	661.6	660.9	660.2	659.9	659.5	659.2	658.9
117.5°	737.8	737.8	737.6	737.3	737.0	736.6	736.3	735.3	734.3	733.2	732.2
120°	817.8	818.5	818.0	817.0	815.9	814.9	813.9	812.2	810.5	808.8	807.1
122.5°	891.3	891.5	891.3	891.0	890.7	890.3	890.0	889.0	888.0	886.9	885.9
125°	966.0	966.0	965.8	965.5	965.2	964.8	964.5	963.8	963.2	962.5	961.8
127.5°	1038.5	1039.0	1038.7	1038.0	1037.3	1036.7	1036.0	1035.3	1034.7	1034.0	1033.3
130°	1111.6	1112.1	1112.1	1112.1	1112.1	1112.1	1112.1	1111.4	1110.7	1110.0	1109.3
132.5°	1184.8	1185.1	1184.9	1184.6	1184.3	1183.9	1183.6	1182.9	1182.2	1181.5	1180.8
135°	1254.1	1255.1	1255.1	1255.1	1255.1	1255.1	1255.1	1254.4	1253.7	1253.0	1252.3
137.5°	1321.5	1322.0	1322.3	1323.0	1323.7	1324.3	1325.0	1324.0	1323.0	1322.0	1321.0
140°	1391.7	1392.0	1392.0	1392.0	1392.0	1392.0	1392.0	1391.7	1391.3	1391.0	1390.7
142.5°	1457.1	1457.4	1457.2	1456.9	1456.6	1456.2	1455.9	1455.9	1455.9	1455.9	1455.9
145°	1519.1	1519.8	1520.0	1520.3	1520.6	1521.0	1521.3	1521.0	1520.6	1520.3	1520.0
147.5°	1581.3	1582.1	1581.9	1581.6	1581.3	1580.9	1580.6	1580.3	1579.9	1579.6	1579.3
150°	1634.7	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4
152.5°	1683.8	1684.1	1684.3	1684.6	1684.9	1685.3	1685.6	1686.6	1687.6	1688.7	1689.7
155°	1734.3	1734.3	1734.1	1733.8	1733.5	1733.1	1732.8	1734.1	1735.5	1736.8	1738.1
157.5°	1777.2	1776.9	1776.9	1776.9	1776.9	1776.9	1776.9	1777.9	1778.9	1779.9	1780.9
160°	1818.1	1817.9	1817.7	1817.4	1817.1	1816.7	1816.4	1817.4	1818.4	1819.5	1820.5
162.5°	1851.9	1851.4	1851.2	1850.9	1850.6	1850.2	1849.9	1851.9	1853.9	1856.0	1858.0
165°	1883.9	1883.4	1883.1	1882.4	1881.7	1881.0	1880.3	1882.3	1884.3	1886.4	1888.4
167.5°	1908.4	1907.7	1907.7	1907.7	1907.7	1907.7	1907.7	1909.7	1911.7	1913.8	1915.8
170°	1928.3	1927.5	1927.7	1928.0	1928.3	1928.7	1929.0	1931.0	1933.0	1935.1	1937.1
172.5°	1944.9	1944.2	1944.2	1944.2	1944.2	1944.2	1944.2	1946.6	1949.0	1951.3	1953.7
175°	1957.2	1956.4	1956.2	1955.9	1955.6	1955.2	1954.9	1957.3	1959.6	1962.0	1964.3
177.5°	1963.3	1962.5	1962.5	1962.5	1962.5	1962.5	1962.5	1964.9	1967.2	1969.6	1971.9
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1247.0	1251.2	1245.9	1249.1	1241.7	1240.6	1241.7	1241.7	1242.7	1243.8	1244.9
5°	1176.8	1175.8	1169.4	1165.1	1161.9	1165.1	1167.3	1169.4	1167.3	1169.4	1170.5
7.5°	1110.9	1107.7	1104.5	1097.1	1099.2	1097.1	1103.5	1100.3	1100.3	1105.6	1109.9
10°	1052.5	1046.1	1043.9	1035.4	1029.1	1028.0	1035.4	1038.6	1041.8	1043.9	1052.5
12.5°	977.0	967.4	960.0	963.2	945.1	952.5	954.6	950.4	963.2	978.0	969.5
15°	896.2	897.2	882.4	877.0	862.2	866.4	867.5	878.1	888.7	887.7	900.4
17.5°	836.6	830.3	817.5	816.4	810.1	813.3	812.2	820.7	817.5	822.8	833.5
20°	781.4	777.1	766.5	762.2	764.4	762.2	763.3	764.4	767.5	779.2	777.1
22.5°	737.8	732.5	732.5	727.1	720.8	718.6	724.0	727.1	731.4	733.5	738.8
25°	699.5	695.3	689.9	686.8	681.4	682.5	685.7	689.9	693.1	697.4	701.6
27.5°	660.2	660.2	654.9	653.8	651.7	650.6	654.9	657.0	657.0	660.2	664.4
30°	629.3	629.3	624.0	623.0	621.9	621.9	625.1	626.2	627.2	630.4	632.5
32.5°	599.6	598.5	596.4	597.5	596.4	597.5	597.5	598.5	600.6	601.7	606.0
35°	571.9	573.0	570.9	570.9	569.8	570.9	573.0	574.1	575.1	577.3	577.3
37.5°	545.4	547.5	546.4	549.6	549.6	549.6	549.6	551.7	551.7	551.7	550.7
40°	522.0	522.0	520.9	523.0	525.2	525.2	526.2	526.2	527.3	527.3	526.2
42.5°	495.4	497.5	500.7	501.8	503.9	502.8	506.0	505.0	506.0	503.9	501.8
45°	470.9	470.9	475.2	479.5	480.5	480.5	480.5	482.6	480.5	477.3	476.3
47.5°	444.4	446.5	448.6	453.9	455.0	455.0	455.0	455.0	452.9	452.9	452.9
50°	417.8	418.9	419.9	422.0	425.2	424.2	424.2	424.2	428.4	424.2	425.2
52.5°	385.9	387.0	388.0	392.3	391.2	391.2	392.3	392.3	395.5	394.4	392.3
55°	354.0	354.0	356.1	356.1	356.1	358.3	359.3	361.4	360.4	361.4	362.5
57.5°	322.1	320.0	318.9	318.9	322.1	321.1	322.1	322.1	326.4	328.5	329.6
60°	284.9	284.9	283.8	277.5	277.5	276.4	279.6	281.7	283.8	293.4	292.3
62.5°	246.6	242.4	238.1	239.2	232.8	236.0	233.9	236.0	242.4	249.8	250.9
65°	208.4	205.2	200.9	199.9	197.7	200.9	199.9	200.9	204.1	208.4	213.7
67.5°	174.3	173.3	171.2	170.1	170.1	170.1	172.2	172.2	173.3	176.5	179.7
70°	148.8	147.8	148.8	146.7	147.8	146.7	147.8	148.8	149.9	151.0	154.1
72.5°	125.4	125.4	125.4	123.3	125.4	124.4	124.4	125.4	126.5	127.6	129.7
75°	99.9	97.8	95.7	93.6	92.5	94.6	95.7	94.6	97.8	102.1	102.1
77.5°	75.5	74.4	74.4	74.4	75.5	74.4	76.5	75.5	76.5	76.5	78.7
80°	58.5	57.4	58.5	58.5	57.4	59.5	58.5	58.5	59.5	60.6	59.5
82.5°	42.5	43.6	42.5	42.5	42.5	44.6	42.5	42.5	42.5	43.6	43.6
85°	26.6	26.6	26.6	26.6	27.6	26.6	27.6	26.6	28.7	27.6	27.6
87.5°	9.6	10.6	11.7	11.7	11.7	11.7	10.6	11.7	12.8	11.7	12.8
90°	42.6	42.9	43.6	44.3	44.9	45.6	44.9	44.3	43.6	42.9	42.6
92.5°	71.5	71.7	72.0	72.3	72.7	73.0	72.7	72.3	72.0	71.7	71.5
95°	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2	120.2
97.5°	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5	176.5
100°	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8	235.8
102.5°	301.2	301.4	301.7	302.0	302.4	302.7	302.4	302.0	301.7	301.4	301.2
105°	366.6	367.1	368.1	369.2	370.2	371.2	370.2	369.2	368.1	367.1	366.6
107.5°	438.1	437.9	437.6	437.3	436.9	436.6	436.9	437.3	437.6	437.9	438.1
110°	503.5	504.0	505.0	506.1	507.1	508.1	507.1	506.1	505.0	504.0	503.5

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1	581.1
115°	658.7	658.5	658.2	657.9	657.5	657.2	657.5	657.9	658.2	658.5	658.7
117.5°	731.7	731.2	730.2	729.2	728.2	727.2	728.2	729.2	730.2	731.2	731.7
120°	806.3	806.6	807.3	808.0	808.6	809.3	808.6	808.0	807.3	806.6	806.3
122.5°	885.4	884.6	882.9	881.2	879.5	877.8	879.5	881.2	882.9	884.6	885.4
125°	961.5	961.2	960.5	959.8	959.1	958.4	959.1	959.8	960.5	961.2	961.5
127.5°	1033.0	1032.8	1032.5	1032.1	1031.8	1031.4	1031.8	1032.1	1032.5	1032.8	1033.0
130°	1109.0	1108.3	1107.0	1105.6	1104.3	1102.9	1104.3	1105.6	1107.0	1108.3	1109.0
132.5°	1180.5	1180.3	1180.0	1179.7	1179.3	1179.0	1179.3	1179.7	1180.0	1180.3	1180.5
135°	1252.0	1251.5	1250.5	1249.5	1248.5	1247.5	1248.5	1249.5	1250.5	1251.5	1252.0
137.5°	1320.5	1320.7	1321.0	1321.3	1321.7	1322.0	1321.7	1321.3	1321.0	1320.7	1320.5
140°	1390.5	1390.3	1390.0	1389.6	1389.3	1388.9	1389.3	1389.6	1390.0	1390.3	1390.5
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9	1455.9
145°	1519.8	1519.3	1518.3	1517.2	1516.2	1515.2	1516.2	1517.2	1518.3	1519.3	1519.8
147.5°	1579.1	1578.9	1578.6	1578.3	1577.9	1577.6	1577.9	1578.3	1578.6	1578.9	1579.1
150°	1635.4	1635.2	1634.9	1634.6	1634.2	1633.9	1634.2	1634.6	1634.9	1635.2	1635.4
152.5°	1690.2	1689.7	1688.7	1687.6	1686.6	1685.6	1686.6	1687.6	1688.7	1689.7	1690.2
155°	1738.8	1738.1	1736.8	1735.5	1734.1	1732.8	1734.1	1735.5	1736.8	1738.1	1738.8
157.5°	1781.4	1780.9	1779.9	1778.9	1777.9	1776.9	1777.9	1778.9	1779.9	1780.9	1781.4
160°	1821.0	1820.2	1818.5	1816.8	1815.1	1813.4	1815.1	1816.8	1818.5	1820.2	1821.0
162.5°	1859.0	1858.2	1856.5	1854.8	1853.1	1851.4	1853.1	1854.8	1856.5	1858.2	1859.0
165°	1889.4	1888.7	1887.4	1886.1	1884.7	1883.4	1884.7	1886.1	1887.4	1888.7	1889.4
167.5°	1916.8	1915.8	1913.8	1911.7	1909.7	1907.7	1909.7	1911.7	1913.8	1915.8	1916.8
170°	1938.1	1936.9	1934.6	1932.2	1929.9	1927.5	1929.9	1932.2	1934.6	1936.9	1938.1
172.5°	1954.9	1953.7	1951.3	1949.0	1946.6	1944.2	1946.6	1949.0	1951.3	1953.7	1954.9
175°	1965.5	1964.3	1962.0	1959.6	1957.3	1954.9	1957.3	1959.6	1962.0	1964.3	1965.5
177.5°	1973.1	1971.7	1969.0	1966.3	1963.6	1960.9	1963.6	1966.3	1969.0	1971.7	1973.1
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3	1319.3
2.5°	1249.1	1254.4	1252.3	1244.9	1248.1	1254.4	1260.8	1269.3	1274.6	1278.9	1281.0
5°	1175.8	1185.3	1183.2	1183.2	1187.5	1198.1	1208.7	1226.8	1233.2	1240.6	1251.2
7.5°	1110.9	1118.4	1124.7	1126.9	1133.2	1147.1	1160.9	1181.1	1197.0	1205.5	1211.9
10°	1053.5	1058.8	1068.4	1073.7	1080.1	1097.1	1117.3	1138.6	1154.5	1169.4	1177.9
12.5°	980.2	1001.4	1014.2	1022.7	1031.2	1056.7	1072.7	1096.0	1115.2	1129.0	1141.8
15°	898.3	923.8	931.3	964.2	985.5	1005.7	1030.1	1057.8	1075.8	1091.8	1108.8
17.5°	829.2	847.3	855.8	890.9	908.9	940.8	975.9	1011.0	1038.6	1050.3	1067.3
20°	785.6	795.2	812.2	823.9	843.0	880.2	918.5	961.0	1002.5	1014.2	1031.2
22.5°	741.0	753.7	765.4	781.4	796.2	821.8	860.0	906.8	951.5	972.7	992.9
25°	700.6	713.3	720.8	737.8	751.6	777.1	803.7	851.5	904.7	922.8	954.6
27.5°	668.7	676.1	688.9	696.3	712.3	735.7	760.1	796.2	848.3	879.2	910.0
30°	636.8	642.1	652.7	663.4	675.1	691.0	718.6	753.7	801.6	828.1	859.0
32.5°	604.9	613.4	619.8	627.2	640.0	659.1	678.2	712.3	750.5	780.3	811.1
35°	578.3	581.5	590.0	598.5	607.0	624.0	644.2	677.2	711.2	734.6	762.2
37.5°	549.6	554.9	561.3	564.5	578.3	588.9	610.2	635.7	676.1	691.0	718.6
40°	527.3	526.2	532.6	537.9	544.3	561.3	574.1	601.7	633.6	657.0	674.0
42.5°	499.6	499.6	501.8	508.2	516.7	527.3	542.2	565.6	598.5	615.5	635.7
45°	477.3	474.1	475.2	479.5	484.8	495.4	510.3	530.5	563.4	577.3	598.5
47.5°	450.7	447.6	447.6	451.8	456.1	463.5	475.2	498.6	525.2	543.2	559.2
50°	421.0	422.0	421.0	424.2	426.3	433.7	446.5	465.6	490.1	505.0	523.0
52.5°	393.3	391.2	390.2	392.3	396.5	401.8	415.7	432.7	456.1	470.9	486.9
55°	359.3	361.4	361.4	361.4	367.8	370.0	380.6	397.6	421.0	432.7	447.6
57.5°	328.5	327.4	329.6	328.5	333.8	341.2	349.8	362.5	385.9	397.6	411.4
60°	294.5	295.5	296.6	296.6	300.9	308.3	317.9	329.6	348.7	360.4	373.1
62.5°	253.0	258.3	263.6	265.8	272.1	277.5	283.8	296.6	313.6	322.1	333.8
65°	213.7	221.1	228.6	233.9	238.1	243.4	252.0	263.6	277.5	286.0	297.7
67.5°	179.7	185.0	194.5	199.9	208.4	214.7	220.1	229.6	246.6	249.8	259.4
70°	155.2	157.3	161.6	165.8	175.4	180.7	187.1	196.7	209.4	216.9	222.2
72.5°	130.8	131.8	133.9	138.2	142.5	148.8	156.3	164.8	176.5	179.7	187.1
75°	104.2	110.6	110.6	113.7	116.9	120.1	126.5	135.0	142.5	147.8	152.0
77.5°	77.6	80.8	82.9	88.2	92.5	95.7	99.9	106.3	110.6	114.8	118.0
80°	60.6	61.7	62.7	62.7	64.8	69.1	73.4	77.6	82.9	85.0	88.2
82.5°	44.6	44.6	44.6	46.8	47.8	48.9	48.9	51.0	56.3	58.5	61.7
85°	28.7	28.7	28.7	28.7	29.8	30.8	31.9	33.0	33.0	33.0	35.1
87.5°	11.7	13.8	12.8	13.8	13.8	13.8	13.8	14.9	14.9	15.9	15.9
90°	41.6	39.6	37.5	35.5	33.5	30.8	28.1	25.4	22.7	21.3	19.4
92.5°	71.0	70.0	68.9	67.9	66.9	65.2	63.5	61.8	60.1	59.3	57.1
95°	119.7	118.7	117.6	116.6	115.6	113.2	110.9	108.5	106.2	105.0	103.5
97.5°	175.8	174.5	173.1	171.8	170.4	167.7	165.0	162.3	159.6	158.2	156.8
100°	235.5	234.8	234.1	233.5	232.8	229.8	226.7	223.7	220.6	219.1	218.4
102.5°	300.7	299.7	298.7	297.7	296.7	294.0	291.3	288.6	285.9	284.5	284.3
105°	366.1	365.1	364.1	363.1	362.1	360.7	359.4	358.0	356.7	356.0	355.8
107.5°	437.4	436.1	434.7	433.4	432.0	431.7	431.3	431.0	430.7	430.5	430.3
110°	503.8	504.5	505.2	505.9	506.6	506.9	507.3	507.6	507.9	508.1	507.8

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	581.1	581.1	581.1	581.1	581.1	581.8	582.5	583.2	583.9	584.2	584.2
115°	658.9	659.2	659.5	659.9	660.2	660.9	661.6	662.3	663.0	663.3	663.3
117.5°	732.2	733.2	734.3	735.3	736.3	736.6	737.0	737.3	737.6	737.8	737.8
120°	807.1	808.8	810.5	812.2	813.9	814.9	815.9	817.0	818.0	818.5	817.8
122.5°	885.9	886.9	888.0	889.0	890.0	890.3	890.7	891.0	891.3	891.5	891.3
125°	961.8	962.5	963.2	963.8	964.5	964.8	965.2	965.5	965.8	966.0	966.0
127.5°	1033.3	1034.0	1034.7	1035.3	1036.0	1036.7	1037.3	1038.0	1038.7	1039.0	1038.5
130°	1109.3	1110.0	1110.7	1111.4	1112.1	1112.1	1112.1	1112.1	1112.1	1112.1	1111.6
132.5°	1180.8	1181.5	1182.2	1182.9	1183.6	1183.9	1184.3	1184.6	1184.9	1185.1	1184.8
135°	1252.3	1253.0	1253.7	1254.4	1255.1	1255.1	1255.1	1255.1	1255.1	1255.1	1254.1
137.5°	1321.0	1322.0	1323.0	1324.0	1325.0	1324.3	1323.7	1323.0	1322.3	1322.0	1321.5
140°	1390.7	1391.0	1391.3	1391.7	1392.0	1392.0	1392.0	1392.0	1392.0	1392.0	1391.7
142.5°	1455.9	1455.9	1455.9	1455.9	1455.9	1456.2	1456.6	1456.9	1457.2	1457.4	1457.1
145°	1520.0	1520.3	1520.6	1521.0	1521.3	1521.0	1520.6	1520.3	1520.0	1519.8	1519.1
147.5°	1579.3	1579.6	1579.9	1580.3	1580.6	1580.9	1581.3	1581.6	1581.9	1582.1	1581.3
150°	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1635.4	1634.7
152.5°	1689.7	1688.7	1687.6	1686.6	1685.6	1685.3	1684.9	1684.6	1684.3	1684.1	1683.8
155°	1738.1	1736.8	1735.5	1734.1	1732.8	1733.1	1733.5	1733.8	1734.1	1734.3	1734.3
157.5°	1780.9	1779.9	1778.9	1777.9	1776.9	1776.9	1776.9	1776.9	1776.9	1776.9	1777.2
160°	1820.5	1819.5	1818.4	1817.4	1816.4	1816.7	1817.1	1817.4	1817.7	1817.9	1818.1
162.5°	1858.0	1856.0	1853.9	1851.9	1849.9	1850.2	1850.6	1850.9	1851.2	1851.4	1851.9
165°	1888.4	1886.4	1884.3	1882.3	1880.3	1881.0	1881.7	1882.4	1883.1	1883.4	1883.9
167.5°	1915.8	1913.8	1911.7	1909.7	1907.7	1907.7	1907.7	1907.7	1907.7	1907.7	1908.4
170°	1937.1	1935.1	1933.0	1931.0	1929.0	1928.7	1928.3	1928.0	1927.7	1927.5	1928.3
172.5°	1953.7	1951.3	1949.0	1946.6	1944.2	1944.2	1944.2	1944.2	1944.2	1944.2	1944.9
175°	1964.3	1962.0	1959.6	1957.3	1954.9	1955.2	1955.6	1955.9	1956.2	1956.4	1957.2
177.5°	1971.9	1969.6	1967.2	1964.9	1962.5	1962.5	1962.5	1962.5	1962.5	1962.5	1963.3
180°	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0	1967.0

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1319.3	1319.3	1319.3	1319.3
2.5°	1289.5	1295.9	1306.5	1321.4
5°	1259.8	1277.8	1294.8	1317.2
7.5°	1233.2	1254.4	1277.8	1309.7
10°	1202.3	1228.9	1258.7	1298.0
12.5°	1166.2	1203.4	1237.4	1280.0
15°	1139.6	1167.3	1210.9	1260.8
17.5°	1102.4	1139.6	1183.2	1239.6
20°	1067.3	1106.7	1155.6	1214.0
22.5°	1030.1	1074.8	1123.7	1186.4
25°	991.9	1039.7	1088.6	1155.6
27.5°	956.8	1000.4	1055.6	1123.7
30°	914.3	964.2	1017.4	1088.6
32.5°	872.8	924.9	979.1	1050.3
35°	828.1	880.2	939.8	1007.8
37.5°	784.6	842.0	896.2	962.1
40°	736.7	796.2	852.6	919.6
42.5°	689.9	751.6	807.9	865.3
45°	646.4	707.0	758.0	812.2
47.5°	604.9	659.1	711.2	760.1
50°	564.5	610.2	658.0	698.4
52.5°	522.0	565.6	603.8	640.0
55°	483.7	517.7	551.7	584.7
57.5°	438.0	472.0	501.8	527.3
60°	399.7	421.0	449.7	476.3
62.5°	356.1	380.6	402.9	419.9
65°	313.6	334.9	351.9	366.8
67.5°	277.5	290.2	303.0	318.9
70°	233.9	244.5	259.4	271.1
72.5°	196.7	205.2	212.6	226.4
75°	159.5	166.9	171.2	183.9
77.5°	123.3	130.8	133.9	141.4
80°	94.6	95.7	99.9	106.3
82.5°	64.8	67.0	68.0	73.4
85°	37.2	42.5	41.5	43.6
87.5°	15.9	17.0	19.1	21.3
90°	15.7	12.0	8.3	4.6
92.5°	52.7	48.4	44.0	39.6
95°	100.4	97.4	94.3	91.3
97.5°	154.1	151.4	148.7	146.0
100°	217.1	215.7	214.4	213.0
102.5°	284.0	283.7	283.3	283.0
105°	355.5	355.2	354.8	354.5
107.5°	430.0	429.7	429.3	429.0
110°	507.1	506.4	505.8	505.1

TEST NUMBER: P1034268

CATALOG NUMBER: S124RDIW-B795D1560UB40-4F0-XX-W2A-A1

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	584.2	584.2	584.2	584.2
115°	663.3	663.3	663.3	663.3
117.5°	737.8	737.8	737.8	737.8
120°	816.5	815.1	813.8	812.4
122.5°	891.0	890.7	890.3	890.0
125°	966.0	966.0	966.0	966.0
127.5°	1037.5	1036.5	1035.5	1034.5
130°	1110.6	1109.5	1108.5	1107.5
132.5°	1184.1	1183.4	1182.7	1182.0
135°	1252.0	1250.0	1247.9	1245.9
137.5°	1320.5	1319.4	1318.4	1317.4
140°	1391.0	1390.3	1389.6	1388.9
142.5°	1456.4	1455.7	1455.1	1454.4
145°	1517.8	1516.4	1515.1	1513.7
147.5°	1579.6	1577.9	1576.2	1574.5
150°	1633.4	1632.0	1630.7	1629.3
152.5°	1683.1	1682.4	1681.7	1681.0
155°	1734.3	1734.3	1734.3	1734.3
157.5°	1777.9	1778.6	1779.2	1779.9
160°	1818.4	1818.8	1819.1	1819.5
162.5°	1852.9	1854.0	1855.0	1856.0
165°	1884.9	1885.9	1886.9	1887.9
167.5°	1909.7	1911.1	1912.4	1913.8
170°	1930.0	1931.7	1933.4	1935.1
172.5°	1946.2	1947.6	1948.9	1950.3
175°	1958.9	1960.6	1962.3	1964.0
177.5°	1965.0	1966.7	1968.4	1970.1
180°	1967.0	1967.0	1967.0	1967.0

(END OF REPORT)