

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034296

Luminaire Tested: S124RDIW-B795D770UB27-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034296
REPORT IS A COMBINATION OF REPORTS P1000878 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B795D770UB27-4F0-XX-W2A-F
Description: Define 4 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6298.0 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034296

CATALOG NUMBER: S124RDIW-B795D770UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1034296

CATALOG NUMBER: S124RDIW-B795D770UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	98	94	90	87	91	87	84	81	74	72	69	62	60	59	51	50	49
2	90	82	76	71	83	76	71	67	65	61	58	55	52	49	45	43	41
3	82	73	65	60	75	67	61	56	58	53	49	49	45	42	40	38	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	46	41	46	41	36	39	35	32	32	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	30	26	24
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	51	40	33	28	34	29	25	30	25	22	25	22	19
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11290	11290	11290
5°	11291	10954	10956
10°	11195	10609	10482
15°	11041	10178	9925
20°	10840	9688	9288
25°	10588	9158	8666
30°	10342	8618	7969
35°	10071	8071	7287
40°	9749	7481	6586
45°	9446	6897	5892
50°	9103	6258	5188
55°	8732	5603	4460
60°	8319	4909	3741
65°	7921	4112	3050
70°	7356	3272	2331
75°	6628	2381	1629
80°	5536	1462	1171
85°	4162	843	643

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9446 cd/sqm

TEST NUMBER: P1034296

CATALOG NUMBER: S124RDIW-B795D770UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.2	2.1
10°-20°	363.0	5.8
20°-30°	524.1	8.3
30°-40°	593.9	9.4
40°-50°	573.5	9.1
50°-60°	476.8	7.6
60°-70°	329.1	5.2
70°-80°	166.3	2.6
80°-90°	44.3	0.7
90°-100°	33.2	0.5
100°-110°	218.8	3.5
110°-120°	417.8	6.6
120°-130°	530.4	8.4
130°-140°	567.4	9.0
140°-150°	530.5	8.4
150°-160°	427.8	6.8
160°-170°	275.9	4.4
170°-180°	95.1	1.5
0°-30°	1017.2	16.2
0°-40°	1611.2	25.6
0°-60°	2661.4	42.3
0°-90°	3201.1	50.8
90°-120°	669.8	10.6
90°-150°	2298.1	36.5
90°-180°	3097.0	49.2
0°-180°	6298.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1384	1384	1384	1384	1384	
5°	1382	1378	1365	1376	1374	131
15°	1317	1307	1281	1278	1271	371
25°	1190	1171	1128	1110	1099	549
35°	1029	995	942	906	887	643
45°	840	800	737	685	666	647
55°	636	594	525	470	450	569
65°	432	387	319	274	261	427
75°	230	191	141	117	110	243
85°	57	36	33	31	31	63
90°	2	10	16	21	22	5
95°	41	16	16	21	22	51
105°	225	230	234	240	213	236
115°	421	423	422	424	424	414
125°	591	594	593	595	596	528
135°	734	733	736	737	739	565
145°	846	848	848	849	850	529
155°	928	928	926	929	927	428
165°	978	975	975	981	974	276
175°	1001	996	997	1004	995	95
180°	1001	1001	1001	1001	1001	

TEST NUMBER: P1034296

CATALOG NUMBER: S124RDIW-B795D770UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1384.5	1384.5	1384.5	1384.5	1384.5
2.5°	1388.7	1384.5	1372.8	1384.5	1383.4
5°	1382.4	1378.1	1365.4	1376.0	1373.9
7.5°	1372.8	1368.6	1352.7	1360.1	1356.9
10°	1358.0	1352.7	1333.6	1337.8	1333.6
12.5°	1338.9	1332.5	1309.2	1311.3	1305.0
15°	1316.6	1307.1	1280.6	1278.5	1271.1
17.5°	1291.2	1277.4	1246.7	1241.4	1230.8
20°	1260.5	1246.7	1210.6	1202.1	1188.4
22.5°	1226.5	1210.6	1171.4	1157.6	1147.0
25°	1190.5	1171.4	1127.9	1109.9	1099.3
27.5°	1153.4	1130.1	1084.5	1063.3	1048.4
30°	1114.2	1087.7	1037.8	1011.3	994.4
32.5°	1072.8	1042.1	990.1	958.3	942.4
35°	1029.4	995.4	942.4	906.4	887.3
37.5°	983.8	948.8	890.5	851.3	832.2
40°	935.0	900.0	839.6	795.1	776.0
42.5°	888.4	851.3	787.7	742.1	721.9
45°	839.6	800.4	736.8	684.8	665.7
47.5°	789.8	749.5	683.8	629.7	608.5
50°	738.9	697.5	629.7	576.7	556.6
52.5°	686.9	646.7	576.7	522.6	501.4
55°	636.1	593.7	524.7	469.6	449.5
57.5°	586.2	541.7	473.9	417.7	402.8
60°	532.2	489.8	421.9	366.8	349.8
62.5°	483.4	438.9	368.9	319.1	306.4
65°	432.5	386.9	319.1	273.5	260.8
67.5°	379.5	336.1	272.4	232.2	217.3
70°	329.7	285.2	224.7	189.8	179.2
72.5°	276.7	237.5	181.3	152.7	143.1
75°	230.0	190.8	141.0	116.6	110.2
77.5°	181.3	147.4	104.9	88.0	85.9
80°	134.6	103.9	72.1	68.9	67.8
82.5°	94.3	66.8	51.9	49.8	48.8
85°	57.2	36.0	32.9	30.7	30.7
87.5°	24.4	15.9	14.8	13.8	14.8
90°	2.2	10.5	16.5	21.0	22.5
92.5°	11.2	9.7	15.7	20.2	20.2
95°	41.2	15.7	16.5	21.0	21.7
97.5°	78.6	95.1	16.5	20.2	21.0
100°	122.8	136.2	32.9	20.2	21.0
102.5°	172.2	181.2	190.1	21.7	21.7
105°	225.3	229.8	233.6	240.3	213.3
107.5°	274.0	276.2	281.5	285.2	288.2
110°	323.4	325.6	330.1	331.6	333.9

TEST NUMBER: P1034296

CATALOG NUMBER: S124RDIW-B795D770UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	375.8	377.3	376.5	379.5
115°	420.7	422.9	422.2	423.7	423.7
117.5°	464.9	467.9	470.1	469.4	469.4
120°	509.8	512.8	512.0	513.5	512.0
122.5°	551.7	553.2	554.7	555.4	553.9
125°	591.4	594.4	592.9	595.1	595.9
127.5°	629.5	630.3	634.0	633.3	632.5
130°	666.2	667.0	669.2	670.0	670.0
132.5°	699.9	701.4	704.4	705.2	704.4
135°	733.6	732.8	735.8	737.3	738.8
137.5°	763.5	763.5	767.3	768.8	768.0
140°	792.7	794.2	795.7	798.0	798.7
142.5°	818.9	821.9	822.7	824.2	824.2
145°	845.9	848.1	848.1	848.9	850.4
147.5°	866.8	871.3	870.6	871.3	872.1
150°	890.0	893.0	892.3	892.3	893.0
152.5°	909.5	911.8	910.3	911.8	911.0
155°	927.5	928.2	926.0	929.0	926.7
157.5°	943.2	943.2	940.2	943.9	940.2
160°	956.7	954.4	953.7	958.2	953.7
162.5°	968.6	965.7	964.9	969.4	964.2
165°	978.4	974.6	974.6	980.6	973.9
167.5°	986.6	982.9	982.1	988.9	981.4
170°	993.3	988.9	989.6	995.6	988.1
172.5°	997.8	993.3	994.1	1000.1	991.9
175°	1000.8	996.3	997.1	1003.8	994.8
177.5°	1003.1	997.8	999.3	1005.3	996.3
180°	1000.8	1000.8	1000.8	1000.8	1000.8

(END OF REPORT)