

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033682

Luminaire Tested: S124DIW-B795D1050UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033682
REPORT IS A COMBINATION OF REPORTS P997946 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1050UB27-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7053.0 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033682

CATALOG NUMBER: S124DIW-B795D1050UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033682

CATALOG NUMBER: S124DIW-B795D1050UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	37	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	31	28
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	46	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	32	27	33	27	24	28	24	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10789	10789	10789
5°	10798	10479	10492
10°	10706	10188	10117
15°	10553	9842	9694
20°	10357	9468	9255
25°	10136	9072	8784
30°	9870	8645	8267
35°	9595	8208	7766
40°	9307	7737	7234
45°	9005	7265	6737
50°	8673	6807	6186
55°	8310	6272	5639
60°	7938	5686	5069
65°	7514	5082	4427
70°	7025	4354	3738
75°	6294	3509	2994
80°	5363	2537	2106
85°	4162	1412	1134

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9005 cd/sqm

TEST NUMBER: P1033682

CATALOG NUMBER: S124DIW-B795D1050UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.7	1.8
10°-20°	351.3	5.0
20°-30°	517.1	7.3
30°-40°	601.1	8.5
40°-50°	601.0	8.5
50°-60°	525.7	7.5
60°-70°	390.3	5.5
70°-80°	221.4	3.1
80°-90°	66.2	0.9
90°-100°	85.9	1.2
100°-110°	257.1	3.6
110°-120°	436.8	6.2
120°-130°	576.1	8.2
130°-140°	647.0	9.2
140°-150°	635.9	9.0
150°-160°	534.9	7.6
160°-170°	355.9	5.0
170°-180°	124.6	1.8
0°-30°	993.1	14.1
0°-40°	1594.2	22.6
0°-60°	2720.9	38.6
0°-90°	3398.8	48.2
90°-120°	779.8	11.1
90°-150°	2638.8	37.4
90°-180°	3654.0	51.8
0°-180°	7053.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1323	1323	1323	1323	1323	
5°	1322	1318	1306	1318	1316	125
15°	1258	1254	1238	1245	1242	355
25°	1140	1132	1117	1118	1114	524
35°	981	973	958	951	946	613
45°	800	793	776	764	761	617
55°	605	602	587	575	568	542
65°	410	405	394	384	378	406
75°	218	213	208	204	202	232
85°	57	57	55	55	54	62
90°	3	14	22	28	31	8
95°	61	70	77	80	80	66
105°	237	238	242	246	248	252
115°	444	444	442	441	440	438
125°	647	647	646	644	642	577
135°	834	840	840	838	835	645
145°	1014	1018	1019	1018	1014	634
155°	1161	1161	1160	1164	1160	534
165°	1264	1261	1259	1265	1261	356
175°	1315	1310	1309	1316	1309	125
180°	1317	1317	1317	1317	1317	

TEST NUMBER: P1033682

CATALOG NUMBER: S124DIW-B795D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1323.1	1323.1	1323.1	1323.1	1323.1
2.5°	1327.3	1324.2	1312.5	1323.1	1322.0
5°	1322.0	1317.8	1306.1	1317.8	1315.7
7.5°	1312.5	1308.3	1295.5	1305.1	1304.0
10°	1298.7	1294.5	1280.7	1289.2	1287.1
12.5°	1280.7	1276.5	1261.6	1271.2	1268.0
15°	1258.4	1254.2	1238.3	1244.6	1241.5
17.5°	1233.0	1227.7	1212.8	1217.1	1215.0
20°	1204.4	1199.1	1183.2	1186.3	1184.2
22.5°	1173.6	1166.2	1150.3	1156.7	1152.4
25°	1139.7	1132.3	1117.4	1118.5	1114.2
27.5°	1101.5	1094.1	1080.3	1078.2	1072.9
30°	1063.4	1054.9	1041.1	1036.9	1031.6
32.5°	1023.1	1015.7	1000.8	995.5	990.2
35°	980.7	973.2	958.4	951.0	945.7
37.5°	936.1	929.8	913.9	906.5	899.0
40°	892.7	884.2	868.3	857.7	852.4
42.5°	846.0	841.8	823.8	811.0	807.9
45°	800.4	793.0	776.1	764.4	761.2
47.5°	752.7	747.4	731.5	718.8	710.3
50°	704.0	699.7	684.9	670.0	663.7
52.5°	656.3	650.9	635.0	622.3	613.8
55°	605.4	602.2	587.3	574.6	568.3
57.5°	557.7	554.5	539.6	526.9	520.5
60°	507.8	502.5	488.7	479.2	473.9
62.5°	459.1	454.8	440.0	431.5	426.2
65°	410.3	405.0	394.4	383.8	378.5
67.5°	360.5	356.2	345.6	335.0	334.0
70°	314.9	307.5	299.0	290.5	287.3
72.5°	266.1	258.7	252.3	246.0	242.8
75°	218.4	213.1	207.8	203.6	202.5
77.5°	171.7	169.6	164.3	163.3	160.1
80°	130.4	127.2	125.1	123.0	121.9
82.5°	90.1	89.1	89.1	88.0	86.9
85°	57.2	57.2	55.1	55.1	54.1
87.5°	27.6	26.5	25.4	25.4	25.4
90°	3.1	14.3	22.4	28.5	30.6
92.5°	26.5	39.7	44.8	47.9	48.9
95°	61.1	70.3	77.4	80.5	80.5
97.5°	97.8	105.9	114.1	118.2	118.2
100°	142.6	146.7	155.8	157.9	157.9
102.5°	189.5	190.5	198.6	201.7	202.7
105°	237.3	238.3	242.4	245.5	248.5
107.5°	287.2	288.3	289.3	293.3	292.3
110°	338.2	340.2	339.2	337.1	340.2

TEST NUMBER: P1033682

CATALOG NUMBER: S124DIW-B795D1050UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	391.1	391.1	389.1	389.1	389.1
115°	444.1	444.1	442.1	441.0	440.0
117.5°	494.0	494.0	493.0	489.9	486.9
120°	543.9	548.0	544.9	539.8	541.9
122.5°	595.9	596.9	595.9	592.8	587.7
125°	646.8	646.8	645.8	643.7	641.7
127.5°	692.6	695.7	693.6	691.6	690.6
130°	741.5	744.6	744.6	742.5	738.5
132.5°	791.4	793.5	792.4	790.4	789.4
135°	834.2	840.3	840.3	838.3	835.2
137.5°	882.1	885.1	887.2	884.1	885.1
140°	929.9	932.0	932.0	931.0	929.9
142.5°	973.7	975.8	974.8	974.8	974.8
145°	1013.5	1017.5	1018.6	1017.5	1014.5
147.5°	1054.2	1059.3	1058.3	1057.3	1056.2
150°	1090.9	1095.0	1095.0	1095.0	1093.9
152.5°	1125.5	1127.5	1128.6	1131.6	1128.6
155°	1161.2	1161.2	1160.1	1164.2	1160.1
157.5°	1191.7	1189.7	1189.7	1192.7	1189.7
160°	1218.2	1217.2	1216.2	1219.2	1214.1
162.5°	1242.6	1239.6	1238.6	1244.7	1239.6
165°	1264.0	1261.0	1258.9	1265.1	1261.0
167.5°	1281.3	1277.3	1277.3	1283.4	1277.3
170°	1295.6	1290.5	1291.5	1297.6	1290.5
172.5°	1305.8	1301.7	1301.7	1308.8	1301.7
175°	1315.0	1309.9	1308.8	1316.0	1308.8
177.5°	1319.0	1313.9	1313.9	1321.1	1312.9
180°	1317.0	1317.0	1317.0	1317.0	1317.0

(END OF REPORT)