

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001126

Luminaire Tested: S124RDW-B1020DB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDW-B1020DB2750-4F0-XX-W2A-F_2700K
Description: Define 4 Regressed Direct Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4112.0 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001126

CATALOG NUMBER: S124RDW-B1020DB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1001126

CATALOG NUMBER: S124RDW-B1020DB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	110	105	101	98	107	103	99	96	99	96	93	95	92	90	91	89	87	87	87	85
2	100	93	86	81	98	91	85	80	87	82	78	84	80	76	81	78	74	74	74	72
3	92	82	74	68	89	80	73	67	77	71	66	75	69	65	72	68	64	64	64	62
4	84	73	65	58	82	72	64	58	69	62	57	67	61	56	65	60	56	56	56	54
5	78	66	57	51	76	65	56	50	62	55	50	61	54	49	59	53	49	49	49	47
6	72	59	51	45	70	58	50	44	57	49	44	55	49	44	53	48	43	43	43	41
7	67	54	46	40	65	53	45	40	52	45	39	50	44	39	49	43	39	39	39	37
8	63	50	41	36	61	49	41	36	48	40	35	46	40	35	45	39	35	35	35	33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	32	32	30
10	55	42	35	29	54	42	34	29	41	34	29	40	33	29	39	33	29	29	29	27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14512	14512	14512
5°	14545	14367	14456
10°	14454	14194	14194
15°	14287	13897	13793
20°	14060	13504	13255
25°	13769	13045	12714
30°	13485	12561	12036
35°	13171	12059	11353
40°	12794	11488	10618
45°	12446	10921	9868
50°	12049	10268	9076
55°	11624	9589	8215
60°	11155	8844	7334
65°	10728	7915	6468
70°	10104	6888	5491
75°	9316	5709	4464
80°	8129	4353	4095
85°	6886	3948	3696

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12446 cd/sqm

TEST NUMBER: P1001126

CATALOG NUMBER: S124RDW-B1020DB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.3	4.1
10°-20°	466.6	11.3
20°-30°	673.6	16.4
30°-40°	763.5	18.6
40°-50°	737.1	17.9
50°-60°	612.8	14.9
60°-70°	423.0	10.3
70°-80°	213.7	5.2
80°-90°	54.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1307.6	31.8
0°-40°	2071.0	50.4
0°-60°	3421.0	83.2
0°-90°	4112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4112.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1780	1780	1780	1780	1780	
5°	1777	1771	1755	1769	1766	169
15°	1692	1680	1646	1643	1634	477
25°	1530	1506	1450	1427	1413	705
35°	1323	1280	1211	1165	1140	827
45°	1079	1029	947	880	856	832
55°	818	763	674	604	578	731
65°	556	497	410	352	335	549
75°	296	245	181	150	142	312
85°	74	46	42	40	40	85
90°	0	0	0	0	0	



TEST NUMBER: P1001126

CATALOG NUMBER: S124RDW-B1020DB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1779.6	1779.6	1779.6	1779.6	1779.6
2.5°	1785.1	1779.6	1764.6	1779.6	1778.3
5°	1776.9	1771.4	1755.1	1768.7	1766.0
7.5°	1764.6	1759.2	1738.7	1748.3	1744.2
10°	1745.6	1738.7	1714.2	1719.7	1714.2
12.5°	1721.0	1712.8	1682.9	1685.6	1677.4
15°	1692.4	1680.1	1646.1	1643.4	1633.8
17.5°	1659.7	1642.0	1602.5	1595.7	1582.0
20°	1620.2	1602.5	1556.1	1545.2	1527.5
22.5°	1576.6	1556.1	1505.7	1488.0	1474.4
25°	1530.3	1505.7	1449.9	1426.7	1413.1
27.5°	1482.6	1452.6	1394.0	1366.7	1347.7
30°	1432.1	1398.1	1334.0	1300.0	1278.2
32.5°	1379.0	1339.5	1272.7	1231.8	1211.4
35°	1323.1	1279.5	1211.4	1165.1	1140.5
37.5°	1264.5	1219.6	1144.6	1094.2	1069.7
40°	1201.9	1156.9	1079.2	1022.0	997.5
42.5°	1141.9	1094.2	1012.4	953.9	928.0
45°	1079.2	1028.8	947.0	880.3	855.7
47.5°	1015.2	963.4	878.9	809.4	782.2
50°	949.8	896.6	809.4	741.3	715.4
52.5°	883.0	831.2	741.3	671.8	644.5
55°	817.6	763.1	674.5	603.7	577.8
57.5°	753.5	696.3	609.1	536.9	517.8
60°	684.0	629.5	542.3	471.5	449.7
62.5°	621.4	564.1	474.2	410.2	393.8
65°	556.0	497.4	410.2	351.6	335.2
67.5°	487.8	432.0	350.2	298.4	279.3
70°	423.8	366.6	288.9	243.9	230.3
72.5°	355.7	305.2	233.0	196.2	184.0
75°	295.7	245.3	181.2	149.9	141.7
77.5°	233.0	189.4	134.9	113.1	110.4
80°	173.1	133.5	92.7	88.6	87.2
82.5°	121.3	85.8	66.8	64.0	62.7
85°	73.6	46.3	42.2	39.5	39.5
87.5°	31.3	20.4	19.1	17.7	19.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)