

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983171

Luminaire Tested: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983171
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K
Description: Define 4 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3689.0 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 31.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983171

CATALOG NUMBER: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P983171

CATALOG NUMBER: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983171

CATALOG NUMBER: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.8	0.1
90°-100°	86.6	2.3
100°-110°	259.4	7.0
110°-120°	440.6	11.9
120°-130°	581.1	15.8
130°-140°	652.7	17.7
140°-150°	641.5	17.4
150°-160°	539.5	14.6
160°-170°	359.0	9.7
170°-180°	125.7	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.8	0.1
90°-120°	786.6	21.3
90°-150°	2661.9	72.2
90°-180°	3686.0	99.9
0°-180°	3689.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	3	14	23	29	31	5
95°	62	71	78	81	81	67
105°	239	240	244	248	251	254
115°	448	448	446	445	444	442
125°	652	652	651	649	647	582
135°	842	848	848	846	842	651
145°	1022	1026	1028	1026	1023	640
155°	1171	1171	1170	1174	1170	539
165°	1275	1272	1270	1276	1272	360
175°	1326	1321	1320	1328	1320	126
180°	1328	1328	1328	1328	1328	

TEST NUMBER: P983171

CATALOG NUMBER: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.1	14.4	22.6	28.8	30.8
92.5°	26.7	40.1	45.2	48.3	49.3
95°	61.6	70.9	78.1	81.2	81.2
97.5°	98.6	106.9	115.1	119.2	119.2
100°	143.8	148.0	157.2	159.3	159.3
102.5°	191.1	192.1	200.4	203.4	204.5
105°	239.4	240.4	244.5	247.6	250.7
107.5°	289.7	290.8	291.8	295.9	294.9
110°	341.1	343.2	342.1	340.1	343.2

TEST NUMBER: P983171

CATALOG NUMBER: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	394.5	394.5	392.5	392.5	392.5
115°	448.0	448.0	445.9	444.9	443.9
117.5°	498.3	498.3	497.3	494.2	491.1
120°	548.7	552.8	549.7	544.6	546.6
122.5°	601.1	602.1	601.1	598.0	592.9
125°	652.4	652.4	651.4	649.4	647.3
127.5°	698.7	701.8	699.7	697.7	696.6
130°	748.0	751.1	751.1	749.0	744.9
132.5°	798.3	800.4	799.4	797.3	796.3
135°	841.5	847.7	847.7	845.6	842.5
137.5°	889.8	892.9	894.9	891.8	892.9
140°	938.1	940.1	940.1	939.1	938.1
142.5°	982.3	984.3	983.3	983.3	983.3
145°	1022.3	1026.4	1027.5	1026.4	1023.4
147.5°	1063.4	1068.6	1067.5	1066.5	1065.5
150°	1100.4	1104.5	1104.5	1104.5	1103.5
152.5°	1135.4	1137.4	1138.4	1141.5	1138.4
155°	1171.3	1171.3	1170.3	1174.4	1170.3
157.5°	1202.1	1200.1	1200.1	1203.2	1200.1
160°	1228.9	1227.8	1226.8	1229.9	1224.7
162.5°	1253.5	1250.4	1249.4	1255.6	1250.4
165°	1275.1	1272.0	1270.0	1276.1	1272.0
167.5°	1292.6	1288.5	1288.5	1294.6	1288.5
170°	1306.9	1301.8	1302.8	1309.0	1301.8
172.5°	1317.2	1313.1	1313.1	1320.3	1313.1
175°	1326.5	1321.3	1320.3	1327.5	1320.3
177.5°	1330.6	1325.4	1325.4	1332.6	1324.4
180°	1328.5	1328.5	1328.5	1328.5	1328.5



TEST NUMBER: P983171

CATALOG NUMBER: S124IW-B1050UB2750-4F0-XX-W2A-1_3000K

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00

END OF REPORT