

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033718

Luminaire Tested: S124DIW-B795D1340UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033718
REPORT IS A COMBINATION OF REPORTS P998042 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1340UB30-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8083.0 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033718

CATALOG NUMBER: S124DIW-B795D1340UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033718

CATALOG NUMBER: S124DIW-B795D1340UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	73	65	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	23	20	17
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	21	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1033718

CATALOG NUMBER: S124DIW-B795D1340UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	1.6
10°-20°	354.3	4.4
20°-30°	521.5	6.5
30°-40°	606.2	7.5
40°-50°	606.2	7.5
50°-60°	530.2	6.6
60°-70°	393.6	4.9
70°-80°	223.3	2.8
80°-90°	67.5	0.8
90°-100°	109.3	1.4
100°-110°	327.5	4.1
110°-120°	556.4	6.9
120°-130°	733.8	9.1
130°-140°	824.1	10.2
140°-150°	810.0	10.0
150°-160°	681.3	8.4
160°-170°	453.3	5.6
170°-180°	158.7	2.0
0°-30°	1001.6	12.4
0°-40°	1607.8	19.9
0°-60°	2744.1	33.9
0°-90°	3428.6	42.4
90°-120°	993.2	12.3
90°-150°	3361.1	41.6
90°-180°	4654.0	57.6
0°-180°	8083.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	4	18	28	36	39	9
95°	78	90	99	102	102	84
105°	302	304	309	313	317	321
115°	566	566	563	562	560	558
125°	824	824	822	820	817	734
135°	1062	1070	1070	1068	1064	822
145°	1291	1296	1297	1296	1292	808
155°	1479	1479	1478	1483	1478	681
165°	1610	1606	1604	1611	1606	454
175°	1675	1668	1667	1676	1667	159
180°	1678	1678	1678	1678	1678	

TEST NUMBER: P1033718

CATALOG NUMBER: S124DIW-B795D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	3.9	18.2	28.5	36.3	38.9
92.5°	33.7	50.6	57.1	61.0	62.3
95°	77.8	89.5	98.6	102.5	102.5
97.5°	124.5	134.9	145.3	150.5	150.5
100°	181.6	186.8	198.5	201.1	201.1
102.5°	241.3	242.6	253.0	256.9	258.2
105°	302.3	303.6	308.8	312.7	316.6
107.5°	365.9	367.2	368.5	373.6	372.3
110°	430.7	433.3	432.0	429.4	433.3

TEST NUMBER: P1033718

CATALOG NUMBER: S124DIW-B795D1340UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	498.2	498.2	495.6	495.6	495.6
115°	565.6	565.6	563.1	561.8	560.5
117.5°	629.2	629.2	627.9	624.0	620.1
120°	692.8	698.0	694.1	687.6	690.2
122.5°	759.0	760.3	759.0	755.1	748.6
125°	823.8	823.8	822.5	819.9	817.3
127.5°	882.2	886.1	883.5	880.9	879.6
130°	944.5	948.4	948.4	945.8	940.6
132.5°	1008.0	1010.6	1009.3	1006.8	1005.5
135°	1062.5	1070.3	1070.3	1067.7	1063.8
137.5°	1123.5	1127.4	1130.0	1126.1	1127.4
140°	1184.5	1187.1	1187.1	1185.8	1184.5
142.5°	1240.3	1242.9	1241.6	1241.6	1241.6
145°	1290.9	1296.1	1297.4	1296.1	1292.2
147.5°	1342.8	1349.3	1348.0	1346.7	1345.4
150°	1389.5	1394.7	1394.7	1394.7	1393.4
152.5°	1433.6	1436.2	1437.5	1441.4	1437.5
155°	1479.0	1479.0	1477.7	1482.9	1477.7
157.5°	1517.9	1515.3	1515.3	1519.2	1515.3
160°	1551.6	1550.3	1549.0	1552.9	1546.5
162.5°	1582.8	1578.9	1577.6	1585.4	1578.9
165°	1610.0	1606.1	1603.5	1611.3	1606.1
167.5°	1632.1	1626.9	1626.9	1634.7	1626.9
170°	1650.2	1643.8	1645.1	1652.8	1643.8
172.5°	1663.2	1658.0	1658.0	1667.1	1658.0
175°	1674.9	1668.4	1667.1	1676.2	1667.1
177.5°	1680.1	1673.6	1673.6	1682.7	1672.3
180°	1677.5	1677.5	1677.5	1677.5	1677.5

(END OF REPORT)