

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033724

Luminaire Tested: S124DIW-B795D1340UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033724
REPORT IS A COMBINATION OF REPORTS P998051 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIW-B795D1340UB35-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8118.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033724

CATALOG NUMBER: S124DIW-B795D1340UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033724

CATALOG NUMBER: S124DIW-B795D1340UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35
3	80	70	63	57	73	65	58	53	53	49	45	43	40	37	34	32	30
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22
6	62	50	42	36	56	46	39	33	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	23	20	17
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1033724

CATALOG NUMBER: S124DIW-B795D1340UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	1.6
10°-20°	355.9	4.4
20°-30°	523.8	6.5
30°-40°	608.9	7.5
40°-50°	608.8	7.5
50°-60°	532.5	6.6
60°-70°	395.3	4.9
70°-80°	224.3	2.8
80°-90°	67.8	0.8
90°-100°	109.8	1.4
100°-110°	328.9	4.1
110°-120°	558.8	6.9
120°-130°	736.9	9.1
130°-140°	827.7	10.2
140°-150°	813.5	10.0
150°-160°	684.2	8.4
160°-170°	455.2	5.6
170°-180°	159.4	2.0
0°-30°	1006.0	12.4
0°-40°	1614.9	19.9
0°-60°	2756.1	34.0
0°-90°	3443.6	42.4
90°-120°	997.5	12.3
90°-150°	3375.5	41.6
90°-180°	4674.0	57.6
0°-180°	8118.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	4	18	29	36	39	10
95°	78	90	99	103	103	85
105°	304	305	310	314	318	322
115°	568	568	566	564	563	560
125°	827	827	826	824	821	738
135°	1067	1075	1075	1072	1068	826
145°	1296	1302	1303	1302	1298	811
155°	1485	1485	1484	1489	1484	684
165°	1617	1613	1610	1618	1613	456
175°	1682	1676	1674	1683	1674	160
180°	1685	1685	1685	1685	1685	

TEST NUMBER: P1033724

CATALOG NUMBER: S124DIW-B795D1340UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	3.9	18.2	28.7	36.5	39.1
92.5°	33.9	50.8	57.3	61.2	62.5
95°	78.2	89.9	99.0	102.9	102.9
97.5°	125.1	135.5	145.9	151.1	151.1
100°	182.4	187.6	199.3	202.0	202.0
102.5°	242.3	243.6	254.1	258.0	259.3
105°	303.6	304.9	310.1	314.0	317.9
107.5°	367.4	368.7	370.0	375.2	373.9
110°	432.6	435.2	433.9	431.3	435.2

TEST NUMBER: P1033724

CATALOG NUMBER: S124DIW-B795D1340UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	500.3	500.3	497.7	497.7	497.7
115°	568.1	568.1	565.5	564.2	562.9
117.5°	631.9	631.9	630.6	626.7	622.8
120°	695.8	701.0	697.1	690.6	693.2
122.5°	762.2	763.5	762.2	758.3	751.8
125°	827.4	827.4	826.1	823.5	820.8
127.5°	886.0	889.9	887.3	884.7	883.4
130°	948.5	952.4	952.4	949.8	944.6
132.5°	1012.4	1015.0	1013.7	1011.1	1009.8
135°	1067.1	1074.9	1074.9	1072.3	1068.4
137.5°	1128.3	1132.2	1134.9	1130.9	1132.2
140°	1189.6	1192.2	1192.2	1190.9	1189.6
142.5°	1245.6	1248.2	1246.9	1246.9	1246.9
145°	1296.4	1301.6	1302.9	1301.6	1297.7
147.5°	1348.5	1355.0	1353.7	1352.4	1351.1
150°	1395.4	1400.7	1400.7	1400.7	1399.3
152.5°	1439.7	1442.3	1443.6	1447.6	1443.6
155°	1485.3	1485.3	1484.0	1489.3	1484.0
157.5°	1524.4	1521.8	1521.8	1525.7	1521.8
160°	1558.3	1557.0	1555.7	1559.6	1553.1
162.5°	1589.6	1585.7	1584.4	1592.2	1585.7
165°	1616.9	1613.0	1610.4	1618.2	1613.0
167.5°	1639.1	1633.9	1633.9	1641.7	1633.9
170°	1657.3	1650.8	1652.1	1659.9	1650.8
172.5°	1670.4	1665.1	1665.1	1674.3	1665.1
175°	1682.1	1675.6	1674.3	1683.4	1674.3
177.5°	1687.3	1680.8	1680.8	1689.9	1679.5
180°	1684.7	1684.7	1684.7	1684.7	1684.7

(END OF REPORT)