

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983194

Luminaire Tested: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983194
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K
Description: Define 4 Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4479.0 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983194

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P983194

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983194

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.4	0.1
90°-100°	105.1	2.3
100°-110°	314.9	7.0
110°-120°	535.0	11.9
120°-130°	705.6	15.8
130°-140°	792.5	17.7
140°-150°	778.9	17.4
150°-160°	655.1	14.6
160°-170°	435.9	9.7
170°-180°	152.6	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.4	0.1
90°-120°	955.0	21.3
90°-150°	3232.0	72.2
90°-180°	4476.0	99.9
0°-180°	4479.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	18	27	35	37	5
95°	75	86	95	99	99	81
105°	291	292	297	301	304	308
115°	544	544	541	540	539	536
125°	792	792	791	788	786	706
135°	1022	1029	1029	1027	1023	790
145°	1241	1246	1248	1246	1242	777
155°	1422	1422	1421	1426	1421	654
165°	1548	1544	1542	1549	1544	437
175°	1610	1604	1603	1612	1603	153
180°	1613	1613	1613	1613	1613	

TEST NUMBER: P983194

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.7	17.5	27.4	34.9	37.4
92.5°	32.4	48.7	54.9	58.6	59.9
95°	74.9	86.1	94.8	98.6	98.6
97.5°	119.8	129.7	139.7	144.7	144.7
100°	174.7	179.6	190.9	193.4	193.4
102.5°	232.0	233.3	243.3	247.0	248.3
105°	290.7	291.9	296.9	300.6	304.4
107.5°	351.8	353.0	354.3	359.3	358.0
110°	414.2	416.7	415.4	412.9	416.7

TEST NUMBER: P983194

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	479.0	479.0	476.5	476.5	476.5
115°	543.9	543.9	541.4	540.2	538.9
117.5°	605.0	605.0	603.8	600.1	596.3
120°	666.2	671.2	667.4	661.2	663.7
122.5°	729.8	731.0	729.8	726.0	719.8
125°	792.2	792.2	790.9	788.4	785.9
127.5°	848.3	852.0	849.6	847.1	845.8
130°	908.2	911.9	911.9	909.4	904.4
132.5°	969.3	971.8	970.6	968.1	966.8
135°	1021.7	1029.2	1029.2	1026.7	1023.0
137.5°	1080.3	1084.1	1086.6	1082.8	1084.1
140°	1139.0	1141.5	1141.5	1140.2	1139.0
142.5°	1192.6	1195.1	1193.9	1193.9	1193.9
145°	1241.3	1246.3	1247.5	1246.3	1242.5
147.5°	1291.2	1297.4	1296.2	1294.9	1293.7
150°	1336.1	1341.1	1341.1	1341.1	1339.8
152.5°	1378.5	1381.0	1382.2	1386.0	1382.2
155°	1422.2	1422.2	1420.9	1425.9	1420.9
157.5°	1459.6	1457.1	1457.1	1460.8	1457.1
160°	1492.0	1490.8	1489.5	1493.3	1487.0
162.5°	1522.0	1518.2	1517.0	1524.5	1518.2
165°	1548.2	1544.4	1541.9	1549.4	1544.4
167.5°	1569.4	1564.4	1564.4	1571.9	1564.4
170°	1586.8	1580.6	1581.8	1589.3	1580.6
172.5°	1599.3	1594.3	1594.3	1603.0	1594.3
175°	1610.5	1604.3	1603.0	1611.8	1603.0
177.5°	1615.5	1609.3	1609.3	1618.0	1608.0
180°	1613.0	1613.0	1613.0	1613.0	1613.0

(END OF REPORT)