

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983196

Luminaire Tested: S124IW-B1340UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1340UB2750-4F0-XX-W2A_3000K
Description: Define 4 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5372.0 lumens
Efficiency: N/A
Efficacy: 127.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 42.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983196

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P983196

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983196

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.6	0.1
90°-100°	57.6	1.1
100°-110°	379.3	7.1
110°-120°	724.2	13.5
120°-130°	919.4	17.1
130°-140°	983.6	18.3
140°-150°	919.7	17.1
150°-160°	741.6	13.8
160°-170°	478.3	8.9
170°-180°	164.8	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.6	0.1
90°-120°	1161.0	21.6
90°-150°	3983.6	74.2
90°-180°	5368.0	99.9
0°-180°	5372.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	4	18	28	36	39	4
95°	71	27	28	36	38	88
105°	391	398	405	416	370	409
115°	729	733	732	734	734	718
125°	1025	1030	1028	1032	1033	915
135°	1272	1270	1276	1278	1281	980
145°	1466	1470	1470	1472	1474	916
155°	1608	1609	1605	1610	1606	741
165°	1696	1690	1690	1700	1688	479
175°	1735	1727	1728	1740	1724	165
180°	1735	1735	1735	1735	1735	

TEST NUMBER: P983196

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	3.9	18.2	28.5	36.3	38.9
92.5°	19.5	16.9	27.2	35.0	35.0
95°	71.4	27.2	28.5	36.3	37.6
97.5°	136.2	164.8	28.5	35.0	36.3
100°	212.8	236.2	57.1	35.0	36.3
102.5°	298.5	314.0	329.6	37.6	37.6
105°	390.6	398.4	404.9	416.5	369.8
107.5°	474.9	478.8	487.9	494.4	499.6
110°	560.6	564.5	572.2	574.8	578.7

TEST NUMBER: P983196

CATALOG NUMBER: S124IW-B1340UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	643.6	651.4	654.0	652.7	657.9
115°	729.3	733.2	731.9	734.4	734.4
117.5°	805.8	811.0	814.9	813.6	813.6
120°	883.7	888.9	887.6	890.2	887.6
122.5°	956.3	958.9	961.5	962.8	960.2
125°	1025.1	1030.3	1027.7	1031.6	1032.9
127.5°	1091.3	1092.6	1099.1	1097.8	1096.5
130°	1154.9	1156.2	1160.1	1161.4	1161.4
132.5°	1213.3	1215.9	1221.1	1222.4	1221.1
135°	1271.7	1270.4	1275.6	1278.1	1280.7
137.5°	1323.6	1323.6	1330.1	1332.6	1331.4
140°	1374.2	1376.8	1379.4	1383.3	1384.6
142.5°	1419.6	1424.8	1426.1	1428.7	1428.7
145°	1466.3	1470.2	1470.2	1471.5	1474.1
147.5°	1502.6	1510.4	1509.1	1510.4	1511.7
150°	1542.9	1548.1	1546.8	1546.8	1548.1
152.5°	1576.6	1580.5	1577.9	1580.5	1579.2
155°	1607.7	1609.0	1605.1	1610.3	1606.4
157.5°	1635.0	1635.0	1629.8	1636.3	1629.8
160°	1658.3	1654.5	1653.2	1660.9	1653.2
162.5°	1679.1	1673.9	1672.6	1680.4	1671.3
165°	1696.0	1689.5	1689.5	1699.9	1688.2
167.5°	1710.3	1703.8	1702.5	1714.1	1701.2
170°	1721.9	1714.1	1715.4	1725.8	1712.8
172.5°	1729.7	1721.9	1723.2	1733.6	1719.3
175°	1734.9	1727.1	1728.4	1740.1	1724.5
177.5°	1738.8	1729.7	1732.3	1742.7	1727.1
180°	1734.9	1734.9	1734.9	1734.9	1734.9

(END OF REPORT)