

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983211

Luminaire Tested: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K
Description: Define 4 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5493.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983211

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983211

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983211

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.2	0.1
90°-100°	129.0	2.3
100°-110°	386.2	7.0
110°-120°	656.1	11.9
120°-130°	865.3	15.8
130°-140°	971.9	17.7
140°-150°	955.2	17.4
150°-160°	803.4	14.6
160°-170°	534.5	9.7
170°-180°	187.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.2	0.1
90°-120°	1171.3	21.3
90°-150°	3963.7	72.2
90°-180°	5489.0	99.9
0°-180°	5493.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	21	34	43	46	7
95°	92	106	116	121	121	99
105°	356	358	364	369	373	378
115°	667	667	664	662	661	658
125°	972	972	970	967	964	866
135°	1253	1262	1262	1259	1254	969
145°	1522	1528	1530	1528	1524	953
155°	1744	1744	1743	1749	1743	803
165°	1899	1894	1891	1900	1894	535
175°	1975	1968	1966	1977	1966	188
180°	1978	1978	1978	1978	1978	

TEST NUMBER: P983211

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.6	21.4	33.7	42.8	45.9
92.5°	39.8	59.7	67.3	71.9	73.4
95°	91.8	105.6	116.3	120.9	120.9
97.5°	146.9	159.1	171.4	177.5	177.5
100°	214.2	220.3	234.1	237.1	237.1
102.5°	284.6	286.1	298.3	302.9	304.5
105°	356.5	358.0	364.1	368.7	373.3
107.5°	431.4	433.0	434.5	440.6	439.1
110°	507.9	511.0	509.5	506.4	511.0

TEST NUMBER: P983211

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	587.5	587.5	584.4	584.4	584.4
115°	667.0	667.0	664.0	662.5	660.9
117.5°	742.0	742.0	740.5	735.9	731.3
120°	817.0	823.1	818.5	810.9	813.9
122.5°	895.0	896.5	895.0	890.4	882.8
125°	971.5	971.5	970.0	966.9	963.9
127.5°	1040.4	1044.9	1041.9	1038.8	1037.3
130°	1113.8	1118.4	1118.4	1115.3	1109.2
132.5°	1188.8	1191.8	1190.3	1187.2	1185.7
135°	1253.0	1262.2	1262.2	1259.1	1254.5
137.5°	1324.9	1329.5	1332.6	1328.0	1329.5
140°	1396.8	1399.9	1399.9	1398.4	1396.8
142.5°	1462.6	1465.7	1464.1	1464.1	1464.1
145°	1522.3	1528.4	1529.9	1528.4	1523.8
147.5°	1583.5	1591.1	1589.6	1588.1	1586.5
150°	1638.6	1644.7	1644.7	1644.7	1643.1
152.5°	1690.6	1693.6	1695.2	1699.8	1695.2
155°	1744.1	1744.1	1742.6	1748.7	1742.6
157.5°	1790.0	1787.0	1787.0	1791.5	1787.0
160°	1829.8	1828.3	1826.7	1831.3	1823.7
162.5°	1866.5	1861.9	1860.4	1869.6	1861.9
165°	1898.6	1894.1	1891.0	1900.2	1894.1
167.5°	1924.7	1918.5	1918.5	1927.7	1918.5
170°	1946.1	1938.4	1939.9	1949.1	1938.4
172.5°	1961.4	1955.2	1955.2	1966.0	1955.2
175°	1975.1	1967.5	1966.0	1976.7	1966.0
177.5°	1981.3	1973.6	1973.6	1984.3	1972.1
180°	1978.2	1978.2	1978.2	1978.2	1978.2

(END OF REPORT)