

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983216

Luminaire Tested: S124IW-B1560UB2750-4F0-XX-W2A_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1560UB2750-4F0-XX-W2A_3000K
Description: Define 4 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6335.0 lumens
Efficiency: N/A
Efficacy: 121.4 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983216

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P983216

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983216

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.2	0.1
90°-100°	67.9	1.1
100°-110°	447.3	7.1
110°-120°	854.0	13.5
120°-130°	1084.2	17.1
130°-140°	1159.8	18.3
140°-150°	1084.5	17.1
150°-160°	874.6	13.8
160°-170°	564.0	8.9
170°-180°	194.4	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.2	0.1
90°-120°	1369.2	21.6
90°-150°	4697.7	74.2
90°-180°	6331.0	99.9
0°-180°	6335.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	21	34	43	46	4
95°	84	32	34	43	44	104
105°	461	470	477	491	436	482
115°	860	865	863	866	866	847
125°	1209	1215	1212	1216	1218	1080
135°	1500	1498	1504	1507	1510	1156
145°	1729	1734	1734	1735	1738	1080
155°	1896	1898	1893	1899	1894	874
165°	2000	1992	1992	2005	1991	565
175°	2046	2037	2038	2052	2034	195
180°	2046	2046	2046	2046	2046	

TEST NUMBER: P983216

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.6	21.4	33.7	42.8	45.9
92.5°	23.0	19.9	32.1	41.3	41.3
95°	84.2	32.1	33.7	42.8	44.4
97.5°	160.7	194.3	33.7	41.3	42.8
100°	251.0	278.5	67.3	41.3	42.8
102.5°	352.0	370.3	388.7	44.4	44.4
105°	460.6	469.8	477.4	491.2	436.1
107.5°	560.1	564.7	575.4	583.0	589.1
110°	661.1	665.6	674.8	677.9	682.5

TEST NUMBER: P983216

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	759.0	768.2	771.2	769.7	775.8
115°	860.0	864.6	863.0	866.1	866.1
117.5°	950.3	956.4	961.0	959.5	959.5
120°	1042.1	1048.2	1046.7	1049.7	1046.7
122.5°	1127.8	1130.8	1133.9	1135.4	1132.4
125°	1208.9	1215.0	1211.9	1216.5	1218.1
127.5°	1286.9	1288.5	1296.1	1294.6	1293.0
130°	1361.9	1363.4	1368.0	1369.6	1369.6
132.5°	1430.8	1433.8	1439.9	1441.5	1439.9
135°	1499.6	1498.1	1504.2	1507.3	1510.3
137.5°	1560.8	1560.8	1568.5	1571.5	1570.0
140°	1620.5	1623.6	1626.6	1631.2	1632.8
142.5°	1674.1	1680.2	1681.7	1684.8	1684.8
145°	1729.2	1733.7	1733.7	1735.3	1738.3
147.5°	1772.0	1781.2	1779.7	1781.2	1782.7
150°	1819.4	1825.6	1824.0	1824.0	1825.6
152.5°	1859.2	1863.8	1860.8	1863.8	1862.3
155°	1896.0	1897.5	1892.9	1899.0	1894.4
157.5°	1928.1	1928.1	1922.0	1929.6	1922.0
160°	1955.6	1951.0	1949.5	1958.7	1949.5
162.5°	1980.1	1974.0	1972.5	1981.6	1970.9
165°	2000.0	1992.4	1992.4	2004.6	1990.8
167.5°	2016.8	2009.2	2007.7	2021.4	2006.1
170°	2030.6	2021.4	2023.0	2035.2	2019.9
172.5°	2039.8	2030.6	2032.1	2044.4	2027.5
175°	2045.9	2036.7	2038.3	2052.0	2033.7
177.5°	2050.5	2039.8	2042.9	2055.1	2036.7
180°	2045.9	2045.9	2045.9	2045.9	2045.9

(END OF REPORT)