

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983217

Luminaire Tested: S124IW-B1560UB2750-4F0-XX-W2A_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B1560UB2750-4F0-XX-W2A_3500K
Description: Define 4 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6362.0 lumens
Efficiency: N/A
Efficacy: 121.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 52.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983217

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983217

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983217

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	4.2	0.1
90°-100°	68.2	1.1
100°-110°	449.2	7.1
110°-120°	857.7	13.5
120°-130°	1088.8	17.1
130°-140°	1164.8	18.3
140°-150°	1089.2	17.1
150°-160°	878.3	13.8
160°-170°	566.4	8.9
170°-180°	195.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	4.2	0.1
90°-120°	1375.0	21.6
90°-150°	4717.8	74.2
90°-180°	6358.0	99.9
0°-180°	6362.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	5	22	34	43	46	4
95°	84	32	34	43	45	104
105°	463	472	480	493	438	484
115°	864	868	867	870	870	850
125°	1214	1220	1217	1222	1223	1084
135°	1506	1504	1511	1514	1517	1160
145°	1736	1741	1741	1743	1746	1085
155°	1904	1906	1901	1907	1902	878
165°	2008	2001	2001	2013	1999	568
175°	2055	2045	2047	2061	2042	196
180°	2055	2055	2055	2055	2055	

TEST NUMBER: P983217

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	4.6	21.5	33.8	43.0	46.1
92.5°	23.1	20.0	32.3	41.5	41.5
95°	84.5	32.3	33.8	43.0	44.6
97.5°	161.4	195.2	33.8	41.5	43.0
100°	252.0	279.7	67.6	41.5	43.0
102.5°	353.5	371.9	390.3	44.6	44.6
105°	462.6	471.8	479.5	493.3	438.0
107.5°	562.4	567.1	577.8	585.5	591.6
110°	663.9	668.5	677.7	680.8	685.4

TEST NUMBER: P983217

CATALOG NUMBER: S124IW-B1560UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	762.2	771.4	774.5	773.0	779.1
115°	863.7	868.3	866.7	869.8	869.8
117.5°	954.3	960.5	965.1	963.5	963.5
120°	1046.5	1052.7	1051.1	1054.2	1051.1
122.5°	1132.6	1135.7	1138.7	1140.3	1137.2
125°	1214.0	1220.2	1217.1	1221.7	1223.3
127.5°	1292.4	1293.9	1301.6	1300.1	1298.6
130°	1367.7	1369.2	1373.9	1375.4	1375.4
132.5°	1436.9	1439.9	1446.1	1447.6	1446.1
135°	1506.0	1504.5	1510.6	1513.7	1516.8
137.5°	1567.5	1567.5	1575.2	1578.2	1576.7
140°	1627.4	1630.5	1633.6	1638.2	1639.7
142.5°	1681.2	1687.3	1688.9	1692.0	1692.0
145°	1736.5	1741.1	1741.1	1742.7	1745.7
147.5°	1779.6	1788.8	1787.2	1788.8	1790.3
150°	1827.2	1833.3	1831.8	1831.8	1833.3
152.5°	1867.1	1871.8	1868.7	1871.8	1870.2
155°	1904.0	1905.6	1901.0	1907.1	1902.5
157.5°	1936.3	1936.3	1930.2	1937.8	1930.2
160°	1964.0	1959.4	1957.8	1967.0	1957.8
162.5°	1988.6	1982.4	1980.9	1990.1	1979.3
165°	2008.5	2000.8	2000.8	2013.1	1999.3
167.5°	2025.4	2017.8	2016.2	2030.0	2014.7
170°	2039.3	2030.0	2031.6	2043.9	2028.5
172.5°	2048.5	2039.3	2040.8	2053.1	2036.2
175°	2054.6	2045.4	2046.9	2060.8	2042.3
177.5°	2059.2	2048.5	2051.6	2063.9	2045.4
180°	2054.6	2054.6	2054.6	2054.6	2054.6

(END OF REPORT)