

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983232

Luminaire Tested: S124IW-B470UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983232
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B470UB2750-4F0-XX-W2A-1_3500K
Description: Define 4 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1652.0 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983232

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983232

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983232

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.3	0.1
90°-100°	38.8	2.3
100°-110°	116.2	7.0
110°-120°	197.3	11.9
120°-130°	260.2	15.8
130°-140°	292.3	17.7
140°-150°	287.3	17.4
150°-160°	241.6	14.6
160°-170°	160.8	9.7
170°-180°	56.3	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.3	0.1
90°-120°	352.3	21.3
90°-150°	1192.1	72.2
90°-180°	1651.0	99.9
0°-180°	1652.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	10	13	14	2
95°	28	32	35	36	36	30
105°	107	108	110	111	112	114
115°	201	201	200	199	199	198
125°	292	292	292	291	290	260
135°	377	380	380	379	377	292
145°	458	460	460	460	458	287
155°	524	524	524	526	524	241
165°	571	570	569	572	570	161
175°	594	592	591	594	591	56
180°	595	595	595	595	595	

TEST NUMBER: P983232

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.4	6.4	10.1	12.9	13.8
92.5°	12.0	17.9	20.2	21.6	22.1
95°	27.6	31.7	35.0	36.3	36.3
97.5°	44.2	47.9	51.5	53.4	53.4
100°	64.4	66.3	70.4	71.3	71.3
102.5°	85.6	86.0	89.7	91.1	91.6
105°	107.2	107.7	109.5	110.9	112.3
107.5°	129.8	130.2	130.7	132.5	132.1
110°	152.8	153.7	153.2	152.3	153.7

TEST NUMBER: P983232

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	176.7	176.7	175.8	175.8	175.8
115°	200.6	200.6	199.7	199.2	198.8
117.5°	223.2	223.2	222.7	221.3	219.9
120°	245.7	247.5	246.2	243.9	244.8
122.5°	269.2	269.6	269.2	267.8	265.5
125°	292.2	292.2	291.7	290.8	289.9
127.5°	312.9	314.3	313.3	312.4	312.0
130°	335.0	336.3	336.3	335.4	333.6
132.5°	357.5	358.4	358.0	357.1	356.6
135°	376.8	379.6	379.6	378.7	377.3
137.5°	398.5	399.8	400.8	399.4	399.8
140°	420.1	421.0	421.0	420.6	420.1
142.5°	439.9	440.8	440.3	440.3	440.3
145°	457.8	459.7	460.1	459.7	458.3
147.5°	476.2	478.5	478.1	477.6	477.1
150°	492.8	494.6	494.6	494.6	494.2
152.5°	508.4	509.4	509.8	511.2	509.8
155°	524.5	524.5	524.1	525.9	524.1
157.5°	538.3	537.4	537.4	538.8	537.4
160°	550.3	549.8	549.4	550.8	548.5
162.5°	561.3	560.0	559.5	562.3	560.0
165°	571.0	569.6	568.7	571.5	569.6
167.5°	578.8	577.0	577.0	579.8	577.0
170°	585.3	583.0	583.4	586.2	583.0
172.5°	589.9	588.0	588.0	591.3	588.0
175°	594.0	591.7	591.3	594.5	591.3
177.5°	595.9	593.6	593.6	596.8	593.1
180°	594.9	594.9	594.9	594.9	594.9

(END OF REPORT)