

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983233

Luminaire Tested: S124IW-B470UB2750-4F0-XX-W2A-1_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B470UB2750-4F0-XX-W2A-1_4000K
Description: Define 4 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1636.0 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983233

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P983233

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983233

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.3	0.1
90°-100°	38.4	2.3
100°-110°	115.0	7.0
110°-120°	195.4	11.9
120°-130°	257.7	15.8
130°-140°	289.5	17.7
140°-150°	284.5	17.4
150°-160°	239.3	14.6
160°-170°	159.2	9.7
170°-180°	55.7	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.3	0.1
90°-120°	348.8	21.3
90°-150°	1180.5	72.2
90°-180°	1635.0	99.9
0°-180°	1636.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	10	13	14	2
95°	27	31	35	36	36	30
105°	106	107	108	110	111	113
115°	199	199	198	197	197	196
125°	289	289	289	288	287	258
135°	373	376	376	375	374	289
145°	453	455	456	455	454	284
155°	520	520	519	521	519	239
165°	566	564	563	566	564	159
175°	588	586	586	589	586	56
180°	589	589	589	589	589	

TEST NUMBER: P983233

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.4	6.4	10.0	12.8	13.7
92.5°	11.8	17.8	20.0	21.4	21.9
95°	27.3	31.4	34.6	36.0	36.0
97.5°	43.7	47.4	51.0	52.9	52.9
100°	63.8	65.6	69.7	70.6	70.6
102.5°	84.8	85.2	88.9	90.2	90.7
105°	106.2	106.6	108.4	109.8	111.2
107.5°	128.5	129.0	129.4	131.2	130.8
110°	151.3	152.2	151.7	150.8	152.2

TEST NUMBER: P983233

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A-1_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	175.0	175.0	174.1	174.1	174.1
115°	198.7	198.7	197.8	197.3	196.8
117.5°	221.0	221.0	220.5	219.2	217.8
120°	243.3	245.1	243.8	241.5	242.4
122.5°	266.6	267.0	266.6	265.2	262.9
125°	289.3	289.3	288.9	288.0	287.1
127.5°	309.9	311.2	310.3	309.4	308.9
130°	331.7	333.1	333.1	332.2	330.4
132.5°	354.1	355.0	354.5	353.6	353.1
135°	373.2	375.9	375.9	375.0	373.6
137.5°	394.6	396.0	396.9	395.5	396.0
140°	416.0	416.9	416.9	416.5	416.0
142.5°	435.6	436.5	436.1	436.1	436.1
145°	453.4	455.2	455.7	455.2	453.8
147.5°	471.6	473.9	473.4	473.0	472.5
150°	488.0	489.8	489.8	489.8	489.4
152.5°	503.5	504.4	504.9	506.2	504.9
155°	519.5	519.5	519.0	520.8	519.0
157.5°	533.1	532.2	532.2	533.6	532.2
160°	545.0	544.5	544.1	545.4	543.2
162.5°	555.9	554.5	554.1	556.8	554.5
165°	565.5	564.1	563.2	565.9	564.1
167.5°	573.2	571.4	571.4	574.1	571.4
170°	579.6	577.3	577.8	580.5	577.3
172.5°	584.2	582.3	582.3	585.5	582.3
175°	588.3	586.0	585.5	588.7	585.5
177.5°	590.1	587.8	587.8	591.0	587.4
180°	589.2	589.2	589.2	589.2	589.2

(END OF REPORT)