

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983238

Luminaire Tested: S124IW-B470UB2750-4F0-XX-W2A_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983238
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B470UB2750-4F0-XX-W2A_4000K
Description: Define 4 Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1886.0 lumens
Efficiency: N/A
Efficacy: 142.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 13.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983238

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P983238

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983238

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.3	0.1
90°-100°	20.2	1.1
100°-110°	133.1	7.1
110°-120°	254.3	13.5
120°-130°	322.8	17.1
130°-140°	345.3	18.3
140°-150°	322.9	17.1
150°-160°	260.4	13.8
160°-170°	167.9	8.9
170°-180°	57.9	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.3	0.1
90°-120°	407.6	21.6
90°-150°	1398.6	74.2
90°-180°	1885.0	99.9
0°-180°	1886.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	6	10	13	14	1
95°	25	10	10	13	13	31
105°	137	140	142	146	130	143
115°	256	257	257	258	258	252
125°	360	362	361	362	363	321
135°	446	446	448	449	450	344
145°	515	516	516	517	518	322
155°	564	565	564	565	564	260
165°	595	593	593	597	593	168
175°	609	606	607	611	605	58
180°	609	609	609	609	609	

TEST NUMBER: P983238

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.4	6.4	10.0	12.8	13.7
92.5°	6.8	5.9	9.6	12.3	12.3
95°	25.1	9.6	10.0	12.8	13.2
97.5°	47.8	57.9	10.0	12.3	12.8
100°	74.7	82.9	20.0	12.3	12.8
102.5°	104.8	110.2	115.7	13.2	13.2
105°	137.1	139.9	142.1	146.2	129.8
107.5°	166.7	168.1	171.3	173.6	175.4
110°	196.8	198.2	200.9	201.8	203.2

TEST NUMBER: P983238

CATALOG NUMBER: S124IW-B470UB2750-4F0-XX-W2A_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	226.0	228.7	229.6	229.1	231.0
115°	256.0	257.4	256.9	257.9	257.9
117.5°	282.9	284.7	286.1	285.6	285.6
120°	310.2	312.1	311.6	312.5	311.6
122.5°	335.8	336.7	337.6	338.0	337.1
125°	359.9	361.7	360.8	362.2	362.6
127.5°	383.1	383.6	385.9	385.4	385.0
130°	405.5	405.9	407.3	407.7	407.7
132.5°	426.0	426.9	428.7	429.1	428.7
135°	446.5	446.0	447.8	448.7	449.6
137.5°	464.7	464.7	467.0	467.9	467.4
140°	482.4	483.4	484.3	485.6	486.1
142.5°	498.4	500.2	500.7	501.6	501.6
145°	514.8	516.2	516.2	516.6	517.5
147.5°	527.5	530.3	529.8	530.3	530.7
150°	541.7	543.5	543.0	543.0	543.5
152.5°	553.5	554.9	554.0	554.9	554.4
155°	564.4	564.9	563.5	565.4	564.0
157.5°	574.0	574.0	572.2	574.5	572.2
160°	582.2	580.8	580.4	583.1	580.4
162.5°	589.5	587.7	587.2	590.0	586.8
165°	595.4	593.1	593.1	596.8	592.7
167.5°	600.4	598.2	597.7	601.8	597.2
170°	604.5	601.8	602.3	605.9	601.3
172.5°	607.3	604.5	605.0	608.6	603.6
175°	609.1	606.4	606.8	610.9	605.4
177.5°	610.5	607.3	608.2	611.8	606.4
180°	609.1	609.1	609.1	609.1	609.1

(END OF REPORT)