

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983252

Luminaire Tested: S124IW-B770UB2750-4F0-XX-W2A-1_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983252
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B770UB2750-4F0-XX-W2A-1_3500K
Description: Define 4 Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2722.0 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983252

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P983252

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983252

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	63.9	2.3
100°-110°	191.4	7.0
110°-120°	325.1	11.9
120°-130°	428.8	15.8
130°-140°	481.6	17.7
140°-150°	473.3	17.4
150°-160°	398.1	14.6
160°-170°	264.9	9.7
170°-180°	92.8	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	580.4	21.3
90°-150°	1964.1	72.2
90°-180°	2720.0	99.9
0°-180°	2722.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	11	17	21	23	3
95°	46	52	58	60	60	49
105°	177	177	180	183	185	187
115°	330	330	329	328	328	326
125°	481	481	481	479	478	429
135°	621	626	626	624	622	480
145°	754	757	758	757	755	472
155°	864	864	864	867	864	398
165°	941	939	937	942	939	265
175°	979	975	974	980	974	93
180°	980	980	980	980	980	

TEST NUMBER: P983252

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.3	10.6	16.7	21.2	22.7
92.5°	19.7	29.6	33.4	35.6	36.4
95°	45.5	52.3	57.6	59.9	59.9
97.5°	72.8	78.8	84.9	87.9	87.9
100°	106.1	109.2	116.0	117.5	117.5
102.5°	141.0	141.8	147.8	150.1	150.9
105°	176.6	177.4	180.4	182.7	185.0
107.5°	213.8	214.6	215.3	218.3	217.6
110°	251.7	253.2	252.5	250.9	253.2

TEST NUMBER: P983252

CATALOG NUMBER: S124IW-B770UB2750-4F0-XX-W2A-1_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.1	291.1	289.6	289.6	289.6
115°	330.5	330.5	329.0	328.3	327.5
117.5°	367.7	367.7	366.9	364.7	362.4
120°	404.8	407.9	405.6	401.8	403.3
122.5°	443.5	444.3	443.5	441.2	437.4
125°	481.4	481.4	480.7	479.1	477.6
127.5°	515.5	517.8	516.3	514.8	514.0
130°	551.9	554.2	554.2	552.7	549.7
132.5°	589.1	590.6	589.8	588.3	587.6
135°	620.9	625.5	625.5	623.9	621.7
137.5°	656.5	658.8	660.3	658.1	658.8
140°	692.2	693.7	693.7	692.9	692.2
142.5°	724.8	726.3	725.5	725.5	725.5
145°	754.3	757.4	758.1	757.4	755.1
147.5°	784.7	788.5	787.7	786.9	786.2
150°	812.0	815.0	815.0	815.0	814.2
152.5°	837.7	839.3	840.0	842.3	840.0
155°	864.3	864.3	863.5	866.6	863.5
157.5°	887.0	885.5	885.5	887.8	885.5
160°	906.7	906.0	905.2	907.5	903.7
162.5°	924.9	922.7	921.9	926.4	922.7
165°	940.9	938.6	937.1	941.6	938.6
167.5°	953.7	950.7	950.7	955.3	950.7
170°	964.4	960.6	961.3	965.9	960.6
172.5°	971.9	968.9	968.9	974.2	968.9
175°	978.8	975.0	974.2	979.5	974.2
177.5°	981.8	978.0	978.0	983.3	977.2
180°	980.3	980.3	980.3	980.3	980.3

(END OF REPORT)