

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P983249

Luminaire Tested: S124IW-B770UB27-4F0-XX-W2A

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P983249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124IW-B770UB27-4F0-XX-W2A
Description: Define 4 Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3099.0 lumens
Efficiency: N/A
Efficacy: 133.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 23.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P983249

CATALOG NUMBER: S124IW-B770UB27-4F0-XX-W2A

Luminous Intensity Polar Plot



TEST NUMBER: P983249

CATALOG NUMBER: S124IW-B770UB27-4F0-XX-W2A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P983249

CATALOG NUMBER: S124IW-B770UB27-4F0-XX-W2A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	33.2	1.1
100°-110°	218.8	7.1
110°-120°	417.8	13.5
120°-130°	530.4	17.1
130°-140°	567.4	18.3
140°-150°	530.5	17.1
150°-160°	427.8	13.8
160°-170°	275.9	8.9
170°-180°	95.1	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	669.8	21.6
90°-150°	2298.1	74.2
90°-180°	3097.0	99.9
0°-180°	3099.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	2	10	16	21	22	2
95°	41	16	16	21	22	51
105°	225	230	234	240	213	236
115°	421	423	422	424	424	414
125°	591	594	593	595	596	528
135°	734	733	736	737	739	565
145°	846	848	848	849	850	529
155°	928	928	926	929	927	428
165°	978	975	975	981	974	276
175°	1001	996	997	1004	995	95
180°	1001	1001	1001	1001	1001	

TEST NUMBER: P983249

CATALOG NUMBER: S124IW-B770UB27-4F0-XX-W2A

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	2.2	10.5	16.5	21.0	22.5
92.5°	11.2	9.7	15.7	20.2	20.2
95°	41.2	15.7	16.5	21.0	21.7
97.5°	78.6	95.1	16.5	20.2	21.0
100°	122.8	136.2	32.9	20.2	21.0
102.5°	172.2	181.2	190.1	21.7	21.7
105°	225.3	229.8	233.6	240.3	213.3
107.5°	274.0	276.2	281.5	285.2	288.2
110°	323.4	325.6	330.1	331.6	333.9

TEST NUMBER: P983249

CATALOG NUMBER: S124IW-B770UB27-4F0-XX-W2A

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	375.8	377.3	376.5	379.5
115°	420.7	422.9	422.2	423.7	423.7
117.5°	464.9	467.9	470.1	469.4	469.4
120°	509.8	512.8	512.0	513.5	512.0
122.5°	551.7	553.2	554.7	555.4	553.9
125°	591.4	594.4	592.9	595.1	595.9
127.5°	629.5	630.3	634.0	633.3	632.5
130°	666.2	667.0	669.2	670.0	670.0
132.5°	699.9	701.4	704.4	705.2	704.4
135°	733.6	732.8	735.8	737.3	738.8
137.5°	763.5	763.5	767.3	768.8	768.0
140°	792.7	794.2	795.7	798.0	798.7
142.5°	818.9	821.9	822.7	824.2	824.2
145°	845.9	848.1	848.1	848.9	850.4
147.5°	866.8	871.3	870.6	871.3	872.1
150°	890.0	893.0	892.3	892.3	893.0
152.5°	909.5	911.8	910.3	911.8	911.0
155°	927.5	928.2	926.0	929.0	926.7
157.5°	943.2	943.2	940.2	943.9	940.2
160°	956.7	954.4	953.7	958.2	953.7
162.5°	968.6	965.7	964.9	969.4	964.2
165°	978.4	974.6	974.6	980.6	973.9
167.5°	986.6	982.9	982.1	988.9	981.4
170°	993.3	988.9	989.6	995.6	988.1
172.5°	997.8	993.3	994.1	1000.1	991.9
175°	1000.8	996.3	997.1	1003.8	994.8
177.5°	1003.1	997.8	999.3	1005.3	996.3
180°	1000.8	1000.8	1000.8	1000.8	1000.8

(END OF REPORT)