

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033832

Luminaire Tested: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033832
REPORT IS A COMBINATION OF REPORTS P999845 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A
Description: Define 4 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8602.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.27 / 1.38
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	56	56	50
1	98	94	90	87	91	87	84	81	74	72	70	62	60	59	51	50	49	49	49	43
2	90	83	77	72	83	77	72	67	65	62	58	55	52	50	45	43	42	42	42	37
3	82	73	66	60	76	68	62	57	58	53	50	49	45	43	40	38	36	36	36	32
4	75	65	57	51	70	60	54	48	52	47	43	44	40	37	36	34	31	31	31	28
5	69	58	50	44	64	54	47	42	47	41	37	39	35	32	33	30	28	28	28	24
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24	24	24	22
7	59	47	39	34	55	44	37	32	38	33	29	33	28	25	27	24	22	22	22	19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	23	25	22	20	20	20	17
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	18	18	16
10	48	36	29	24	44	34	27	23	30	24	21	26	21	18	22	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13968	13968	13968	13968
5°	13968	15783	13991	12063
10°	13894	18194	13882	10491
15°	13728	20477	13728	8783
20°	13555	22202	13484	7734
25°	13343	22295	13282	6986
30°	13119	18959	13016	6470
35°	12802	14305	12639	6087
40°	12448	10367	12204	5786
45°	11864	7879	11569	5522
50°	11171	6368	10865	5133
55°	10420	5273	10080	4615
60°	9667	4458	9234	3839
65°	8721	3632	8442	3051
70°	7853	2946	7483	2478
75°	6882	2122	6403	1816
80°	5676	1406	5166	1335
85°	4119	723	3413	723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 17486 cd/sqm

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.9	1.9
10°-20°	500.9	5.8
20°-30°	784.6	9.1
30°-40°	871.3	10.1
40°-50°	772.0	9.0
50°-60°	601.7	7.0
60°-70°	393.6	4.6
70°-80°	193.1	2.2
80°-90°	49.9	0.6
90°-100°	45.8	0.5
100°-110°	301.6	3.5
110°-120°	575.9	6.7
120°-130°	731.1	8.5
130°-140°	782.1	9.1
140°-150°	731.3	8.5
150°-160°	589.8	6.9
160°-170°	380.4	4.4
170°-180°	131.1	1.5
0°-30°	1451.3	16.9
0°-40°	2322.6	27.0
0°-60°	3696.3	43.0
0°-90°	4332.8	50.4
90°-120°	923.3	10.7
90°-150°	3167.9	36.8
90°-180°	4269.0	49.6
0°-180°	8602.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1713	1713	1713	1713	1713	
5°	1710	1979	1713	1513	1710	162
15°	1637	2622	1637	1125	1637	462
25°	1500	2828	1493	886	1500	691
35°	1308	1742	1292	741	1308	818
45°	1054	890	1028	624	1054	813
55°	759	531	734	465	759	679
65°	476	311	461	261	476	475
75°	239	144	222	123	239	253
85°	57	34	47	34	57	64
90°	3	31	3	31	3	7
95°	57	30	57	30	57	70
105°	311	294	311	294	311	325
115°	580	584	580	584	580	571
125°	815	821	815	821	815	728
135°	1011	1018	1011	1018	1011	779
145°	1166	1172	1166	1172	1166	729
155°	1278	1278	1278	1278	1278	590
165°	1349	1342	1349	1342	1349	381
175°	1380	1371	1380	1371	1380	131
180°	1380	1380	1380	1380	1380	

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1715.7	1730.8	1739.1	1746.0	1759.8	1765.3	1776.4	1779.1	1790.2	1788.8	1784.7
5°	1710.1	1736.4	1755.7	1776.4	1801.2	1815.0	1830.2	1852.3	1863.3	1878.5	1888.2
7.5°	1700.5	1736.4	1768.1	1799.9	1839.9	1862.0	1881.3	1915.8	1944.8	1969.6	1997.2
10°	1685.3	1730.8	1777.8	1820.6	1875.8	1902.0	1931.0	1982.0	2022.1	2056.6	2100.7
12.5°	1661.8	1725.3	1777.8	1835.7	1906.1	1942.0	1980.7	2041.4	2088.3	2144.9	2200.1
15°	1637.0	1707.4	1776.4	1852.3	1932.4	1973.8	2012.4	2093.8	2165.6	2230.5	2291.2
17.5°	1609.4	1686.7	1762.6	1846.8	1943.4	1994.5	2040.0	2138.0	2216.7	2300.9	2361.6
20°	1576.3	1660.4	1747.4	1841.3	1950.3	2006.9	2058.0	2169.8	2256.7	2347.8	2423.7
22.5°	1540.4	1631.5	1726.7	1828.8	1942.0	2004.1	2063.5	2183.6	2284.3	2368.5	2470.7
25°	1500.3	1597.0	1695.0	1802.6	1929.6	1997.2	2058.0	2176.7	2284.3	2394.7	2494.1
27.5°	1458.9	1558.3	1660.4	1773.6	1903.4	1969.6	2038.6	2153.2	2278.8	2398.9	2499.6
30°	1413.4	1510.0	1617.7	1725.3	1863.3	1929.6	2000.0	2124.2	2260.9	2380.9	2490.0
32.5°	1363.7	1463.1	1565.2	1677.0	1812.3	1884.0	1948.9	2089.7	2229.1	2347.8	2450.0
35°	1308.5	1402.3	1499.0	1613.5	1747.4	1812.3	1889.6	2035.9	2176.7	2302.3	2368.5
37.5°	1249.1	1338.8	1428.6	1541.7	1670.1	1748.8	1824.7	1972.4	2121.5	2205.6	2240.2
40°	1193.9	1272.6	1351.3	1460.3	1590.1	1671.5	1748.8	1902.0	2033.1	2098.0	2071.8
42.5°	1123.5	1205.0	1275.4	1376.1	1507.2	1583.2	1661.8	1820.6	1926.8	1953.1	1888.2
45°	1054.5	1122.1	1189.8	1287.8	1425.8	1490.7	1574.9	1722.6	1810.9	1787.4	1692.2
47.5°	986.9	1042.1	1105.6	1200.8	1325.0	1402.3	1481.0	1609.4	1671.5	1638.4	1505.9
50°	906.8	962.0	1028.3	1111.1	1231.2	1305.7	1367.8	1486.5	1533.5	1452.0	1291.9
52.5°	830.9	879.2	935.8	1013.1	1127.7	1195.3	1262.9	1365.1	1380.3	1286.4	1118.0
55°	759.1	797.8	857.1	919.2	1024.1	1095.9	1142.9	1229.8	1225.7	1108.3	963.4
57.5°	684.6	720.5	760.5	825.4	924.8	978.6	1029.7	1105.6	1065.6	966.2	822.6
60°	618.4	639.1	679.1	741.2	825.4	872.3	912.3	953.8	919.2	811.6	701.2
62.5°	545.2	568.7	597.7	647.3	721.9	766.0	795.0	813.0	777.1	694.3	593.5
65°	476.2	496.9	527.3	571.4	628.0	661.1	676.3	688.7	669.4	575.6	495.5
67.5°	414.1	427.9	455.5	484.5	545.2	553.5	574.2	579.7	541.1	469.3	405.8
70°	352.0	365.8	378.2	412.7	440.3	455.5	459.6	459.6	421.0	374.0	321.6
72.5°	294.0	302.3	314.7	338.2	353.3	364.4	369.9	363.0	327.1	288.5	249.8
75°	238.8	242.9	254.0	269.1	281.6	277.4	276.1	267.8	241.5	213.9	191.9
77.5°	183.6	186.3	198.8	202.9	202.9	207.0	201.5	193.2	171.2	150.4	140.8
80°	138.0	142.2	143.5	146.3	143.5	143.5	139.4	125.6	114.6	104.9	98.0
82.5°	95.2	98.0	99.4	95.2	98.0	93.9	87.0	77.3	70.4	69.0	66.3
85°	56.6	58.0	56.6	56.6	52.4	51.1	45.5	44.2	41.4	41.4	40.0
87.5°	27.6	26.2	23.5	20.7	20.7	19.3	20.7	17.9	20.7	19.3	17.9
90°	3.1	5.6	8.1	10.6	13.1	14.4	15.3	17.2	19.0	20.9	22.7
92.5°	15.5	15.0	14.6	14.1	13.6	13.4	14.3	16.2	18.0	19.9	21.7
95°	56.8	49.0	41.2	33.4	25.6	21.7	21.8	22.0	22.3	22.5	22.7
97.5°	108.4	113.4	118.5	123.5	128.6	131.1	119.1	95.0	70.9	46.8	22.7
100°	169.2	173.3	177.5	181.6	185.7	187.8	172.0	140.3	108.7	77.0	45.4
102.5°	237.3	240.1	242.8	245.6	248.3	249.7	251.1	253.8	256.6	259.3	262.1
105°	310.6	312.0	313.4	314.7	316.1	316.8	317.4	318.5	319.7	320.8	322.0
107.5°	377.7	378.4	379.1	379.8	380.5	380.8	381.6	383.2	384.8	386.4	388.0
110°	445.8	446.5	447.2	447.9	448.6	448.9	449.6	451.0	452.3	453.7	455.1

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	511.8	513.2	514.6	515.9	517.3	518.0	518.2	518.7	519.2	519.6	520.1
115°	579.9	580.6	581.3	582.0	582.7	583.0	582.9	582.7	582.4	582.2	582.0
117.5°	640.8	641.7	642.6	643.5	644.4	644.9	645.2	645.9	646.6	647.3	648.0
120°	702.7	703.6	704.6	705.5	706.4	706.9	706.8	706.5	706.3	706.0	705.8
122.5°	760.5	761.0	761.4	761.9	762.4	762.6	762.8	763.3	763.7	764.2	764.6
125°	815.2	816.1	817.0	817.9	818.8	819.3	819.1	818.6	818.2	817.7	817.3
127.5°	867.8	868.0	868.3	868.5	868.8	868.9	869.5	870.6	871.7	872.9	874.0
130°	918.4	918.6	918.8	919.1	919.3	919.4	919.7	920.4	921.1	921.8	922.5
132.5°	964.8	965.3	965.7	966.2	966.7	966.9	967.4	968.3	969.2	970.1	971.0
135°	1011.3	1011.1	1010.8	1010.6	1010.3	1010.2	1010.7	1011.6	1012.5	1013.5	1014.4
137.5°	1052.5	1052.5	1052.5	1052.5	1052.5	1052.5	1053.1	1054.2	1055.4	1056.5	1057.7
140°	1092.8	1093.3	1093.7	1094.2	1094.7	1094.9	1095.1	1095.6	1096.0	1096.5	1096.9
142.5°	1128.9	1129.8	1130.7	1131.6	1132.5	1133.0	1133.1	1133.4	1133.6	1133.9	1134.1
145°	1166.1	1166.8	1167.4	1168.1	1168.8	1169.1	1169.1	1169.1	1169.1	1169.1	1169.1
147.5°	1194.9	1196.3	1197.7	1199.0	1200.4	1201.1	1201.0	1200.8	1200.5	1200.3	1200.1
150°	1226.9	1227.8	1228.8	1229.7	1230.6	1231.1	1231.0	1230.7	1230.5	1230.2	1230.0
152.5°	1253.8	1254.5	1255.2	1255.9	1256.6	1256.9	1256.7	1256.2	1255.7	1255.3	1254.8
155°	1278.5	1278.7	1279.0	1279.2	1279.5	1279.6	1279.3	1278.6	1277.9	1277.2	1276.5
157.5°	1300.2	1300.2	1300.2	1300.2	1300.2	1300.2	1299.7	1298.8	1297.9	1297.0	1296.1
160°	1318.8	1318.1	1317.4	1316.7	1316.0	1315.7	1315.6	1315.3	1315.1	1314.8	1314.6
162.5°	1335.3	1334.4	1333.5	1332.6	1331.7	1331.2	1331.1	1330.8	1330.6	1330.3	1330.1
165°	1348.7	1347.5	1346.4	1345.2	1344.1	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5
167.5°	1360.1	1358.9	1357.8	1356.6	1355.5	1354.9	1354.8	1354.6	1354.3	1354.1	1353.9
170°	1369.3	1367.9	1366.5	1365.2	1363.8	1363.1	1363.2	1363.5	1363.7	1364.0	1364.2
172.5°	1375.5	1374.1	1372.7	1371.4	1370.0	1369.3	1369.4	1369.7	1369.9	1370.2	1370.4
175°	1379.7	1378.3	1376.9	1375.6	1374.2	1373.5	1373.6	1373.8	1374.1	1374.3	1374.5
177.5°	1382.8	1381.2	1379.6	1377.9	1376.3	1375.5	1375.7	1376.2	1376.7	1377.1	1377.6
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1795.7	1810.9	1812.3	1826.1	1821.9	1815.0	1827.5	1819.2	1835.7	1830.2	1837.1
5°	1900.6	1921.3	1939.3	1950.3	1969.6	1965.5	1986.2	1979.3	1994.5	1979.3	1998.6
7.5°	2023.5	2058.0	2075.9	2104.9	2113.2	2114.6	2139.4	2144.9	2154.6	2144.9	2156.0
10°	2143.5	2184.9	2226.4	2249.8	2265.0	2285.7	2307.8	2317.4	2324.3	2314.7	2321.6
12.5°	2252.6	2317.4	2363.0	2409.9	2421.0	2438.9	2462.4	2459.6	2487.2	2481.7	2494.1
15°	2353.3	2425.1	2480.3	2517.6	2547.9	2563.1	2607.3	2610.1	2608.7	2622.5	2614.2
17.5°	2443.1	2503.8	2582.5	2630.8	2668.0	2668.0	2692.9	2743.9	2739.8	2738.4	2746.7
20°	2516.2	2585.2	2658.4	2739.8	2770.2	2775.7	2810.2	2836.4	2840.6	2840.6	2840.6
22.5°	2571.4	2652.8	2731.5	2789.5	2813.0	2832.3	2862.6	2879.2	2884.7	2882.0	2884.7
25°	2599.0	2676.3	2756.4	2808.8	2822.6	2833.7	2836.4	2846.1	2844.7	2828.1	2837.8
27.5°	2604.5	2679.1	2731.5	2745.3	2738.4	2731.5	2687.4	2691.5	2679.1	2654.2	2663.9
30°	2579.7	2619.7	2618.3	2575.6	2563.1	2534.1	2494.1	2434.8	2386.5	2365.8	2372.7
32.5°	2490.0	2490.0	2440.3	2343.7	2300.9	2248.4	2176.7	2122.8	2059.3	2045.5	2071.8
35°	2365.8	2295.4	2204.3	2077.3	2012.4	1973.8	1849.5	1810.9	1757.1	1741.9	1754.3
37.5°	2172.5	2055.2	1922.7	1804.0	1748.8	1679.8	1570.7	1515.5	1476.9	1450.6	1463.1
40°	1955.8	1813.7	1675.6	1529.3	1468.6	1412.0	1330.6	1280.9	1218.8	1221.5	1225.7
42.5°	1748.8	1581.8	1427.2	1291.9	1233.9	1187.0	1130.4	1069.7	1047.6	1040.7	1033.8
45°	1529.3	1351.3	1206.3	1105.6	1053.1	1009.0	956.5	922.0	895.8	890.3	897.2
47.5°	1322.3	1171.8	1033.8	940.0	897.2	875.1	833.7	801.9	785.4	771.6	779.8
50°	1134.6	993.8	883.4	804.7	774.3	759.1	720.5	703.9	687.4	683.2	681.8
52.5°	980.0	859.9	764.7	701.2	677.7	669.4	640.4	617.0	603.2	607.3	610.1
55°	839.2	737.1	662.5	611.5	592.1	582.5	561.8	545.2	535.5	531.4	534.2
57.5°	715.0	626.6	572.8	531.4	516.2	512.1	490.0	484.5	477.6	473.4	473.4
60°	601.8	539.7	490.0	466.5	450.0	445.8	429.3	422.4	421.0	416.8	414.1
62.5°	506.6	455.5	421.0	396.1	389.2	387.9	376.8	368.5	364.4	361.6	361.6
65°	423.7	386.5	357.5	339.5	334.0	331.3	318.8	316.1	313.3	310.6	309.2
67.5°	353.3	320.2	299.5	287.1	280.2	281.6	274.7	269.1	269.1	267.8	266.4
70°	285.7	265.0	247.1	240.2	237.4	234.6	231.9	227.7	226.4	226.4	226.4
72.5°	225.0	211.2	201.5	197.4	194.6	191.9	189.1	189.1	189.1	187.7	187.7
75°	172.5	167.0	160.1	156.0	156.0	158.7	154.6	150.4	146.3	143.5	144.9
77.5°	129.7	127.0	122.8	115.9	117.3	114.6	114.6	111.8	113.2	113.2	110.4
80°	95.2	91.1	89.7	85.6	87.0	85.6	84.2	84.2	81.4	81.4	81.4
82.5°	66.3	62.1	62.1	60.7	59.4	59.4	58.0	58.0	59.4	56.6	56.6
85°	40.0	38.6	38.6	35.9	35.9	35.9	35.9	37.3	35.9	34.5	34.5
87.5°	17.9	19.3	17.9	16.6	16.6	16.6	15.2	15.2	13.8	15.2	15.2
90°	24.1	25.5	26.8	28.2	28.9	29.1	29.6	30.1	30.5	31.0	30.5
92.5°	23.1	24.5	25.8	27.2	27.9	27.9	27.9	27.9	27.9	27.9	27.9
95°	24.1	25.5	26.8	28.2	28.9	29.0	29.2	29.5	29.7	29.9	29.7
97.5°	23.9	25.0	26.2	27.3	27.9	28.0	28.2	28.5	28.7	28.9	28.7
100°	41.5	37.6	33.7	29.8	27.9	28.0	28.2	28.5	28.7	28.9	28.7
102.5°	210.5	158.9	107.3	55.7	29.9	29.9	29.9	29.9	29.9	29.9	29.9
105°	324.0	326.1	328.1	330.2	331.2	327.1	318.8	310.6	302.3	294.1	302.3
107.5°	389.2	390.3	391.5	392.6	393.2	393.7	394.6	395.5	396.4	397.3	396.4
110°	455.5	456.0	456.4	456.9	457.1	457.4	458.1	458.8	459.5	460.2	459.5

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	519.9	519.6	519.4	519.1	519.0	519.5	520.4	521.3	522.3	523.2	522.3
115°	582.5	582.9	583.4	583.9	584.1	584.1	584.1	584.1	584.1	584.1	584.1
117.5°	647.8	647.6	647.3	647.1	647.0	647.0	647.0	647.0	647.0	647.0	647.0
120°	706.3	706.7	707.2	707.7	707.9	707.7	707.2	706.7	706.3	705.8	706.3
122.5°	764.8	765.1	765.3	765.6	765.7	765.5	765.0	764.5	764.1	763.6	764.1
125°	818.0	818.7	819.4	820.1	820.4	820.5	820.7	821.0	821.2	821.4	821.2
127.5°	873.8	873.6	873.3	873.1	873.0	872.9	872.7	872.4	872.2	872.0	872.2
130°	922.7	923.0	923.2	923.5	923.6	923.6	923.6	923.6	923.6	923.6	923.6
132.5°	971.2	971.5	971.7	972.0	972.1	972.0	971.7	971.5	971.2	971.0	971.2
135°	1014.8	1015.3	1015.7	1016.2	1016.4	1016.6	1017.1	1017.6	1018.0	1018.5	1018.0
137.5°	1058.2	1058.6	1059.1	1059.6	1059.8	1059.7	1059.4	1059.2	1058.9	1058.7	1058.9
140°	1097.6	1098.3	1099.0	1099.7	1100.0	1100.1	1100.3	1100.6	1100.8	1101.0	1100.8
142.5°	1134.5	1135.0	1135.4	1135.9	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
145°	1169.3	1169.6	1169.8	1170.1	1170.2	1170.4	1170.9	1171.3	1171.8	1172.2	1171.8
147.5°	1200.3	1200.5	1200.8	1201.0	1201.1	1201.2	1201.5	1201.7	1202.0	1202.2	1202.0
150°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.1	1230.4	1230.6	1230.9	1231.1	1230.9
152.5°	1255.3	1255.7	1256.2	1256.7	1256.9	1256.8	1256.5	1256.3	1256.0	1255.8	1256.0
155°	1277.4	1278.3	1279.2	1280.1	1280.6	1280.3	1279.6	1278.9	1278.2	1277.5	1278.2
157.5°	1297.2	1298.4	1299.5	1300.6	1301.2	1300.6	1299.5	1298.4	1297.2	1296.1	1297.2
160°	1316.0	1317.4	1318.7	1320.1	1320.8	1320.1	1318.7	1317.4	1316.0	1314.6	1316.0
162.5°	1331.5	1332.9	1334.2	1335.6	1336.3	1335.5	1333.9	1332.3	1330.7	1329.1	1330.7
165°	1345.3	1347.2	1349.0	1350.9	1351.8	1350.8	1348.7	1346.6	1344.6	1342.5	1344.6
167.5°	1355.9	1358.0	1360.0	1362.1	1363.1	1362.0	1359.7	1357.4	1355.1	1352.8	1355.1
170°	1366.0	1367.8	1369.7	1371.5	1372.4	1371.3	1369.0	1366.7	1364.4	1362.1	1364.4
172.5°	1372.2	1374.0	1375.9	1377.7	1378.6	1377.3	1374.8	1372.3	1369.8	1367.3	1369.8
175°	1376.6	1378.6	1380.7	1382.8	1383.8	1382.4	1379.7	1376.9	1374.2	1371.4	1374.2
177.5°	1379.4	1381.3	1383.1	1385.0	1385.9	1384.5	1381.8	1379.0	1376.3	1373.5	1376.3
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1841.3	1831.6	1830.2	1830.2	1815.0	1823.3	1806.8	1788.8	1780.5	1780.5	1765.3
5°	1994.5	1984.8	1975.1	1960.0	1960.0	1951.7	1925.5	1899.2	1879.9	1863.3	1845.4
7.5°	2151.8	2142.2	2114.6	2099.4	2107.6	2091.1	2056.6	2012.4	1979.3	1953.1	1915.8
10°	2323.0	2296.7	2282.9	2274.7	2245.7	2227.7	2187.7	2122.8	2081.4	2046.9	1998.6
12.5°	2462.4	2470.7	2418.2	2422.3	2393.4	2368.5	2306.4	2244.3	2182.2	2133.9	2062.1
15°	2612.8	2588.0	2556.2	2531.4	2521.7	2491.4	2438.9	2356.1	2288.5	2212.5	2131.1
17.5°	2731.5	2712.2	2681.8	2658.4	2637.7	2564.5	2520.3	2447.2	2354.7	2280.2	2180.8
20°	2832.3	2814.3	2771.6	2756.4	2719.1	2666.7	2603.2	2490.0	2407.2	2325.7	2229.1
22.5°	2875.1	2857.1	2819.9	2800.5	2777.1	2726.0	2665.3	2557.6	2455.5	2353.3	2251.2
25°	2839.2	2839.2	2821.2	2814.3	2793.6	2748.1	2686.0	2594.9	2485.8	2375.4	2254.0
27.5°	2665.3	2699.8	2712.2	2719.1	2719.1	2720.5	2677.7	2589.4	2483.1	2375.4	2248.4
30°	2414.1	2472.0	2523.1	2538.3	2564.5	2593.5	2611.4	2568.7	2473.4	2360.2	2233.3
32.5°	2098.0	2172.5	2267.8	2291.2	2327.1	2414.1	2462.4	2480.3	2427.9	2328.5	2193.2
35°	1783.3	1877.1	1935.1	2006.9	2040.0	2168.4	2276.0	2340.9	2328.5	2269.1	2146.3
37.5°	1508.6	1562.4	1632.8	1708.8	1775.0	1897.9	2031.7	2157.3	2208.4	2179.4	2086.9
40°	1245.0	1308.5	1392.7	1454.8	1500.3	1623.2	1788.8	1925.5	2037.3	2055.2	1998.6
42.5°	1058.7	1122.1	1173.2	1240.8	1276.7	1395.4	1541.7	1712.9	1845.4	1915.8	1890.9
45°	915.1	953.8	995.2	1033.8	1078.0	1182.9	1318.1	1505.9	1654.9	1754.3	1764.0
47.5°	789.5	824.0	859.9	895.8	920.6	1002.1	1126.3	1279.5	1442.4	1579.0	1632.8
50°	701.2	717.7	744.0	764.7	793.6	864.0	963.4	1095.9	1268.5	1416.1	1486.5
52.5°	614.2	634.9	655.6	673.6	692.9	742.6	833.7	948.2	1097.3	1249.1	1336.1
55°	541.1	557.6	576.9	589.4	600.4	644.6	713.6	801.9	930.3	1073.8	1181.5
57.5°	481.7	488.6	505.2	512.1	524.5	560.4	610.1	688.7	792.3	931.7	1020.0
60°	416.8	430.6	443.1	448.6	458.2	483.1	517.6	590.7	680.5	782.6	883.4
62.5°	364.4	369.9	379.6	386.5	393.4	419.6	448.6	503.8	571.4	657.0	749.5
65°	316.1	318.8	324.4	334.0	338.2	357.5	374.0	414.1	477.6	542.4	634.9
67.5°	266.4	269.1	276.1	281.6	285.7	298.1	316.1	345.1	379.6	451.3	502.4
70°	227.7	227.7	231.9	234.6	238.8	244.3	254.0	276.1	307.8	353.3	400.3
72.5°	190.5	190.5	190.5	194.6	194.6	198.8	204.3	219.5	241.5	277.4	307.8
75°	147.7	149.1	151.8	151.8	153.2	158.7	162.9	167.0	178.1	201.5	229.1
77.5°	111.8	114.6	115.9	113.2	115.9	115.9	121.5	127.0	132.5	139.4	160.1
80°	82.8	84.2	81.4	82.8	82.8	85.6	88.3	87.0	89.7	98.0	103.5
82.5°	55.2	56.6	56.6	56.6	56.6	60.7	60.7	59.4	60.7	62.1	63.5
85°	34.5	33.1	33.1	34.5	33.1	33.1	34.5	35.9	34.5	35.9	37.3
87.5°	15.2	15.2	15.2	15.2	13.8	13.8	15.2	13.8	15.2	13.8	12.4
90°	30.1	29.6	29.1	28.9	28.2	26.8	25.5	24.1	22.7	20.9	19.0
92.5°	27.9	27.9	27.9	27.9	27.2	25.8	24.5	23.1	21.7	19.9	18.0
95°	29.5	29.2	29.0	28.9	28.2	26.8	25.5	24.1	22.7	22.5	22.3
97.5°	28.5	28.2	28.0	27.9	27.3	26.2	25.0	23.9	22.7	46.8	70.9
100°	28.5	28.2	28.0	27.9	29.8	33.7	37.6	41.5	45.4	77.0	108.7
102.5°	29.9	29.9	29.9	29.9	55.7	107.3	158.9	210.5	262.1	259.3	256.6
105°	310.6	318.8	327.1	331.2	330.2	328.1	326.1	324.0	322.0	320.8	319.7
107.5°	395.5	394.6	393.7	393.2	392.6	391.5	390.3	389.2	388.0	386.4	384.8
110°	458.8	458.1	457.4	457.1	456.9	456.4	456.0	455.5	455.1	453.7	452.3

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	521.3	520.4	519.5	519.0	519.1	519.4	519.6	519.9	520.1	519.6	519.2
115°	584.1	584.1	584.1	584.1	583.9	583.4	582.9	582.5	582.0	582.2	582.4
117.5°	647.0	647.0	647.0	647.0	647.1	647.3	647.6	647.8	648.0	647.3	646.6
120°	706.7	707.2	707.7	707.9	707.7	707.2	706.7	706.3	705.8	706.0	706.3
122.5°	764.5	765.0	765.5	765.7	765.6	765.3	765.1	764.8	764.6	764.2	763.7
125°	821.0	820.7	820.5	820.4	820.1	819.4	818.7	818.0	817.3	817.7	818.2
127.5°	872.4	872.7	872.9	873.0	873.1	873.3	873.6	873.8	874.0	872.9	871.7
130°	923.6	923.6	923.6	923.6	923.5	923.2	923.0	922.7	922.5	921.8	921.1
132.5°	971.5	971.7	972.0	972.1	972.0	971.7	971.5	971.2	971.0	970.1	969.2
135°	1017.6	1017.1	1016.6	1016.4	1016.2	1015.7	1015.3	1014.8	1014.4	1013.5	1012.5
137.5°	1059.2	1059.4	1059.7	1059.8	1059.6	1059.1	1058.6	1058.2	1057.7	1056.5	1055.4
140°	1100.6	1100.3	1100.1	1100.0	1099.7	1099.0	1098.3	1097.6	1096.9	1096.5	1096.0
142.5°	1136.1	1136.1	1136.1	1136.1	1135.9	1135.4	1135.0	1134.5	1134.1	1133.9	1133.6
145°	1171.3	1170.9	1170.4	1170.2	1170.1	1169.8	1169.6	1169.3	1169.1	1169.1	1169.1
147.5°	1201.7	1201.5	1201.2	1201.1	1201.0	1200.8	1200.5	1200.3	1200.1	1200.3	1200.5
150°	1230.6	1230.4	1230.1	1230.0	1230.0	1230.0	1230.0	1230.0	1230.0	1230.2	1230.5
152.5°	1256.3	1256.5	1256.8	1256.9	1256.7	1256.2	1255.7	1255.3	1254.8	1255.3	1255.7
155°	1278.9	1279.6	1280.3	1280.6	1280.1	1279.2	1278.3	1277.4	1276.5	1277.2	1277.9
157.5°	1298.4	1299.5	1300.6	1301.2	1300.6	1299.5	1298.4	1297.2	1296.1	1297.0	1297.9
160°	1317.4	1318.7	1320.1	1320.8	1320.1	1318.7	1317.4	1316.0	1314.6	1314.8	1315.1
162.5°	1332.3	1333.9	1335.5	1336.3	1335.6	1334.2	1332.9	1331.5	1330.1	1330.3	1330.6
165°	1346.6	1348.7	1350.8	1351.8	1350.9	1349.0	1347.2	1345.3	1343.5	1343.5	1343.5
167.5°	1357.4	1359.7	1362.0	1363.1	1362.1	1360.0	1358.0	1355.9	1353.9	1354.1	1354.3
170°	1366.7	1369.0	1371.3	1372.4	1371.5	1369.7	1367.8	1366.0	1364.2	1364.0	1363.7
172.5°	1372.3	1374.8	1377.3	1378.6	1377.7	1375.9	1374.0	1372.2	1370.4	1370.2	1369.9
175°	1376.9	1379.7	1382.4	1383.8	1382.8	1380.7	1378.6	1376.6	1374.5	1374.3	1374.1
177.5°	1379.0	1381.8	1384.5	1385.9	1385.0	1383.1	1381.3	1379.4	1377.6	1377.1	1376.7
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1757.1	1750.2	1746.0	1744.6	1732.2	1725.3	1721.2	1718.4	1714.3	1703.2	1693.6
5°	1823.3	1804.0	1794.3	1783.3	1764.0	1741.9	1723.9	1712.9	1699.1	1677.0	1656.3
7.5°	1885.4	1856.4	1837.1	1821.9	1788.8	1752.9	1723.9	1700.5	1674.2	1643.9	1614.9
10°	1950.3	1903.4	1878.5	1855.1	1806.8	1759.8	1718.4	1683.9	1646.6	1606.6	1574.9
12.5°	2001.4	1939.3	1911.7	1878.5	1819.2	1764.0	1711.5	1664.6	1616.3	1573.5	1527.9
15°	2060.7	1983.4	1951.7	1908.9	1827.5	1755.7	1688.1	1637.0	1587.3	1523.8	1475.5
17.5°	2095.2	2005.5	1960.0	1922.7	1834.4	1747.4	1668.7	1605.2	1547.3	1483.8	1432.7
20°	2129.7	2027.6	1976.5	1924.1	1819.2	1726.7	1643.9	1568.0	1507.2	1438.2	1385.8
22.5°	2140.8	2022.1	1968.2	1919.9	1809.5	1706.0	1610.8	1533.5	1463.1	1394.1	1334.7
25°	2140.8	2020.7	1957.2	1895.1	1779.1	1672.9	1577.6	1493.4	1414.8	1345.7	1286.4
27.5°	2118.7	1993.1	1926.8	1870.2	1750.2	1635.6	1537.6	1445.1	1369.2	1300.2	1232.6
30°	2091.1	1953.1	1886.8	1819.2	1703.2	1594.2	1487.9	1402.3	1322.3	1243.6	1182.9
32.5°	2056.6	1910.3	1837.1	1768.1	1645.3	1532.1	1434.1	1349.9	1274.0	1192.5	1124.9
35°	2006.9	1846.8	1765.3	1704.6	1585.9	1468.6	1374.7	1291.9	1218.8	1134.6	1061.4
37.5°	1943.4	1788.8	1706.0	1631.5	1508.6	1401.0	1312.6	1232.6	1160.8	1083.5	1002.1
40°	1868.9	1707.4	1635.6	1556.9	1427.2	1325.0	1242.2	1170.5	1098.7	1025.5	946.9
42.5°	1784.7	1624.6	1544.5	1468.6	1344.4	1243.6	1166.3	1101.4	1035.2	967.6	883.4
45°	1683.9	1533.5	1456.2	1384.4	1264.3	1160.8	1090.4	1028.3	971.7	902.7	828.2
47.5°	1570.7	1439.6	1360.9	1283.6	1166.3	1076.6	1007.6	955.1	906.8	837.8	770.2
50°	1460.3	1330.6	1267.1	1188.4	1080.7	996.5	926.2	882.0	844.7	777.1	716.4
52.5°	1320.9	1222.9	1162.2	1094.5	991.0	905.4	850.2	811.6	767.4	715.0	661.1
55°	1198.1	1107.0	1058.7	995.2	893.0	817.1	770.2	734.3	699.8	652.9	610.1
57.5°	1058.7	1002.1	953.8	898.5	797.8	732.9	691.5	661.1	629.4	590.7	556.2
60°	912.3	886.1	839.2	795.0	709.5	652.9	618.4	590.7	560.4	528.6	499.7
62.5°	782.6	767.4	739.8	705.3	625.3	576.9	542.4	521.7	499.7	470.7	443.1
65°	659.8	652.9	626.6	601.8	546.6	503.8	473.4	461.0	436.2	414.1	389.2
67.5°	550.7	542.4	527.3	516.2	469.3	429.3	414.1	397.5	376.8	360.2	339.5
70°	440.3	438.9	429.3	415.5	390.6	361.6	346.4	335.4	314.7	302.3	287.1
72.5°	342.3	349.2	340.9	335.4	318.8	298.1	284.3	277.4	260.9	251.2	240.2
75°	255.3	260.9	265.0	255.3	251.2	241.5	229.1	222.2	213.9	200.1	196.0
77.5°	173.9	186.3	186.3	189.1	190.5	185.0	175.3	169.8	160.1	157.3	151.8
80°	114.6	125.6	127.0	129.7	133.9	133.9	127.0	125.6	115.9	114.6	110.4
82.5°	66.3	75.9	81.4	85.6	84.2	89.7	84.2	82.8	77.3	77.3	74.5
85°	35.9	37.3	40.0	42.8	45.5	48.3	48.3	46.9	45.5	44.2	41.4
87.5°	13.8	13.8	15.2	13.8	15.2	17.9	19.3	19.3	17.9	16.6	13.8
90°	17.2	15.3	14.4	13.1	10.6	8.1	5.6	3.1	5.6	8.1	10.6
92.5°	16.2	14.3	13.4	13.6	14.1	14.6	15.0	15.5	15.0	14.6	14.1
95°	22.0	21.8	21.7	25.6	33.4	41.2	49.0	56.8	49.0	41.2	33.4
97.5°	95.0	119.1	131.1	128.6	123.5	118.5	113.4	108.4	113.4	118.5	123.5
100°	140.3	172.0	187.8	185.7	181.6	177.5	173.3	169.2	173.3	177.5	181.6
102.5°	253.8	251.1	249.7	248.3	245.6	242.8	240.1	237.3	240.1	242.8	245.6
105°	318.5	317.4	316.8	316.1	314.7	313.4	312.0	310.6	312.0	313.4	314.7
107.5°	383.2	381.6	380.8	380.5	379.8	379.1	378.4	377.7	378.4	379.1	379.8
110°	451.0	449.6	448.9	448.6	447.9	447.2	446.5	445.8	446.5	447.2	447.9

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	518.7	518.2	518.0	517.3	515.9	514.6	513.2	511.8	513.2	514.6	515.9
115°	582.7	582.9	583.0	582.7	582.0	581.3	580.6	579.9	580.6	581.3	582.0
117.5°	645.9	645.2	644.9	644.4	643.5	642.6	641.7	640.8	641.7	642.6	643.5
120°	706.5	706.8	706.9	706.4	705.5	704.6	703.6	702.7	703.6	704.6	705.5
122.5°	763.3	762.8	762.6	762.4	761.9	761.4	761.0	760.5	761.0	761.4	761.9
125°	818.6	819.1	819.3	818.8	817.9	817.0	816.1	815.2	816.1	817.0	817.9
127.5°	870.6	869.5	868.9	868.8	868.5	868.3	868.0	867.8	868.0	868.3	868.5
130°	920.4	919.7	919.4	919.3	919.1	918.8	918.6	918.4	918.6	918.8	919.1
132.5°	968.3	967.4	966.9	966.7	966.2	965.7	965.3	964.8	965.3	965.7	966.2
135°	1011.6	1010.7	1010.2	1010.3	1010.6	1010.8	1011.1	1011.3	1011.1	1010.8	1010.6
137.5°	1054.2	1053.1	1052.5	1052.5	1052.5	1052.5	1052.5	1052.5	1052.5	1052.5	1052.5
140°	1095.6	1095.1	1094.9	1094.7	1094.2	1093.7	1093.3	1092.8	1093.3	1093.7	1094.2
142.5°	1133.4	1133.1	1133.0	1132.5	1131.6	1130.7	1129.8	1128.9	1129.8	1130.7	1131.6
145°	1169.1	1169.1	1169.1	1168.8	1168.1	1167.4	1166.8	1166.1	1166.8	1167.4	1168.1
147.5°	1200.8	1201.0	1201.1	1200.4	1199.0	1197.7	1196.3	1194.9	1196.3	1197.7	1199.0
150°	1230.7	1231.0	1231.1	1230.6	1229.7	1228.8	1227.8	1226.9	1227.8	1228.8	1229.7
152.5°	1256.2	1256.7	1256.9	1256.6	1255.9	1255.2	1254.5	1253.8	1254.5	1255.2	1255.9
155°	1278.6	1279.3	1279.6	1279.5	1279.2	1279.0	1278.7	1278.5	1278.7	1279.0	1279.2
157.5°	1298.8	1299.7	1300.2	1300.2	1300.2	1300.2	1300.2	1300.2	1300.2	1300.2	1300.2
160°	1315.3	1315.6	1315.7	1316.0	1316.7	1317.4	1318.1	1318.8	1318.1	1317.4	1316.7
162.5°	1330.8	1331.1	1331.2	1331.7	1332.6	1333.5	1334.4	1335.3	1334.4	1333.5	1332.6
165°	1343.5	1343.5	1343.5	1344.1	1345.2	1346.4	1347.5	1348.7	1347.5	1346.4	1345.2
167.5°	1354.6	1354.8	1354.9	1355.5	1356.6	1357.8	1358.9	1360.1	1358.9	1357.8	1356.6
170°	1363.5	1363.2	1363.1	1363.8	1365.2	1366.5	1367.9	1369.3	1367.9	1366.5	1365.2
172.5°	1369.7	1369.4	1369.3	1370.0	1371.4	1372.7	1374.1	1375.5	1374.1	1372.7	1371.4
175°	1373.8	1373.6	1373.5	1374.2	1375.6	1376.9	1378.3	1379.7	1378.3	1376.9	1375.6
177.5°	1376.2	1375.7	1375.5	1376.3	1377.9	1379.6	1381.2	1382.8	1381.2	1379.6	1377.9
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1685.3	1682.5	1679.8	1668.7	1659.1	1642.5	1628.7	1623.2	1621.8	1623.2	1619.0
5°	1637.0	1635.6	1625.9	1606.6	1588.7	1569.3	1555.5	1541.7	1533.5	1533.5	1523.8
7.5°	1591.4	1581.8	1573.5	1548.6	1527.9	1501.7	1481.0	1468.6	1461.7	1446.5	1446.5
10°	1543.1	1529.3	1518.3	1494.8	1464.5	1438.2	1412.0	1396.8	1384.4	1373.4	1369.2
12.5°	1494.8	1483.8	1463.1	1438.2	1407.9	1374.7	1347.1	1336.1	1307.1	1283.6	1285.0
15°	1449.3	1424.4	1414.8	1378.9	1343.0	1311.2	1271.2	1239.5	1216.0	1200.8	1181.5
17.5°	1398.2	1373.4	1355.4	1325.0	1278.1	1228.4	1189.8	1147.0	1123.5	1097.3	1084.9
20°	1341.6	1320.9	1307.1	1258.8	1202.2	1142.9	1100.1	1073.8	1047.6	1028.3	1017.2
22.5°	1293.3	1267.1	1250.5	1185.6	1123.5	1064.2	1031.1	1009.0	986.9	970.3	964.8
25°	1231.2	1216.0	1176.0	1119.4	1043.5	1003.4	974.5	945.5	933.1	922.0	909.6
27.5°	1180.1	1142.9	1115.2	1040.7	993.8	948.2	919.2	897.2	882.0	870.9	861.3
30°	1116.6	1082.1	1043.5	981.4	938.6	895.8	869.6	851.6	835.1	828.2	819.9
32.5°	1050.4	1018.6	981.4	931.7	879.2	846.1	825.4	806.1	795.0	788.1	778.5
35°	991.0	951.0	926.2	879.2	836.4	799.2	779.8	763.3	750.9	748.1	746.7
37.5°	927.5	897.2	873.7	825.4	789.5	757.8	739.8	721.9	715.0	713.6	708.1
40°	872.3	846.1	824.0	778.5	739.8	710.8	697.0	686.0	679.1	679.1	677.7
42.5°	824.0	796.4	774.3	732.9	698.4	672.2	657.0	646.0	643.2	644.6	643.2
45°	770.2	746.7	724.6	681.8	652.9	633.5	617.0	611.5	607.3	608.7	610.1
47.5°	719.1	699.8	677.7	643.2	610.1	589.4	579.7	574.2	574.2	574.2	576.9
50°	673.6	651.5	632.2	596.3	565.9	549.3	541.1	534.2	535.5	536.9	538.3
52.5°	619.7	600.4	586.6	550.7	528.6	507.9	498.3	499.7	498.3	498.3	501.0
55°	572.8	553.5	539.7	506.6	484.5	470.7	462.4	458.2	459.6	456.9	462.4
57.5°	520.4	503.8	494.1	462.4	443.1	430.6	423.7	416.8	419.6	418.2	416.8
60°	474.8	455.5	440.3	418.2	401.7	386.5	382.3	375.4	378.2	375.4	374.0
62.5°	422.4	407.2	396.1	374.0	360.2	347.8	338.2	334.0	332.6	328.5	324.4
65°	369.9	361.6	350.6	328.5	314.7	305.0	299.5	295.4	294.0	283.0	270.5
67.5°	321.6	316.1	305.0	288.5	276.1	266.4	258.1	251.2	242.9	234.6	227.7
70°	276.1	267.8	260.9	245.7	234.6	225.0	216.7	208.4	204.3	196.0	193.2
72.5°	231.9	223.6	216.7	202.9	193.2	183.6	180.8	171.2	167.0	165.6	165.6
75°	186.3	179.4	175.3	162.9	154.6	147.7	143.5	140.8	138.0	135.3	131.1
77.5°	142.2	138.0	135.3	127.0	120.1	115.9	114.6	104.9	102.1	99.4	96.6
80°	103.5	102.1	99.4	92.5	89.7	80.1	80.1	77.3	75.9	75.9	75.9
82.5°	70.4	67.6	66.3	59.4	58.0	56.6	55.2	53.8	55.2	53.8	55.2
85°	37.3	35.9	34.5	34.5	34.5	34.5	34.5	34.5	34.5	33.1	34.5
87.5°	13.8	13.8	13.8	13.8	12.4	13.8	13.8	12.4	13.8	13.8	13.8
90°	13.1	14.4	15.3	17.2	19.0	20.9	22.7	24.1	25.5	26.8	28.2
92.5°	13.6	13.4	14.3	16.2	18.0	19.9	21.7	23.1	24.5	25.8	27.2
95°	25.6	21.7	21.8	22.0	22.3	22.5	22.7	24.1	25.5	26.8	28.2
97.5°	128.6	131.1	119.1	95.0	70.9	46.8	22.7	23.9	25.0	26.2	27.3
100°	185.7	187.8	172.0	140.3	108.7	77.0	45.4	41.5	37.6	33.7	29.8
102.5°	248.3	249.7	251.1	253.8	256.6	259.3	262.1	210.5	158.9	107.3	55.7
105°	316.1	316.8	317.4	318.5	319.7	320.8	322.0	324.0	326.1	328.1	330.2
107.5°	380.5	380.8	381.6	383.2	384.8	386.4	388.0	389.2	390.3	391.5	392.6
110°	448.6	448.9	449.6	451.0	452.3	453.7	455.1	455.5	456.0	456.4	456.9

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	517.3	518.0	518.2	518.7	519.2	519.6	520.1	519.9	519.6	519.4	519.1
115°	582.7	583.0	582.9	582.7	582.4	582.2	582.0	582.5	582.9	583.4	583.9
117.5°	644.4	644.9	645.2	645.9	646.6	647.3	648.0	647.8	647.6	647.3	647.1
120°	706.4	706.9	706.8	706.5	706.3	706.0	705.8	706.3	706.7	707.2	707.7
122.5°	762.4	762.6	762.8	763.3	763.7	764.2	764.6	764.8	765.1	765.3	765.6
125°	818.8	819.3	819.1	818.6	818.2	817.7	817.3	818.0	818.7	819.4	820.1
127.5°	868.8	868.9	869.5	870.6	871.7	872.9	874.0	873.8	873.6	873.3	873.1
130°	919.3	919.4	919.7	920.4	921.1	921.8	922.5	922.7	923.0	923.2	923.5
132.5°	966.7	966.9	967.4	968.3	969.2	970.1	971.0	971.2	971.5	971.7	972.0
135°	1010.3	1010.2	1010.7	1011.6	1012.5	1013.5	1014.4	1014.8	1015.3	1015.7	1016.2
137.5°	1052.5	1052.5	1053.1	1054.2	1055.4	1056.5	1057.7	1058.2	1058.6	1059.1	1059.6
140°	1094.7	1094.9	1095.1	1095.6	1096.0	1096.5	1096.9	1097.6	1098.3	1099.0	1099.7
142.5°	1132.5	1133.0	1133.1	1133.4	1133.6	1133.9	1134.1	1134.5	1135.0	1135.4	1135.9
145°	1168.8	1169.1	1169.1	1169.1	1169.1	1169.1	1169.1	1169.3	1169.6	1169.8	1170.1
147.5°	1200.4	1201.1	1201.0	1200.8	1200.5	1200.3	1200.1	1200.3	1200.5	1200.8	1201.0
150°	1230.6	1231.1	1231.0	1230.7	1230.5	1230.2	1230.0	1230.0	1230.0	1230.0	1230.0
152.5°	1256.6	1256.9	1256.7	1256.2	1255.7	1255.3	1254.8	1255.3	1255.7	1256.2	1256.7
155°	1279.5	1279.6	1279.3	1278.6	1277.9	1277.2	1276.5	1277.4	1278.3	1279.2	1280.1
157.5°	1300.2	1300.2	1299.7	1298.8	1297.9	1297.0	1296.1	1297.2	1298.4	1299.5	1300.6
160°	1316.0	1315.7	1315.6	1315.3	1315.1	1314.8	1314.6	1316.0	1317.4	1318.7	1320.1
162.5°	1331.7	1331.2	1331.1	1330.8	1330.6	1330.3	1330.1	1331.5	1332.9	1334.2	1335.6
165°	1344.1	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1345.3	1347.2	1349.0	1350.9
167.5°	1355.5	1354.9	1354.8	1354.6	1354.3	1354.1	1353.9	1355.9	1358.0	1360.0	1362.1
170°	1363.8	1363.1	1363.2	1363.5	1363.7	1364.0	1364.2	1366.0	1367.8	1369.7	1371.5
172.5°	1370.0	1369.3	1369.4	1369.7	1369.9	1370.2	1370.4	1372.2	1374.0	1375.9	1377.7
175°	1374.2	1373.5	1373.6	1373.8	1374.1	1374.3	1374.5	1376.6	1378.6	1380.7	1382.8
177.5°	1376.3	1375.5	1375.7	1376.2	1376.7	1377.1	1377.6	1379.4	1381.3	1383.1	1385.0
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1619.0	1624.6	1617.7	1621.8	1612.1	1610.8	1612.1	1612.1	1613.5	1614.9	1616.3
5°	1527.9	1526.6	1518.3	1512.8	1508.6	1512.8	1515.5	1518.3	1515.5	1518.3	1519.7
7.5°	1442.4	1438.2	1434.1	1424.4	1427.2	1424.4	1432.7	1428.6	1428.6	1435.5	1441.0
10°	1366.5	1358.2	1355.4	1344.4	1336.1	1334.7	1344.4	1348.5	1352.6	1355.4	1366.5
12.5°	1268.5	1256.0	1246.4	1250.5	1227.0	1236.7	1239.5	1233.9	1250.5	1269.8	1258.8
15°	1163.6	1164.9	1145.6	1138.7	1119.4	1124.9	1126.3	1140.1	1153.9	1152.5	1169.1
17.5°	1086.3	1078.0	1061.4	1060.0	1051.8	1055.9	1054.5	1065.6	1061.4	1068.3	1082.1
20°	1014.5	1009.0	995.2	989.6	992.4	989.6	991.0	992.4	996.5	1011.7	1009.0
22.5°	957.9	951.0	951.0	944.1	935.8	933.1	940.0	944.1	949.6	952.4	959.3
25°	908.2	902.7	895.8	891.6	884.7	886.1	890.3	895.8	899.9	905.4	911.0
27.5°	857.1	857.1	850.2	848.9	846.1	844.7	850.2	853.0	853.0	857.1	862.7
30°	817.1	817.1	810.2	808.8	807.4	807.4	811.6	813.0	814.4	818.5	821.3
32.5°	778.5	777.1	774.3	775.7	774.3	775.7	775.7	777.1	779.8	781.2	786.7
35°	742.6	744.0	741.2	741.2	739.8	741.2	744.0	745.3	746.7	749.5	749.5
37.5°	708.1	710.8	709.5	713.6	713.6	713.6	713.6	716.4	716.4	716.4	715.0
40°	677.7	677.7	676.3	679.1	681.8	681.8	683.2	683.2	684.6	684.6	683.2
42.5°	643.2	646.0	650.1	651.5	654.2	652.9	657.0	655.6	657.0	654.2	651.5
45°	611.5	611.5	617.0	622.5	623.9	623.9	623.9	626.6	623.9	619.7	618.4
47.5°	576.9	579.7	582.5	589.4	590.7	590.7	590.7	590.7	588.0	588.0	588.0
50°	542.4	543.8	545.2	548.0	552.1	550.7	550.7	550.7	556.2	550.7	552.1
52.5°	501.0	502.4	503.8	509.3	507.9	507.9	509.3	509.3	513.5	512.1	509.3
55°	459.6	459.6	462.4	462.4	462.4	465.1	466.5	469.3	467.9	469.3	470.7
57.5°	418.2	415.5	414.1	414.1	418.2	416.8	418.2	418.2	423.7	426.5	427.9
60°	369.9	369.9	368.5	360.2	360.2	358.9	363.0	365.8	368.5	381.0	379.6
62.5°	320.2	314.7	309.2	310.6	302.3	306.4	303.7	306.4	314.7	324.4	325.7
65°	270.5	266.4	260.9	259.5	256.7	260.9	259.5	260.9	265.0	270.5	277.4
67.5°	226.4	225.0	222.2	220.8	220.8	220.8	223.6	223.6	225.0	229.1	233.3
70°	193.2	191.9	193.2	190.5	191.9	190.5	191.9	193.2	194.6	196.0	200.1
72.5°	162.9	162.9	162.9	160.1	162.9	161.5	161.5	162.9	164.3	165.6	168.4
75°	129.7	127.0	124.2	121.5	120.1	122.8	124.2	122.8	127.0	132.5	132.5
77.5°	98.0	96.6	96.6	96.6	98.0	96.6	99.4	98.0	99.4	99.4	102.1
80°	75.9	74.5	75.9	75.9	74.5	77.3	75.9	75.9	77.3	78.7	77.3
82.5°	55.2	56.6	55.2	55.2	55.2	58.0	55.2	55.2	55.2	56.6	56.6
85°	34.5	34.5	34.5	34.5	35.9	34.5	35.9	34.5	37.3	35.9	35.9
87.5°	12.4	13.8	15.2	15.2	15.2	15.2	13.8	15.2	16.6	15.2	16.6
90°	28.9	29.1	29.6	30.1	30.5	31.0	30.5	30.1	29.6	29.1	28.9
92.5°	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9	27.9
95°	28.9	29.0	29.2	29.5	29.7	29.9	29.7	29.5	29.2	29.0	28.9
97.5°	27.9	28.0	28.2	28.5	28.7	28.9	28.7	28.5	28.2	28.0	27.9
100°	27.9	28.0	28.2	28.5	28.7	28.9	28.7	28.5	28.2	28.0	27.9
102.5°	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9	29.9
105°	331.2	327.1	318.8	310.6	302.3	294.1	302.3	310.6	318.8	327.1	331.2
107.5°	393.2	393.7	394.6	395.5	396.4	397.3	396.4	395.5	394.6	393.7	393.2
110°	457.1	457.4	458.1	458.8	459.5	460.2	459.5	458.8	458.1	457.4	457.1

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	519.0	519.5	520.4	521.3	522.3	523.2	522.3	521.3	520.4	519.5	519.0
115°	584.1	584.1	584.1	584.1	584.1	584.1	584.1	584.1	584.1	584.1	584.1
117.5°	647.0	647.0	647.0	647.0	647.0	647.0	647.0	647.0	647.0	647.0	647.0
120°	707.9	707.7	707.2	706.7	706.3	705.8	706.3	706.7	707.2	707.7	707.9
122.5°	765.7	765.5	765.0	764.5	764.1	763.6	764.1	764.5	765.0	765.5	765.7
125°	820.4	820.5	820.7	821.0	821.2	821.4	821.2	821.0	820.7	820.5	820.4
127.5°	873.0	872.9	872.7	872.4	872.2	872.0	872.2	872.4	872.7	872.9	873.0
130°	923.6	923.6	923.6	923.6	923.6	923.6	923.6	923.6	923.6	923.6	923.6
132.5°	972.1	972.0	971.7	971.5	971.2	971.0	971.2	971.5	971.7	972.0	972.1
135°	1016.4	1016.6	1017.1	1017.6	1018.0	1018.5	1018.0	1017.6	1017.1	1016.6	1016.4
137.5°	1059.8	1059.7	1059.4	1059.2	1058.9	1058.7	1058.9	1059.2	1059.4	1059.7	1059.8
140°	1100.0	1100.1	1100.3	1100.6	1100.8	1101.0	1100.8	1100.6	1100.3	1100.1	1100.0
142.5°	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1	1136.1
145°	1170.2	1170.4	1170.9	1171.3	1171.8	1172.2	1171.8	1171.3	1170.9	1170.4	1170.2
147.5°	1201.1	1201.2	1201.5	1201.7	1202.0	1202.2	1202.0	1201.7	1201.5	1201.2	1201.1
150°	1230.0	1230.1	1230.4	1230.6	1230.9	1231.1	1230.9	1230.6	1230.4	1230.1	1230.0
152.5°	1256.9	1256.8	1256.5	1256.3	1256.0	1255.8	1256.0	1256.3	1256.5	1256.8	1256.9
155°	1280.6	1280.3	1279.6	1278.9	1278.2	1277.5	1278.2	1278.9	1279.6	1280.3	1280.6
157.5°	1301.2	1300.6	1299.5	1298.4	1297.2	1296.1	1297.2	1298.4	1299.5	1300.6	1301.2
160°	1320.8	1320.1	1318.7	1317.4	1316.0	1314.6	1316.0	1317.4	1318.7	1320.1	1320.8
162.5°	1336.3	1335.5	1333.9	1332.3	1330.7	1329.1	1330.7	1332.3	1333.9	1335.5	1336.3
165°	1351.8	1350.8	1348.7	1346.6	1344.6	1342.5	1344.6	1346.6	1348.7	1350.8	1351.8
167.5°	1363.1	1362.0	1359.7	1357.4	1355.1	1352.8	1355.1	1357.4	1359.7	1362.0	1363.1
170°	1372.4	1371.3	1369.0	1366.7	1364.4	1362.1	1364.4	1366.7	1369.0	1371.3	1372.4
172.5°	1378.6	1377.3	1374.8	1372.3	1369.8	1367.3	1369.8	1372.3	1374.8	1377.3	1378.6
175°	1383.8	1382.4	1379.7	1376.9	1374.2	1371.4	1374.2	1376.9	1379.7	1382.4	1383.8
177.5°	1385.9	1384.5	1381.8	1379.0	1376.3	1373.5	1376.3	1379.0	1381.8	1384.5	1385.9
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9	1712.9
2.5°	1621.8	1628.7	1625.9	1616.3	1620.4	1628.7	1637.0	1648.0	1654.9	1660.4	1663.2
5°	1526.6	1539.0	1536.2	1536.2	1541.7	1555.5	1569.3	1592.8	1601.1	1610.8	1624.6
7.5°	1442.4	1452.0	1460.3	1463.1	1471.4	1489.3	1507.2	1533.5	1554.2	1565.2	1573.5
10°	1367.8	1374.7	1387.2	1394.1	1402.3	1424.4	1450.6	1478.3	1499.0	1518.3	1529.3
12.5°	1272.6	1300.2	1316.8	1327.8	1338.8	1372.0	1392.7	1423.0	1447.9	1465.8	1482.4
15°	1166.3	1199.4	1209.1	1251.9	1279.5	1305.7	1337.5	1373.4	1396.8	1417.5	1439.6
17.5°	1076.6	1100.1	1111.1	1156.7	1180.1	1221.5	1267.1	1312.6	1348.5	1363.7	1385.8
20°	1020.0	1032.4	1054.5	1069.7	1094.5	1142.9	1192.5	1247.8	1301.6	1316.8	1338.8
22.5°	962.0	978.6	993.8	1014.5	1033.8	1066.9	1116.6	1177.4	1235.3	1262.9	1289.2
25°	909.6	926.2	935.8	957.9	975.8	1009.0	1043.5	1105.6	1174.6	1198.1	1239.5
27.5°	868.2	877.8	894.4	904.1	924.8	955.1	986.9	1033.8	1101.4	1141.5	1181.5
30°	826.8	833.7	847.5	861.3	876.5	897.2	933.1	978.6	1040.7	1075.2	1115.2
32.5°	785.4	796.4	804.7	814.4	830.9	855.8	880.6	924.8	974.5	1013.1	1053.1
35°	750.9	755.0	766.0	777.1	788.1	810.2	836.4	879.2	923.4	953.8	989.6
37.5°	713.6	720.5	728.8	732.9	750.9	764.7	792.3	825.4	877.8	897.2	933.1
40°	684.6	683.2	691.5	698.4	706.7	728.8	745.3	781.2	822.6	853.0	875.1
42.5°	648.7	648.7	651.5	659.8	670.8	684.6	703.9	734.3	777.1	799.2	825.4
45°	619.7	615.6	617.0	622.5	629.4	643.2	662.5	688.7	731.5	749.5	777.1
47.5°	585.2	581.1	581.1	586.6	592.1	601.8	617.0	647.3	681.8	705.3	726.0
50°	546.6	548.0	546.6	550.7	553.5	563.1	579.7	604.6	636.3	655.6	679.1
52.5°	510.7	507.9	506.6	509.3	514.8	521.7	539.7	561.8	592.1	611.5	632.2
55°	466.5	469.3	469.3	469.3	477.6	480.3	494.1	516.2	546.6	561.8	581.1
57.5°	426.5	425.1	427.9	426.5	433.4	443.1	454.1	470.7	501.0	516.2	534.2
60°	382.3	383.7	385.1	385.1	390.6	400.3	412.7	427.9	452.7	467.9	484.5
62.5°	328.5	335.4	342.3	345.1	353.3	360.2	368.5	385.1	407.2	418.2	433.4
65°	277.4	287.1	296.8	303.7	309.2	316.1	327.1	342.3	360.2	371.3	386.5
67.5°	233.3	240.2	252.6	259.5	270.5	278.8	285.7	298.1	320.2	324.4	336.8
70°	201.5	204.3	209.8	215.3	227.7	234.6	242.9	255.3	271.9	281.6	288.5
72.5°	169.8	171.2	173.9	179.4	185.0	193.2	202.9	213.9	229.1	233.3	242.9
75°	135.3	143.5	143.5	147.7	151.8	156.0	164.3	175.3	185.0	191.9	197.4
77.5°	100.8	104.9	107.7	114.6	120.1	124.2	129.7	138.0	143.5	149.1	153.2
80°	78.7	80.1	81.4	81.4	84.2	89.7	95.2	100.8	107.7	110.4	114.6
82.5°	58.0	58.0	58.0	60.7	62.1	63.5	63.5	66.3	73.2	75.9	80.1
85°	37.3	37.3	37.3	37.3	38.6	40.0	41.4	42.8	42.8	42.8	45.5
87.5°	15.2	17.9	16.6	17.9	17.9	17.9	17.9	19.3	19.3	20.7	20.7
90°	28.2	26.8	25.5	24.1	22.7	20.9	19.0	17.2	15.3	14.4	13.1
92.5°	27.2	25.8	24.5	23.1	21.7	19.9	18.0	16.2	14.3	13.4	13.6
95°	28.2	26.8	25.5	24.1	22.7	22.5	22.3	22.0	21.8	21.7	25.6
97.5°	27.3	26.2	25.0	23.9	22.7	46.8	70.9	95.0	119.1	131.1	128.6
100°	29.8	33.7	37.6	41.5	45.4	77.0	108.7	140.3	172.0	187.8	185.7
102.5°	55.7	107.3	158.9	210.5	262.1	259.3	256.6	253.8	251.1	249.7	248.3
105°	330.2	328.1	326.1	324.0	322.0	320.8	319.7	318.5	317.4	316.8	316.1
107.5°	392.6	391.5	390.3	389.2	388.0	386.4	384.8	383.2	381.6	380.8	380.5
110°	456.9	456.4	456.0	455.5	455.1	453.7	452.3	451.0	449.6	448.9	448.6

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	519.1	519.4	519.6	519.9	520.1	519.6	519.2	518.7	518.2	518.0	517.3
115°	583.9	583.4	582.9	582.5	582.0	582.2	582.4	582.7	582.9	583.0	582.7
117.5°	647.1	647.3	647.6	647.8	648.0	647.3	646.6	645.9	645.2	644.9	644.4
120°	707.7	707.2	706.7	706.3	705.8	706.0	706.3	706.5	706.8	706.9	706.4
122.5°	765.6	765.3	765.1	764.8	764.6	764.2	763.7	763.3	762.8	762.6	762.4
125°	820.1	819.4	818.7	818.0	817.3	817.7	818.2	818.6	819.1	819.3	818.8
127.5°	873.1	873.3	873.6	873.8	874.0	872.9	871.7	870.6	869.5	868.9	868.8
130°	923.5	923.2	923.0	922.7	922.5	921.8	921.1	920.4	919.7	919.4	919.3
132.5°	972.0	971.7	971.5	971.2	971.0	970.1	969.2	968.3	967.4	966.9	966.7
135°	1016.2	1015.7	1015.3	1014.8	1014.4	1013.5	1012.5	1011.6	1010.7	1010.2	1010.3
137.5°	1059.6	1059.1	1058.6	1058.2	1057.7	1056.5	1055.4	1054.2	1053.1	1052.5	1052.5
140°	1099.7	1099.0	1098.3	1097.6	1096.9	1096.5	1096.0	1095.6	1095.1	1094.9	1094.7
142.5°	1135.9	1135.4	1135.0	1134.5	1134.1	1133.9	1133.6	1133.4	1133.1	1133.0	1132.5
145°	1170.1	1169.8	1169.6	1169.3	1169.1	1169.1	1169.1	1169.1	1169.1	1169.1	1168.8
147.5°	1201.0	1200.8	1200.5	1200.3	1200.1	1200.3	1200.5	1200.8	1201.0	1201.1	1200.4
150°	1230.0	1230.0	1230.0	1230.0	1230.0	1230.2	1230.5	1230.7	1231.0	1231.1	1230.6
152.5°	1256.7	1256.2	1255.7	1255.3	1254.8	1255.3	1255.7	1256.2	1256.7	1256.9	1256.6
155°	1280.1	1279.2	1278.3	1277.4	1276.5	1277.2	1277.9	1278.6	1279.3	1279.6	1279.5
157.5°	1300.6	1299.5	1298.4	1297.2	1296.1	1297.0	1297.9	1298.8	1299.7	1300.2	1300.2
160°	1320.1	1318.7	1317.4	1316.0	1314.6	1314.8	1315.1	1315.3	1315.6	1315.7	1316.0
162.5°	1335.6	1334.2	1332.9	1331.5	1330.1	1330.3	1330.6	1330.8	1331.1	1331.2	1331.7
165°	1350.9	1349.0	1347.2	1345.3	1343.5	1343.5	1343.5	1343.5	1343.5	1343.5	1344.1
167.5°	1362.1	1360.0	1358.0	1355.9	1353.9	1354.1	1354.3	1354.6	1354.8	1354.9	1355.5
170°	1371.5	1369.7	1367.8	1366.0	1364.2	1364.0	1363.7	1363.5	1363.2	1363.1	1363.8
172.5°	1377.7	1375.9	1374.0	1372.2	1370.4	1370.2	1369.9	1369.7	1369.4	1369.3	1370.0
175°	1382.8	1380.7	1378.6	1376.6	1374.5	1374.3	1374.1	1373.8	1373.6	1373.5	1374.2
177.5°	1385.0	1383.1	1381.3	1379.4	1377.6	1377.1	1376.7	1376.2	1375.7	1375.5	1376.3
180°	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7	1379.7

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1712.9	1712.9	1712.9	1712.9
2.5°	1674.2	1682.5	1696.3	1715.7
5°	1635.6	1659.1	1681.2	1710.1
7.5°	1601.1	1628.7	1659.1	1700.5
10°	1561.1	1595.6	1634.2	1685.3
12.5°	1514.1	1562.4	1606.6	1661.8
15°	1479.6	1515.5	1572.1	1637.0
17.5°	1431.3	1479.6	1536.2	1609.4
20°	1385.8	1436.8	1500.3	1576.3
22.5°	1337.5	1395.4	1458.9	1540.4
25°	1287.8	1349.9	1413.4	1500.3
27.5°	1242.2	1298.8	1370.6	1458.9
30°	1187.0	1251.9	1320.9	1413.4
32.5°	1133.2	1200.8	1271.2	1363.7
35°	1075.2	1142.9	1220.1	1308.5
37.5°	1018.6	1093.2	1163.6	1249.1
40°	956.5	1033.8	1107.0	1193.9
42.5°	895.8	975.8	1049.0	1123.5
45°	839.2	917.9	984.1	1054.5
47.5°	785.4	855.8	923.4	986.9
50°	732.9	792.3	854.4	906.8
52.5°	677.7	734.3	784.0	830.9
55°	628.0	672.2	716.4	759.1
57.5°	568.7	612.8	651.5	684.6
60°	519.0	546.6	583.8	618.4
62.5°	462.4	494.1	523.1	545.2
65°	407.2	434.8	456.9	476.2
67.5°	360.2	376.8	393.4	414.1
70°	303.7	317.5	336.8	352.0
72.5°	255.3	266.4	276.1	294.0
75°	207.0	216.7	222.2	238.8
77.5°	160.1	169.8	173.9	183.6
80°	122.8	124.2	129.7	138.0
82.5°	84.2	87.0	88.3	95.2
85°	48.3	55.2	53.8	56.6
87.5°	20.7	22.1	24.8	27.6
90°	10.6	8.1	5.6	3.1
92.5°	14.1	14.6	15.0	15.5
95°	33.4	41.2	49.0	56.8
97.5°	123.5	118.5	113.4	108.4
100°	181.6	177.5	173.3	169.2
102.5°	245.6	242.8	240.1	237.3
105°	314.7	313.4	312.0	310.6
107.5°	379.8	379.1	378.4	377.7
110°	447.9	447.2	446.5	445.8

TEST NUMBER: P1033832

CATALOG NUMBER: S124RDIW-B1020D1050UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	515.9	514.6	513.2	511.8
115°	582.0	581.3	580.6	579.9
117.5°	643.5	642.6	641.7	640.8
120°	705.5	704.6	703.6	702.7
122.5°	761.9	761.4	761.0	760.5
125°	817.9	817.0	816.1	815.2
127.5°	868.5	868.3	868.0	867.8
130°	919.1	918.8	918.6	918.4
132.5°	966.2	965.7	965.3	964.8
135°	1010.6	1010.8	1011.1	1011.3
137.5°	1052.5	1052.5	1052.5	1052.5
140°	1094.2	1093.7	1093.3	1092.8
142.5°	1131.6	1130.7	1129.8	1128.9
145°	1168.1	1167.4	1166.8	1166.1
147.5°	1199.0	1197.7	1196.3	1194.9
150°	1229.7	1228.8	1227.8	1226.9
152.5°	1255.9	1255.2	1254.5	1253.8
155°	1279.2	1279.0	1278.7	1278.5
157.5°	1300.2	1300.2	1300.2	1300.2
160°	1316.7	1317.4	1318.1	1318.8
162.5°	1332.6	1333.5	1334.4	1335.3
165°	1345.2	1346.4	1347.5	1348.7
167.5°	1356.6	1357.8	1358.9	1360.1
170°	1365.2	1366.5	1367.9	1369.3
172.5°	1371.4	1372.7	1374.1	1375.5
175°	1375.6	1376.9	1378.3	1379.7
177.5°	1377.9	1379.6	1381.2	1382.8
180°	1379.7	1379.7	1379.7	1379.7

(END OF REPORT)