

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1033839

Luminaire Tested: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1033839
REPORT IS A COMBINATION OF REPORTS P999855 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1
Description: Define 4 Regressed Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7792.0 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1033839

CATALOG NUMBER: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1033839

CATALOG NUMBER: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	99	95	91	87	91	88	84	81	75	73	70	63	62	60	52	51	50
2	90	83	77	72	83	77	72	67	66	62	59	56	53	51	47	45	43
3	82	73	66	60	76	68	62	57	58	54	50	50	46	43	41	39	37
4	76	65	57	51	70	60	54	48	52	47	43	44	40	37	37	34	32
5	69	58	50	44	64	54	47	42	47	41	37	40	36	32	34	30	28
6	64	52	44	38	59	49	41	36	42	37	32	36	32	28	31	27	25
7	59	47	39	34	55	44	37	32	38	33	29	33	29	25	28	25	22
8	55	43	35	30	51	40	33	28	35	29	25	30	26	23	26	22	20
9	51	39	32	27	48	37	30	25	32	27	23	28	24	20	24	20	18
10	48	36	29	24	45	34	27	23	30	24	21	26	22	19	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14554	14554	14554
5°	14556	14122	14123
10°	14432	13676	13513
15°	14233	13122	12794
20°	13973	12489	11974
25°	13649	11806	11172
30°	13332	11110	10273
35°	12983	10404	9394
40°	12568	9645	8490
45°	12178	8891	7595
50°	11734	8068	6687
55°	11256	7225	5749
60°	10724	6328	4824
65°	10212	5301	3932
70°	9482	4219	3005
75°	8547	3070	2101
80°	7140	1884	1511
85°	5370	1086	830

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12178 cd/sqm

TEST NUMBER: P1033839

CATALOG NUMBER: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.8	2.2
10°-20°	467.9	6.0
20°-30°	675.6	8.7
30°-40°	765.7	9.8
40°-50°	739.3	9.5
50°-60°	614.6	7.9
60°-70°	424.2	5.4
70°-80°	214.4	2.8
80°-90°	57.3	0.7
90°-100°	86.1	1.1
100°-110°	257.9	3.3
110°-120°	438.1	5.6
120°-130°	577.8	7.4
130°-140°	649.0	8.3
140°-150°	637.9	8.2
150°-160°	536.5	6.9
160°-170°	356.9	4.6
170°-180°	125.0	1.6
0°-30°	1311.4	16.8
0°-40°	2077.1	26.7
0°-60°	3431.0	44.0
0°-90°	4126.8	53.0
90°-120°	782.1	10.0
90°-150°	2646.7	34.0
90°-180°	3665.0	47.0
0°-180°	7792.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1785	1785	1785	1785	1785	
5°	1782	1777	1760	1774	1771	169
15°	1697	1685	1651	1648	1639	478
25°	1535	1510	1454	1431	1417	707
35°	1327	1283	1215	1168	1144	829
45°	1082	1032	950	883	858	835
55°	820	765	676	605	579	734
65°	558	499	411	353	336	551
75°	297	246	182	150	142	313
85°	74	46	42	40	40	81
90°	3	14	22	29	31	9
95°	61	70	78	81	81	66
105°	238	239	243	246	249	252
115°	445	445	443	442	441	439
125°	649	649	648	646	644	578
135°	837	843	843	841	838	647
145°	1016	1021	1022	1021	1018	636
155°	1165	1165	1164	1168	1164	536
165°	1268	1265	1263	1269	1265	357
175°	1319	1314	1313	1320	1313	125
180°	1321	1321	1321	1321	1321	

TEST NUMBER: P1033839

CATALOG NUMBER: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1784.8	1784.8	1784.8	1784.8	1784.8
2.5°	1790.3	1784.8	1769.8	1784.8	1783.4
5°	1782.1	1776.6	1760.2	1773.9	1771.1
7.5°	1769.8	1764.3	1743.8	1753.4	1749.3
10°	1750.6	1743.8	1719.2	1724.7	1719.2
12.5°	1726.0	1717.8	1687.8	1690.5	1682.3
15°	1697.3	1685.0	1650.9	1648.2	1638.6
17.5°	1664.5	1646.8	1607.2	1600.3	1586.7
20°	1624.9	1607.2	1560.7	1549.8	1532.0
22.5°	1581.2	1560.7	1510.1	1492.4	1478.7
25°	1534.7	1510.1	1454.1	1430.9	1417.2
27.5°	1486.9	1456.8	1398.1	1370.7	1351.6
30°	1436.3	1402.2	1337.9	1303.8	1281.9
32.5°	1383.0	1343.4	1276.4	1235.4	1214.9
35°	1327.0	1283.3	1214.9	1168.5	1143.9
37.5°	1268.2	1223.1	1148.0	1097.4	1072.8
40°	1205.4	1160.3	1082.4	1025.0	1000.4
42.5°	1145.2	1097.4	1015.4	956.6	930.7
45°	1082.4	1031.8	949.8	882.8	858.2
47.5°	1018.1	966.2	881.5	811.8	784.4
50°	952.5	899.2	811.8	743.4	717.5
52.5°	885.6	833.6	743.4	673.7	646.4
55°	820.0	765.3	676.5	605.4	579.4
57.5°	755.7	698.3	610.9	538.5	519.3
60°	686.0	631.4	543.9	472.9	451.0
62.5°	623.2	565.8	475.6	411.4	395.0
65°	557.6	498.8	411.4	352.6	336.2
67.5°	489.3	433.2	351.2	299.3	280.2
70°	425.0	367.6	289.7	244.6	231.0
72.5°	356.7	306.1	233.7	196.8	184.5
75°	296.6	246.0	181.8	150.3	142.1
77.5°	233.7	190.0	135.3	113.4	110.7
80°	173.6	133.9	92.9	88.8	87.5
82.5°	121.6	86.1	67.0	64.2	62.9
85°	73.8	46.5	42.4	39.6	39.6
87.5°	31.4	20.5	19.1	17.8	19.1
90°	3.1	14.3	22.5	28.6	30.6
92.5°	26.6	39.8	45.0	48.0	49.0
95°	61.3	70.5	77.6	80.7	80.7
97.5°	98.1	106.2	114.4	118.5	118.5
100°	143.0	147.1	156.3	158.4	158.4
102.5°	190.0	191.0	199.2	202.3	203.3
105°	238.0	239.1	243.1	246.2	249.3
107.5°	288.1	289.1	290.1	294.2	293.2
110°	339.2	341.2	340.2	338.2	341.2

TEST NUMBER: P1033839

CATALOG NUMBER: S124RDIW-B1020D1050UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	392.3	390.3	390.3	390.3
115°	445.4	445.4	443.4	442.4	441.3
117.5°	495.5	495.5	494.5	491.4	488.3
120°	545.5	549.6	546.6	541.5	543.5
122.5°	597.6	598.7	597.6	594.6	589.5
125°	648.7	648.7	647.7	645.7	643.6
127.5°	694.7	697.8	695.7	693.7	692.7
130°	743.7	746.8	746.8	744.8	740.7
132.5°	793.8	795.8	794.8	792.8	791.8
135°	836.7	842.8	842.8	840.8	837.7
137.5°	884.7	887.8	889.8	886.8	887.8
140°	932.7	934.8	934.8	933.8	932.7
142.5°	976.7	978.7	977.7	977.7	977.7
145°	1016.5	1020.6	1021.6	1020.6	1017.5
147.5°	1057.4	1062.5	1061.5	1060.4	1059.4
150°	1094.2	1098.2	1098.2	1098.2	1097.2
152.5°	1128.9	1130.9	1132.0	1135.0	1132.0
155°	1164.7	1164.7	1163.6	1167.7	1163.6
157.5°	1195.3	1193.3	1193.3	1196.3	1193.3
160°	1221.9	1220.8	1219.8	1222.9	1217.8
162.5°	1246.4	1243.3	1242.3	1248.4	1243.3
165°	1267.8	1264.8	1262.7	1268.9	1264.8
167.5°	1285.2	1281.1	1281.1	1287.2	1281.1
170°	1299.5	1294.4	1295.4	1301.5	1294.4
172.5°	1309.7	1305.6	1305.6	1312.8	1305.6
175°	1318.9	1313.8	1312.8	1319.9	1312.8
177.5°	1323.0	1317.9	1317.9	1325.0	1316.9
180°	1321.0	1321.0	1321.0	1321.0	1321.0

(END OF REPORT)