

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034369

Luminaire Tested: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034369
REPORT IS A COMBINATION OF REPORTS P1002940 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5826.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034369

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034369

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	93	90	87	84	81	79	76	74	72	68	67	65
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55
3	85	75	68	62	81	72	65	59	65	60	55	59	54	51	53	50	47
4	78	67	59	52	74	64	56	50	58	52	47	52	47	43	47	43	40
5	72	60	51	45	68	57	49	43	52	46	41	47	42	38	43	38	35
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31
7	61	49	40	35	58	47	39	33	43	36	31	39	33	29	35	31	27
8	57	44	36	31	54	42	35	30	39	33	28	36	30	26	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	37	30	25	47	36	29	24	33	27	23	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10450	10450	10450
5°	10450	10207	10227
10°	10364	9973	9942
15°	10228	9693	9606
20°	10043	9369	9222
25°	9846	9015	8810
30°	9608	8646	8375
35°	9354	8259	7889
40°	9091	7851	7457
45°	8806	7453	6997
50°	8493	7001	6462
55°	8183	6503	5969
60°	7813	5978	5396
65°	7372	5370	4804
70°	6920	4671	4121
75°	6166	3846	3332
80°	5254	2873	2451
85°	4059	1700	1351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8806 cd/sqm

TEST NUMBER: P1034369

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	2.6
10°-20°	434.7	7.5
20°-30°	641.8	11.0
30°-40°	748.8	12.9
40°-50°	752.0	12.9
50°-60°	660.2	11.3
60°-70°	491.7	8.4
70°-80°	280.8	4.8
80°-90°	81.9	1.4
90°-100°	37.7	0.6
100°-110°	111.8	1.9
110°-120°	189.7	3.3
120°-130°	249.7	4.3
130°-140°	279.8	4.8
140°-150°	274.3	4.7
150°-160°	230.4	4.0
160°-170°	153.1	2.6
170°-180°	53.6	0.9
0°-30°	1230.4	21.1
0°-40°	1979.2	34.0
0°-60°	3391.4	58.2
0°-90°	4245.9	72.9
90°-120°	339.2	5.8
90°-150°	1143.0	19.6
90°-180°	1580.0	27.1
0°-180°	5826.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1628	1626	1613	1624	1623	155
15°	1552	1548	1534	1541	1541	438
25°	1409	1403	1386	1388	1384	648
35°	1217	1212	1194	1187	1177	761
45°	996	991	976	960	956	767
55°	759	755	737	725	716	677
65°	512	510	496	484	479	508
75°	272	270	263	259	254	290
85°	71	72	72	71	68	78
90°	0	4	7	9	11	7
95°	29	30	34	37	38	30
105°	100	103	105	108	109	107
115°	190	192	192	192	192	188
125°	277	280	280	279	279	248
135°	360	363	364	364	362	278
145°	437	438	440	440	438	273
155°	500	500	500	502	500	230
165°	543	542	543	545	542	153
175°	565	563	563	566	563	54
180°	566	566	566	566	566	

TEST NUMBER: P1034369

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.0	1631.0	1631.0	1631.0	1631.0
2.5°	1636.1	1632.3	1619.4	1632.3	1631.0
5°	1628.4	1625.8	1612.9	1624.5	1623.2
7.5°	1616.8	1614.2	1600.0	1611.6	1610.3
10°	1600.0	1597.4	1583.2	1593.5	1592.3
12.5°	1579.4	1574.2	1561.3	1569.0	1569.0
15°	1552.3	1548.4	1534.2	1540.6	1540.6
17.5°	1523.9	1517.4	1503.2	1511.0	1504.5
20°	1486.4	1483.9	1467.1	1476.1	1469.7
22.5°	1449.0	1443.9	1428.4	1433.5	1429.7
25°	1409.0	1402.6	1385.8	1388.4	1384.5
27.5°	1362.6	1358.7	1341.9	1343.2	1339.4
30°	1317.4	1313.5	1294.2	1291.6	1287.7
32.5°	1268.4	1261.9	1245.2	1240.0	1232.3
35°	1216.8	1211.6	1193.5	1187.1	1176.8
37.5°	1163.9	1157.4	1140.6	1131.6	1125.2
40°	1109.7	1103.2	1085.2	1073.5	1069.7
42.5°	1051.6	1046.4	1028.4	1018.1	1011.6
45°	996.1	991.0	975.5	960.0	956.1
47.5°	935.5	936.8	917.4	901.9	892.9
50°	877.4	873.5	858.1	841.3	832.3
52.5°	818.1	815.5	798.7	784.5	774.2
55°	758.7	754.8	736.8	725.2	716.1
57.5°	695.5	694.2	678.7	663.2	659.4
60°	636.1	631.0	616.8	603.9	594.8
62.5°	574.2	570.3	558.7	544.5	538.1
65°	512.3	509.7	495.5	483.9	478.7
67.5°	451.6	446.5	436.1	425.8	423.2
70°	394.8	388.4	376.8	369.0	363.9
72.5°	332.9	329.0	322.6	313.5	308.4
75°	272.3	269.7	263.2	259.4	254.2
77.5°	215.5	214.2	210.3	207.7	203.9
80°	162.6	162.6	160.0	158.7	156.1
82.5°	116.1	113.5	113.5	111.0	111.0
85°	71.0	72.3	72.3	71.0	68.4
87.5°	34.8	34.8	33.5	33.5	31.0
90°	0.4	4.0	7.0	9.3	10.6
92.5°	13.2	15.4	19.4	22.5	23.4
95°	28.6	29.5	33.9	37.0	37.9
97.5°	44.1	44.5	50.7	53.3	53.8
100°	61.7	61.7	67.4	71.4	72.3
102.5°	80.6	82.8	85.0	89.4	90.8
105°	100.5	102.7	105.3	107.9	109.3
107.5°	122.0	124.2	126.5	127.8	127.8
110°	144.5	146.7	148.0	149.4	148.9



TEST NUMBER: P1034369

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	167.4	168.3	170.1	170.5	169.6
115°	189.9	191.7	192.5	192.1	191.7
117.5°	212.8	213.2	214.1	214.6	212.8
120°	234.0	236.2	236.6	236.6	234.8
122.5°	256.9	257.3	258.6	258.2	256.9
125°	277.1	279.8	280.2	279.3	278.9
127.5°	299.6	300.9	301.4	300.9	300.0
130°	319.4	321.6	322.5	322.1	321.2
132.5°	339.3	343.2	342.8	342.3	341.0
135°	360.4	363.1	363.5	363.5	361.7
137.5°	380.2	382.9	383.8	384.2	382.0
140°	399.2	401.4	402.7	403.6	401.4
142.5°	418.1	419.9	421.6	422.1	419.9
145°	436.6	438.4	439.7	439.7	438.4
147.5°	453.8	455.1	456.0	457.3	453.8
150°	471.0	470.6	472.3	472.3	471.4
152.5°	485.1	486.0	486.4	487.7	486.0
155°	499.6	499.6	500.1	501.8	499.6
157.5°	512.9	512.0	512.4	514.2	511.1
160°	524.3	523.0	523.4	525.2	523.0
162.5°	534.4	533.6	533.6	535.8	533.1
165°	543.3	542.4	542.8	544.6	541.9
167.5°	551.2	549.4	549.4	552.1	549.4
170°	557.4	555.6	555.6	558.2	555.1
172.5°	561.8	560.0	560.0	562.6	560.0
175°	564.8	563.1	563.1	565.7	562.6
177.5°	567.0	565.3	564.8	567.5	564.4
180°	566.2	566.2	566.2	566.2	566.2

(END OF REPORT)