

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034371

Luminaire Tested: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034371
REPORT IS A COMBINATION OF REPORTS P1002943 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K
Description: Define 5 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6311.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034371

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034371

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21
10	50	37	30	25	47	35	29	24	32	26	22	30	25	21	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10868	10868	10868
5°	10869	10616	10636
10°	10779	10372	10340
15°	10637	10081	9991
20°	10446	9744	9591
25°	10241	9376	9163
30°	9993	8992	8711
35°	9728	8590	8205
40°	9454	8165	7755
45°	9158	7751	7278
50°	8833	7281	6721
55°	8511	6763	6209
60°	8126	6217	5613
65°	7666	5584	4997
70°	7199	4858	4285
75°	6412	4000	3466
80°	5465	2988	2549
85°	4220	1768	1405

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9158 cd/sqm

TEST NUMBER: P1034371

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.5
10°-20°	452.1	7.2
20°-30°	667.5	10.6
30°-40°	778.8	12.3
40°-50°	782.2	12.4
50°-60°	686.6	10.9
60°-70°	511.4	8.1
70°-80°	292.1	4.6
80°-90°	85.2	1.4
90°-100°	20.9	0.3
100°-110°	139.2	2.2
110°-120°	250.7	4.0
120°-130°	321.8	5.1
130°-140°	346.1	5.5
140°-150°	324.9	5.1
150°-160°	262.8	4.2
160°-170°	170.0	2.7
170°-180°	58.6	0.9
0°-30°	1279.7	20.3
0°-40°	2058.4	32.6
0°-60°	3527.2	55.9
0°-90°	4415.9	70.0
90°-120°	410.9	6.5
90°-150°	1403.8	22.2
90°-180°	1895.0	30.0
0°-180°	6311.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1694	1691	1678	1690	1688	161
15°	1614	1610	1596	1602	1602	455
25°	1466	1459	1441	1444	1440	674
35°	1266	1260	1241	1235	1224	792
45°	1036	1031	1014	998	994	798
55°	789	785	766	754	745	704
65°	533	530	515	503	498	528
75°	283	280	274	270	264	301
85°	74	75	75	74	71	81
90°	0	4	7	10	11	6
95°	26	25	7	10	10	32
105°	134	136	136	136	136	142
115°	252	255	255	253	251	250
125°	359	362	362	360	359	321
135°	448	450	450	449	446	345
145°	519	520	520	520	518	325
155°	572	569	570	571	568	263
165°	603	600	601	604	600	170
175°	617	614	615	618	614	59
180°	617	617	617	617	617	

TEST NUMBER: P1034371

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1696.3	1696.3	1696.3	1696.3	1696.3
2.5°	1701.6	1697.6	1684.2	1697.6	1696.3
5°	1693.6	1690.9	1677.5	1689.6	1688.2
7.5°	1681.5	1678.8	1664.1	1676.2	1674.8
10°	1664.1	1661.4	1646.6	1657.4	1656.0
12.5°	1642.6	1637.2	1623.8	1631.9	1631.9
15°	1614.4	1610.4	1595.6	1602.3	1602.3
17.5°	1584.9	1578.2	1563.4	1571.5	1564.8
20°	1546.0	1543.3	1525.8	1535.2	1528.5
22.5°	1507.1	1501.7	1485.6	1491.0	1486.9
25°	1465.5	1458.7	1441.3	1444.0	1440.0
27.5°	1417.1	1413.1	1395.7	1397.0	1393.0
30°	1370.2	1366.1	1346.0	1343.3	1339.3
32.5°	1319.2	1312.5	1295.0	1289.7	1281.6
35°	1265.5	1260.1	1241.3	1234.6	1223.9
37.5°	1210.5	1203.8	1186.3	1176.9	1170.2
40°	1154.1	1147.4	1128.6	1116.5	1112.5
42.5°	1093.7	1088.4	1069.6	1058.8	1052.1
45°	1036.0	1030.7	1014.5	998.4	994.4
47.5°	972.9	974.3	954.2	938.1	928.7
50°	912.6	908.5	892.4	875.0	865.6
52.5°	850.8	848.1	830.7	815.9	805.2
55°	789.1	785.1	766.3	754.2	744.8
57.5°	723.3	722.0	705.9	689.8	685.8
60°	661.6	656.2	641.5	628.1	618.7
62.5°	597.2	593.2	581.1	566.3	559.6
65°	532.8	530.1	515.3	503.2	497.9
67.5°	469.7	464.3	453.6	442.9	440.2
70°	410.7	403.9	391.9	383.8	378.4
72.5°	346.2	342.2	335.5	326.1	320.7
75°	283.2	280.5	273.8	269.7	264.4
77.5°	224.1	222.8	218.7	216.1	212.0
80°	169.1	169.1	166.4	165.1	162.4
82.5°	120.8	118.1	118.1	115.4	115.4
85°	73.8	75.2	75.2	73.8	71.1
87.5°	36.2	36.2	34.9	34.9	32.2
90°	0.5	4.1	7.3	9.6	11.0
92.5°	8.7	4.6	7.3	9.6	10.1
95°	26.1	24.7	7.3	9.6	9.6
97.5°	48.9	51.7	8.2	9.1	9.6
100°	76.4	77.7	79.6	11.4	9.6
102.5°	104.3	106.1	107.0	107.9	69.5
105°	134.5	136.3	136.3	136.3	135.8
107.5°	165.6	165.6	166.5	166.9	165.1
110°	195.7	195.7	196.6	195.3	195.7

TEST NUMBER: P1034371

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	224.1	225.5	225.9	224.1	223.2
115°	252.4	254.7	255.2	253.4	250.6
117.5°	282.2	282.2	284.0	281.3	280.3
120°	309.6	309.2	310.5	309.6	307.3
122.5°	333.8	336.1	336.6	335.7	332.9
125°	359.0	362.2	362.2	360.4	359.0
127.5°	383.2	385.5	385.1	384.2	380.5
130°	405.2	407.5	407.9	406.6	404.3
132.5°	427.1	429.9	428.5	428.5	426.2
135°	447.7	450.5	449.6	448.6	445.9
137.5°	466.9	469.7	468.8	468.8	466.5
140°	485.7	486.6	486.1	487.1	484.3
142.5°	502.6	503.1	504.0	504.0	501.2
145°	519.1	520.0	520.0	520.4	517.7
147.5°	533.7	533.7	534.2	534.6	531.4
150°	547.4	546.5	547.4	548.3	544.7
152.5°	560.7	558.4	559.3	560.2	557.0
155°	571.7	568.9	569.8	571.2	567.5
157.5°	580.3	579.0	579.0	580.3	576.7
160°	589.5	586.7	587.2	589.0	585.4
162.5°	596.8	594.1	594.5	597.3	593.2
165°	603.2	600.5	600.9	603.7	600.0
167.5°	608.2	605.5	606.0	609.2	605.0
170°	612.4	609.2	609.6	613.3	609.2
172.5°	615.1	611.9	612.8	616.0	611.9
175°	616.9	614.2	614.6	618.3	614.2
177.5°	618.3	615.6	616.0	619.2	615.6
180°	616.9	616.9	616.9	616.9	616.9

(END OF REPORT)