

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1034373

Luminaire Tested: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1034373
REPORT IS A COMBINATION OF REPORTS P1002946 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K
Description: Define 5 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6068.0 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.42' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1034373

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1034373

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74
1	102	98	94	90	96	93	89	86	83	80	78	74	72	70	66	64	63	63	63	59
2	93	85	79	74	88	81	75	70	73	68	64	65	61	58	58	55	53	53	53	49
3	85	75	67	61	80	71	64	59	64	59	54	57	53	49	51	48	45	45	45	42
4	78	66	58	52	73	63	56	50	57	51	46	51	46	42	46	42	39	39	39	36
5	71	59	51	45	67	56	49	43	51	45	40	46	41	37	41	37	34	34	34	31
6	66	53	45	39	62	51	43	38	46	40	35	42	36	32	37	33	30	30	30	27
7	61	48	40	34	58	46	38	33	42	35	31	38	33	29	34	30	26	26	26	24
8	57	44	36	30	54	42	35	29	38	32	27	35	29	26	31	27	24	24	24	22
9	53	40	32	27	50	38	31	26	35	29	25	32	27	23	29	25	21	21	21	19
10	50	37	30	25	47	35	29	24	32	26	22	30	25	21	27	23	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10450	10450	10450
5°	10450	10207	10227
10°	10364	9973	9942
15°	10228	9693	9606
20°	10043	9369	9222
25°	9846	9015	8810
30°	9608	8646	8375
35°	9354	8259	7889
40°	9091	7851	7457
45°	8806	7453	6997
50°	8493	7001	6462
55°	8183	6503	5969
60°	7813	5978	5396
65°	7372	5370	4804
70°	6920	4671	4121
75°	6166	3846	3332
80°	5254	2873	2451
85°	4059	1700	1351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8806 cd/sqm

TEST NUMBER: P1034373

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.9	2.5
10°-20°	434.7	7.2
20°-30°	641.8	10.6
30°-40°	748.8	12.3
40°-50°	752.0	12.4
50°-60°	660.2	10.9
60°-70°	491.7	8.1
70°-80°	280.8	4.6
80°-90°	81.9	1.4
90°-100°	20.1	0.3
100°-110°	133.9	2.2
110°-120°	241.1	4.0
120°-130°	309.4	5.1
130°-140°	332.8	5.5
140°-150°	312.4	5.1
150°-160°	252.7	4.2
160°-170°	163.4	2.7
170°-180°	56.4	0.9
0°-30°	1230.4	20.3
0°-40°	1979.2	32.6
0°-60°	3391.4	55.9
0°-90°	4245.9	70.0
90°-120°	395.1	6.5
90°-150°	1349.7	22.2
90°-180°	1822.0	30.0
0°-180°	6068.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1631	1631	1631	1631	1631	
5°	1628	1626	1613	1624	1623	155
15°	1552	1548	1534	1541	1541	438
25°	1409	1403	1386	1388	1384	648
35°	1217	1212	1194	1187	1177	761
45°	996	991	976	960	956	767
55°	759	755	737	725	716	677
65°	512	510	496	484	479	508
75°	272	270	263	259	254	290
85°	71	72	72	71	68	78
90°	0	4	7	9	11	6
95°	25	24	7	9	9	31
105°	129	131	131	131	131	137
115°	243	245	245	244	241	241
125°	345	348	348	346	345	308
135°	430	433	432	431	429	332
145°	499	500	500	500	498	312
155°	550	547	548	549	546	253
165°	580	577	578	580	577	164
175°	593	590	591	594	590	56
180°	593	593	593	593	593	

TEST NUMBER: P1034373

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1631.0	1631.0	1631.0	1631.0	1631.0
2.5°	1636.1	1632.3	1619.4	1632.3	1631.0
5°	1628.4	1625.8	1612.9	1624.5	1623.2
7.5°	1616.8	1614.2	1600.0	1611.6	1610.3
10°	1600.0	1597.4	1583.2	1593.5	1592.3
12.5°	1579.4	1574.2	1561.3	1569.0	1569.0
15°	1552.3	1548.4	1534.2	1540.6	1540.6
17.5°	1523.9	1517.4	1503.2	1511.0	1504.5
20°	1486.4	1483.9	1467.1	1476.1	1469.7
22.5°	1449.0	1443.9	1428.4	1433.5	1429.7
25°	1409.0	1402.6	1385.8	1388.4	1384.5
27.5°	1362.6	1358.7	1341.9	1343.2	1339.4
30°	1317.4	1313.5	1294.2	1291.6	1287.7
32.5°	1268.4	1261.9	1245.2	1240.0	1232.3
35°	1216.8	1211.6	1193.5	1187.1	1176.8
37.5°	1163.9	1157.4	1140.6	1131.6	1125.2
40°	1109.7	1103.2	1085.2	1073.5	1069.7
42.5°	1051.6	1046.4	1028.4	1018.1	1011.6
45°	996.1	991.0	975.5	960.0	956.1
47.5°	935.5	936.8	917.4	901.9	892.9
50°	877.4	873.5	858.1	841.3	832.3
52.5°	818.1	815.5	798.7	784.5	774.2
55°	758.7	754.8	736.8	725.2	716.1
57.5°	695.5	694.2	678.7	663.2	659.4
60°	636.1	631.0	616.8	603.9	594.8
62.5°	574.2	570.3	558.7	544.5	538.1
65°	512.3	509.7	495.5	483.9	478.7
67.5°	451.6	446.5	436.1	425.8	423.2
70°	394.8	388.4	376.8	369.0	363.9
72.5°	332.9	329.0	322.6	313.5	308.4
75°	272.3	269.7	263.2	259.4	254.2
77.5°	215.5	214.2	210.3	207.7	203.9
80°	162.6	162.6	160.0	158.7	156.1
82.5°	116.1	113.5	113.5	111.0	111.0
85°	71.0	72.3	72.3	71.0	68.4
87.5°	34.8	34.8	33.5	33.5	31.0
90°	0.4	4.0	7.0	9.2	10.6
92.5°	8.4	4.4	7.0	9.2	9.7
95°	25.1	23.7	7.0	9.2	9.2
97.5°	47.0	49.7	7.9	8.8	9.2
100°	73.4	74.8	76.5	11.0	9.2
102.5°	100.3	102.0	102.9	103.8	66.8
105°	129.3	131.0	131.0	131.0	130.6
107.5°	159.2	159.2	160.1	160.5	158.7
110°	188.2	188.2	189.1	187.8	188.2



TEST NUMBER: P1034373

CATALOG NUMBER: S125DIW-B1090D470UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	215.5	216.8	217.2	215.5	214.6
115°	242.7	244.9	245.4	243.6	241.0
117.5°	271.3	271.3	273.1	270.4	269.5
120°	297.7	297.2	298.6	297.7	295.5
122.5°	321.0	323.2	323.6	322.8	320.1
125°	345.2	348.3	348.3	346.5	345.2
127.5°	368.5	370.7	370.2	369.4	365.8
130°	389.6	391.8	392.2	390.9	388.7
132.5°	410.7	413.3	412.0	412.0	409.8
135°	430.5	433.1	432.2	431.4	428.7
137.5°	449.0	451.6	450.7	450.7	448.5
140°	467.0	467.9	467.4	468.3	465.7
142.5°	483.2	483.7	484.6	484.6	481.9
145°	499.1	500.0	500.0	500.4	497.8
147.5°	513.2	513.2	513.6	514.0	511.0
150°	526.3	525.5	526.3	527.2	523.7
152.5°	539.1	536.9	537.8	538.7	535.6
155°	549.6	547.0	547.9	549.2	545.7
157.5°	558.0	556.7	556.7	558.0	554.5
160°	566.8	564.2	564.6	566.4	562.8
162.5°	573.8	571.2	571.6	574.3	570.3
165°	580.0	577.3	577.8	580.4	576.9
167.5°	584.8	582.2	582.6	585.7	581.7
170°	588.8	585.7	586.1	589.7	585.7
172.5°	591.4	588.3	589.2	592.3	588.3
175°	593.2	590.5	591.0	594.5	590.5
177.5°	594.5	591.9	592.3	595.4	591.9
180°	593.2	593.2	593.2	593.2	593.2

(END OF REPORT)